

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438705

Luminaire Tested: CB2-085U-030D-930-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438705
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-085U-030D-930-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 850 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5233.6 lumens
Efficiency: N/A
Efficacy: 153.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438705

CATALOG NUMBER: CB2-085U-030D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438705

CATALOG NUMBER: CB2-085U-030D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23																				
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19																				
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16																				
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19	14																				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12																				
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14	10																				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9																				
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8																				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	13	11	10	7																				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7																				
10	43	32	25	20	38	29	23	19	23	18	15	17	14	12	11	9	8	6																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8862	8862	8862
5°	8787	8801	8863
10°	8737	8716	8709
15°	8599	8542	8473
20°	8463	8276	8159
25°	8237	8004	7779
30°	8009	7655	7365
35°	7746	7297	6951
40°	7467	6962	6555
45°	7188	6611	6170
50°	6937	6270	5796
55°	6626	5915	5442
60°	6270	5577	5089
65°	5893	5201	4735
70°	5474	4782	4288
75°	4980	4327	3883
80°	4453	3791	3521
85°	3417	3118	2578

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7188 cd/sqm



TEST NUMBER: P1438705

CATALOG NUMBER: CB2-085U-030D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	0.9
10°-20°	133.4	2.5
20°-30°	191.8	3.7
30°-40°	215.6	4.1
40°-50°	208.2	4.0
50°-60°	175.9	3.4
60°-70°	126.4	2.4
70°-80°	69.1	1.3
80°-90°	18.4	0.4
90°-100°	24.7	0.5
100°-110°	157.4	3.0
110°-120°	500.2	9.6
120°-130°	725.9	13.9
130°-140°	780.6	14.9
140°-150°	735.0	14.0
150°-160°	598.8	11.4
160°-170°	389.7	7.4
170°-180°	134.7	2.6
0°-30°	373.0	7.1
0°-40°	588.6	11.2
0°-60°	972.7	18.6
0°-90°	1186.5	22.7
90°-120°	682.4	13.0
90°-150°	2923.8	55.9
90°-180°	4047.0	77.3
0°-180°	5233.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	503	509	503	503	507	48
15°	477	481	474	469	470	134
25°	429	429	416	407	405	197
35°	364	360	343	330	327	228
45°	292	286	268	254	250	225
55°	218	210	195	183	179	195
65°	143	138	126	117	115	142
75°	74	70	64	59	58	79
85°	17	16	16	14	13	20
90°	0	0	0	1	1	3
95°	56	16	17	11	10	71
105°	296	307	31	36	38	311
115°	559	571	577	583	335	550
125°	794	808	809	822	833	710
135°	1000	1012	1010	1016	1029	771
145°	1170	1179	1171	1172	1187	731
155°	1299	1307	1293	1290	1308	599
165°	1386	1390	1375	1369	1383	391
175°	1426	1430	1411	1402	1409	136
180°	1419	1419	1419	1419	1419	

TEST NUMBER: P1438705

CATALOG NUMBER: CB2-085U-030D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	508.8	508.8	508.8	508.8	508.8
2.5°	505.4	511.5	506.9	507.6	508.5
5°	502.6	509.4	503.4	503.4	506.9
7.5°	499.0	505.5	497.8	496.4	499.6
10°	494.0	500.5	492.8	490.2	492.4
12.5°	487.5	493.6	486.3	482.1	484.0
15°	476.9	481.1	473.7	469.1	469.9
17.5°	465.3	467.9	457.4	453.5	452.7
20°	456.6	458.9	446.5	441.0	440.2
22.5°	445.4	447.4	434.3	427.6	426.5
25°	428.6	428.9	416.5	407.1	404.8
27.5°	410.9	409.7	395.9	384.8	381.8
30°	398.2	396.6	380.6	368.9	366.2
32.5°	384.5	381.7	365.7	353.0	350.3
35°	364.3	360.1	343.2	329.9	326.9
37.5°	342.8	338.0	321.5	307.0	303.6
40°	328.4	323.1	306.2	291.7	288.3
42.5°	314.1	308.1	290.9	276.4	272.7
45°	291.8	285.7	268.4	254.3	250.5
47.5°	270.6	262.8	246.1	232.0	228.2
50°	256.0	247.6	231.4	217.7	213.9
52.5°	241.0	232.3	216.8	203.7	199.9
55°	218.2	210.2	194.8	182.6	179.2
57.5°	195.6	187.9	173.8	162.2	158.9
60°	180.0	173.5	160.1	149.1	146.1
62.5°	165.0	159.2	146.4	136.4	133.3
65°	143.0	137.6	126.2	117.2	114.9
67.5°	121.6	116.2	107.0	98.9	96.3
70°	107.5	102.2	93.9	86.4	84.2
72.5°	94.1	88.5	81.7	74.9	73.2
75°	74.0	69.5	64.3	59.2	57.7
77.5°	56.3	51.8	48.1	44.5	44.1
80°	44.4	40.6	37.8	35.4	35.1
82.5°	33.2	30.3	28.4	26.7	26.6
85°	17.1	16.0	15.6	13.6	12.9
87.5°	5.0	5.0	4.4	3.9	3.9
90°	0.0	0.0	0.0	1.0	1.0
92.5°	15.6	6.0	4.1	6.0	6.0
95°	56.4	16.3	17.4	11.3	10.3
97.5°	117.2	26.3	25.2	27.7	28.7
100°	163.2	53.8	27.7	31.8	32.8
102.5°	214.1	202.6	28.5	34.3	36.1
105°	295.6	306.6	30.8	36.0	38.0
107.5°	375.6	386.7	143.3	37.2	39.2
110°	429.0	440.0	453.6	38.0	40.0



TEST NUMBER: P1438705

CATALOG NUMBER: CB2-085U-030D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	479.1	492.5	502.9	84.6	41.7
115°	559.3	571.4	576.8	583.4	334.6
117.5°	630.1	645.0	651.1	662.6	673.8
120°	679.4	693.4	697.9	709.4	721.5
122.5°	727.8	740.3	743.0	756.2	767.4
125°	794.3	808.4	808.7	822.3	833.3
127.5°	860.8	872.9	872.3	882.5	894.7
130°	905.2	913.2	913.4	921.9	934.9
132.5°	942.1	953.3	953.6	960.5	973.5
135°	999.6	1011.6	1009.8	1016.3	1029.3
137.5°	1053.6	1065.2	1062.0	1067.4	1080.9
140°	1088.9	1098.9	1094.0	1099.5	1114.5
142.5°	1121.7	1131.7	1124.4	1129.0	1144.9
145°	1169.9	1179.0	1171.0	1172.3	1187.4
147.5°	1212.8	1221.7	1212.0	1213.4	1227.4
150°	1240.8	1248.8	1236.6	1238.0	1252.0
152.5°	1265.4	1272.6	1259.6	1259.4	1275.9
155°	1299.2	1307.3	1293.1	1290.4	1308.5
157.5°	1330.0	1337.5	1323.3	1321.3	1335.4
160°	1350.6	1355.6	1341.3	1338.6	1352.6
162.5°	1364.5	1370.3	1356.1	1351.7	1365.8
165°	1385.5	1389.5	1375.2	1369.4	1383.4
167.5°	1403.5	1408.1	1389.8	1384.6	1399.6
170°	1414.2	1417.2	1398.8	1392.0	1407.0
172.5°	1420.8	1423.0	1404.5	1396.8	1407.0
175°	1426.5	1429.5	1411.1	1402.0	1409.1
177.5°	1427.5	1429.1	1415.2	1407.3	1419.3
180°	1419.3	1419.3	1419.3	1419.3	1419.3



TEST NUMBER: P1438705

CATALOG NUMBER: CB2-085U-030D-930-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.24	11.90	12.40	13.04	14.66	10.14	10.80	11.30	11.94	13.56
	3H	12.87	13.46	14.04	14.61	16.24	11.65	12.24	12.82	13.39	15.02
	4H	13.49	14.05	14.67	15.20	16.84	12.22	12.77	13.39	13.93	15.56
	6H	13.88	14.39	15.07	15.55	17.20	12.58	13.09	13.76	14.25	15.89
	8H	14.02	14.51	15.21	15.68	17.32	12.71	13.20	13.90	14.37	16.01
	12H	14.09	14.55	15.28	15.72	17.38	12.77	13.23	13.96	14.40	16.05
4H	2H	11.63	12.18	12.81	13.34	14.97	10.75	11.31	11.94	12.46	14.10
	3H	13.48	13.94	14.67	15.12	16.77	12.47	12.93	13.66	14.11	15.76
	4H	14.21	14.64	15.40	15.81	17.47	13.13	13.56	14.32	14.73	16.39
	6H	14.72	15.09	15.92	16.28	17.93	13.60	13.96	14.79	15.15	16.81
	8H	14.92	15.26	16.12	16.45	18.12	13.78	14.12	14.97	15.30	16.97
	12H	15.02	15.33	16.23	16.52	18.20	13.86	14.17	15.07	15.36	17.04
8H	4H	14.35	14.69	15.55	15.88	17.55	13.39	13.73	14.58	14.91	16.58
	6H	14.99	15.27	16.20	16.49	18.16	13.98	14.27	15.20	15.49	17.16
	8H	15.28	15.52	16.49	16.72	18.41	14.26	14.50	15.48	15.70	17.39
	12H	15.44	15.65	16.66	16.85	18.57	14.40	14.61	15.62	15.81	17.53
12H	4H	14.32	14.63	15.53	15.83	17.50	13.38	13.69	14.59	14.89	16.56
	6H	15.01	15.26	16.23	16.46	18.15	14.05	14.29	15.26	15.49	17.18
	8H	15.32	15.54	16.54	16.74	18.45	14.34	14.56	15.56	15.76	17.47