

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438815

Luminaire Tested: CB2-125U-055D-930-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438815
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-125U-055D-930-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8343.2 lumens
Efficiency: N/A
Efficacy: 145.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438815

CATALOG NUMBER: CB2-125U-055D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438815

CATALOG NUMBER: CB2-125U-055D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	85	77	72	67	75	69	65	60	54	51	48	40	38	36	28	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	13
6	59	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16930	16930	16930
5°	16786	16812	16930
10°	16690	16651	16639
15°	16427	16319	16185
20°	16168	15809	15588
25°	15734	15290	14861
30°	15297	14623	14070
35°	14797	13942	13276
40°	14265	13301	12523
45°	13732	12631	11789
50°	13250	11979	11072
55°	12657	11299	10397
60°	11980	10656	9722
65°	11255	9936	9050
70°	10460	9136	8189
75°	9516	8264	7416
80°	8506	7242	6720
85°	6535	5955	4916

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13732 cd/sqm



TEST NUMBER: P1438815

CATALOG NUMBER: CB2-125U-055D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.1
10°-20°	254.8	3.1
20°-30°	366.4	4.4
30°-40°	411.8	4.9
40°-50°	397.8	4.8
50°-60°	336.1	4.0
60°-70°	241.4	2.9
70°-80°	131.9	1.6
80°-90°	35.2	0.4
90°-100°	37.1	0.4
100°-110°	236.4	2.8
110°-120°	751.0	9.0
120°-130°	1089.8	13.1
130°-140°	1172.1	14.0
140°-150°	1103.6	13.2
150°-160°	899.0	10.8
160°-170°	585.2	7.0
170°-180°	202.3	2.4
0°-30°	712.6	8.5
0°-40°	1124.4	13.5
0°-60°	1858.2	22.3
0°-90°	2266.7	27.2
90°-120°	1024.5	12.3
90°-150°	4390.0	52.6
90°-180°	6076.0	72.8
0°-180°	8343.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	972	972	972	972	972	
5°	960	973	962	962	968	91
15°	911	919	905	896	898	257
25°	819	819	796	778	773	377
35°	696	688	656	630	624	435
45°	558	546	513	486	479	431
55°	417	402	372	349	342	373
65°	273	263	241	224	220	271
75°	141	133	123	113	110	151
85°	33	31	30	26	25	39
90°	0	0	0	2	2	5
95°	85	24	26	17	15	107
105°	444	460	46	54	57	467
115°	840	858	866	876	502	826
125°	1193	1214	1214	1235	1251	1066
135°	1501	1519	1516	1526	1546	1157
145°	1757	1770	1758	1760	1783	1098
155°	1951	1963	1942	1938	1965	899
165°	2080	2086	2065	2056	2077	588
175°	2142	2146	2119	2105	2116	204
180°	2131	2131	2131	2131	2131	



TEST NUMBER: P1438815

CATALOG NUMBER: CB2-125U-055D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	972.0	972.0	972.0	972.0	972.0
2.5°	965.5	977.1	968.4	969.7	971.4
5°	960.1	973.2	961.6	961.7	968.3
7.5°	953.3	965.6	951.0	948.3	954.4
10°	943.7	956.1	941.5	936.4	940.8
12.5°	931.2	943.0	929.0	920.9	924.7
15°	911.0	919.0	905.0	896.1	897.6
17.5°	889.0	893.9	873.8	866.3	864.8
20°	872.3	876.6	852.9	842.5	841.0
22.5°	850.8	854.6	829.7	816.9	814.8
25°	818.7	819.4	795.6	777.7	773.3
27.5°	785.1	782.7	756.3	735.1	729.4
30°	760.6	757.7	727.1	704.7	699.6
32.5°	734.4	729.2	698.6	674.3	669.2
35°	695.9	687.9	655.7	630.3	624.4
37.5°	654.8	645.8	614.2	586.5	579.9
40°	627.4	617.2	585.0	557.3	550.8
42.5°	600.0	588.7	555.8	528.1	521.0
45°	557.5	545.8	512.8	485.8	478.6
47.5°	517.0	502.1	470.1	443.3	436.0
50°	489.0	473.0	442.1	415.9	408.6
52.5°	460.4	443.8	414.1	389.1	381.8
55°	416.8	401.5	372.1	348.9	342.4
57.5°	373.6	358.9	332.1	309.9	303.5
60°	343.9	331.5	305.9	284.9	279.1
62.5°	315.3	304.1	279.7	260.5	254.7
65°	273.1	263.0	241.1	223.9	219.6
67.5°	232.2	222.0	204.4	188.9	184.0
70°	205.4	195.2	179.4	165.1	160.8
72.5°	179.8	169.0	156.1	143.1	139.9
75°	141.4	132.7	122.8	113.1	110.2
77.5°	107.5	99.0	91.8	85.0	84.3
80°	84.8	77.6	72.2	67.7	67.0
82.5°	63.4	57.9	54.3	51.1	50.9
85°	32.7	30.6	29.8	26.0	24.6
87.5°	9.5	9.5	8.3	7.5	7.5
90°	0.0	0.0	0.0	1.5	1.5
92.5°	23.4	9.0	6.2	8.9	8.9
95°	84.7	24.5	26.2	16.9	15.4
97.5°	176.0	39.5	37.9	41.6	43.1
100°	245.0	80.8	41.6	47.8	49.3
102.5°	321.4	304.3	42.8	51.5	54.2
105°	443.8	460.4	46.2	54.0	57.0
107.5°	564.0	580.5	215.1	55.8	58.9
110°	644.1	660.7	681.1	57.1	60.1



TEST NUMBER: P1438815

CATALOG NUMBER: CB2-125U-055D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.3	739.5	755.0	127.0	62.6
115°	839.8	857.9	866.0	876.0	502.3
117.5°	946.1	968.4	977.5	994.9	1011.8
120°	1020.1	1041.2	1047.8	1065.2	1083.3
122.5°	1092.8	1111.5	1115.6	1135.4	1152.3
125°	1192.7	1213.8	1214.2	1234.6	1251.2
127.5°	1292.5	1310.6	1309.8	1325.0	1343.4
130°	1359.1	1371.1	1371.4	1384.2	1403.8
132.5°	1414.6	1431.4	1431.8	1442.1	1461.7
135°	1500.8	1518.9	1516.3	1525.9	1545.5
137.5°	1581.9	1599.4	1594.5	1602.7	1622.9
140°	1634.9	1650.0	1642.6	1650.8	1673.4
142.5°	1684.2	1699.3	1688.2	1695.2	1719.0
145°	1756.6	1770.2	1758.2	1760.2	1782.8
147.5°	1821.0	1834.3	1819.8	1821.8	1842.9
150°	1863.0	1875.0	1856.8	1858.8	1879.9
152.5°	1899.9	1910.8	1891.3	1890.9	1915.7
155°	1950.8	1962.8	1941.5	1937.5	1964.7
157.5°	1997.0	2008.2	1986.8	1983.9	2005.0
160°	2027.8	2035.4	2014.0	2009.8	2030.9
162.5°	2048.8	2057.5	2036.2	2029.5	2050.6
165°	2080.2	2086.2	2064.8	2056.0	2077.1
167.5°	2107.3	2114.3	2086.7	2078.9	2101.5
170°	2123.4	2127.9	2100.3	2090.0	2112.6
172.5°	2133.2	2136.5	2108.9	2097.2	2112.6
175°	2141.9	2146.4	2118.7	2105.1	2115.7
177.5°	2143.4	2145.8	2124.9	2113.0	2131.1
180°	2131.1	2131.1	2131.1	2131.1	2131.1

TEST NUMBER: P1438815

CATALOG NUMBER: CB2-125U-055D-930-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.21	14.89	15.34	16.01	17.58	13.11	13.79	14.24	14.91	16.48
	3H	15.84	16.45	16.98	17.58	19.16	14.62	15.23	15.76	16.37	17.95
	4H	16.46	17.04	17.61	18.17	19.76	15.19	15.77	16.34	16.90	18.49
	6H	16.85	17.39	18.01	18.52	20.12	15.55	16.08	16.71	17.22	18.82
	8H	17.00	17.50	18.16	18.65	20.24	15.69	16.19	16.85	17.34	18.93
	12H	17.06	17.55	18.23	18.69	20.30	15.74	16.22	16.91	17.37	18.98
4H	2H	14.60	15.18	15.75	16.31	17.89	13.72	14.30	14.88	15.43	17.02
	3H	16.45	16.93	17.61	18.09	19.69	15.44	15.92	16.60	17.08	18.68
	4H	17.19	17.63	18.35	18.78	20.40	16.11	16.55	17.27	17.70	19.31
	6H	17.70	18.08	18.87	19.25	20.85	16.57	16.95	17.74	18.12	19.73
	8H	17.90	18.25	19.07	19.41	21.04	16.76	17.11	17.93	18.27	19.90
	12H	18.00	18.32	19.18	19.49	21.12	16.84	17.16	18.02	18.33	19.96
8H	4H	17.33	17.69	18.50	18.85	20.47	16.37	16.72	17.54	17.88	19.51
	6H	17.96	18.26	19.15	19.46	21.08	16.96	17.26	18.15	18.46	20.08
	8H	18.25	18.51	19.45	19.69	21.33	17.24	17.49	18.43	18.67	20.31
	12H	18.42	18.64	19.62	19.82	21.49	17.38	17.60	18.58	18.78	20.45
12H	4H	17.30	17.62	18.49	18.79	20.42	16.36	16.68	17.55	17.86	19.48
	6H	17.99	18.25	19.19	19.43	21.07	17.03	17.28	18.22	18.46	20.10
	8H	18.30	18.52	19.50	19.70	21.38	17.32	17.55	18.52	18.73	20.40