

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438971

Luminaire Tested: CB2-B-125U-120D-930-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438971
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-125U-120D-930-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11860.4 lumens
Efficiency: N/A
Efficacy: 144.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438971

CATALOG NUMBER: CB2-B-125U-120D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438971

CATALOG NUMBER: CB2-B-125U-120D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42																												
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35																												
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30																												
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	32	30	25																												
4	73	63	55	49	67	57	51	46	48	43	39	39	35	32	30	28	26	22																												
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19																												
6	62	50	42	36	56	46	39	34	39	33	29	31	28	25	25	22	20	17																												
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																												
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	14																												
9	49	37	30	25	45	35	28	24	29	24	21	24	20	17	19	17	14	12																												
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	36787	36787	36787
5°	36475	36531	36786
10°	36267	36182	36152
15°	35694	35459	35167
20°	35132	34351	33871
25°	34187	33224	32292
30°	33241	31777	30574
35°	32151	30295	28849
40°	30997	28901	27209
45°	29837	27447	25615
50°	28790	26029	24056
55°	27500	24554	22589
60°	26025	23155	21127
65°	24460	21596	19663
70°	22728	19845	17788
75°	20680	17954	16104
80°	18496	15737	14594
85°	14229	12930	10672

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29837 cd/sqm



TEST NUMBER: P1438971

CATALOG NUMBER: CB2-B-125U-120D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.6	1.7
10°-20°	553.7	4.7
20°-30°	796.1	6.7
30°-40°	894.8	7.5
40°-50°	864.3	7.3
50°-60°	730.3	6.2
60°-70°	524.6	4.4
70°-80°	286.7	2.4
80°-90°	76.1	0.6
90°-100°	79.1	0.7
100°-110°	489.7	4.1
110°-120°	1235.1	10.4
120°-130°	1484.7	12.5
130°-140°	1346.1	11.3
140°-150°	1073.4	9.1
150°-160°	732.2	6.2
160°-170°	387.2	3.3
170°-180°	107.8	0.9
0°-30°	1548.3	13.1
0°-40°	2443.1	20.6
0°-60°	4037.7	34.0
0°-90°	4925.1	41.5
90°-120°	1803.9	15.2
90°-150°	5708.0	48.1
90°-180°	6935.0	58.5
0°-180°	11860.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2112	2112	2112	2112	2112	
5°	2086	2115	2089	2090	2104	198
15°	1980	1997	1966	1947	1950	558
25°	1779	1780	1729	1690	1680	819
35°	1512	1495	1425	1370	1357	945
45°	1211	1186	1114	1056	1040	936
55°	906	872	809	758	744	810
65°	594	571	524	487	477	589
75°	307	288	267	246	239	329
85°	71	66	65	56	53	85
90°	0	0	0	0	0	4
95°	41	103	32	23	23	52
105°	200	560	810	203	136	210
115°	346	764	1847	1720	1310	339
125°	450	926	2015	2293	2307	403
135°	564	1027	2020	2365	2539	439
145°	723	1079	1906	2298	2502	452
155°	878	1100	1697	2045	2152	404
165°	996	1090	1369	1612	1688	280
175°	1056	1069	1087	1106	1128	100
180°	1056	1056	1056	1056	1056	

TEST NUMBER: P1438971

CATALOG NUMBER: CB2-B-125U-120D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2112.1	2112.1	2112.1	2112.1	2112.1
2.5°	2097.8	2123.1	2104.3	2107.0	2110.8
5°	2086.2	2114.7	2089.4	2089.7	2104.0
7.5°	2071.3	2098.2	2066.5	2060.6	2073.9
10°	2050.6	2077.5	2045.8	2034.7	2044.1
12.5°	2023.4	2049.1	2018.6	2001.0	2009.2
15°	1979.5	1996.8	1966.5	1947.2	1950.3
17.5°	1931.6	1942.3	1898.6	1882.4	1879.2
20°	1895.4	1904.8	1853.3	1830.6	1827.4
22.5°	1848.8	1857.0	1802.9	1774.9	1770.5
25°	1778.9	1780.5	1728.8	1689.8	1680.3
27.5°	1705.8	1700.8	1643.4	1597.2	1584.9
30°	1652.8	1646.5	1580.0	1531.2	1520.2
32.5°	1595.9	1584.5	1517.9	1465.3	1454.2
35°	1512.1	1494.7	1424.8	1369.5	1356.8
37.5°	1422.8	1403.2	1334.5	1274.4	1260.1
40°	1363.3	1341.2	1271.1	1211.0	1196.7
42.5°	1303.8	1279.1	1207.7	1147.5	1132.0
45°	1211.3	1186.0	1114.3	1055.7	1039.9
47.5°	1123.3	1091.1	1021.4	963.2	947.4
50°	1062.5	1027.7	960.6	903.7	887.8
52.5°	1000.4	964.3	899.8	845.4	829.6
55°	905.6	872.4	808.6	758.1	743.9
57.5°	811.8	779.9	721.6	673.4	659.5
60°	747.1	720.3	664.7	619.1	606.5
62.5°	685.0	660.7	607.7	566.1	553.4
65°	593.5	571.4	524.0	486.6	477.1
67.5°	504.6	482.4	444.1	410.5	399.8
70°	446.3	424.2	389.7	358.8	349.3
72.5°	390.7	367.3	339.3	311.0	304.0
75°	307.3	288.3	266.8	245.7	239.3
77.5°	233.5	215.2	199.6	184.6	183.1
80°	184.4	168.5	156.9	147.1	145.5
82.5°	137.8	125.8	118.1	110.9	110.6
85°	71.2	66.4	64.7	56.5	53.4
87.5°	20.7	20.7	18.1	15.5	15.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.9	18.0	7.3	7.3	7.3
95°	40.9	103.2	31.8	22.7	22.7
97.5°	85.5	247.4	172.0	46.3	40.0
100°	118.3	358.5	295.7	67.9	54.6
102.5°	151.0	455.3	466.8	107.7	83.7
105°	200.2	560.5	809.8	203.2	136.5
107.5°	248.4	629.2	1241.1	419.3	252.9
110°	277.5	669.0	1565.0	653.7	391.3



TEST NUMBER: P1438971

CATALOG NUMBER: CB2-B-125U-120D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	306.6	708.8	1743.3	1047.9	675.1
115°	345.8	763.9	1847.1	1719.5	1310.2
117.5°	378.5	814.5	1936.2	2126.4	2006.3
120°	400.4	854.1	1983.6	2184.6	2224.7
122.5°	422.2	883.0	2009.0	2207.3	2282.9
125°	450.4	926.4	2015.4	2293.2	2306.6
127.5°	478.6	959.0	2045.4	2372.2	2378.5
130°	500.4	980.9	2074.5	2398.7	2447.6
132.5°	525.9	999.2	2085.5	2413.8	2487.6
135°	564.1	1026.8	2020.0	2365.1	2538.6
137.5°	612.4	1046.5	1957.2	2363.7	2475.8
140°	641.5	1050.7	1924.4	2416.0	2424.9
142.5°	674.2	1062.1	1917.1	2410.2	2486.7
145°	723.4	1079.2	1906.2	2297.6	2502.2
147.5°	772.5	1090.1	1864.4	2173.2	2352.1
150°	805.3	1094.4	1824.3	2131.7	2242.9
152.5°	838.0	1098.7	1773.4	2105.8	2199.2
155°	878.0	1100.5	1696.9	2045.1	2151.9
157.5°	919.9	1095.2	1605.0	1934.3	2050.9
160°	941.7	1088.5	1546.8	1854.0	1956.3
162.5°	963.6	1085.5	1495.9	1748.8	1868.9
165°	996.3	1089.7	1369.4	1612.2	1687.8
167.5°	1018.2	1085.8	1251.1	1450.1	1556.8
170°	1032.7	1086.1	1178.3	1325.9	1414.9
172.5°	1043.6	1068.6	1134.6	1212.4	1272.9
175°	1055.5	1068.8	1087.3	1106.0	1128.3
177.5°	1059.1	1066.2	1051.8	1048.4	1055.5
180°	1055.5	1055.5	1055.5	1055.5	1055.5



TEST NUMBER: P1438971
 CATALOG NUMBER: CB2-B-125U-120D-930-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.69	19.47	19.72	20.50	21.89	17.59	18.37	18.62	19.40	20.79
	3H	20.33	21.02	21.36	22.07	23.48	19.11	19.81	20.15	20.85	22.26
	4H	20.95	21.61	22.00	22.66	24.07	19.68	20.34	20.73	21.39	22.80
	6H	21.35	21.96	22.41	23.01	24.44	20.05	20.66	21.11	21.71	23.13
	8H	21.49	22.08	22.56	23.14	24.56	20.18	20.76	21.25	21.83	23.25
	12H	21.57	22.12	22.64	23.18	24.62	20.24	20.79	21.31	21.85	23.30
4H	2H	19.09	19.75	20.14	20.79	22.21	18.21	18.87	19.27	19.92	21.34
	3H	20.95	21.50	22.01	22.57	24.00	19.94	20.49	21.00	21.57	22.99
	4H	21.69	22.20	22.76	23.26	24.71	20.61	21.12	21.68	22.18	23.63
	6H	22.21	22.64	23.29	23.73	25.17	21.08	21.51	22.16	22.60	24.05
	8H	22.41	22.81	23.49	23.89	25.35	21.27	21.67	22.35	22.75	24.21
	12H	22.51	22.88	23.61	23.97	25.44	21.35	21.72	22.45	22.81	24.28
8H	4H	21.84	22.25	22.92	23.33	24.79	20.88	21.28	21.96	22.36	23.82
	6H	22.48	22.81	23.58	23.94	25.39	21.48	21.81	22.58	22.94	24.39
	8H	22.77	23.06	23.88	24.17	25.64	21.75	22.05	22.86	23.15	24.63
	12H	22.94	23.20	24.05	24.30	25.81	21.90	22.16	23.01	23.26	24.77
12H	4H	21.82	22.18	22.91	23.28	24.74	20.88	21.24	21.97	22.34	23.80
	6H	22.51	22.80	23.62	23.91	25.38	21.54	21.83	22.65	22.94	24.42
	8H	22.82	23.08	23.93	24.18	25.69	21.84	22.10	22.96	23.20	24.72