

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439083

Luminaire Tested: CB2-D-125U-055D-930-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439083
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-125U-055D-930-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7446.7 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439083

CATALOG NUMBER: CB2-D-125U-055D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439083

CATALOG NUMBER: CB2-D-125U-055D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	32	26
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	23	19
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	21	19	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	12
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16930	16930	16930
5°	16786	16812	16930
10°	16690	16651	16639
15°	16427	16319	16185
20°	16168	15809	15588
25°	15734	15290	14861
30°	15297	14623	14070
35°	14797	13942	13276
40°	14265	13301	12523
45°	13732	12631	11789
50°	13250	11979	11072
55°	12657	11299	10397
60°	11980	10656	9722
65°	11255	9936	9050
70°	10460	9136	8189
75°	9516	8264	7416
80°	8506	7242	6720
85°	6535	5955	4916

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13732 cd/sqm



TEST NUMBER: P1439083

CATALOG NUMBER: CB2-D-125U-055D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.2
10°-20°	254.8	3.4
20°-30°	366.4	4.9
30°-40°	411.8	5.5
40°-50°	397.8	5.3
50°-60°	336.1	4.5
60°-70°	241.4	3.2
70°-80°	131.9	1.8
80°-90°	35.2	0.5
90°-100°	78.5	1.1
100°-110°	323.6	4.3
110°-120°	587.5	7.9
120°-130°	799.4	10.7
130°-140°	922.8	12.4
140°-150°	929.9	12.5
150°-160°	802.5	10.8
160°-170°	543.9	7.3
170°-180°	191.9	2.6
0°-30°	712.6	9.6
0°-40°	1124.4	15.1
0°-60°	1858.2	25.0
0°-90°	2266.7	30.4
90°-120°	989.5	13.3
90°-150°	3641.7	48.9
90°-180°	5180.0	69.6
0°-180°	7446.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	972	972	972	972	972	
5°	960	973	962	962	968	91
15°	911	919	905	896	898	257
25°	819	819	796	778	773	377
35°	696	688	656	630	624	435
45°	558	546	513	486	479	431
55°	417	402	372	349	342	373
65°	273	263	241	224	220	271
75°	141	133	123	113	110	151
85°	33	31	30	26	25	39
90°	0	0	2	0	2	4
95°	76	67	63	49	49	88
105°	320	315	307	290	287	340
115°	608	607	596	578	577	600
125°	905	914	895	876	878	808
135°	1206	1220	1199	1177	1185	928
145°	1494	1511	1488	1470	1481	933
155°	1748	1765	1740	1729	1743	804
165°	1931	1951	1926	1916	1933	544
175°	2023	2045	2018	2006	2010	192
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P1439083

CATALOG NUMBER: CB2-D-125U-055D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	972.0	972.0	972.0	972.0	972.0
2.5°	965.5	977.1	968.4	969.7	971.4
5°	960.1	973.2	961.6	961.7	968.3
7.5°	953.3	965.6	951.0	948.3	954.4
10°	943.7	956.1	941.5	936.4	940.8
12.5°	931.2	943.0	929.0	920.9	924.7
15°	911.0	919.0	905.0	896.1	897.6
17.5°	889.0	893.9	873.8	866.3	864.8
20°	872.3	876.6	852.9	842.5	841.0
22.5°	850.8	854.6	829.7	816.9	814.8
25°	818.7	819.4	795.6	777.7	773.3
27.5°	785.1	782.7	756.3	735.1	729.4
30°	760.6	757.7	727.1	704.7	699.6
32.5°	734.4	729.2	698.6	674.3	669.2
35°	695.9	687.9	655.7	630.3	624.4
37.5°	654.8	645.8	614.2	586.5	579.9
40°	627.4	617.2	585.0	557.3	550.8
42.5°	600.0	588.7	555.8	528.1	521.0
45°	557.5	545.8	512.8	485.8	478.6
47.5°	517.0	502.1	470.1	443.3	436.0
50°	489.0	473.0	442.1	415.9	408.6
52.5°	460.4	443.8	414.1	389.1	381.8
55°	416.8	401.5	372.1	348.9	342.4
57.5°	373.6	358.9	332.1	309.9	303.5
60°	343.9	331.5	305.9	284.9	279.1
62.5°	315.3	304.1	279.7	260.5	254.7
65°	273.1	263.0	241.1	223.9	219.6
67.5°	232.2	222.0	204.4	188.9	184.0
70°	205.4	195.2	179.4	165.1	160.8
72.5°	179.8	169.0	156.1	143.1	139.9
75°	141.4	132.7	122.8	113.1	110.2
77.5°	107.5	99.0	91.8	85.0	84.3
80°	84.8	77.6	72.2	67.7	67.0
82.5°	63.4	57.9	54.3	51.1	50.9
85°	32.7	30.6	29.8	26.0	24.6
87.5°	9.5	9.5	8.7	7.2	7.5
90°	0.0	0.0	1.6	0.0	1.6
92.5°	19.0	16.5	15.5	10.2	11.7
95°	76.0	66.8	63.4	49.1	49.1
97.5°	143.5	134.2	129.3	114.6	111.5
100°	191.7	182.4	177.4	161.5	158.4
102.5°	241.1	236.8	228.1	211.0	207.9
105°	320.0	315.4	307.4	289.9	286.8
107.5°	401.2	402.1	390.1	375.7	371.4
110°	459.5	457.9	448.4	434.0	430.9



TEST NUMBER: P1439083

CATALOG NUMBER: CB2-D-125U-055D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	519.0	516.2	506.7	492.3	489.2
115°	608.4	606.8	595.7	578.2	576.7
117.5°	693.3	698.3	685.1	666.7	666.1
120°	754.1	760.3	744.6	728.7	725.6
122.5°	813.7	821.1	805.5	787.1	787.7
125°	904.7	913.9	895.1	876.2	877.7
127.5°	992.4	1003.9	986.4	967.1	969.0
130°	1052.0	1065.9	1047.2	1026.7	1029.8
132.5°	1112.8	1126.8	1108.1	1086.3	1091.9
135°	1205.7	1219.6	1199.3	1177.3	1185.1
137.5°	1293.1	1307.1	1284.9	1266.4	1275.7
140°	1351.4	1365.4	1341.9	1324.7	1334.0
142.5°	1408.5	1424.9	1400.2	1381.8	1393.6
145°	1494.0	1511.1	1487.7	1470.5	1481.3
147.5°	1575.1	1592.2	1568.5	1551.9	1563.1
150°	1627.1	1644.1	1619.2	1605.2	1617.6
152.5°	1675.3	1694.8	1668.6	1654.7	1670.8
155°	1747.5	1764.6	1739.6	1728.8	1742.8
157.5°	1810.3	1830.1	1805.2	1795.9	1807.1
160°	1852.1	1870.7	1845.7	1836.5	1848.9
162.5°	1883.8	1903.6	1880.0	1869.5	1884.4
165°	1931.3	1951.4	1926.5	1915.8	1932.9
167.5°	1968.7	1990.1	1964.9	1953.9	1971.2
170°	1991.5	2011.6	1985.2	1972.9	1991.5
172.5°	2006.7	2028.1	2000.4	1988.0	2000.4
175°	2023.2	2044.9	2018.4	2005.9	2010.5
177.5°	2031.1	2048.5	2027.3	2016.2	2031.1
180°	2031.1	2031.1	2031.1	2031.1	2031.1



TEST NUMBER: P1439083
 CATALOG NUMBER: CB2-D-125U-055D-930-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.67	15.37	15.78	16.48	18.01	13.57	14.28	14.68	15.38	16.91
	3H	16.30	16.93	17.42	18.05	19.59	15.09	15.72	16.21	16.83	18.37
	4H	16.93	17.52	18.05	18.64	20.19	15.65	16.25	16.78	17.36	18.91
	6H	17.32	17.87	18.46	18.99	20.55	16.02	16.57	17.15	17.68	19.24
	8H	17.46	17.99	18.60	19.12	20.67	16.15	16.68	17.29	17.81	19.36
	12H	17.53	18.03	18.68	19.15	20.73	16.21	16.71	17.36	17.83	19.41
4H	2H	15.06	15.66	16.20	16.77	18.32	14.19	14.78	15.32	15.90	17.45
	3H	16.92	17.41	18.06	18.55	20.11	15.91	16.41	17.05	17.55	19.11
	4H	17.66	18.11	18.80	19.24	20.82	16.58	17.03	17.72	18.16	19.74
	6H	18.17	18.56	19.32	19.71	21.28	17.04	17.43	18.19	18.59	20.16
	8H	18.37	18.73	19.52	19.88	21.46	17.23	17.59	18.38	18.74	20.33
	12H	18.47	18.80	19.63	19.95	21.55	17.31	17.64	18.48	18.80	20.39
8H	4H	17.80	18.17	18.95	19.31	20.90	16.84	17.20	17.99	18.35	19.93
	6H	18.44	18.74	19.61	19.92	21.51	17.43	17.74	18.61	18.92	20.51
	8H	18.72	18.99	19.90	20.15	21.76	17.71	17.97	18.88	19.14	20.74
	12H	18.89	19.12	20.07	20.28	21.92	17.85	18.08	19.03	19.24	20.88
12H	4H	17.77	18.10	18.94	19.26	20.85	16.83	17.16	18.00	18.32	19.91
	6H	18.46	18.73	19.64	19.89	21.50	17.50	17.76	18.67	18.92	20.53
	8H	18.77	19.00	19.95	20.17	21.80	17.79	18.03	18.97	19.19	20.83