

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438644

Luminaire Tested: CB2-055U-030D-835-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438644
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-055U-030D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7539.1 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438644

CATALOG NUMBER: CB2-055U-030D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438644

CATALOG NUMBER: CB2-055U-030D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	12
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8636	8636	8636
5°	8562	8576	8635
10°	8513	8494	8487
15°	8378	8323	8256
20°	8246	8064	7952
25°	8025	7799	7581
30°	7803	7459	7177
35°	7547	7111	6772
40°	7276	6785	6387
45°	7004	6442	6013
50°	6758	6110	5647
55°	6456	5764	5303
60°	6110	5436	4959
65°	5741	5069	4616
70°	5337	4660	4176
75°	4855	4216	3782
80°	4343	3691	3425
85°	3337	3038	2508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7004 cd/sqm



TEST NUMBER: P1438644

CATALOG NUMBER: CB2-055U-030D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.2	1.2
10°-20°	259.9	3.4
20°-30°	373.7	5.0
30°-40°	420.1	5.6
40°-50°	405.8	5.4
50°-60°	342.9	4.5
60°-70°	246.3	3.3
70°-80°	134.6	1.8
80°-90°	35.8	0.5
90°-100°	31.9	0.4
100°-110°	203.3	2.7
110°-120°	646.0	8.6
120°-130°	937.4	12.4
130°-140°	1008.2	13.4
140°-150°	949.3	12.6
150°-160°	773.3	10.3
160°-170°	503.3	6.7
170°-180°	174.0	2.3
0°-30°	726.9	9.6
0°-40°	1147.0	15.2
0°-60°	1895.6	25.1
0°-90°	2312.3	30.7
90°-120°	881.3	11.7
90°-150°	3776.2	50.1
90°-180°	5227.0	69.3
0°-180°	7539.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	992	992	992	992	992	
5°	979	993	981	981	988	93
15°	929	938	923	914	916	262
25°	835	836	812	793	789	384
35°	710	702	669	643	637	443
45°	569	557	523	496	488	439
55°	425	410	380	356	349	380
65°	279	268	246	228	224	276
75°	144	135	125	115	112	154
85°	33	31	30	26	25	40
90°	0	0	0	1	1	4
95°	73	21	22	15	13	92
105°	382	396	40	46	49	402
115°	722	738	745	754	432	710
125°	1026	1044	1044	1062	1076	917
135°	1291	1306	1304	1313	1329	996
145°	1511	1523	1512	1514	1534	944
155°	1678	1688	1670	1667	1690	774
165°	1789	1794	1776	1768	1787	505
175°	1842	1846	1822	1811	1820	175
180°	1833	1833	1833	1833	1833	

TEST NUMBER: P1438644

CATALOG NUMBER: CB2-055U-030D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	991.6	991.6	991.6	991.6	991.6
2.5°	984.9	996.8	987.9	989.2	991.0
5°	979.4	992.8	981.0	981.1	987.8
7.5°	972.4	985.1	970.2	967.4	973.7
10°	962.7	975.3	960.5	955.2	959.7
12.5°	950.0	962.0	947.7	939.4	943.3
15°	929.3	937.5	923.2	914.2	915.7
17.5°	906.8	911.9	891.4	883.7	882.2
20°	889.8	894.3	870.1	859.4	858.0
22.5°	868.0	871.8	846.4	833.3	831.2
25°	835.2	835.9	811.6	793.3	788.9
27.5°	800.9	798.5	771.5	749.9	744.1
30°	776.0	773.0	741.8	718.9	713.7
32.5°	749.2	743.9	712.6	687.9	682.7
35°	709.9	701.7	668.9	642.9	637.0
37.5°	668.0	658.8	626.5	598.3	591.6
40°	640.0	629.7	596.8	568.5	561.8
42.5°	612.1	600.5	567.0	538.8	531.5
45°	568.7	556.8	523.1	495.6	488.2
47.5°	527.4	512.2	479.5	452.2	444.8
50°	498.8	482.5	451.0	424.3	416.8
52.5°	469.7	452.7	422.4	396.9	389.5
55°	425.2	409.6	379.6	355.9	349.3
57.5°	381.1	366.1	338.8	316.2	309.6
60°	350.8	338.2	312.1	290.7	284.7
62.5°	321.6	310.2	285.3	265.8	259.8
65°	278.6	268.3	246.0	228.4	224.0
67.5°	236.9	226.5	208.5	192.7	187.7
70°	209.6	199.2	183.0	168.5	164.0
72.5°	183.4	172.4	159.3	146.0	142.7
75°	144.3	135.3	125.3	115.3	112.4
77.5°	109.6	101.0	93.7	86.7	85.9
80°	86.6	79.1	73.6	69.1	68.3
82.5°	64.7	59.0	55.4	52.1	51.9
85°	33.4	31.2	30.4	26.5	25.1
87.5°	9.7	9.7	8.5	7.6	7.6
90°	0.0	0.0	0.0	1.3	1.3
92.5°	20.1	7.7	5.3	7.7	7.7
95°	72.9	21.1	22.5	14.6	13.3
97.5°	151.4	33.9	32.6	35.8	37.1
100°	210.7	69.5	35.8	41.1	42.4
102.5°	276.5	261.7	36.8	44.3	46.7
105°	381.7	396.0	39.8	46.4	49.0
107.5°	485.1	499.4	185.0	48.0	50.6
110°	554.0	568.3	585.8	49.1	51.7



TEST NUMBER: P1438644

CATALOG NUMBER: CB2-055U-030D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	618.7	636.1	649.5	109.3	53.8
115°	722.4	737.9	744.9	753.5	432.1
117.5°	813.8	833.0	840.9	855.8	870.3
120°	877.4	895.6	901.3	916.2	931.8
122.5°	940.0	956.1	959.6	976.6	991.2
125°	1025.9	1044.0	1044.4	1062.0	1076.3
127.5°	1111.8	1127.3	1126.6	1139.7	1155.5
130°	1169.0	1179.4	1179.6	1190.6	1207.5
132.5°	1216.8	1231.3	1231.6	1240.5	1257.3
135°	1291.0	1306.5	1304.2	1312.6	1329.4
137.5°	1360.7	1375.7	1371.6	1378.6	1396.0
140°	1406.3	1419.3	1412.9	1420.0	1439.4
142.5°	1448.7	1461.7	1452.2	1458.2	1478.7
145°	1511.0	1522.7	1512.3	1514.1	1533.5
147.5°	1566.4	1577.8	1565.3	1567.1	1585.2
150°	1602.5	1612.8	1597.2	1598.9	1617.0
152.5°	1634.3	1643.6	1626.8	1626.5	1647.8
155°	1678.0	1688.4	1670.1	1666.6	1689.9
157.5°	1717.8	1727.4	1709.0	1706.5	1724.7
160°	1744.3	1750.8	1732.4	1728.8	1746.9
162.5°	1762.3	1769.8	1751.4	1745.8	1763.9
165°	1789.3	1794.5	1776.1	1768.5	1786.7
167.5°	1812.7	1818.6	1794.9	1788.2	1807.6
170°	1826.5	1830.3	1806.6	1797.7	1817.2
172.5°	1834.9	1837.8	1814.0	1804.0	1817.2
175°	1842.4	1846.3	1822.5	1810.8	1819.8
177.5°	1843.7	1845.8	1827.8	1817.5	1833.1
180°	1833.1	1833.1	1833.1	1833.1	1833.1



TEST NUMBER: P1438644

CATALOG NUMBER: CB2-055U-030D-835-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.36	13.07	13.47	14.17	15.69	11.27	11.97	12.37	13.07	14.60
	3H	14.00	14.63	15.11	15.74	17.28	12.78	13.41	13.90	14.52	16.06
	4H	14.62	15.22	15.75	16.33	17.88	13.35	13.95	14.47	15.06	16.60
	6H	15.01	15.56	16.15	16.68	18.24	13.71	14.26	14.85	15.38	16.93
	8H	15.16	15.68	16.30	16.81	18.36	13.85	14.37	14.98	15.50	17.05
	12H	15.23	15.72	16.37	16.85	18.42	13.90	14.40	15.05	15.52	17.10
4H	2H	12.75	13.35	13.89	14.46	16.01	11.88	12.48	13.02	13.59	15.14
	3H	14.61	15.11	15.75	16.25	17.80	13.60	14.10	14.74	15.24	16.80
	4H	15.35	15.81	16.49	16.93	18.51	14.27	14.73	15.41	15.85	17.43
	6H	15.86	16.25	17.01	17.40	18.97	14.73	15.13	15.88	16.28	17.85
	8H	16.06	16.43	17.21	17.57	19.15	14.92	15.29	16.07	16.43	18.01
	12H	16.16	16.49	17.32	17.65	19.24	15.00	15.33	16.17	16.49	18.08
8H	4H	15.49	15.86	16.64	17.00	18.59	14.53	14.90	15.68	16.04	17.62
	6H	16.13	16.43	17.30	17.61	19.20	15.13	15.43	16.30	16.61	18.20
	8H	16.42	16.68	17.59	17.84	19.45	15.40	15.66	16.58	16.83	18.43
	12H	16.58	16.82	17.76	17.98	19.61	15.54	15.78	16.72	16.94	18.57
12H	4H	15.46	15.80	16.63	16.95	18.54	14.53	14.86	15.69	16.01	17.60
	6H	16.16	16.42	17.33	17.58	19.19	15.19	15.45	16.36	16.62	18.22
	8H	16.46	16.70	17.64	17.86	19.49	15.49	15.72	16.67	16.88	18.52