

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056951

Luminaire Tested: CB2-0U-030D-835-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056951
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-030D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2312.3 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 18.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056951

CATALOG NUMBER: CB2-0U-030D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056951

CATALOG NUMBER: CB2-OU-030D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	95	98	95	92		94	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		83	79	76		80
3	91	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	73	64	58	82	71	63	57	69	62	56		66	60	56		64
5	78	65	56	50	76	64	56	50	62	55	49		60	54	49		58
6	72	59	50	44	70	58	50	44	56	49	43		55	48	43		53
7	67	54	45	39	65	53	45	39	51	44	39		50	43	38		49
8	62	49	41	35	61	48	41	35	47	40	35		46	39	35		45
9	58	45	37	32	57	45	37	32	44	37	32		42	36	31		41
10	55	42	34	29	54	41	34	29	40	34	29		39	33	29		39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8636	8636	8636
5°	8562	8576	8635
10°	8513	8494	8487
15°	8378	8323	8256
20°	8246	8064	7952
25°	8025	7799	7581
30°	7803	7459	7177
35°	7547	7111	6772
40°	7276	6785	6387
45°	7004	6442	6013
50°	6758	6110	5647
55°	6456	5764	5303
60°	6110	5436	4959
65°	5741	5069	4616
70°	5337	4660	4176
75°	4855	4216	3782
80°	4343	3691	3425
85°	3337	3038	2508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7004 cd/sqm

TEST NUMBER: P1056951

CATALOG NUMBER: CB2-0U-030D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.2	4.0
10°-20°	259.9	11.2
20°-30°	373.7	16.2
30°-40°	420.1	18.2
40°-50°	405.8	17.5
50°-60°	342.9	14.8
60°-70°	246.3	10.7
70°-80°	134.6	5.8
80°-90°	35.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	726.9	31.4
0°-40°	1147.0	49.6
0°-60°	1895.6	82.0
0°-90°	2312.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2312.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	992	992	992	992	992	
5°	979	993	981	981	988	93
15°	929	938	923	914	916	262
25°	835	836	812	793	789	384
35°	710	702	669	643	637	443
45°	569	557	523	496	488	439
55°	425	410	380	356	349	380
65°	279	268	246	228	224	276
75°	144	135	125	115	112	154
85°	33	31	30	26	25	41
90°	0	0	0	0	0	

TEST NUMBER: P1056951

CATALOG NUMBER: CB2-OU-030D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	991.6	991.6	991.6	991.6	991.6
2.5°	984.9	996.8	987.9	989.2	991.0
5°	979.4	992.8	981.0	981.1	987.8
7.5°	972.4	985.1	970.2	967.4	973.7
10°	962.7	975.3	960.5	955.2	959.7
12.5°	950.0	962.0	947.7	939.4	943.3
15°	929.3	937.5	923.2	914.2	915.7
17.5°	906.8	911.9	891.4	883.7	882.2
20°	889.8	894.3	870.1	859.4	858.0
22.5°	868.0	871.8	846.4	833.3	831.2
25°	835.2	835.9	811.6	793.3	788.9
27.5°	800.9	798.5	771.5	749.9	744.1
30°	776.0	773.0	741.8	718.9	713.7
32.5°	749.2	743.9	712.6	687.9	682.7
35°	709.9	701.7	668.9	642.9	637.0
37.5°	668.0	658.8	626.5	598.3	591.6
40°	640.0	629.7	596.8	568.5	561.8
42.5°	612.1	600.5	567.0	538.8	531.5
45°	568.7	556.8	523.1	495.6	488.2
47.5°	527.4	512.2	479.5	452.2	444.8
50°	498.8	482.5	451.0	424.3	416.8
52.5°	469.7	452.7	422.4	396.9	389.5
55°	425.2	409.6	379.6	355.9	349.3
57.5°	381.1	366.1	338.8	316.2	309.6
60°	350.8	338.2	312.1	290.7	284.7
62.5°	321.6	310.2	285.3	265.8	259.8
65°	278.6	268.3	246.0	228.4	224.0
67.5°	236.9	226.5	208.5	192.7	187.7
70°	209.6	199.2	183.0	168.5	164.0
72.5°	183.4	172.4	159.3	146.0	142.7
75°	144.3	135.3	125.3	115.3	112.4
77.5°	109.6	101.0	93.7	86.7	85.9
80°	86.6	79.1	73.6	69.1	68.3
82.5°	64.7	59.0	55.4	52.1	51.9
85°	33.4	31.2	30.4	26.5	25.1
87.5°	9.7	9.7	8.5	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)