

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056957

Luminaire Tested: CB2-0U-085D-835-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056957
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-085D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6742.4 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056957

CATALOG NUMBER: CB2-0U-085D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056957

CATALOG NUMBER: CB2-OU-085D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25180	25180	25180
5°	24967	25005	25179
10°	24825	24766	24746
15°	24431	24272	24072
20°	24047	23514	23185
25°	23401	22742	22103
30°	22752	21751	20927
35°	22007	20736	19748
40°	21217	19782	18625
45°	20422	18787	17533
50°	19706	17817	16467
55°	18824	16808	15462
60°	17814	15848	14460
65°	16743	14781	13458
70°	15558	13587	12176
75°	14152	12292	11026
80°	12658	10772	9995
85°	9732	8853	7304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20422 cd/sqm

TEST NUMBER: P1056957

CATALOG NUMBER: CB2-0U-085D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.9	4.0
10°-20°	757.9	11.2
20°-30°	1089.8	16.2
30°-40°	1224.9	18.2
40°-50°	1183.3	17.5
50°-60°	999.8	14.8
60°-70°	718.1	10.7
70°-80°	392.5	5.8
80°-90°	104.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2119.6	31.4
0°-40°	3344.5	49.6
0°-60°	5527.6	82.0
0°-90°	6742.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6742.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2891	2891	2891	2891	2891	
5°	2856	2895	2860	2861	2880	271
15°	2710	2734	2692	2666	2670	764
25°	2435	2438	2367	2313	2300	1121
35°	2070	2046	1950	1875	1858	1293
45°	1658	1624	1525	1445	1424	1281
55°	1240	1194	1107	1038	1018	1108
65°	812	782	717	666	653	806
75°	421	395	365	336	328	450
85°	97	91	89	77	73	120
90°	0	0	0	0	0	

TEST NUMBER: P1056957

CATALOG NUMBER: CB2-OU-085D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2891.4	2891.4	2891.4	2891.4	2891.4
2.5°	2871.9	2906.5	2880.8	2884.4	2889.6
5°	2856.0	2894.9	2860.4	2860.8	2880.3
7.5°	2835.6	2872.4	2829.0	2821.0	2839.1
10°	2807.3	2844.1	2800.6	2785.4	2798.4
12.5°	2770.1	2805.1	2763.4	2739.3	2750.6
15°	2709.8	2733.7	2692.1	2665.7	2670.0
17.5°	2644.3	2659.0	2599.1	2576.9	2572.6
20°	2594.7	2607.7	2537.2	2506.1	2501.7
22.5°	2531.0	2542.2	2468.1	2429.9	2423.8
25°	2435.3	2437.5	2366.7	2313.3	2300.3
27.5°	2335.2	2328.3	2249.8	2186.5	2169.6
30°	2262.6	2254.0	2163.0	2096.2	2081.1
32.5°	2184.7	2169.1	2078.0	2005.9	1990.8
35°	2070.0	2046.2	1950.5	1874.8	1857.5
37.5°	1947.8	1921.0	1826.9	1744.6	1725.1
40°	1866.3	1836.0	1740.1	1657.8	1638.3
42.5°	1784.9	1751.1	1653.4	1571.0	1549.7
45°	1658.2	1623.6	1525.4	1445.2	1423.6
47.5°	1537.8	1493.6	1398.3	1318.6	1296.9
50°	1454.5	1406.9	1315.1	1237.1	1215.4
52.5°	1369.5	1320.2	1231.8	1157.4	1135.7
55°	1239.8	1194.3	1107.0	1037.9	1018.4
57.5°	1111.4	1067.7	987.9	921.9	902.8
60°	1022.8	986.0	909.9	847.5	830.2
62.5°	937.8	904.5	832.0	774.9	757.6
65°	812.5	782.2	717.3	666.1	653.1
67.5°	690.7	660.4	607.9	562.0	547.3
70°	611.0	580.7	533.6	491.2	478.2
72.5°	534.9	502.8	464.5	425.7	416.2
75°	420.6	394.7	365.3	336.3	327.7
77.5°	319.7	294.6	273.2	252.8	250.6
80°	252.4	230.7	214.8	201.4	199.3
82.5°	188.6	172.2	161.6	151.9	151.4
85°	97.4	90.9	88.6	77.4	73.1
87.5°	28.3	28.3	24.8	21.3	21.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)