

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438756

Luminaire Tested: CB2-0U-030D-930-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438756  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-0U-030D-930-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE  
2-INCH APERTURE  
DOWNLIGHT 300 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2373.0 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')  
CIE Type: Direct

Input Watts (W): 18.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438756

CATALOG NUMBER: CB2-OU-030D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1438756

CATALOG NUMBER: CB2-OU-030D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87	85					85			
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72					72			
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61					61			
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55	53					53			
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48	46					46			
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43	41					41			
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38	36					36			
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	33					33			
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	29					29			
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	27					27			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8862	8862	8862
5°	8787	8801	8862
10°	8737	8717	8709
15°	8598	8543	8472
20°	8463	8276	8160
25°	8236	8004	7779
30°	8008	7656	7365
35°	7745	7298	6950
40°	7468	6962	6555
45°	7188	6612	6170
50°	6935	6270	5796
55°	6624	5915	5442
60°	6270	5577	5089
65°	5893	5203	4737
70°	5477	4782	4285
75°	4980	4327	3880
80°	4453	3791	3516
85°	3427	3118	2568

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7188 cd/sqm



TEST NUMBER: P1438756

CATALOG NUMBER: CB2-OU-030D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.7	4.0
10°-20°	266.8	11.2
20°-30°	383.6	16.2
30°-40°	431.1	18.2
40°-50°	416.4	17.5
50°-60°	351.9	14.8
60°-70°	252.7	10.7
70°-80°	138.1	5.8
80°-90°	36.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.0	31.4
0°-40°	1177.1	49.6
0°-60°	1945.4	82.0
0°-90°	2373.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2373.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1018	1018	1018	1018	1018	
5°	1005	1019	1007	1007	1014	95
15°	954	962	948	938	940	269
25°	857	858	833	814	810	395
35°	728	720	686	660	654	455
45°	584	571	537	509	501	451
55°	436	420	390	365	358	390
65°	286	275	252	234	230	284
75°	148	139	129	118	115	158
85°	34	32	31	27	26	42
90°	0	0	0	0	0	

TEST NUMBER: P1438756

CATALOG NUMBER: CB2-OU-030D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1017.6	1017.6	1017.6	1017.6	1017.6
2.5°	1010.8	1023.0	1013.9	1015.2	1017.0
5°	1005.2	1018.9	1006.7	1006.9	1013.7
7.5°	998.0	1010.9	995.6	992.8	999.2
10°	988.0	1001.0	985.7	980.3	984.9
12.5°	974.9	987.3	972.6	964.1	968.1
15°	953.7	962.1	947.5	938.2	939.7
17.5°	930.7	935.8	914.8	906.9	905.4
20°	913.2	917.8	893.0	882.0	880.5
22.5°	890.8	894.7	868.6	855.2	853.1
25°	857.1	857.9	833.0	814.1	809.6
27.5°	821.9	819.5	791.8	769.5	763.6
30°	796.3	793.3	761.3	737.8	732.4
32.5°	768.9	763.4	731.3	706.0	700.6
35°	728.5	720.2	686.5	659.8	653.7
37.5°	685.5	676.1	643.0	614.0	607.1
40°	656.9	646.2	612.4	583.5	576.6
42.5°	628.2	616.3	581.9	552.9	545.4
45°	583.6	571.4	536.9	508.6	501.0
47.5°	541.2	525.7	492.1	464.1	456.4
50°	511.9	495.2	462.8	435.4	427.8
52.5°	482.0	464.6	433.5	407.3	399.7
55°	436.3	420.3	389.6	365.3	358.4
57.5°	391.2	375.8	347.7	324.5	317.8
60°	360.0	347.0	320.2	298.3	292.2
62.5°	330.1	318.3	292.8	272.7	266.6
65°	286.0	275.3	252.5	234.4	229.9
67.5°	243.1	232.4	214.0	197.8	192.6
70°	215.1	204.4	187.8	172.9	168.3
72.5°	188.3	177.0	163.5	149.8	146.5
75°	148.0	138.9	128.6	118.4	115.3
77.5°	112.5	103.7	96.2	89.0	88.2
80°	88.8	81.2	75.6	70.9	70.1
82.5°	66.4	60.6	56.9	53.4	53.3
85°	34.3	32.0	31.2	27.2	25.7
87.5°	10.0	10.0	8.7	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1438756  
 CATALOG NUMBER: CB2-0U-030D-930-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.43	20.01	18.80	20.32	20.64	17.33	18.91	17.70	19.23	19.54
	3H	20.13	21.55	20.50	21.88	22.24	18.91	20.33	19.29	20.66	21.02
	4H	20.78	22.12	21.18	22.47	22.85	19.51	20.85	19.91	21.20	21.58
	6H	21.22	22.46	21.63	22.83	23.22	19.92	21.16	20.33	21.52	21.91
	8H	21.39	22.57	21.81	22.96	23.36	20.08	21.26	20.50	21.65	22.05
	12H	21.49	22.62	21.92	23.00	23.43	20.16	21.29	20.59	21.68	22.11
4H	2H	18.92	20.26	19.32	20.61	20.98	18.05	19.38	18.45	19.73	20.11
	3H	20.85	21.97	21.26	22.37	22.77	19.84	20.96	20.25	21.36	21.76
	4H	21.62	22.63	22.06	23.05	23.48	20.54	21.55	20.97	21.97	22.40
	6H	22.18	23.06	22.64	23.50	23.96	21.06	21.94	21.51	22.38	22.83
	8H	22.40	23.22	22.86	23.67	24.13	21.26	22.08	21.72	22.53	22.99
	12H	22.54	23.28	23.02	23.76	24.23	21.38	22.12	21.86	22.60	23.07
8H	4H	21.83	22.66	22.30	23.10	23.57	20.87	21.69	21.33	22.14	22.60
	6H	22.50	23.19	23.00	23.67	24.15	21.50	22.18	22.00	22.67	23.15
	8H	22.80	23.41	23.31	23.92	24.41	21.78	22.39	22.29	22.90	23.39
	12H	23.01	23.55	23.51	24.04	24.60	21.96	22.51	22.47	23.00	23.56
12H	4H	21.85	22.58	22.33	23.06	23.53	20.91	21.64	21.39	22.12	22.59
	6H	22.54	23.15	23.05	23.66	24.14	21.57	22.18	22.08	22.69	23.18
	8H	22.89	23.43	23.39	23.92	24.48	21.91	22.45	22.42	22.94	23.50