

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056960

Luminaire Tested: CB2-0U-120D-835-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056960
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-120D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9598.1 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 88.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056960

CATALOG NUMBER: CB2-0U-120D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1056960

CATALOG NUMBER: CB2-OU-120D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48	46
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	35845	35845	35845
5°	35541	35596	35845
10°	35339	35255	35228
15°	34780	34552	34268
20°	34232	33473	33005
25°	33312	32374	31465
30°	32390	30963	29791
35°	31328	29519	28111
40°	30203	28162	26513
45°	29073	26744	24958
50°	28053	25364	23441
55°	26797	23926	22012
60°	25361	22561	20586
65°	23833	21041	19158
70°	22150	19339	17335
75°	20148	17497	15693
80°	18019	15331	14223
85°	13859	12600	10392

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29073 cd/sqm



TEST NUMBER: P1056960

CATALOG NUMBER: CB2-OU-120D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.1	4.0
10°-20°	1079.0	11.2
20°-30°	1551.4	16.2
30°-40°	1743.7	18.2
40°-50°	1684.4	17.5
50°-60°	1423.2	14.8
60°-70°	1022.3	10.7
70°-80°	558.7	5.8
80°-90°	148.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3017.4	31.4
0°-40°	4761.1	49.6
0°-60°	7868.8	82.0
0°-90°	9598.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9598.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4116	4116	4116	4116	4116	
5°	4066	4121	4072	4072	4100	386
15°	3858	3892	3832	3795	3801	1087
25°	3467	3470	3369	3293	3274	1596
35°	2947	2913	2777	2669	2644	1841
45°	2361	2311	2172	2057	2026	1824
55°	1765	1700	1576	1478	1450	1578
65°	1157	1114	1021	948	930	1147
75°	599	562	520	479	466	641
85°	139	129	126	110	104	171
90°	0	0	0	0	0	



TEST NUMBER: P1056960

CATALOG NUMBER: CB2-OU-120D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4116.0	4116.0	4116.0	4116.0	4116.0
2.5°	4088.3	4137.6	4100.9	4106.1	4113.5
5°	4065.6	4121.1	4071.9	4072.5	4100.3
7.5°	4036.6	4089.0	4027.2	4015.8	4041.7
10°	3996.3	4048.7	3986.8	3965.2	3983.7
12.5°	3943.3	3993.2	3933.9	3899.6	3915.6
15°	3857.6	3891.5	3832.4	3794.7	3800.9
17.5°	3764.3	3785.3	3700.0	3668.4	3662.2
20°	3693.7	3712.2	3611.8	3567.5	3561.3
22.5°	3602.9	3619.0	3513.4	3459.0	3450.4
25°	3466.8	3469.9	3369.1	3293.0	3274.5
27.5°	3324.3	3314.5	3202.7	3112.6	3088.6
30°	3221.0	3208.6	3079.1	2984.1	2962.5
32.5°	3110.0	3087.8	2958.1	2855.5	2833.9
35°	2946.8	2912.9	2776.6	2668.9	2644.2
37.5°	2772.8	2734.6	2600.7	2483.5	2455.8
40°	2656.8	2613.7	2477.2	2359.9	2332.2
42.5°	2540.8	2492.8	2353.6	2236.3	2206.1
45°	2360.6	2311.3	2171.5	2057.3	2026.5
47.5°	2189.1	2126.3	1990.6	1877.0	1846.2
50°	2070.6	2002.8	1872.1	1761.1	1730.2
52.5°	1949.6	1879.3	1753.6	1647.6	1616.8
55°	1764.9	1700.2	1575.8	1477.5	1449.8
57.5°	1582.1	1519.9	1406.3	1312.4	1285.2
60°	1456.1	1403.7	1295.3	1206.5	1181.9
62.5°	1335.0	1287.6	1184.4	1103.1	1078.5
65°	1156.6	1113.5	1021.1	948.2	929.7
67.5°	983.3	940.2	865.4	800.0	779.1
70°	869.9	826.7	759.5	699.2	680.8
72.5°	761.4	715.8	661.2	606.1	592.5
75°	598.8	561.8	520.0	478.8	466.4
77.5°	455.1	419.3	388.9	359.8	356.8
80°	359.3	328.5	305.7	286.7	283.6
82.5°	268.5	245.1	230.1	216.2	215.6
85°	138.7	129.4	126.1	110.2	104.0
87.5°	40.3	40.3	35.3	30.3	30.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)