

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438988

Luminaire Tested: CB2-D-030U-055D-930-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438988  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-D-030U-055D-930-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 550 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6902.0 lumens  
Efficiency: N/A  
Efficacy: 125.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 54.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438988

CATALOG NUMBER: CB2-D-030U-055D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1438988

CATALOG NUMBER: CB2-D-030U-055D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56				
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47				
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40				
4	78	67	59	53	73	63	56	50	56	51	46	50	46	42	44	41	38	35				
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30				
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27				
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24				
8	57	44	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21				
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19				
10	50	37	30	25	47	36	29	24	32	27	23	29	25	21	26	22	20	18				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16930	16930	16930
5°	16786	16812	16930
10°	16691	16651	16638
15°	16427	16320	16185
20°	16168	15810	15588
25°	15734	15290	14861
30°	15298	14624	14070
35°	14797	13942	13277
40°	14265	13301	12522
45°	13731	12631	11788
50°	13250	11979	11072
55°	12657	11301	10396
60°	11978	10656	9722
65°	11257	9938	9048
70°	10460	9133	8186
75°	9516	8264	7413
80°	8511	7242	6720
85°	6545	5945	4906

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13731 cd/sqm



TEST NUMBER: P1438988

CATALOG NUMBER: CB2-D-030U-055D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.8	2.6
10°-20°	509.6	7.4
20°-30°	732.7	10.6
30°-40°	823.6	11.9
40°-50°	795.6	11.5
50°-60°	672.2	9.7
60°-70°	482.8	7.0
70°-80°	263.9	3.8
80°-90°	70.1	1.0
90°-100°	35.9	0.5
100°-110°	148.0	2.1
110°-120°	268.6	3.9
120°-130°	365.5	5.3
130°-140°	422.0	6.1
140°-150°	425.2	6.2
150°-160°	367.0	5.3
160°-170°	248.7	3.6
170°-180°	87.7	1.3
0°-30°	1425.1	20.6
0°-40°	2248.7	32.6
0°-60°	3716.5	53.8
0°-90°	4533.3	65.7
90°-120°	452.5	6.6
90°-150°	1665.2	24.1
90°-180°	2369.0	34.3
0°-180°	6902.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1944	1944	1944	1944	1944	
5°	1920	1946	1923	1924	1937	182
15°	1822	1838	1810	1792	1795	514
25°	1637	1639	1591	1555	1547	754
35°	1392	1376	1311	1260	1249	869
45°	1115	1092	1026	972	957	861
55°	834	803	744	698	685	745
65°	546	526	482	448	439	542
75°	283	265	246	226	220	302
85°	66	61	60	52	49	78
90°	0	0	1	0	1	4
95°	35	30	29	22	22	40
105°	146	144	140	132	131	155
115°	278	278	272	264	264	275
125°	414	418	409	401	401	369
135°	551	558	548	538	542	425
145°	683	691	680	672	677	427
155°	799	807	796	790	797	367
165°	883	892	881	876	884	249
175°	925	935	923	917	919	88
180°	929	929	929	929	929	

TEST NUMBER: P1438988

CATALOG NUMBER: CB2-D-030U-055D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1944.0	1944.0	1944.0	1944.0	1944.0
2.5°	1930.9	1954.2	1936.9	1939.3	1942.8
5°	1920.2	1946.4	1923.2	1923.5	1936.6
7.5°	1906.5	1931.3	1902.1	1896.7	1908.9
10°	1887.5	1912.2	1883.0	1872.8	1881.5
12.5°	1862.5	1886.0	1858.0	1841.8	1849.4
15°	1822.0	1838.0	1810.1	1792.3	1795.2
17.5°	1777.9	1787.8	1747.5	1732.6	1729.7
20°	1744.6	1753.3	1705.9	1685.0	1682.0
22.5°	1701.7	1709.3	1659.4	1633.7	1629.6
25°	1637.4	1638.8	1591.2	1555.3	1546.6
27.5°	1570.1	1565.5	1512.7	1470.1	1458.8
30°	1521.3	1515.5	1454.3	1409.4	1399.2
32.5°	1468.9	1458.4	1397.1	1348.7	1338.5
35°	1391.8	1375.8	1311.4	1260.5	1248.9
37.5°	1309.6	1291.6	1228.3	1173.0	1159.9
40°	1254.8	1234.5	1170.0	1114.6	1101.5
42.5°	1200.1	1177.4	1111.6	1056.2	1042.0
45°	1114.9	1091.6	1025.6	971.7	957.1
47.5°	1033.9	1004.2	940.2	886.5	872.0
50°	978.0	945.9	884.2	831.8	817.2
52.5°	920.8	887.6	828.2	778.2	763.6
55°	833.6	803.0	744.3	697.8	684.7
57.5°	747.2	717.8	664.2	619.8	607.0
60°	687.7	663.0	611.8	569.8	558.2
62.5°	630.5	608.1	559.4	521.0	509.4
65°	546.3	525.9	482.3	447.9	439.1
67.5°	464.4	444.0	408.8	377.9	368.0
70°	410.8	390.5	358.7	330.3	321.5
72.5°	359.6	338.1	312.3	286.2	279.8
75°	282.8	265.4	245.6	226.1	220.3
77.5°	214.9	198.1	183.7	170.0	168.5
80°	169.7	155.1	144.4	135.4	134.0
82.5°	126.8	115.8	108.7	102.1	101.8
85°	65.5	61.1	59.5	52.0	49.1
87.5°	19.1	19.1	16.8	14.3	14.4
90°	0.0	0.0	0.7	0.0	0.7
92.5°	8.7	7.6	7.1	4.7	5.4
95°	34.8	30.5	29.0	22.5	22.5
97.5°	65.6	61.4	59.1	52.4	51.0
100°	87.7	83.4	81.1	73.9	72.4
102.5°	110.3	108.3	104.3	96.5	95.0
105°	146.3	144.2	140.5	132.5	131.1
107.5°	183.4	183.9	178.4	171.8	169.8
110°	210.1	209.4	205.0	198.5	197.1



TEST NUMBER: P1438988

CATALOG NUMBER: CB2-D-030U-055D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	237.3	236.1	231.7	225.1	223.7
115°	278.2	277.5	272.4	264.4	263.7
117.5°	317.0	319.3	313.3	304.8	304.6
120°	344.8	347.7	340.5	333.2	331.8
122.5°	372.1	375.5	368.3	359.9	360.2
125°	413.7	417.9	409.3	400.6	401.4
127.5°	453.8	459.0	451.0	442.2	443.1
130°	481.0	487.4	478.9	469.5	470.9
132.5°	508.9	515.2	506.7	496.7	499.3
135°	551.3	557.7	548.4	538.4	541.9
137.5°	591.3	597.7	587.5	579.1	583.3
140°	618.0	624.3	613.6	605.7	610.0
142.5°	644.0	651.6	640.3	631.9	637.2
145°	683.2	691.0	680.3	672.4	677.4
147.5°	720.3	728.1	717.2	709.7	714.8
150°	744.0	751.8	740.4	734.0	739.7
152.5°	766.0	775.0	763.0	756.6	764.0
155°	799.1	806.9	795.5	790.5	796.9
157.5°	827.8	836.8	825.5	821.2	826.3
160°	846.9	855.4	844.0	839.8	845.4
162.5°	861.4	870.5	859.6	854.9	861.7
165°	883.1	892.3	880.9	876.1	883.8
167.5°	900.2	910.0	898.5	893.4	901.4
170°	910.6	919.9	907.7	902.1	910.6
172.5°	917.6	927.4	914.7	909.0	914.7
175°	925.1	935.1	923.0	917.2	919.3
177.5°	928.8	936.7	927.0	922.0	928.8
180°	928.8	928.8	928.8	928.8	928.8



TEST NUMBER: P1438988  
 CATALOG NUMBER: CB2-D-030U-055D-930-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.17	19.17	18.98	20.01	21.04	17.07	18.08	17.88	18.91	19.94
	3H	19.82	20.73	20.65	21.57	22.63	18.61	19.51	19.43	20.35	21.41
	4H	20.46	21.31	21.30	22.16	23.23	19.19	20.04	20.03	20.89	21.96
	6H	20.87	21.65	21.72	22.51	23.59	19.57	20.35	20.42	21.21	22.29
	8H	21.02	21.77	21.89	22.65	23.73	19.71	20.46	20.57	21.33	22.42
	12H	21.10	21.81	21.97	22.68	23.79	19.78	20.49	20.65	21.36	22.47
4H	2H	18.60	19.45	19.44	20.30	21.37	17.72	18.57	18.57	19.42	20.49
	3H	20.48	21.19	21.34	22.07	23.15	19.47	20.18	20.33	21.06	22.15
	4H	21.23	21.88	22.10	22.76	23.87	20.15	20.79	21.02	21.68	22.79
	6H	21.76	22.32	22.64	23.22	24.33	20.63	21.19	21.52	22.09	23.21
	8H	21.97	22.49	22.85	23.39	24.51	20.82	21.35	21.71	22.25	23.37
	12H	22.08	22.55	22.99	23.47	24.60	20.92	21.39	21.83	22.31	23.44
8H	4H	21.40	21.92	22.29	22.82	23.94	20.43	20.95	21.32	21.85	22.98
	6H	22.04	22.48	22.96	23.42	24.54	21.04	21.48	21.96	22.42	23.54
	8H	22.34	22.72	23.26	23.65	24.80	21.32	21.70	22.25	22.64	23.78
	12H	22.52	22.85	23.45	23.78	24.97	21.48	21.81	22.41	22.74	23.93
12H	4H	21.38	21.85	22.29	22.77	23.90	20.44	20.91	21.35	21.83	22.96
	6H	22.07	22.46	23.00	23.39	24.53	21.11	21.49	22.03	22.42	23.57
	8H	22.40	22.74	23.33	23.66	24.86	21.42	21.76	22.35	22.68	23.88