

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439035

Luminaire Tested: CB2-D-055U-120D-930-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1439035  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-D-055U-120D-930-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 550 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7211.5 lumens  
Efficiency: N/A  
Efficacy: 121.4 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 59.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1439035

CATALOG NUMBER: CB2-D-055U-120D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1439035

CATALOG NUMBER: CB2-D-055U-120D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68																												
1	102	98	94	90	96	92	89	86	82	80	77	73	71	70	65	63	62	58																												
2	93	86	79	74	88	81	76	71	73	68	65	65	61	58	57	55	53	49																												
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42																												
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36																												
5	72	60	52	46	68	57	50	44	52	45	41	46	41	37	41	37	34	32																												
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28																												
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25																												
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22																												
9	54	41	33	28	51	39	32	27	36	30	26	33	27	24	29	25	22	20																												
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	36787	36787	36787
5°	36475	36531	36786
10°	36267	36182	36152
15°	35694	35459	35167
20°	35132	34351	33871
25°	34187	33224	32292
30°	33241	31777	30574
35°	32151	30295	28849
40°	30997	28901	27209
45°	29837	27447	25615
50°	28790	26029	24056
55°	27500	24554	22589
60°	26025	23155	21127
65°	24460	21596	19663
70°	22728	19845	17788
75°	20680	17954	16104
80°	18496	15737	14594
85°	14229	12930	10672

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29837 cd/sqm



TEST NUMBER: P1439035

CATALOG NUMBER: CB2-D-055U-120D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	198.6	2.8
10°-20°	553.7	7.7
20°-30°	796.1	11.0
30°-40°	894.8	12.4
40°-50°	864.3	12.0
50°-60°	730.3	10.1
60°-70°	524.6	7.3
70°-80°	286.7	4.0
80°-90°	76.2	1.1
90°-100°	34.7	0.5
100°-110°	142.8	2.0
110°-120°	259.3	3.6
120°-130°	352.8	4.9
130°-140°	407.3	5.6
140°-150°	410.5	5.7
150°-160°	354.2	4.9
160°-170°	240.1	3.3
170°-180°	84.7	1.2
0°-30°	1548.3	21.5
0°-40°	2443.1	33.9
0°-60°	4037.7	56.0
0°-90°	4925.2	68.3
90°-120°	436.8	6.1
90°-150°	1607.4	22.3
90°-180°	2286.0	31.7
0°-180°	7211.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2112	2112	2112	2112	2112	
5°	2086	2115	2089	2090	2104	198
15°	1980	1997	1966	1947	1950	558
25°	1779	1780	1729	1690	1680	819
35°	1512	1495	1425	1370	1357	945
45°	1211	1186	1114	1056	1040	936
55°	906	872	809	758	744	810
65°	594	571	524	487	477	589
75°	307	288	267	246	239	329
85°	71	66	65	56	53	85
90°	0	0	1	0	1	4
95°	34	30	28	22	22	39
105°	141	139	136	128	127	150
115°	268	268	263	255	254	265
125°	399	403	395	387	387	357
135°	532	538	529	520	523	410
145°	659	667	657	649	654	412
155°	771	779	768	763	769	355
165°	852	861	850	846	853	240
175°	893	903	891	885	887	85
180°	896	896	896	896	896	

TEST NUMBER: P1439035

CATALOG NUMBER: CB2-D-055U-120D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2112.1	2112.1	2112.1	2112.1	2112.1
2.5°	2097.8	2123.1	2104.3	2107.0	2110.8
5°	2086.2	2114.7	2089.4	2089.7	2104.0
7.5°	2071.3	2098.2	2066.5	2060.6	2073.9
10°	2050.6	2077.5	2045.8	2034.7	2044.1
12.5°	2023.4	2049.1	2018.6	2001.0	2009.2
15°	1979.5	1996.8	1966.5	1947.2	1950.3
17.5°	1931.6	1942.3	1898.6	1882.4	1879.2
20°	1895.4	1904.8	1853.3	1830.6	1827.4
22.5°	1848.8	1857.0	1802.9	1774.9	1770.5
25°	1778.9	1780.5	1728.8	1689.8	1680.3
27.5°	1705.8	1700.8	1643.4	1597.2	1584.9
30°	1652.8	1646.5	1580.0	1531.2	1520.2
32.5°	1595.9	1584.5	1517.9	1465.3	1454.2
35°	1512.1	1494.7	1424.8	1369.5	1356.8
37.5°	1422.8	1403.2	1334.5	1274.4	1260.1
40°	1363.3	1341.2	1271.1	1211.0	1196.7
42.5°	1303.8	1279.1	1207.7	1147.5	1132.0
45°	1211.3	1186.0	1114.3	1055.7	1039.9
47.5°	1123.3	1091.1	1021.4	963.2	947.4
50°	1062.5	1027.7	960.6	903.7	887.8
52.5°	1000.4	964.3	899.8	845.4	829.6
55°	905.6	872.4	808.6	758.1	743.9
57.5°	811.8	779.9	721.6	673.4	659.5
60°	747.1	720.3	664.7	619.1	606.5
62.5°	685.0	660.7	607.7	566.1	553.4
65°	593.5	571.4	524.0	486.6	477.1
67.5°	504.6	482.4	444.1	410.5	399.8
70°	446.3	424.2	389.7	358.8	349.3
72.5°	390.7	367.3	339.3	311.0	304.0
75°	307.3	288.3	266.8	245.7	239.3
77.5°	233.5	215.2	199.6	184.6	183.1
80°	184.4	168.5	156.9	147.1	145.5
82.5°	137.8	125.8	118.1	110.9	110.6
85°	71.2	66.4	64.7	56.5	53.4
87.5°	20.7	20.7	18.3	15.5	15.7
90°	0.0	0.0	0.7	0.0	0.7
92.5°	8.4	7.3	6.9	4.5	5.2
95°	33.6	29.5	28.0	21.7	21.7
97.5°	63.4	59.3	57.1	50.6	49.2
100°	84.6	80.5	78.3	71.3	69.9
102.5°	106.4	104.5	100.7	93.1	91.7
105°	141.3	139.2	135.7	127.9	126.6
107.5°	177.1	177.5	172.2	165.8	163.9
110°	202.8	202.1	197.9	191.6	190.2



TEST NUMBER: P1439035

CATALOG NUMBER: CB2-D-055U-120D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	229.1	227.9	223.6	217.3	215.9
115°	268.5	267.8	262.9	255.2	254.5
117.5°	306.0	308.2	302.4	294.3	294.0
120°	332.9	335.6	328.7	321.6	320.3
122.5°	359.2	362.4	355.5	347.4	347.7
125°	399.3	403.4	395.1	386.7	387.4
127.5°	438.0	443.1	435.4	426.9	427.7
130°	464.3	470.5	462.2	453.2	454.5
132.5°	491.2	497.3	489.1	479.5	482.0
135°	532.2	538.3	529.4	519.7	523.1
137.5°	570.8	576.9	567.1	559.0	563.1
140°	596.5	602.6	592.3	584.7	588.8
142.5°	621.7	628.9	618.0	609.9	615.1
145°	659.4	667.0	656.6	649.1	653.8
147.5°	695.2	702.8	692.3	685.0	689.9
150°	718.2	725.7	714.7	708.5	714.0
152.5°	739.4	748.0	736.5	730.4	737.5
155°	771.3	778.8	767.8	763.1	769.2
157.5°	799.0	807.8	796.8	792.7	797.6
160°	817.5	825.7	814.7	810.6	816.1
162.5°	831.5	840.2	829.8	825.2	831.7
165°	852.4	861.3	850.3	845.6	853.1
167.5°	868.9	878.4	867.3	862.4	870.1
170°	879.0	887.9	876.2	870.8	879.0
172.5°	885.7	895.2	882.9	877.5	882.9
175°	893.0	902.6	890.9	885.3	887.4
177.5°	896.5	904.1	894.8	889.9	896.5
180°	896.5	896.5	896.5	896.5	896.5



TEST NUMBER: P1439035  
 CATALOG NUMBER: CB2-D-055U-120D-930-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.07	22.11	21.86	22.91	23.90	19.97	21.01	20.76	21.81	22.80
	3H	22.73	23.66	23.53	24.47	25.49	21.51	22.44	22.31	23.26	24.27
	4H	23.37	24.24	24.18	25.07	26.09	22.09	22.97	22.91	23.79	24.82
	6H	23.78	24.59	24.60	25.42	26.46	22.47	23.28	23.30	24.11	25.15
	8H	23.93	24.70	24.77	25.55	26.59	22.62	23.39	23.46	24.24	25.28
	12H	24.01	24.74	24.85	25.59	26.65	22.69	23.42	23.53	24.27	25.33
4H	2H	21.50	22.38	22.32	23.20	24.23	20.63	21.50	21.45	22.33	23.35
	3H	23.39	24.12	24.22	24.97	26.02	22.38	23.11	23.21	23.97	25.01
	4H	24.14	24.80	24.98	25.66	26.73	23.06	23.72	23.90	24.58	25.65
	6H	24.67	25.24	25.53	26.12	27.20	23.54	24.12	24.40	25.00	26.07
	8H	24.88	25.41	25.74	26.29	27.37	23.74	24.27	24.60	25.15	26.23
	12H	24.99	25.48	25.88	26.37	27.46	23.83	24.32	24.72	25.21	26.30
8H	4H	24.31	24.85	25.17	25.72	26.81	23.34	23.88	24.21	24.76	25.84
	6H	24.96	25.40	25.85	26.32	27.40	23.96	24.40	24.85	25.32	26.40
	8H	25.25	25.64	26.15	26.55	27.66	24.23	24.63	25.13	25.54	26.64
	12H	25.43	25.78	26.34	26.68	27.84	24.39	24.74	25.29	25.64	26.79
12H	4H	24.30	24.78	25.18	25.67	26.77	23.36	23.84	24.24	24.73	25.83
	6H	24.99	25.38	25.89	26.29	27.39	24.02	24.41	24.92	25.32	26.43
	8H	25.31	25.66	26.22	26.56	27.72	24.33	24.68	25.24	25.58	26.74