

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438713

Luminaire Tested: CB2-085U-055D-835-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438713
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-085U-055D-835-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 850 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6152.1 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438713

CATALOG NUMBER: CB2-085U-055D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438713

CATALOG NUMBER: CB2-085U-055D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36																				
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30																				
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26																				
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22																				
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19																				
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17																				
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15																				
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13																				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12																				
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13	11																				
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	13	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16496	16496	16496
5°	16356	16382	16496
10°	16264	16225	16213
15°	16007	15902	15771
20°	15755	15405	15190
25°	15330	14900	14481
30°	14907	14249	13710
35°	14418	13585	12938
40°	13901	12960	12203
45°	13380	12309	11486
50°	12912	11673	10787
55°	12332	11011	10130
60°	11673	10384	9475
65°	10971	9685	8815
70°	10195	8902	7975
75°	9273	8055	7221
80°	8295	7051	6550
85°	6375	5795	4776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13380 cd/sqm



TEST NUMBER: P1438713

CATALOG NUMBER: CB2-085U-055D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.1	1.4
10°-20°	248.3	4.0
20°-30°	357.0	5.8
30°-40°	401.2	6.5
40°-50°	387.6	6.3
50°-60°	327.5	5.3
60°-70°	235.2	3.8
70°-80°	128.6	2.1
80°-90°	34.2	0.6
90°-100°	24.1	0.4
100°-110°	153.4	2.5
110°-120°	487.4	7.9
120°-130°	707.3	11.5
130°-140°	760.7	12.4
140°-150°	716.2	11.6
150°-160°	583.4	9.5
160°-170°	379.7	6.2
170°-180°	131.3	2.1
0°-30°	694.3	11.3
0°-40°	1095.6	17.8
0°-60°	1810.7	29.4
0°-90°	2208.7	35.9
90°-120°	664.9	10.8
90°-150°	2849.0	46.3
90°-180°	3943.0	64.1
0°-180°	6152.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	936	948	937	937	944	89
15°	888	896	882	873	875	250
25°	798	798	775	758	754	367
35°	678	670	639	614	608	424
45°	543	532	500	473	466	420
55°	406	391	363	340	334	363
65°	266	256	235	218	214	264
75°	138	129	120	110	107	147
85°	32	30	29	25	24	38
90°	0	0	0	1	1	3
95°	55	16	17	11	10	70
105°	288	299	30	35	37	303
115°	545	557	562	568	326	536
125°	774	788	788	801	812	692
135°	974	986	984	990	1003	751
145°	1140	1149	1141	1142	1157	713
155°	1266	1274	1260	1257	1275	584
165°	1350	1354	1340	1334	1348	381
175°	1390	1393	1375	1366	1373	132
180°	1383	1383	1383	1383	1383	

TEST NUMBER: P1438713

CATALOG NUMBER: CB2-085U-055D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	947.1	947.1	947.1	947.1	947.1
2.5°	940.8	952.1	943.7	944.9	946.6
5°	935.5	948.3	937.0	937.1	943.5
7.5°	928.9	940.9	926.7	924.1	930.0
10°	919.6	931.6	917.4	912.4	916.7
12.5°	907.4	918.9	905.2	897.3	901.0
15°	887.7	895.5	881.9	873.2	874.6
17.5°	866.2	871.0	851.4	844.1	842.7
20°	850.0	854.2	831.1	820.9	819.5
22.5°	829.1	832.8	808.5	796.0	794.0
25°	797.7	798.5	775.3	757.8	753.5
27.5°	765.0	762.7	737.0	716.2	710.7
30°	741.2	738.3	708.5	686.7	681.7
32.5°	715.6	710.5	680.7	657.1	652.1
35°	678.1	670.3	638.9	614.1	608.5
37.5°	638.1	629.3	598.5	571.5	565.1
40°	611.4	601.4	570.0	543.0	536.7
42.5°	584.7	573.6	541.6	514.6	507.7
45°	543.2	531.8	499.7	473.4	466.3
47.5°	503.7	489.3	458.1	431.9	424.8
50°	476.5	460.9	430.8	405.2	398.1
52.5°	448.6	432.5	403.5	379.1	372.0
55°	406.1	391.2	362.6	340.0	333.6
57.5°	364.1	349.7	323.6	302.0	295.7
60°	335.1	323.0	298.1	277.6	272.0
62.5°	307.2	296.3	272.5	253.8	248.2
65°	266.2	256.2	235.0	218.2	213.9
67.5°	226.3	216.3	199.1	184.1	179.3
70°	200.2	190.2	174.8	160.9	156.6
72.5°	175.2	164.7	152.2	139.5	136.3
75°	137.8	129.3	119.7	110.2	107.3
77.5°	104.7	96.5	89.5	82.8	82.1
80°	82.7	75.6	70.3	66.0	65.3
82.5°	61.8	56.4	52.9	49.7	49.6
85°	31.9	29.8	29.0	25.4	23.9
87.5°	9.3	9.3	8.1	7.2	7.2
90°	0.0	0.0	0.0	1.0	1.0
92.5°	15.2	5.8	4.0	5.8	5.8
95°	55.0	15.9	17.0	11.0	10.0
97.5°	114.2	25.6	24.6	27.0	28.0
100°	159.0	52.4	27.0	31.0	32.0
102.5°	208.6	197.5	27.8	33.4	35.2
105°	288.0	298.8	30.0	35.0	37.0
107.5°	366.0	376.8	139.6	36.2	38.2
110°	418.0	428.8	442.0	37.0	39.0



TEST NUMBER: P1438713

CATALOG NUMBER: CB2-085U-055D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	479.9	490.0	82.4	40.6
115°	545.0	556.7	562.0	568.5	326.0
117.5°	614.0	628.5	634.4	645.6	656.6
120°	662.0	675.7	680.0	691.3	703.0
122.5°	709.2	721.3	724.0	736.8	747.8
125°	774.0	787.7	788.0	801.2	812.0
127.5°	838.8	850.5	850.0	859.9	871.8
130°	882.0	889.8	890.0	898.3	911.0
132.5°	918.0	929.0	929.2	935.9	948.6
135°	974.0	985.7	984.0	990.3	1003.0
137.5°	1026.6	1037.9	1034.8	1040.1	1053.2
140°	1061.0	1070.8	1066.0	1071.3	1086.0
142.5°	1093.0	1102.8	1095.6	1100.2	1115.6
145°	1140.0	1148.8	1141.0	1142.3	1157.0
147.5°	1181.8	1190.4	1181.0	1182.3	1196.0
150°	1209.0	1216.8	1205.0	1206.3	1220.0
152.5°	1233.0	1240.0	1227.4	1227.2	1243.2
155°	1266.0	1273.8	1260.0	1257.4	1275.0
157.5°	1296.0	1303.2	1289.4	1287.5	1301.2
160°	1316.0	1320.9	1307.0	1304.3	1318.0
162.5°	1329.6	1335.3	1321.4	1317.1	1330.8
165°	1350.0	1353.9	1340.0	1334.3	1348.0
167.5°	1367.6	1372.1	1354.2	1349.1	1363.8
170°	1378.0	1380.9	1363.0	1356.3	1371.0
172.5°	1384.4	1386.6	1368.6	1361.0	1371.0
175°	1390.0	1392.9	1375.0	1366.2	1373.0
177.5°	1391.0	1392.6	1379.0	1371.3	1383.0
180°	1383.0	1383.0	1383.0	1383.0	1383.0



TEST NUMBER: P1438713

CATALOG NUMBER: CB2-085U-055D-835-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.27	16.01	16.34	17.08	18.54	14.17	14.91	15.24	15.98	17.44
	3H	16.91	17.57	17.99	18.65	20.13	15.69	16.35	16.77	17.43	18.91
	4H	17.53	18.16	18.62	19.24	20.72	16.26	16.89	17.35	17.97	19.45
	6H	17.93	18.50	19.03	19.59	21.09	16.62	17.20	17.72	18.29	19.78
	8H	18.07	18.62	19.18	19.72	21.21	16.76	17.31	17.86	18.41	19.90
	12H	18.14	18.66	19.25	19.76	21.27	16.82	17.34	17.93	18.44	19.95
4H	2H	15.67	16.29	16.76	17.38	18.86	14.79	15.42	15.89	16.50	17.99
	3H	17.52	18.05	18.63	19.16	20.65	16.52	17.04	17.62	18.15	19.64
	4H	18.26	18.75	19.37	19.84	21.36	17.18	17.66	18.29	18.76	20.28
	6H	18.78	19.19	19.89	20.31	21.82	17.65	18.06	18.77	19.19	20.70
	8H	18.98	19.36	20.10	20.48	22.00	17.84	18.22	18.96	19.34	20.86
	12H	19.08	19.43	20.21	20.55	22.09	17.92	18.27	19.06	19.40	20.93
8H	4H	18.41	18.80	19.53	19.91	21.44	17.45	17.83	18.57	18.95	20.47
	6H	19.05	19.37	20.19	20.52	22.04	18.05	18.37	19.19	19.52	21.04
	8H	19.34	19.62	20.48	20.75	22.30	18.32	18.60	19.47	19.73	21.28
	12H	19.51	19.75	20.66	20.88	22.46	18.47	18.71	19.61	19.84	21.42
12H	4H	18.39	18.73	19.52	19.86	21.39	17.45	17.79	18.58	18.92	20.45
	6H	19.08	19.35	20.22	20.49	22.03	18.11	18.39	19.25	19.52	21.07
	8H	19.39	19.63	20.54	20.76	22.34	18.41	18.65	19.56	19.79	21.37