

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438658

Luminaire Tested: CB2-055U-055D-835-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438658
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-055U-055D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9644.1 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 74.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438658

CATALOG NUMBER: CB2-055U-055D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438658

CATALOG NUMBER: CB2-055U-055D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33				
3	81	72	64	59	74	66	60	55	55	51	47	46	42	39	37	34	32	28				
4	74	63	56	50	68	58	52	46	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	29	30	27	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	14				
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16497	16497	16497
5°	16357	16382	16496
10°	16264	16225	16213
15°	16006	15901	15771
20°	15754	15405	15190
25°	15331	14899	14481
30°	14907	14250	13710
35°	14418	13585	12937
40°	13900	12960	12202
45°	13380	12309	11486
50°	12910	11673	10788
55°	12332	11011	10130
60°	11671	10382	9473
65°	10969	9683	8818
70°	10193	8902	7977
75°	9273	8052	7224
80°	8295	7056	6545
85°	6375	5795	4786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13380 cd/sqm



TEST NUMBER: P1438658

CATALOG NUMBER: CB2-055U-055D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.1	1.8
10°-20°	496.6	5.1
20°-30°	714.0	7.4
30°-40°	802.5	8.3
40°-50°	775.2	8.0
50°-60°	655.0	6.8
60°-70°	470.5	4.9
70°-80°	257.1	2.7
80°-90°	68.4	0.7
90°-100°	31.9	0.3
100°-110°	203.3	2.1
110°-120°	646.0	6.7
120°-130°	937.4	9.7
130°-140°	1008.2	10.5
140°-150°	949.3	9.8
150°-160°	773.3	8.0
160°-170°	503.3	5.2
170°-180°	174.0	1.8
0°-30°	1388.7	14.4
0°-40°	2191.2	22.7
0°-60°	3621.4	37.5
0°-90°	4417.4	45.8
90°-120°	881.3	9.1
90°-150°	3776.2	39.2
90°-180°	5227.0	54.2
0°-180°	9644.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1894	1894	1894	1894	1894	
5°	1871	1897	1874	1874	1887	178
15°	1775	1791	1764	1746	1749	500
25°	1596	1597	1550	1516	1507	734
35°	1356	1341	1278	1228	1217	847
45°	1086	1064	999	947	933	839
55°	812	782	725	680	667	726
65°	532	512	470	436	428	528
75°	276	259	239	220	215	295
85°	64	60	58	51	48	76
90°	0	0	0	1	1	5
95°	73	21	22	15	13	92
105°	382	396	40	46	49	402
115°	722	738	745	754	432	710
125°	1026	1044	1044	1062	1076	917
135°	1291	1306	1304	1313	1329	996
145°	1511	1523	1512	1514	1534	944
155°	1678	1688	1670	1667	1690	774
165°	1789	1794	1776	1768	1787	505
175°	1842	1846	1822	1811	1820	175
180°	1833	1833	1833	1833	1833	



TEST NUMBER: P1438658

CATALOG NUMBER: CB2-055U-055D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1894.3	1894.3	1894.3	1894.3	1894.3
2.5°	1881.5	1904.2	1887.3	1889.7	1893.1
5°	1871.1	1896.6	1874.0	1874.3	1887.0
7.5°	1857.7	1881.8	1853.4	1848.1	1860.0
10°	1839.2	1863.3	1834.8	1824.9	1833.4
12.5°	1814.8	1837.8	1810.4	1794.7	1802.0
15°	1775.3	1790.9	1763.7	1746.4	1749.2
17.5°	1732.4	1742.1	1702.8	1688.3	1685.4
20°	1699.9	1708.4	1662.2	1641.8	1639.0
22.5°	1658.1	1665.5	1617.0	1591.9	1587.9
25°	1595.5	1596.9	1550.5	1515.5	1507.0
27.5°	1529.9	1525.4	1473.9	1432.5	1421.4
30°	1482.4	1476.7	1417.1	1373.3	1363.4
32.5°	1431.3	1421.1	1361.4	1314.2	1304.2
35°	1356.2	1340.6	1277.8	1228.3	1216.9
37.5°	1276.1	1258.5	1196.9	1142.9	1130.2
40°	1222.7	1202.9	1140.0	1086.1	1073.3
42.5°	1169.3	1147.2	1083.2	1029.2	1015.3
45°	1086.4	1063.7	999.4	946.8	932.6
47.5°	1007.5	978.5	916.1	863.9	849.7
50°	952.9	921.7	861.6	810.5	796.3
52.5°	897.2	864.9	807.0	758.3	744.1
55°	812.2	782.5	725.2	680.0	667.2
57.5°	728.1	699.5	647.2	604.0	591.5
60°	670.1	646.0	596.1	555.3	543.9
62.5°	614.4	592.6	545.1	507.7	496.3
65°	532.3	512.5	469.9	436.4	427.9
67.5°	452.5	432.7	398.3	368.2	358.5
70°	400.3	380.5	349.6	321.8	313.3
72.5°	350.4	329.4	304.3	278.9	272.7
75°	275.6	258.6	239.3	220.3	214.7
77.5°	209.4	193.0	179.0	165.6	164.2
80°	165.4	151.2	140.7	132.0	130.5
82.5°	123.6	112.8	105.9	99.5	99.2
85°	63.8	59.6	58.0	50.7	47.9
87.5°	18.6	18.6	16.2	14.2	14.2
90°	0.0	0.0	0.0	1.3	1.3
92.5°	20.1	7.7	5.3	7.7	7.7
95°	72.9	21.1	22.5	14.6	13.3
97.5°	151.4	33.9	32.6	35.8	37.1
100°	210.7	69.5	35.8	41.1	42.4
102.5°	276.5	261.7	36.8	44.3	46.7
105°	381.7	396.0	39.8	46.4	49.0
107.5°	485.1	499.4	185.0	48.0	50.6
110°	554.0	568.3	585.8	49.1	51.7



TEST NUMBER: P1438658

CATALOG NUMBER: CB2-055U-055D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	618.7	636.1	649.5	109.3	53.8
115°	722.4	737.9	744.9	753.5	432.1
117.5°	813.8	833.0	840.9	855.8	870.3
120°	877.4	895.6	901.3	916.2	931.8
122.5°	940.0	956.1	959.6	976.6	991.2
125°	1025.9	1044.0	1044.4	1062.0	1076.3
127.5°	1111.8	1127.3	1126.6	1139.7	1155.5
130°	1169.0	1179.4	1179.6	1190.6	1207.5
132.5°	1216.8	1231.3	1231.6	1240.5	1257.3
135°	1291.0	1306.5	1304.2	1312.6	1329.4
137.5°	1360.7	1375.7	1371.6	1378.6	1396.0
140°	1406.3	1419.3	1412.9	1420.0	1439.4
142.5°	1448.7	1461.7	1452.2	1458.2	1478.7
145°	1511.0	1522.7	1512.3	1514.1	1533.5
147.5°	1566.4	1577.8	1565.3	1567.1	1585.2
150°	1602.5	1612.8	1597.2	1598.9	1617.0
152.5°	1634.3	1643.6	1626.8	1626.5	1647.8
155°	1678.0	1688.4	1670.1	1666.6	1689.9
157.5°	1717.8	1727.4	1709.0	1706.5	1724.7
160°	1744.3	1750.8	1732.4	1728.8	1746.9
162.5°	1762.3	1769.8	1751.4	1745.8	1763.9
165°	1789.3	1794.5	1776.1	1768.5	1786.7
167.5°	1812.7	1818.6	1794.9	1788.2	1807.6
170°	1826.5	1830.3	1806.6	1797.7	1817.2
172.5°	1834.9	1837.8	1814.0	1804.0	1817.2
175°	1842.4	1846.3	1822.5	1810.8	1819.8
177.5°	1843.7	1845.8	1827.8	1817.5	1833.1
180°	1833.1	1833.1	1833.1	1833.1	1833.1

TEST NUMBER: P1438658

CATALOG NUMBER: CB2-055U-055D-835-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.34	17.15	17.33	18.16	19.49	15.24	16.05	16.23	17.06	18.39
	3H	17.98	18.71	18.98	19.72	21.07	16.76	17.49	17.77	18.51	19.86
	4H	18.61	19.30	19.62	20.31	21.67	17.33	18.02	18.35	19.04	20.40
	6H	19.01	19.64	20.03	20.66	22.04	17.70	18.34	18.73	19.36	20.73
	8H	19.15	19.76	20.19	20.80	22.16	17.84	18.45	18.88	19.48	20.85
	12H	19.23	19.80	20.26	20.83	22.22	17.90	18.48	18.94	19.51	20.90
4H	2H	16.74	17.43	17.77	18.45	19.81	15.87	16.56	16.89	17.57	18.93
	3H	18.61	19.18	19.64	20.23	21.60	17.60	18.17	18.63	19.22	20.59
	4H	19.35	19.88	20.39	20.91	22.31	18.27	18.80	19.31	19.83	21.23
	6H	19.87	20.32	20.92	21.38	22.77	18.74	19.19	19.79	20.26	21.65
	8H	20.07	20.49	21.12	21.55	22.95	18.93	19.35	19.98	20.41	21.81
	12H	20.18	20.56	21.24	21.63	23.04	19.02	19.40	20.09	20.47	21.88
8H	4H	19.50	19.93	20.55	20.98	22.39	18.54	18.96	19.59	20.02	21.42
	6H	20.14	20.49	21.22	21.59	22.99	19.14	19.49	20.22	20.59	21.99
	8H	20.43	20.74	21.52	21.82	23.24	19.42	19.72	20.50	20.80	22.23
	12H	20.61	20.88	21.69	21.95	23.41	19.56	19.83	20.65	20.91	22.37
12H	4H	19.48	19.86	20.55	20.93	22.34	18.54	18.92	19.61	19.99	21.40
	6H	20.17	20.48	21.25	21.56	22.98	19.20	19.51	20.29	20.59	22.01
	8H	20.49	20.76	21.57	21.83	23.29	19.51	19.78	20.59	20.85	22.32