

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438837

Luminaire Tested: CB2-125U-120D-835-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438837  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-125U-120D-835-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10720.1 lumens  
Efficiency: N/A  
Efficacy: 130.3 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 82.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438837

CATALOG NUMBER: CB2-125U-120D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1438837

CATALOG NUMBER: CB2-125U-120D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32				
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27				
4	74	63	55	50	67	58	51	46	49	44	40	40	37	34	32	30	27	24				
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	27	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	35845	35845	35845
5°	35541	35597	35844
10°	35338	35255	35227
15°	34780	34552	34268
20°	34233	33473	33006
25°	33312	32373	31465
30°	32390	30964	29792
35°	31328	29519	28111
40°	30203	28162	26513
45°	29073	26743	24959
50°	28053	25362	23441
55°	26798	23926	22012
60°	25360	22562	20584
65°	23833	21043	19160
70°	22147	19341	17335
75°	20148	17497	15693
80°	18014	15336	14223
85°	13849	12590	10392

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29073 cd/sqm



TEST NUMBER: P1438837

CATALOG NUMBER: CB2-125U-120D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.5	1.8
10°-20°	539.5	5.0
20°-30°	775.7	7.2
30°-40°	871.9	8.1
40°-50°	842.2	7.9
50°-60°	711.6	6.6
60°-70°	511.1	4.8
70°-80°	279.4	2.6
80°-90°	74.3	0.7
90°-100°	36.2	0.3
100°-110°	230.3	2.1
110°-120°	731.8	6.8
120°-130°	1062.0	9.9
130°-140°	1142.1	10.7
140°-150°	1075.3	10.0
150°-160°	876.0	8.2
160°-170°	570.2	5.3
170°-180°	197.1	1.8
0°-30°	1508.7	14.1
0°-40°	2380.6	22.2
0°-60°	3934.4	36.7
0°-90°	4799.2	44.8
90°-120°	998.3	9.3
90°-150°	4277.7	39.9
90°-180°	5921.0	55.2
0°-180°	10720.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2058	2058	2058	2058	2058	
5°	2033	2060	2036	2036	2050	193
15°	1929	1946	1916	1897	1900	544
25°	1733	1735	1684	1646	1637	798
35°	1473	1456	1388	1334	1322	920
45°	1180	1156	1086	1029	1013	912
55°	882	850	788	739	725	789
65°	578	557	511	474	465	573
75°	299	281	260	239	233	320
85°	69	65	63	55	52	83
90°	0	0	0	2	2	6
95°	83	24	26	16	15	105
105°	432	449	45	53	56	455
115°	818	836	844	854	490	804
125°	1162	1183	1183	1203	1219	1039
135°	1462	1480	1477	1487	1506	1128
145°	1712	1725	1713	1715	1737	1070
155°	1901	1913	1892	1888	1914	876
165°	2027	2033	2012	2003	2024	573
175°	2087	2092	2064	2051	2062	199
180°	2076	2076	2076	2076	2076	

TEST NUMBER: P1438837

CATALOG NUMBER: CB2-125U-120D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2058.0	2058.0	2058.0	2058.0	2058.0
2.5°	2044.1	2068.8	2050.5	2053.1	2056.8
5°	2032.8	2060.5	2036.0	2036.3	2050.1
7.5°	2018.3	2044.5	2013.6	2007.9	2020.8
10°	1998.1	2024.3	1993.4	1982.6	1991.8
12.5°	1971.7	1996.6	1966.9	1949.8	1957.8
15°	1928.8	1945.7	1916.2	1897.4	1900.4
17.5°	1882.2	1892.6	1850.0	1834.2	1831.1
20°	1846.9	1856.1	1805.9	1783.8	1780.7
22.5°	1801.5	1809.5	1756.7	1729.5	1725.2
25°	1733.4	1734.9	1684.5	1646.5	1637.3
27.5°	1662.2	1657.2	1601.3	1556.3	1544.3
30°	1610.5	1604.3	1539.6	1492.1	1481.3
32.5°	1555.0	1543.9	1479.1	1427.8	1417.0
35°	1473.4	1456.4	1388.3	1334.4	1322.1
37.5°	1386.4	1367.3	1300.4	1241.7	1227.9
40°	1328.4	1306.8	1238.6	1180.0	1166.1
42.5°	1270.4	1246.4	1176.8	1118.2	1103.1
45°	1180.3	1155.6	1085.7	1028.7	1013.3
47.5°	1094.6	1063.1	995.3	938.5	923.1
50°	1035.3	1001.4	936.0	880.5	865.1
52.5°	974.8	939.7	876.8	823.8	808.4
55°	882.5	850.1	787.9	738.7	724.9
57.5°	791.1	759.9	703.1	656.2	642.6
60°	728.0	701.8	647.7	603.3	590.9
62.5°	667.5	643.8	592.2	551.6	539.2
65°	578.3	556.8	510.6	474.1	464.9
67.5°	491.7	470.1	432.7	400.0	389.5
70°	434.9	413.4	379.8	349.6	340.4
72.5°	380.7	357.9	330.6	303.0	296.3
75°	299.4	280.9	260.0	239.4	233.2
77.5°	227.5	209.7	194.5	179.9	178.4
80°	179.6	164.2	152.9	143.4	141.8
82.5°	134.3	122.5	115.0	108.1	107.8
85°	69.3	64.7	63.0	55.1	52.0
87.5°	20.2	20.2	17.6	15.4	15.4
90°	0.0	0.0	0.0	1.5	1.5
92.5°	22.8	8.7	6.0	8.7	8.7
95°	82.6	23.9	25.5	16.5	15.0
97.5°	171.5	38.5	36.9	40.6	42.0
100°	238.7	78.7	40.5	46.6	48.0
102.5°	313.2	296.5	41.7	50.2	52.9
105°	432.4	448.6	45.0	52.6	55.6
107.5°	549.5	565.7	209.6	54.4	57.4
110°	627.6	643.8	663.7	55.6	58.6

TEST NUMBER: P1438837

CATALOG NUMBER: CB2-125U-120D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	700.9	720.6	735.7	123.8	61.0
115°	818.3	835.9	843.8	853.6	489.5
117.5°	921.9	943.6	952.5	969.4	985.9
120°	994.0	1014.5	1021.0	1037.9	1055.5
122.5°	1064.8	1083.0	1087.1	1106.4	1122.8
125°	1162.1	1182.7	1183.2	1203.0	1219.2
127.5°	1259.4	1277.1	1276.3	1291.1	1309.0
130°	1324.3	1336.0	1336.3	1348.8	1367.8
132.5°	1378.4	1394.8	1395.2	1405.2	1424.3
135°	1462.4	1480.1	1477.4	1486.9	1506.0
137.5°	1541.4	1558.4	1553.7	1561.7	1581.4
140°	1593.1	1607.7	1600.6	1608.6	1630.6
142.5°	1641.1	1655.8	1645.0	1651.8	1675.0
145°	1711.7	1724.9	1713.2	1715.2	1737.2
147.5°	1774.4	1787.4	1773.2	1775.2	1795.8
150°	1815.3	1827.0	1809.3	1811.2	1831.8
152.5°	1851.3	1861.9	1842.9	1842.6	1866.6
155°	1900.9	1912.6	1891.9	1888.0	1914.4
157.5°	1945.9	1956.8	1936.0	1933.2	1953.7
160°	1975.9	1983.3	1962.4	1958.4	1978.9
162.5°	1996.4	2004.9	1984.0	1977.6	1998.2
165°	2027.0	2032.9	2012.0	2003.4	2024.0
167.5°	2053.4	2060.2	2033.3	2025.7	2047.7
170°	2069.0	2073.4	2046.5	2036.5	2058.5
172.5°	2078.6	2081.9	2054.9	2043.5	2058.5
175°	2087.0	2091.5	2064.5	2051.2	2061.5
177.5°	2088.5	2090.9	2070.5	2058.9	2076.5
180°	2076.5	2076.5	2076.5	2076.5	2076.5



TEST NUMBER: P1438837

CATALOG NUMBER: CB2-125U-120D-835-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.93	19.74	19.93	20.75	22.09	17.83	18.64	18.83	19.65	20.99
	3H	20.57	21.29	21.59	22.31	23.68	19.35	20.08	20.37	21.10	22.46
	4H	21.20	21.88	22.22	22.91	24.28	19.93	20.61	20.95	21.63	23.01
	6H	21.60	22.23	22.63	23.26	24.64	20.29	20.92	21.33	21.95	23.34
	8H	21.74	22.34	22.79	23.39	24.77	20.43	21.03	21.47	22.08	23.46
	12H	21.82	22.39	22.86	23.42	24.83	20.49	21.06	21.54	22.10	23.51
4H	2H	19.33	20.02	20.37	21.04	22.41	18.46	19.14	19.49	20.17	21.54
	3H	21.20	21.77	22.24	22.82	24.21	20.19	20.76	21.23	21.81	23.20
	4H	21.94	22.46	22.99	23.51	24.92	20.86	21.38	21.91	22.43	23.84
	6H	22.46	22.91	23.52	23.97	25.38	21.33	21.78	22.39	22.85	24.25
	8H	22.66	23.08	23.72	24.14	25.56	21.52	21.94	22.58	23.00	24.42
	12H	22.77	23.14	23.84	24.22	25.64	21.61	21.98	22.68	23.06	24.48
8H	4H	22.09	22.51	23.15	23.57	24.99	21.13	21.55	22.19	22.61	24.03
	6H	22.73	23.08	23.81	24.18	25.60	21.73	22.08	22.81	23.18	24.60
	8H	23.02	23.33	24.11	24.41	25.85	22.01	22.31	23.09	23.40	24.83
	12H	23.19	23.46	24.29	24.54	26.02	22.15	22.42	23.25	23.50	24.98
12H	4H	22.07	22.45	23.15	23.52	24.95	21.13	21.51	22.21	22.58	24.01
	6H	22.76	23.07	23.85	24.15	25.59	21.79	22.10	22.88	23.18	24.62
	8H	23.08	23.34	24.17	24.42	25.90	22.10	22.36	23.19	23.45	24.92