

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438796

Luminaire Tested: CB2-125U-030D-835-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438796
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-125U-030D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14154.4 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 114.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438796

CATALOG NUMBER: CB2-125U-030D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438796

CATALOG NUMBER: CB2-125U-030D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	99	99	99	99	87	87	87	87	65	65	65	44	44	44	25	25	25	16																				
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	22	22	21	14																				
2	82	75	70	65	72	66	62	58	50	46	44	34	32	31	20	19	18	12																				
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	17	16	15	10																				
4	68	58	51	45	60	52	45	41	39	35	31	27	24	22	16	14	13	9																				
5	63	52	44	39	55	46	39	35	34	30	27	24	21	19	14	13	12	8																				
6	58	46	39	33	50	41	35	30	31	26	23	22	19	17	13	11	10	7																				
7	53	42	34	29	47	37	30	26	28	23	20	19	17	15	12	10	9	6																				
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5																				
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5																				
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8636	8636	8636
5°	8562	8576	8635
10°	8513	8494	8487
15°	8378	8323	8256
20°	8246	8064	7952
25°	8025	7799	7581
30°	7803	7459	7177
35°	7547	7111	6772
40°	7276	6785	6387
45°	7004	6442	6013
50°	6758	6110	5647
55°	6456	5764	5303
60°	6110	5436	4959
65°	5741	5069	4616
70°	5337	4660	4176
75°	4855	4216	3782
80°	4343	3691	3425
85°	3337	3038	2508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7004 cd/sqm



TEST NUMBER: P1438796

CATALOG NUMBER: CB2-125U-030D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.2	0.7
10°-20°	259.9	1.8
20°-30°	373.7	2.6
30°-40°	420.1	3.0
40°-50°	405.8	2.9
50°-60°	342.9	2.4
60°-70°	246.3	1.7
70°-80°	134.6	1.0
80°-90°	36.0	0.3
90°-100°	72.4	0.5
100°-110°	460.6	3.3
110°-120°	1463.6	10.3
120°-130°	2123.9	15.0
130°-140°	2284.2	16.1
140°-150°	2150.6	15.2
150°-160°	1752.0	12.4
160°-170°	1140.4	8.1
170°-180°	394.2	2.8
0°-30°	726.9	5.1
0°-40°	1147.0	8.1
0°-60°	1895.6	13.4
0°-90°	2312.5	16.3
90°-120°	1996.6	14.1
90°-150°	8555.3	60.4
90°-180°	11842.0	83.7
0°-180°	14154.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	992	992	992	992	992	
5°	979	993	981	981	988	93
15°	929	938	923	914	916	262
25°	835	836	812	793	789	384
35°	710	702	669	643	637	443
45°	569	557	523	496	488	439
55°	425	410	380	356	349	380
65°	279	268	246	228	224	276
75°	144	135	125	115	112	154
85°	33	31	30	26	25	40
90°	0	0	0	3	3	8
95°	165	48	51	33	30	209
105°	865	897	90	105	111	911
115°	1637	1672	1688	1707	979	1609
125°	2324	2365	2366	2406	2438	2078
135°	2925	2960	2955	2974	3012	2256
145°	3423	3450	3426	3430	3474	2140
155°	3802	3825	3784	3776	3829	1753
165°	4054	4066	4024	4007	4048	1145
175°	4174	4183	4129	4102	4123	397
180°	4153	4153	4153	4153	4153	



TEST NUMBER: P1438796

CATALOG NUMBER: CB2-125U-030D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	991.6	991.6	991.6	991.6	991.6
2.5°	984.9	996.8	987.9	989.2	991.0
5°	979.4	992.8	981.0	981.1	987.8
7.5°	972.4	985.1	970.2	967.4	973.7
10°	962.7	975.3	960.5	955.2	959.7
12.5°	950.0	962.0	947.7	939.4	943.3
15°	929.3	937.5	923.2	914.2	915.7
17.5°	906.8	911.9	891.4	883.7	882.2
20°	889.8	894.3	870.1	859.4	858.0
22.5°	868.0	871.8	846.4	833.3	831.2
25°	835.2	835.9	811.6	793.3	788.9
27.5°	800.9	798.5	771.5	749.9	744.1
30°	776.0	773.0	741.8	718.9	713.7
32.5°	749.2	743.9	712.6	687.9	682.7
35°	709.9	701.7	668.9	642.9	637.0
37.5°	668.0	658.8	626.5	598.3	591.6
40°	640.0	629.7	596.8	568.5	561.8
42.5°	612.1	600.5	567.0	538.8	531.5
45°	568.7	556.8	523.1	495.6	488.2
47.5°	527.4	512.2	479.5	452.2	444.8
50°	498.8	482.5	451.0	424.3	416.8
52.5°	469.7	452.7	422.4	396.9	389.5
55°	425.2	409.6	379.6	355.9	349.3
57.5°	381.1	366.1	338.8	316.2	309.6
60°	350.8	338.2	312.1	290.7	284.7
62.5°	321.6	310.2	285.3	265.8	259.8
65°	278.6	268.3	246.0	228.4	224.0
67.5°	236.9	226.5	208.5	192.7	187.7
70°	209.6	199.2	183.0	168.5	164.0
72.5°	183.4	172.4	159.3	146.0	142.7
75°	144.3	135.3	125.3	115.3	112.4
77.5°	109.6	101.0	93.7	86.7	85.9
80°	86.6	79.1	73.6	69.1	68.3
82.5°	64.7	59.0	55.4	52.1	51.9
85°	33.4	31.2	30.4	26.5	25.1
87.5°	9.7	9.7	8.5	7.9	7.9
90°	0.0	0.0	0.0	3.0	3.0
92.5°	45.6	17.5	12.0	17.4	17.4
95°	165.2	47.7	51.1	33.0	30.0
97.5°	342.9	76.9	73.9	81.1	84.1
100°	477.5	157.4	81.1	93.2	96.1
102.5°	626.4	592.9	83.5	100.4	105.7
105°	864.8	897.1	90.1	105.2	111.1
107.5°	1099.1	1131.4	419.2	108.8	114.7
110°	1255.2	1287.5	1327.3	111.2	117.1

TEST NUMBER: P1438796

CATALOG NUMBER: CB2-125U-030D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1401.8	1441.1	1471.4	247.6	121.9
115°	1636.6	1671.8	1687.7	1707.1	979.0
117.5°	1843.8	1887.3	1905.1	1938.8	1971.7
120°	1987.9	2029.1	2042.0	2075.8	2111.1
122.5°	2129.7	2166.1	2174.1	2212.7	2245.6
125°	2324.3	2365.4	2366.3	2406.1	2438.4
127.5°	2518.9	2554.1	2552.5	2582.1	2618.0
130°	2648.6	2672.1	2672.6	2697.5	2735.7
132.5°	2756.7	2789.6	2790.3	2810.4	2848.6
135°	2924.9	2960.1	2954.9	2973.8	3012.0
137.5°	3082.8	3116.9	3107.4	3123.4	3162.7
140°	3186.1	3215.5	3201.1	3217.2	3261.2
142.5°	3282.2	3311.6	3290.0	3303.7	3350.1
145°	3423.4	3449.8	3426.4	3430.4	3474.4
147.5°	3548.9	3574.7	3546.5	3550.4	3591.5
150°	3630.6	3654.0	3618.5	3622.5	3663.6
152.5°	3702.6	3723.8	3685.8	3685.1	3733.3
155°	3801.7	3825.2	3783.7	3775.9	3828.8
157.5°	3891.8	3913.5	3872.0	3866.3	3907.4
160°	3951.9	3966.6	3924.8	3916.8	3957.9
162.5°	3992.7	4009.7	3968.1	3955.2	3996.3
165°	4054.0	4065.7	4023.9	4006.9	4048.0
167.5°	4106.8	4120.3	4066.6	4051.4	4095.4
170°	4138.1	4146.9	4093.0	4073.0	4117.0
172.5°	4157.3	4163.7	4109.8	4087.1	4117.0
175°	4174.1	4182.9	4129.0	4102.5	4123.0
177.5°	4177.1	4181.8	4141.1	4117.8	4153.1
180°	4153.1	4153.1	4153.1	4153.1	4153.1



TEST NUMBER: P1438796

CATALOG NUMBER: CB2-125U-030D-835-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.89	10.51	11.09	11.69	13.37	8.79	9.41	9.99	10.59	12.27
	3H	11.52	12.07	12.72	13.26	14.95	10.30	10.85	11.51	12.04	13.74
	4H	12.13	12.66	13.35	13.85	15.55	10.86	11.39	12.08	12.57	14.27
	6H	12.52	13.01	13.74	14.19	15.91	11.22	11.70	12.44	12.89	14.60
	8H	12.66	13.12	13.89	14.33	16.03	11.35	11.81	12.58	13.02	14.72
	12H	12.73	13.17	13.96	14.36	16.09	11.41	11.84	12.63	13.04	14.76
4H	2H	10.27	10.80	11.49	11.98	13.68	9.39	9.92	10.62	11.11	12.81
	3H	12.12	12.55	13.34	13.77	15.48	11.11	11.55	12.33	12.76	14.47
	4H	12.85	13.26	14.08	14.45	16.18	11.77	12.18	13.00	13.37	15.10
	6H	13.36	13.70	14.59	14.92	16.64	12.23	12.58	13.46	13.80	15.51
	8H	13.56	13.88	14.78	15.09	16.82	12.42	12.74	13.64	13.95	15.68
	12H	13.65	13.94	14.89	15.17	16.90	12.49	12.79	13.73	14.01	15.75
8H	4H	12.99	13.31	14.22	14.52	16.26	12.02	12.35	13.25	13.56	15.29
	6H	13.62	13.89	14.87	15.14	16.87	12.62	12.89	13.86	14.14	15.87
	8H	13.91	14.14	15.16	15.37	17.12	12.89	13.12	14.14	14.35	16.10
	12H	14.07	14.27	15.32	15.50	17.28	13.03	13.23	14.28	14.46	16.24
12H	4H	12.96	13.25	14.20	14.47	16.21	12.02	12.31	13.26	13.53	15.27
	6H	13.65	13.88	14.90	15.11	16.86	12.68	12.91	13.93	14.14	15.89
	8H	13.95	14.15	15.21	15.38	17.16	12.97	13.18	14.23	14.40	16.18