

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438809

Luminaire Tested: CB2-125U-055D-835-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438809
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-125U-055D-835-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8129.7 lumens
Efficiency: N/A
Efficacy: 141.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438809

CATALOG NUMBER: CB2-125U-055D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438809

CATALOG NUMBER: CB2-125U-055D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27																												
1	93	89	85	82	83	79	76	73	62	60	58	46	45	43	31	30	30	23																												
2	85	77	72	67	75	69	65	60	54	51	48	40	38	36	28	26	25	19																												
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	22	17																												
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14																												
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	13																												
6	59	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14	11																												
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10																												
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9																												
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8																												
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16496	16496	16496
5°	16356	16382	16496
10°	16264	16225	16213
15°	16007	15902	15771
20°	15755	15405	15190
25°	15330	14900	14481
30°	14907	14249	13710
35°	14418	13585	12938
40°	13901	12960	12203
45°	13380	12309	11486
50°	12912	11673	10787
55°	12332	11011	10130
60°	11673	10384	9475
65°	10971	9685	8815
70°	10195	8902	7975
75°	9273	8055	7221
80°	8295	7051	6550
85°	6375	5795	4776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13380 cd/sqm



TEST NUMBER: P1438809

CATALOG NUMBER: CB2-125U-055D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.1	1.1
10°-20°	248.3	3.1
20°-30°	357.0	4.4
30°-40°	401.2	4.9
40°-50°	387.6	4.8
50°-60°	327.5	4.0
60°-70°	235.2	2.9
70°-80°	128.6	1.6
80°-90°	34.3	0.4
90°-100°	36.2	0.4
100°-110°	230.3	2.8
110°-120°	731.8	9.0
120°-130°	1062.0	13.1
130°-140°	1142.1	14.0
140°-150°	1075.3	13.2
150°-160°	876.0	10.8
160°-170°	570.2	7.0
170°-180°	197.1	2.4
0°-30°	694.3	8.5
0°-40°	1095.6	13.5
0°-60°	1810.7	22.3
0°-90°	2208.7	27.2
90°-120°	998.3	12.3
90°-150°	4277.7	52.6
90°-180°	5921.0	72.8
0°-180°	8129.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	936	948	937	937	944	89
15°	888	896	882	873	875	250
25°	798	798	775	758	754	367
35°	678	670	639	614	608	424
45°	543	532	500	473	466	420
55°	406	391	363	340	334	363
65°	266	256	235	218	214	264
75°	138	129	120	110	107	147
85°	32	30	29	25	24	38
90°	0	0	0	2	2	4
95°	83	24	26	16	15	105
105°	432	449	45	53	56	455
115°	818	836	844	854	490	804
125°	1162	1183	1183	1203	1219	1039
135°	1462	1480	1477	1487	1506	1128
145°	1712	1725	1713	1715	1737	1070
155°	1901	1913	1892	1888	1914	876
165°	2027	2033	2012	2003	2024	573
175°	2087	2092	2064	2051	2062	199
180°	2076	2076	2076	2076	2076	



TEST NUMBER: P1438809

CATALOG NUMBER: CB2-125U-055D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	947.1	947.1	947.1	947.1	947.1
2.5°	940.8	952.1	943.7	944.9	946.6
5°	935.5	948.3	937.0	937.1	943.5
7.5°	928.9	940.9	926.7	924.1	930.0
10°	919.6	931.6	917.4	912.4	916.7
12.5°	907.4	918.9	905.2	897.3	901.0
15°	887.7	895.5	881.9	873.2	874.6
17.5°	866.2	871.0	851.4	844.1	842.7
20°	850.0	854.2	831.1	820.9	819.5
22.5°	829.1	832.8	808.5	796.0	794.0
25°	797.7	798.5	775.3	757.8	753.5
27.5°	765.0	762.7	737.0	716.2	710.7
30°	741.2	738.3	708.5	686.7	681.7
32.5°	715.6	710.5	680.7	657.1	652.1
35°	678.1	670.3	638.9	614.1	608.5
37.5°	638.1	629.3	598.5	571.5	565.1
40°	611.4	601.4	570.0	543.0	536.7
42.5°	584.7	573.6	541.6	514.6	507.7
45°	543.2	531.8	499.7	473.4	466.3
47.5°	503.7	489.3	458.1	431.9	424.8
50°	476.5	460.9	430.8	405.2	398.1
52.5°	448.6	432.5	403.5	379.1	372.0
55°	406.1	391.2	362.6	340.0	333.6
57.5°	364.1	349.7	323.6	302.0	295.7
60°	335.1	323.0	298.1	277.6	272.0
62.5°	307.2	296.3	272.5	253.8	248.2
65°	266.2	256.2	235.0	218.2	213.9
67.5°	226.3	216.3	199.1	184.1	179.3
70°	200.2	190.2	174.8	160.9	156.6
72.5°	175.2	164.7	152.2	139.5	136.3
75°	137.8	129.3	119.7	110.2	107.3
77.5°	104.7	96.5	89.5	82.8	82.1
80°	82.7	75.6	70.3	66.0	65.3
82.5°	61.8	56.4	52.9	49.7	49.6
85°	31.9	29.8	29.0	25.4	23.9
87.5°	9.3	9.3	8.1	7.3	7.3
90°	0.0	0.0	0.0	1.5	1.5
92.5°	22.8	8.7	6.0	8.7	8.7
95°	82.6	23.9	25.5	16.5	15.0
97.5°	171.5	38.5	36.9	40.6	42.0
100°	238.7	78.7	40.5	46.6	48.0
102.5°	313.2	296.5	41.7	50.2	52.9
105°	432.4	448.6	45.0	52.6	55.6
107.5°	549.5	565.7	209.6	54.4	57.4
110°	627.6	643.8	663.7	55.6	58.6

TEST NUMBER: P1438809

CATALOG NUMBER: CB2-125U-055D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.9	720.6	735.7	123.8	61.0
115°	818.3	835.9	843.8	853.6	489.5
117.5°	921.9	943.6	952.5	969.4	985.9
120°	994.0	1014.5	1021.0	1037.9	1055.5
122.5°	1064.8	1083.0	1087.1	1106.4	1122.8
125°	1162.1	1182.7	1183.2	1203.0	1219.2
127.5°	1259.4	1277.1	1276.3	1291.1	1309.0
130°	1324.3	1336.0	1336.3	1348.8	1367.8
132.5°	1378.4	1394.8	1395.2	1405.2	1424.3
135°	1462.4	1480.1	1477.4	1486.9	1506.0
137.5°	1541.4	1558.4	1553.7	1561.7	1581.4
140°	1593.1	1607.7	1600.6	1608.6	1630.6
142.5°	1641.1	1655.8	1645.0	1651.8	1675.0
145°	1711.7	1724.9	1713.2	1715.2	1737.2
147.5°	1774.4	1787.4	1773.2	1775.2	1795.8
150°	1815.3	1827.0	1809.3	1811.2	1831.8
152.5°	1851.3	1861.9	1842.9	1842.6	1866.6
155°	1900.9	1912.6	1891.9	1888.0	1914.4
157.5°	1945.9	1956.8	1936.0	1933.2	1953.7
160°	1975.9	1983.3	1962.4	1958.4	1978.9
162.5°	1996.4	2004.9	1984.0	1977.6	1998.2
165°	2027.0	2032.9	2012.0	2003.4	2024.0
167.5°	2053.4	2060.2	2033.3	2025.7	2047.7
170°	2069.0	2073.4	2046.5	2036.5	2058.5
172.5°	2078.6	2081.9	2054.9	2043.5	2058.5
175°	2087.0	2091.5	2064.5	2051.2	2061.5
177.5°	2088.5	2090.9	2070.5	2058.9	2076.5
180°	2076.5	2076.5	2076.5	2076.5	2076.5



TEST NUMBER: P1438809

CATALOG NUMBER: CB2-125U-055D-835-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.12	14.80	15.25	15.92	17.49	13.02	13.70	14.15	14.83	16.39
	3H	15.75	16.36	16.89	17.49	19.07	14.53	15.14	15.67	16.28	17.86
	4H	16.37	16.95	17.52	18.08	19.67	15.10	15.68	16.25	16.81	18.40
	6H	16.76	17.30	17.92	18.43	20.03	15.46	15.99	16.62	17.13	18.73
	8H	16.91	17.41	18.07	18.56	20.15	15.60	16.10	16.76	17.25	18.84
	12H	16.98	17.46	18.14	18.60	20.21	15.65	16.13	16.82	17.28	18.89
4H	2H	14.51	15.09	15.66	16.22	17.80	13.63	14.21	14.79	15.34	16.93
	3H	16.36	16.84	17.52	18.00	19.60	15.35	15.83	16.51	16.99	18.59
	4H	17.10	17.54	18.26	18.69	20.31	16.02	16.46	17.18	17.61	19.23
	6H	17.61	17.99	18.78	19.16	20.76	16.48	16.86	17.65	18.03	19.64
	8H	17.81	18.16	18.98	19.32	20.95	16.67	17.02	17.84	18.18	19.81
	12H	17.91	18.23	19.09	19.40	21.03	16.75	17.07	17.93	18.24	19.87
8H	4H	17.24	17.60	18.41	18.76	20.38	16.28	16.63	17.45	17.79	19.42
	6H	17.88	18.17	19.06	19.37	20.99	16.87	17.17	18.06	18.37	19.99
	8H	18.16	18.42	19.36	19.60	21.24	17.15	17.40	18.34	18.58	20.22
	12H	18.33	18.55	19.53	19.73	21.41	17.29	17.51	18.49	18.69	20.36
12H	4H	17.21	17.53	18.40	18.71	20.33	16.27	16.59	17.46	17.77	19.39
	6H	17.90	18.16	19.10	19.34	20.98	16.94	17.19	18.13	18.37	20.01
	8H	18.21	18.44	19.41	19.61	21.29	17.23	17.46	18.43	18.64	20.31