

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438823

Luminaire Tested: CB2-125U-085D-835-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438823
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-125U-085D-835-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9292.3 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 67.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438823

CATALOG NUMBER: CB2-125U-085D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438823

CATALOG NUMBER: CB2-125U-085D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	63	57	52	52	47	44	41	38	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25180	25180	25180
5°	24967	25005	25180
10°	24824	24766	24746
15°	24431	24273	24072
20°	24047	23514	23186
25°	23402	22741	22103
30°	22752	21751	20926
35°	22007	20735	19747
40°	21218	19783	18626
45°	20422	18787	17533
50°	19707	17816	16467
55°	18824	16808	15462
60°	17814	15850	14460
65°	16745	14783	13460
70°	15558	13587	12176
75°	14152	12288	11023
80°	12658	10772	9990
85°	9732	8853	7294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20422 cd/sqm



TEST NUMBER: P1438823

CATALOG NUMBER: CB2-125U-085D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	1.5
10°-20°	379.0	4.1
20°-30°	544.9	5.9
30°-40°	612.5	6.6
40°-50°	591.6	6.4
50°-60°	499.9	5.4
60°-70°	359.1	3.9
70°-80°	196.2	2.1
80°-90°	52.2	0.6
90°-100°	36.2	0.4
100°-110°	230.3	2.5
110°-120°	731.8	7.9
120°-130°	1062.0	11.4
130°-140°	1142.1	12.3
140°-150°	1075.3	11.6
150°-160°	876.0	9.4
160°-170°	570.2	6.1
170°-180°	197.1	2.1
0°-30°	1059.8	11.4
0°-40°	1672.3	18.0
0°-60°	2763.8	29.7
0°-90°	3371.3	36.3
90°-120°	998.3	10.7
90°-150°	4277.7	46.0
90°-180°	5921.0	63.7
0°-180°	9292.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1446	1446	1446	1446	1446	
5°	1428	1448	1430	1430	1440	136
15°	1355	1367	1346	1333	1335	382
25°	1218	1219	1183	1157	1150	561
35°	1035	1023	975	937	929	647
45°	829	812	763	723	712	641
55°	620	597	554	519	509	554
65°	406	391	359	333	327	403
75°	210	197	183	168	164	225
85°	49	46	44	39	36	58
90°	0	0	0	2	2	5
95°	83	24	26	16	15	105
105°	432	449	45	53	56	455
115°	818	836	844	854	490	804
125°	1162	1183	1183	1203	1219	1039
135°	1462	1480	1477	1487	1506	1128
145°	1712	1725	1713	1715	1737	1070
155°	1901	1913	1892	1888	1914	876
165°	2027	2033	2012	2003	2024	573
175°	2087	2092	2064	2051	2062	199
180°	2076	2076	2076	2076	2076	

TEST NUMBER: P1438823

CATALOG NUMBER: CB2-125U-085D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.7	1445.7	1445.7	1445.7	1445.7
2.5°	1436.0	1453.3	1440.4	1442.2	1444.8
5°	1428.0	1447.5	1430.2	1430.4	1440.2
7.5°	1417.8	1436.2	1414.5	1410.5	1419.6
10°	1403.6	1422.0	1400.3	1392.7	1399.2
12.5°	1385.0	1402.6	1381.7	1369.7	1375.3
15°	1354.9	1366.8	1346.1	1332.8	1335.0
17.5°	1322.2	1329.5	1299.6	1288.5	1286.3
20°	1297.4	1303.9	1268.6	1253.0	1250.9
22.5°	1265.5	1271.1	1234.0	1214.9	1211.9
25°	1217.7	1218.7	1183.3	1156.6	1150.1
27.5°	1167.6	1164.2	1124.9	1093.3	1084.8
30°	1131.3	1127.0	1081.5	1048.1	1040.5
32.5°	1092.3	1084.6	1039.0	1003.0	995.4
35°	1035.0	1023.1	975.2	937.4	928.7
37.5°	973.9	960.5	913.5	872.3	862.5
40°	933.2	918.0	870.1	828.9	819.2
42.5°	892.4	875.5	826.7	785.5	774.9
45°	829.1	811.8	762.7	722.6	711.8
47.5°	768.9	746.8	699.2	659.3	648.5
50°	727.3	703.5	657.5	618.5	607.7
52.5°	684.8	660.1	615.9	578.7	567.9
55°	619.9	597.2	553.5	518.9	509.2
57.5°	555.7	533.8	493.9	460.9	451.4
60°	511.4	493.0	455.0	423.8	415.1
62.5°	468.9	452.2	416.0	387.5	378.8
65°	406.3	391.1	358.7	333.0	326.6
67.5°	345.4	330.2	304.0	281.0	273.6
70°	305.5	290.4	266.8	245.6	239.1
72.5°	267.4	251.4	232.2	212.9	208.1
75°	210.3	197.3	182.6	168.2	163.8
77.5°	159.8	147.3	136.6	126.4	125.3
80°	126.2	115.4	107.4	100.7	99.6
82.5°	94.3	86.1	80.8	75.9	75.7
85°	48.7	45.5	44.3	38.7	36.5
87.5°	14.2	14.2	12.4	10.9	10.9
90°	0.0	0.0	0.0	1.5	1.5
92.5°	22.8	8.7	6.0	8.7	8.7
95°	82.6	23.9	25.5	16.5	15.0
97.5°	171.5	38.5	36.9	40.6	42.0
100°	238.7	78.7	40.5	46.6	48.0
102.5°	313.2	296.5	41.7	50.2	52.9
105°	432.4	448.6	45.0	52.6	55.6
107.5°	549.5	565.7	209.6	54.4	57.4
110°	627.6	643.8	663.7	55.6	58.6



TEST NUMBER: P1438823

CATALOG NUMBER: CB2-125U-085D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.9	720.6	735.7	123.8	61.0
115°	818.3	835.9	843.8	853.6	489.5
117.5°	921.9	943.6	952.5	969.4	985.9
120°	994.0	1014.5	1021.0	1037.9	1055.5
122.5°	1064.8	1083.0	1087.1	1106.4	1122.8
125°	1162.1	1182.7	1183.2	1203.0	1219.2
127.5°	1259.4	1277.1	1276.3	1291.1	1309.0
130°	1324.3	1336.0	1336.3	1348.8	1367.8
132.5°	1378.4	1394.8	1395.2	1405.2	1424.3
135°	1462.4	1480.1	1477.4	1486.9	1506.0
137.5°	1541.4	1558.4	1553.7	1561.7	1581.4
140°	1593.1	1607.7	1600.6	1608.6	1630.6
142.5°	1641.1	1655.8	1645.0	1651.8	1675.0
145°	1711.7	1724.9	1713.2	1715.2	1737.2
147.5°	1774.4	1787.4	1773.2	1775.2	1795.8
150°	1815.3	1827.0	1809.3	1811.2	1831.8
152.5°	1851.3	1861.9	1842.9	1842.6	1866.6
155°	1900.9	1912.6	1891.9	1888.0	1914.4
157.5°	1945.9	1956.8	1936.0	1933.2	1953.7
160°	1975.9	1983.3	1962.4	1958.4	1978.9
162.5°	1996.4	2004.9	1984.0	1977.6	1998.2
165°	2027.0	2032.9	2012.0	2003.4	2024.0
167.5°	2053.4	2060.2	2033.3	2025.7	2047.7
170°	2069.0	2073.4	2046.5	2036.5	2058.5
172.5°	2078.6	2081.9	2054.9	2043.5	2058.5
175°	2087.0	2091.5	2064.5	2051.2	2061.5
177.5°	2088.5	2090.9	2070.5	2058.9	2076.5
180°	2076.5	2076.5	2076.5	2076.5	2076.5



TEST NUMBER: P1438823

CATALOG NUMBER: CB2-125U-085D-835-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.78	17.53	17.85	18.60	20.05	15.69	16.43	16.75	17.50	18.95
	3H	18.42	19.09	19.50	20.16	21.64	17.20	17.87	18.28	18.95	20.42
	4H	19.04	19.67	20.13	20.75	22.23	17.77	18.40	18.86	19.48	20.96
	6H	19.44	20.02	20.54	21.10	22.59	18.14	18.72	19.24	19.80	21.29
	8H	19.59	20.14	20.69	21.24	22.72	18.27	18.83	19.38	19.92	21.41
	12H	19.66	20.18	20.76	21.27	22.78	18.33	18.86	19.44	19.95	21.46
4H	2H	17.18	17.81	18.28	18.89	20.37	16.31	16.94	17.40	18.01	19.49
	3H	19.04	19.56	20.14	20.67	22.16	18.03	18.55	19.13	19.66	21.15
	4H	19.78	20.26	20.89	21.36	22.87	18.70	19.18	19.81	20.28	21.79
	6H	20.29	20.71	21.41	21.83	23.33	19.17	19.58	20.28	20.70	22.21
	8H	20.49	20.88	21.61	21.99	23.51	19.35	19.74	20.47	20.85	22.37
	12H	20.59	20.94	21.73	22.07	23.60	19.44	19.79	20.57	20.91	22.44
8H	4H	19.93	20.31	21.04	21.42	22.95	18.96	19.35	20.08	20.46	21.98
	6H	20.56	20.88	21.70	22.04	23.55	19.56	19.88	20.70	21.03	22.55
	8H	20.85	21.13	22.00	22.27	23.80	19.84	20.11	20.98	21.25	22.79
	12H	21.02	21.27	22.17	22.40	23.97	19.98	20.23	21.13	21.36	22.93
12H	4H	19.90	20.25	21.03	21.37	22.90	18.96	19.31	20.09	20.43	21.96
	6H	20.59	20.87	21.73	22.00	23.54	19.62	19.90	20.77	21.04	22.58
	8H	20.90	21.15	22.05	22.28	23.85	19.92	20.17	21.07	21.30	22.88