

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439038

Luminaire Tested: CB2-D-055U-120D-935-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439038
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-055U-120D-935-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14541.7 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 126.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439038

CATALOG NUMBER: CB2-D-055U-120D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1439038

CATALOG NUMBER: CB2-D-055U-120D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68																				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	70	65	63	62	58																				
2	93	86	79	74	88	81	76	71	73	68	65	65	61	58	57	55	53	49																				
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42																				
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36																				
5	72	60	52	46	68	57	50	44	52	45	41	46	41	37	41	37	34	32																				
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28																				
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25																				
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22																				
9	54	41	33	28	51	39	32	27	36	30	26	33	27	24	29	25	22	20																				
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	37089	37089	37089
5°	36775	36832	37089
10°	36566	36479	36450
15°	35987	35752	35458
20°	35420	34634	34150
25°	34468	33497	32557
30°	33514	32038	30825
35°	32415	30544	29087
40°	31252	29139	27433
45°	30082	27671	25824
50°	29027	26243	24255
55°	27727	24756	22776
60°	26241	23344	21300
65°	24662	21773	19823
70°	22916	20011	17936
75°	20848	18106	16238
80°	18646	15863	14719
85°	14339	13030	10751

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30082 cd/sqm



TEST NUMBER: P1439038

CATALOG NUMBER: CB2-D-055U-120D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.5	2.8
10°-20°	1116.4	7.7
20°-30°	1605.2	11.0
30°-40°	1804.2	12.4
40°-50°	1742.9	12.0
50°-60°	1472.6	10.1
60°-70°	1057.8	7.3
70°-80°	578.1	4.0
80°-90°	153.6	1.1
90°-100°	69.8	0.5
100°-110°	288.0	2.0
110°-120°	522.9	3.6
120°-130°	711.5	4.9
130°-140°	821.3	5.6
140°-150°	827.7	5.7
150°-160°	714.3	4.9
160°-170°	484.1	3.3
170°-180°	170.8	1.2
0°-30°	3122.1	21.5
0°-40°	4926.4	33.9
0°-60°	8141.9	56.0
0°-90°	9931.4	68.3
90°-120°	880.7	6.1
90°-150°	3241.2	22.3
90°-180°	4610.0	31.7
0°-180°	14541.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4259	4259	4259	4259	4259	
5°	4207	4264	4213	4214	4243	399
15°	3992	4027	3965	3926	3933	1125
25°	3587	3590	3486	3407	3388	1651
35°	3049	3014	2873	2762	2736	1905
45°	2442	2392	2247	2129	2097	1887
55°	1826	1759	1630	1529	1500	1633
65°	1197	1152	1057	981	962	1187
75°	620	581	538	495	483	663
85°	144	134	130	114	108	171
90°	0	0	1	0	1	8
95°	68	59	56	44	44	79
105°	285	281	274	258	255	302
115°	542	540	530	515	513	534
125°	805	813	797	780	781	719
135°	1073	1086	1067	1048	1055	826
145°	1330	1345	1324	1309	1318	831
155°	1555	1570	1548	1539	1551	715
165°	1719	1737	1715	1705	1720	484
175°	1801	1820	1796	1785	1789	171
180°	1808	1808	1808	1808	1808	

TEST NUMBER: P1439038

CATALOG NUMBER: CB2-D-055U-120D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4258.9	4258.9	4258.9	4258.9	4258.9
2.5°	4230.2	4281.2	4243.2	4248.6	4256.3
5°	4206.7	4264.1	4213.2	4213.9	4242.6
7.5°	4176.7	4230.9	4166.9	4155.1	4181.9
10°	4135.0	4189.2	4125.2	4102.8	4121.9
12.5°	4080.2	4131.8	4070.4	4034.9	4051.5
15°	3991.5	4026.6	3965.4	3926.4	3932.8
17.5°	3895.0	3916.6	3828.4	3795.7	3789.3
20°	3821.9	3841.0	3737.1	3691.3	3684.9
22.5°	3728.0	3744.6	3635.4	3579.1	3570.2
25°	3587.1	3590.3	3486.0	3407.3	3388.2
27.5°	3439.7	3429.5	3313.8	3220.7	3195.8
30°	3332.8	3320.0	3186.0	3087.7	3065.4
32.5°	3218.0	3195.0	3060.8	2954.6	2932.3
35°	3049.0	3014.0	2873.0	2761.5	2736.0
37.5°	2869.0	2829.5	2691.0	2569.7	2541.0
40°	2749.0	2704.4	2563.2	2441.8	2413.1
42.5°	2629.0	2579.3	2435.3	2314.0	2282.7
45°	2442.5	2391.5	2246.8	2128.7	2096.8
47.5°	2265.1	2200.1	2059.7	1942.2	1910.3
50°	2142.5	2072.3	1937.0	1822.2	1790.3
52.5°	2017.3	1944.6	1814.4	1704.8	1672.9
55°	1826.2	1759.2	1630.5	1528.8	1500.1
57.5°	1637.0	1572.6	1455.1	1357.9	1329.8
60°	1506.6	1452.4	1340.3	1248.4	1222.9
62.5°	1381.4	1332.3	1225.5	1141.4	1115.9
65°	1196.8	1152.2	1056.6	981.1	962.0
67.5°	1017.4	972.8	895.5	827.8	806.1
70°	900.0	855.4	785.9	723.5	704.4
72.5°	787.9	740.7	684.2	627.1	613.1
75°	619.6	581.3	538.1	495.4	482.6
77.5°	470.9	433.9	402.4	372.3	369.1
80°	371.8	339.9	316.3	296.7	293.5
82.5°	277.8	253.6	238.1	223.7	223.1
85°	143.5	133.9	130.4	114.0	107.6
87.5°	41.7	41.7	36.8	31.3	31.6
90°	0.0	0.0	1.4	0.0	1.4
92.5°	16.9	14.7	13.8	9.1	10.4
95°	67.7	59.4	56.4	43.7	43.7
97.5°	127.8	119.5	115.1	102.0	99.3
100°	170.6	162.3	157.9	143.8	141.0
102.5°	214.6	210.8	203.1	187.8	185.0
105°	284.8	280.7	273.6	258.0	255.2
107.5°	357.0	357.9	347.2	334.4	330.5
110°	408.9	407.5	399.1	386.3	383.5



TEST NUMBER: P1439038

CATALOG NUMBER: CB2-D-055U-120D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	461.9	459.5	450.9	438.2	435.4
115°	541.5	540.1	530.2	514.7	513.3
117.5°	617.1	621.5	609.7	593.4	592.8
120°	671.2	676.7	662.7	648.6	645.8
122.5°	724.2	730.8	716.9	700.5	701.1
125°	805.2	813.4	796.7	779.8	781.2
127.5°	883.3	893.5	877.9	860.8	862.4
130°	936.3	948.7	932.1	913.8	916.6
132.5°	990.4	1002.9	986.2	966.9	971.8
135°	1073.1	1085.5	1067.4	1047.9	1054.7
137.5°	1150.9	1163.3	1143.6	1127.1	1135.4
140°	1202.8	1215.2	1194.3	1179.0	1187.3
142.5°	1253.6	1268.2	1246.2	1229.8	1240.3
145°	1329.7	1344.9	1324.1	1308.8	1318.4
147.5°	1401.9	1417.1	1396.0	1381.3	1391.2
150°	1448.2	1463.3	1441.1	1428.7	1439.7
152.5°	1491.0	1508.4	1485.1	1472.7	1487.1
155°	1555.3	1570.5	1548.3	1538.7	1551.1
157.5°	1611.2	1628.8	1606.7	1598.4	1608.3
160°	1648.4	1664.9	1642.8	1634.5	1645.6
162.5°	1676.6	1694.2	1673.2	1663.9	1677.2
165°	1718.9	1736.8	1714.7	1705.1	1720.3
167.5°	1752.2	1771.2	1748.8	1739.0	1754.4
170°	1772.5	1790.4	1766.8	1755.9	1772.5
172.5°	1786.0	1805.0	1780.4	1769.3	1780.4
175°	1800.7	1820.0	1796.5	1785.3	1789.4
177.5°	1807.7	1823.2	1804.3	1794.5	1807.7
180°	1807.7	1807.7	1807.7	1807.7	1807.7

TEST NUMBER: P1439038

CATALOG NUMBER: CB2-D-055U-120D-935-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.10	22.14	21.88	22.94	23.93	20.00	21.04	20.78	21.84	22.83
	3H	22.76	23.69	23.56	24.50	25.52	21.54	22.47	22.34	23.29	24.30
	4H	23.39	24.27	24.21	25.09	26.12	22.12	23.00	22.94	23.82	24.85
	6H	23.81	24.61	24.63	25.45	26.48	22.50	23.31	23.33	24.14	25.18
	8H	23.96	24.73	24.80	25.58	26.62	22.65	23.42	23.48	24.27	25.31
	12H	24.04	24.77	24.88	25.62	26.68	22.72	23.45	23.56	24.29	25.36
4H	2H	21.53	22.41	22.35	23.23	24.26	20.65	21.53	21.47	22.36	23.38
	3H	23.41	24.15	24.25	25.00	26.04	22.41	23.14	23.24	23.99	25.04
	4H	24.17	24.83	25.01	25.69	26.76	23.09	23.75	23.93	24.61	25.68
	6H	24.70	25.27	25.56	26.15	27.22	23.57	24.15	24.43	25.03	26.10
	8H	24.91	25.44	25.77	26.32	27.40	23.76	24.30	24.63	25.18	26.26
	12H	25.02	25.50	25.90	26.40	27.49	23.86	24.34	24.74	25.24	26.33
8H	4H	24.34	24.87	25.20	25.75	26.83	23.37	23.91	24.24	24.79	25.87
	6H	24.99	25.43	25.88	26.35	27.43	23.98	24.43	24.88	25.35	26.43
	8H	25.28	25.67	26.18	26.58	27.69	24.26	24.66	25.16	25.57	26.67
	12H	25.46	25.81	26.37	26.71	27.86	24.42	24.77	25.32	25.67	26.82
12H	4H	24.33	24.81	25.21	25.70	26.79	23.39	23.87	24.27	24.76	25.85
	6H	25.02	25.41	25.92	26.32	27.42	24.05	24.44	24.95	25.35	26.46
	8H	25.34	25.69	26.25	26.59	27.75	24.36	24.71	25.27	25.61	26.77