

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056958

Luminaire Tested: CB2-0U-085D-840-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056958
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-085D-840-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6652.5 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056958

CATALOG NUMBER: CB2-0U-085D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056958

CATALOG NUMBER: CB2-0U-085D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24844	24844	24844
5°	24634	24672	24844
10°	24493	24436	24416
15°	24106	23948	23751
20°	23726	23200	22876
25°	23089	22438	21808
30°	22450	21461	20648
35°	21713	20460	19484
40°	20935	19518	18377
45°	20150	18537	17299
50°	19444	17579	16247
55°	18573	16583	15256
60°	17578	15637	14268
65°	16520	14583	13279
70°	15351	13403	12013
75°	13964	12127	10878
80°	12488	10627	9860
85°	9602	8733	7204

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20150 cd/sqm

TEST NUMBER: P1056958

CATALOG NUMBER: CB2-0U-085D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.3	4.0
10°-20°	747.8	11.2
20°-30°	1075.3	16.2
30°-40°	1208.6	18.2
40°-50°	1167.5	17.5
50°-60°	986.4	14.8
60°-70°	708.5	10.7
70°-80°	387.3	5.8
80°-90°	102.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2091.4	31.4
0°-40°	3300.0	49.6
0°-60°	5453.9	82.0
0°-90°	6652.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6652.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2853	2853	2853	2853	2853	
5°	2818	2856	2822	2823	2842	268
15°	2674	2697	2656	2630	2634	754
25°	2403	2405	2335	2282	2270	1106
35°	2042	2019	1924	1850	1833	1276
45°	1636	1602	1505	1426	1405	1264
55°	1223	1178	1092	1024	1005	1094
65°	802	772	708	657	644	795
75°	415	389	360	332	323	444
85°	96	90	87	76	72	118
90°	0	0	0	0	0	

TEST NUMBER: P1056958

CATALOG NUMBER: CB2-OU-085D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2852.8	2852.8	2852.8	2852.8	2852.8
2.5°	2833.6	2867.8	2842.4	2846.0	2851.1
5°	2817.9	2856.3	2822.3	2822.7	2841.9
7.5°	2797.8	2834.1	2791.2	2783.3	2801.3
10°	2769.8	2806.1	2763.3	2748.3	2761.1
12.5°	2733.1	2767.7	2726.6	2702.8	2713.9
15°	2673.7	2697.2	2656.2	2630.1	2634.4
17.5°	2609.1	2623.6	2564.5	2542.6	2538.3
20°	2560.1	2572.9	2503.3	2472.7	2468.4
22.5°	2497.2	2508.3	2435.2	2397.5	2391.5
25°	2402.9	2405.0	2335.1	2282.4	2269.6
27.5°	2304.1	2297.3	2219.8	2157.4	2140.7
30°	2232.5	2223.9	2134.2	2068.3	2053.3
32.5°	2155.6	2140.2	2050.3	1979.2	1964.2
35°	2042.4	2018.9	1924.5	1849.8	1832.7
37.5°	1921.8	1895.4	1802.6	1721.3	1702.1
40°	1841.5	1811.6	1716.9	1635.7	1616.5
42.5°	1761.1	1727.8	1631.3	1550.0	1529.1
45°	1636.1	1601.9	1505.1	1425.9	1404.6
47.5°	1517.3	1473.7	1379.7	1301.0	1279.6
50°	1435.2	1388.2	1297.5	1220.6	1199.2
52.5°	1351.3	1302.6	1215.4	1142.0	1120.6
55°	1223.3	1178.4	1092.2	1024.1	1004.8
57.5°	1096.6	1053.4	974.7	909.6	890.8
60°	1009.2	972.9	897.8	836.2	819.2
62.5°	925.3	892.4	820.9	764.6	747.5
65°	801.7	771.8	707.7	657.2	644.4
67.5°	681.5	651.6	599.8	554.5	540.0
70°	602.9	573.0	526.4	484.6	471.8
72.5°	527.8	496.1	458.3	420.1	410.7
75°	415.0	389.4	360.4	331.8	323.3
77.5°	315.4	290.7	269.6	249.4	247.3
80°	249.0	227.7	211.9	198.7	196.6
82.5°	186.1	169.9	159.5	149.8	149.4
85°	96.1	89.7	87.4	76.4	72.1
87.5°	28.0	28.0	24.5	21.0	21.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)