

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438826

Luminaire Tested: CB2-125U-085D-840-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438826  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-125U-085D-840-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 850 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 18336.8 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 151.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438826

CATALOG NUMBER: CB2-125U-085D-840-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1438826

CATALOG NUMBER: CB2-125U-085D-840-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36																				
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31																				
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31	26																				
3	79	70	63	57	71	63	57	52	52	47	44	41	38	35	30	28	27	22																				
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19																				
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17																				
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15																				
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13																				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12																				
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11																				
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24844	24844	24844
5°	24634	24672	24844
10°	24493	24436	24416
15°	24106	23948	23751
20°	23726	23200	22876
25°	23089	22438	21808
30°	22450	21461	20648
35°	21713	20460	19484
40°	20935	19518	18377
45°	20150	18537	17299
50°	19444	17579	16247
55°	18573	16583	15256
60°	17578	15637	14268
65°	16520	14583	13279
70°	15351	13403	12013
75°	13964	12127	10878
80°	12488	10627	9860
85°	9602	8733	7204

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20150 cd/sqm



TEST NUMBER: P1438826

CATALOG NUMBER: CB2-125U-085D-840-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	268.3	1.5
10°-20°	747.8	4.1
20°-30°	1075.3	5.9
30°-40°	1208.6	6.6
40°-50°	1167.5	6.4
50°-60°	986.4	5.4
60°-70°	708.5	3.9
70°-80°	387.3	2.1
80°-90°	103.1	0.6
90°-100°	71.4	0.4
100°-110°	454.5	2.5
110°-120°	1444.1	7.9
120°-130°	2095.6	11.4
130°-140°	2253.7	12.3
140°-150°	2122.0	11.6
150°-160°	1728.6	9.4
160°-170°	1125.2	6.1
170°-180°	388.9	2.1
0°-30°	2091.4	11.4
0°-40°	3300.0	18.0
0°-60°	5453.9	29.7
0°-90°	6652.7	36.3
90°-120°	1970.0	10.7
90°-150°	8441.3	46.0
90°-180°	11684.0	63.7
0°-180°	18336.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2853	2853	2853	2853	2853	
5°	2818	2856	2822	2823	2842	268
15°	2674	2697	2656	2630	2634	754
25°	2403	2405	2335	2282	2270	1106
35°	2042	2019	1924	1850	1833	1276
45°	1636	1602	1505	1426	1405	1264
55°	1223	1178	1092	1024	1005	1094
65°	802	772	708	657	644	795
75°	415	389	360	332	323	444
85°	96	90	87	76	72	114
90°	0	0	0	3	3	10
95°	163	47	50	32	30	206
105°	853	885	89	104	110	899
115°	1615	1650	1665	1684	966	1587
125°	2293	2334	2335	2374	2406	2050
135°	2886	2921	2916	2934	2972	2225
145°	3378	3404	3381	3385	3428	2111
155°	3751	3774	3733	3726	3778	1729
165°	4000	4012	3970	3953	3994	1130
175°	4118	4127	4074	4048	4068	392
180°	4098	4098	4098	4098	4098	

TEST NUMBER: P1438826

CATALOG NUMBER: CB2-125U-085D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2852.8	2852.8	2852.8	2852.8	2852.8
2.5°	2833.6	2867.8	2842.4	2846.0	2851.1
5°	2817.9	2856.3	2822.3	2822.7	2841.9
7.5°	2797.8	2834.1	2791.2	2783.3	2801.3
10°	2769.8	2806.1	2763.3	2748.3	2761.1
12.5°	2733.1	2767.7	2726.6	2702.8	2713.9
15°	2673.7	2697.2	2656.2	2630.1	2634.4
17.5°	2609.1	2623.6	2564.5	2542.6	2538.3
20°	2560.1	2572.9	2503.3	2472.7	2468.4
22.5°	2497.2	2508.3	2435.2	2397.5	2391.5
25°	2402.9	2405.0	2335.1	2282.4	2269.6
27.5°	2304.1	2297.3	2219.8	2157.4	2140.7
30°	2232.5	2223.9	2134.2	2068.3	2053.3
32.5°	2155.6	2140.2	2050.3	1979.2	1964.2
35°	2042.4	2018.9	1924.5	1849.8	1832.7
37.5°	1921.8	1895.4	1802.6	1721.3	1702.1
40°	1841.5	1811.6	1716.9	1635.7	1616.5
42.5°	1761.1	1727.8	1631.3	1550.0	1529.1
45°	1636.1	1601.9	1505.1	1425.9	1404.6
47.5°	1517.3	1473.7	1379.7	1301.0	1279.6
50°	1435.2	1388.2	1297.5	1220.6	1199.2
52.5°	1351.3	1302.6	1215.4	1142.0	1120.6
55°	1223.3	1178.4	1092.2	1024.1	1004.8
57.5°	1096.6	1053.4	974.7	909.6	890.8
60°	1009.2	972.9	897.8	836.2	819.2
62.5°	925.3	892.4	820.9	764.6	747.5
65°	801.7	771.8	707.7	657.2	644.4
67.5°	681.5	651.6	599.8	554.5	540.0
70°	602.9	573.0	526.4	484.6	471.8
72.5°	527.8	496.1	458.3	420.1	410.7
75°	415.0	389.4	360.4	331.8	323.3
77.5°	315.4	290.7	269.6	249.4	247.3
80°	249.0	227.7	211.9	198.7	196.6
82.5°	186.1	169.9	159.5	149.8	149.4
85°	96.1	89.7	87.4	76.4	72.1
87.5°	28.0	28.0	24.5	21.6	21.6
90°	0.0	0.0	0.0	3.0	3.0
92.5°	45.0	17.2	11.9	17.2	17.2
95°	163.0	47.1	50.4	32.5	29.6
97.5°	338.4	75.9	72.9	80.1	83.0
100°	471.1	155.3	80.0	91.9	94.8
102.5°	618.1	585.0	82.4	99.1	104.3
105°	853.3	885.2	88.9	103.8	109.6
107.5°	1084.4	1116.3	413.6	107.4	113.2
110°	1238.5	1270.4	1309.6	109.8	115.6



TEST NUMBER: P1438826

CATALOG NUMBER: CB2-125U-085D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1383.1	1421.9	1451.8	244.3	120.3
115°	1614.8	1649.6	1665.2	1684.4	965.9
117.5°	1819.2	1862.1	1879.7	1913.0	1945.4
120°	1961.4	2002.0	2014.8	2048.2	2082.9
122.5°	2101.3	2137.2	2145.1	2183.2	2215.7
125°	2293.3	2333.9	2334.8	2374.0	2405.9
127.5°	2485.3	2520.1	2518.5	2547.7	2583.1
130°	2613.3	2636.5	2637.0	2661.6	2699.2
132.5°	2720.0	2752.4	2753.1	2773.0	2810.6
135°	2885.9	2920.6	2915.5	2934.1	2971.8
137.5°	3041.7	3075.3	3066.0	3081.7	3120.5
140°	3143.6	3172.6	3158.5	3174.3	3217.7
142.5°	3238.5	3267.4	3246.2	3259.7	3305.4
145°	3377.7	3403.8	3380.7	3384.6	3428.1
147.5°	3501.6	3527.1	3499.2	3503.1	3543.6
150°	3582.2	3605.3	3570.3	3574.2	3614.8
152.5°	3653.3	3674.1	3636.7	3636.0	3683.5
155°	3751.0	3774.2	3733.3	3725.6	3777.7
157.5°	3839.9	3861.4	3820.4	3814.8	3855.3
160°	3899.2	3913.7	3872.5	3864.6	3905.1
162.5°	3939.5	3956.3	3915.2	3902.5	3943.0
165°	3999.9	4011.5	3970.3	3953.4	3994.0
167.5°	4052.1	4065.4	4012.4	3997.4	4040.8
170°	4082.9	4091.6	4038.4	4018.7	4062.2
172.5°	4101.9	4108.2	4055.0	4032.6	4062.2
175°	4118.4	4127.1	4074.0	4047.8	4068.1
177.5°	4121.4	4126.0	4085.9	4062.9	4097.7
180°	4097.7	4097.7	4097.7	4097.7	4097.7



TEST NUMBER: P1438826  
 CATALOG NUMBER: CB2-125U-085D-840-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.74	17.48	17.81	18.55	20.01	15.64	16.38	16.71	17.45	18.91
	3H	18.37	19.04	19.45	20.12	21.59	17.16	17.82	18.24	18.90	20.37
	4H	19.00	19.63	20.09	20.71	22.19	17.73	18.36	18.81	19.43	20.91
	6H	19.39	19.97	20.49	21.06	22.55	18.09	18.67	19.19	19.75	21.25
	8H	19.54	20.09	20.64	21.19	22.67	18.23	18.78	19.33	19.88	21.36
	12H	19.61	20.13	20.72	21.23	22.73	18.29	18.81	19.39	19.90	21.41
4H	2H	17.13	17.76	18.23	18.84	20.32	16.26	16.89	17.35	17.97	19.45
	3H	18.99	19.52	20.09	20.62	22.12	17.98	18.51	19.09	19.61	21.11
	4H	19.73	20.21	20.84	21.31	22.82	18.65	19.13	19.76	20.23	21.74
	6H	20.25	20.66	21.36	21.78	23.28	19.12	19.53	20.23	20.65	22.16
	8H	20.45	20.83	21.56	21.95	23.47	19.31	19.69	20.42	20.80	22.33
	12H	20.55	20.90	21.68	22.02	23.55	19.39	19.74	20.52	20.86	22.39
8H	4H	19.88	20.27	20.99	21.38	22.90	18.92	19.30	20.03	20.41	21.94
	6H	20.52	20.84	21.65	21.99	23.51	19.52	19.83	20.65	20.99	22.51
	8H	20.81	21.09	21.95	22.22	23.76	19.79	20.07	20.93	21.20	22.74
	12H	20.98	21.22	22.12	22.35	23.93	19.93	20.18	21.08	21.31	22.88
12H	4H	19.85	20.20	20.99	21.33	22.85	18.91	19.26	20.05	20.39	21.91
	6H	20.54	20.82	21.69	21.96	23.50	19.58	19.86	20.72	20.99	22.53
	8H	20.86	21.10	22.00	22.23	23.81	19.88	20.12	21.02	21.25	22.83