

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438872

Luminaire Tested: CB2-B-030U-085D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438872
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-030U-085D-940-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10767.2 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 74.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438872

CATALOG NUMBER: CB2-B-030U-085D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438872

CATALOG NUMBER: CB2-B-030U-085D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																				
1	102	98	94	90	96	93	89	86	83	80	78	73	72	70	65	64	62	58																				
2	93	86	80	74	88	81	76	71	73	68	65	65	62	59	58	55	53	49																				
3	85	76	68	62	80	72	65	60	64	59	55	58	53	50	51	48	45	42																				
4	78	67	59	53	74	64	57	51	57	52	47	52	47	43	46	42	39	36																				
5	72	60	52	46	68	57	50	44	52	45	41	46	41	38	42	38	34	32																				
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28																				
7	62	49	41	35	58	47	39	34	43	36	32	38	33	29	35	30	27	25																				
8	57	45	37	31	54	43	36	30	39	33	28	35	30	26	32	28	25	22																				
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	25	22	20																				
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27573	27573	27573
5°	27340	27382	27573
10°	27184	27120	27099
15°	26754	26579	26361
20°	26333	25748	25389
25°	25625	24904	24204
30°	24916	23818	22916
35°	24099	22707	21625
40°	23235	21664	20395
45°	22364	20573	19199
50°	21580	19511	18033
55°	20614	18405	16932
60°	19509	17355	15834
65°	18334	16186	14738
70°	17037	14878	13335
75°	15498	13459	12073
80°	13862	11796	10943
85°	10662	9692	7994

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22364 cd/sqm



TEST NUMBER: P1438872

CATALOG NUMBER: CB2-B-030U-085D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.7	2.8
10°-20°	830.0	7.7
20°-30°	1193.4	11.1
30°-40°	1341.4	12.5
40°-50°	1295.7	12.0
50°-60°	1094.8	10.2
60°-70°	786.4	7.3
70°-80°	429.8	4.0
80°-90°	114.2	1.1
90°-100°	38.6	0.4
100°-110°	239.0	2.2
110°-120°	602.6	5.6
120°-130°	724.4	6.7
130°-140°	656.8	6.1
140°-150°	523.7	4.9
150°-160°	357.3	3.3
160°-170°	188.9	1.8
170°-180°	52.6	0.5
0°-30°	2321.1	21.6
0°-40°	3662.5	34.0
0°-60°	6053.0	56.2
0°-90°	7383.4	68.6
90°-120°	880.1	8.2
90°-150°	2785.1	25.9
90°-180°	3384.0	31.4
0°-180°	10767.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3166	3166	3166	3166	3166	
5°	3127	3170	3132	3133	3154	297
15°	2967	2994	2948	2919	2924	836
25°	2667	2669	2592	2533	2519	1228
35°	2267	2241	2136	2053	2034	1416
45°	1816	1778	1670	1583	1559	1403
55°	1358	1308	1212	1136	1115	1214
65°	890	857	786	729	715	882
75°	461	432	400	368	359	493
85°	107	100	97	85	80	127
90°	0	0	0	0	0	5
95°	20	50	16	11	11	25
105°	98	274	395	99	67	103
115°	169	373	901	839	639	165
125°	220	452	983	1119	1125	197
135°	275	501	986	1154	1239	214
145°	353	527	930	1121	1221	221
155°	428	537	828	998	1050	197
165°	486	532	668	787	824	136
175°	515	522	530	540	550	49
180°	515	515	515	515	515	

TEST NUMBER: P1438872

CATALOG NUMBER: CB2-B-030U-085D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3166.2	3166.2	3166.2	3166.2	3166.2
2.5°	3144.9	3182.8	3154.6	3158.6	3164.3
5°	3127.4	3170.1	3132.3	3132.8	3154.1
7.5°	3105.1	3145.4	3097.9	3089.1	3109.0
10°	3074.1	3114.4	3066.8	3050.2	3064.4
12.5°	3033.4	3071.8	3026.1	2999.7	3012.0
15°	2967.4	2993.5	2948.0	2919.1	2923.8
17.5°	2895.7	2911.8	2846.2	2821.9	2817.1
20°	2841.4	2855.6	2778.3	2744.3	2739.5
22.5°	2771.5	2783.9	2702.7	2660.8	2654.2
25°	2666.8	2669.2	2591.7	2533.2	2518.9
27.5°	2557.2	2549.6	2463.7	2394.4	2375.9
30°	2477.7	2468.2	2368.6	2295.5	2278.9
32.5°	2392.4	2375.3	2275.5	2196.6	2180.0
35°	2266.8	2240.7	2135.9	2053.0	2034.1
37.5°	2133.0	2103.6	2000.6	1910.4	1889.1
40°	2043.8	2010.6	1905.6	1815.4	1794.0
42.5°	1954.5	1917.6	1810.5	1720.3	1697.1
45°	1815.9	1777.9	1670.4	1582.6	1558.9
47.5°	1684.0	1635.6	1531.2	1443.9	1420.2
50°	1592.8	1540.7	1440.1	1354.7	1331.0
52.5°	1499.7	1445.7	1348.9	1267.4	1243.7
55°	1357.7	1307.9	1212.2	1136.5	1115.2
57.5°	1217.0	1169.2	1081.8	1009.5	988.7
60°	1120.1	1079.8	996.4	928.1	909.1
62.5°	1027.0	990.5	911.1	848.6	829.6
65°	889.7	856.6	785.5	729.4	715.2
67.5°	756.4	723.2	665.7	615.4	599.3
70°	669.1	635.9	584.3	537.9	523.7
72.5°	585.7	550.6	508.6	466.2	455.8
75°	460.6	432.2	400.0	368.3	358.8
77.5°	350.1	322.6	299.2	276.8	274.4
80°	276.4	252.7	235.2	220.6	218.2
82.5°	206.6	188.5	177.0	166.3	165.8
85°	106.7	99.6	97.0	84.7	80.0
87.5°	31.0	31.0	27.2	23.3	23.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.3	8.8	3.6	3.6	3.6
95°	20.0	50.4	15.5	11.1	11.1
97.5°	41.7	120.7	83.9	22.6	19.5
100°	57.7	174.9	144.3	33.1	26.6
102.5°	73.7	222.2	227.7	52.6	40.8
105°	97.7	273.5	395.1	99.1	66.6
107.5°	121.2	307.0	605.6	204.6	123.4
110°	135.4	326.4	763.6	319.0	190.9



TEST NUMBER: P1438872

CATALOG NUMBER: CB2-B-030U-085D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	149.6	345.8	850.6	511.3	329.4
115°	168.7	372.7	901.2	839.0	639.3
117.5°	184.7	397.4	944.7	1037.5	978.9
120°	195.3	416.7	967.8	1065.9	1085.5
122.5°	206.0	430.9	980.3	1077.0	1113.9
125°	219.8	452.0	983.4	1118.9	1125.4
127.5°	233.5	467.9	998.0	1157.5	1160.5
130°	244.2	478.6	1012.2	1170.4	1194.2
132.5°	256.6	487.5	1017.5	1177.7	1213.8
135°	275.3	501.0	985.6	1154.0	1238.6
137.5°	298.8	510.6	954.9	1153.3	1208.0
140°	313.0	512.7	939.0	1178.8	1183.1
142.5°	329.0	518.2	935.4	1176.0	1213.3
145°	352.9	526.6	930.1	1121.0	1220.9
147.5°	376.9	531.9	909.7	1060.4	1147.6
150°	392.9	534.0	890.1	1040.1	1094.3
152.5°	408.9	536.1	865.3	1027.5	1073.0
155°	428.4	536.9	828.0	997.9	1050.0
157.5°	448.8	534.4	783.1	943.8	1000.7
160°	459.5	531.1	754.7	904.6	954.5
162.5°	470.1	529.6	729.9	853.3	911.9
165°	486.1	531.7	668.2	786.6	823.5
167.5°	496.8	529.8	610.4	707.5	759.6
170°	503.9	529.9	574.9	646.9	690.3
172.5°	509.2	521.4	553.6	591.6	621.1
175°	515.0	521.5	530.5	539.7	550.5
177.5°	516.8	520.2	513.2	511.5	515.0
180°	515.0	515.0	515.0	515.0	515.0



TEST NUMBER: P1438872
 CATALOG NUMBER: CB2-B-030U-085D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.09	21.13	20.87	21.93	22.91	18.99	20.03	19.77	20.83	21.81
	3H	21.75	22.68	22.54	23.49	24.50	20.53	21.46	21.33	22.28	23.29
	4H	22.39	23.27	23.20	24.09	25.11	21.11	21.99	21.93	22.81	23.83
	6H	22.80	23.61	23.62	24.44	25.47	21.49	22.31	22.32	23.13	24.17
	8H	22.95	23.72	23.79	24.57	25.61	21.64	22.41	22.47	23.26	24.29
	12H	23.03	23.77	23.87	24.61	25.67	21.71	22.44	22.55	23.29	24.35
4H	2H	20.52	21.40	21.34	22.22	23.24	19.65	20.53	20.46	21.35	22.37
	3H	22.41	23.14	23.24	23.99	25.03	21.40	22.13	22.23	22.99	24.02
	4H	23.16	23.83	24.00	24.68	25.74	22.08	22.75	22.92	23.60	24.66
	6H	23.69	24.27	24.55	25.14	26.21	22.56	23.14	23.42	24.02	25.09
	8H	23.90	24.44	24.76	25.31	26.39	22.76	23.30	23.62	24.17	25.25
	12H	24.01	24.50	24.89	25.39	26.48	22.85	23.34	23.73	24.23	25.32
8H	4H	23.33	23.87	24.19	24.74	25.82	22.37	22.91	23.23	23.78	24.86
	6H	23.98	24.42	24.87	25.34	26.42	22.98	23.42	23.87	24.34	25.42
	8H	24.27	24.67	25.17	25.57	26.67	23.25	23.65	24.15	24.56	25.66
	12H	24.45	24.80	25.36	25.70	26.85	23.41	23.76	24.31	24.66	25.81
12H	4H	23.32	23.80	24.20	24.70	25.78	22.38	22.86	23.26	23.75	24.84
	6H	24.01	24.40	24.91	25.31	26.41	23.04	23.44	23.94	24.35	25.44
	8H	24.33	24.68	25.24	25.58	26.73	23.36	23.70	24.26	24.60	25.75