

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438960

Luminaire Tested: CB2-B-125U-055D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438960
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-125U-055D-940-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19637.5 lumens
Efficiency: N/A
Efficacy: 148.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 132.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438960

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438960

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	17911	17939	18064
10°	17810	17767	17753
15°	17528	17413	17270
20°	17252	16869	16633
25°	16789	16315	15858
30°	16324	15605	15013
35°	15789	14876	14167
40°	15222	14192	13362
45°	14652	13479	12578
50°	14138	12783	11814
55°	13505	12058	11093
60°	12781	11370	10374
65°	12012	10604	9656
70°	11163	9747	8736
75°	10155	8819	7911
80°	9082	7728	7167
85°	6984	6345	5236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14652 cd/sqm



TEST NUMBER: P1438960

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.1	1.0
10°-20°	543.8	2.8
20°-30°	781.9	4.0
30°-40°	878.8	4.5
40°-50°	848.9	4.3
50°-60°	717.2	3.7
60°-70°	515.2	2.6
70°-80°	281.6	1.4
80°-90°	74.8	0.4
90°-100°	168.8	0.9
100°-110°	1045.1	5.3
110°-120°	2635.7	13.4
120°-130°	3168.4	16.1
130°-140°	2872.7	14.6
140°-150°	2290.7	11.7
150°-160°	1562.6	8.0
160°-170°	826.4	4.2
170°-180°	230.0	1.2
0°-30°	1520.7	7.7
0°-40°	2399.5	12.2
0°-60°	3965.6	20.2
0°-90°	4837.1	24.6
90°-120°	3849.6	19.6
90°-150°	12181.4	62.0
90°-180°	14800.0	75.4
0°-180°	19637.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2074	2074	2074	2074	2074	
5°	2049	2077	2052	2052	2066	195
15°	1944	1961	1931	1912	1916	548
25°	1747	1749	1698	1660	1650	804
35°	1485	1468	1399	1345	1333	928
45°	1190	1165	1094	1037	1021	919
55°	890	857	794	745	731	795
65°	583	561	515	478	469	578
75°	302	283	262	241	235	323
85°	70	65	64	56	52	83
90°	0	0	0	0	0	6
95°	87	220	68	48	48	111
105°	427	1196	1728	434	291	449
115°	738	1630	3942	3670	2796	724
125°	961	1977	4301	4894	4922	860
135°	1204	2191	4311	5047	5418	936
145°	1544	2303	4068	4903	5340	965
155°	1874	2348	3621	4364	4592	862
165°	2126	2326	2922	3441	3602	597
175°	2252	2281	2320	2360	2408	213
180°	2252	2252	2252	2252	2252	

TEST NUMBER: P1438960

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2074.3	2074.3	2074.3	2074.3	2074.3
2.5°	2060.4	2085.2	2066.7	2069.4	2073.1
5°	2048.9	2076.9	2052.1	2052.4	2066.4
7.5°	2034.3	2060.7	2029.6	2023.8	2036.9
10°	2014.0	2040.4	2009.2	1998.3	2007.6
12.5°	1987.3	2012.5	1982.5	1965.3	1973.3
15°	1944.1	1961.2	1931.4	1912.4	1915.5
17.5°	1897.1	1907.7	1864.7	1848.7	1845.6
20°	1861.5	1870.8	1820.2	1797.9	1794.8
22.5°	1815.8	1823.8	1770.7	1743.2	1738.9
25°	1747.2	1748.7	1697.9	1659.6	1650.3
27.5°	1675.4	1670.4	1614.1	1568.7	1556.6
30°	1623.3	1617.1	1551.8	1503.9	1493.0
32.5°	1567.4	1556.2	1490.8	1439.1	1428.2
35°	1485.1	1468.0	1399.3	1345.0	1332.6
37.5°	1397.4	1378.1	1310.7	1251.6	1237.6
40°	1339.0	1317.2	1248.4	1189.3	1175.4
42.5°	1280.5	1256.3	1186.2	1127.0	1111.8
45°	1189.7	1164.8	1094.4	1036.8	1021.3
47.5°	1103.2	1071.6	1003.2	946.0	930.4
50°	1043.5	1009.4	943.5	887.5	872.0
52.5°	982.5	947.1	883.7	830.3	814.8
55°	889.5	856.8	794.2	744.6	730.6
57.5°	797.3	766.0	708.7	661.4	647.7
60°	733.8	707.4	652.8	608.0	595.6
62.5°	672.8	648.9	596.9	555.9	543.5
65°	582.9	561.2	514.6	477.9	468.6
67.5°	495.6	473.8	436.2	403.2	392.6
70°	438.4	416.6	382.8	352.4	343.1
72.5°	383.7	360.8	333.2	305.4	298.6
75°	301.8	283.1	262.1	241.3	235.1
77.5°	229.4	211.3	196.0	181.4	179.8
80°	181.1	165.5	154.1	144.5	142.9
82.5°	135.3	123.5	115.9	109.0	108.6
85°	69.9	65.2	63.5	55.5	52.4
87.5°	20.3	20.3	17.8	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	23.3	38.5	15.5	15.5	15.5
95°	87.4	220.3	68.0	48.5	48.5
97.5°	182.5	528.1	367.0	98.7	85.4
100°	252.4	765.1	631.1	145.0	116.5
102.5°	322.3	971.7	996.1	229.9	178.6
105°	427.2	1196.1	1728.2	433.7	291.3
107.5°	530.1	1342.7	2648.6	894.9	539.8
110°	592.2	1427.6	3339.8	1395.1	835.0



TEST NUMBER: P1438960

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	654.4	1512.6	3720.4	2236.3	1440.8
115°	737.9	1630.2	3941.8	3669.5	2796.2
117.5°	807.8	1738.1	4132.1	4537.9	4281.6
120°	854.4	1822.7	4233.1	4662.2	4747.6
122.5°	901.0	1884.5	4287.4	4710.5	4871.9
125°	961.2	1976.9	4301.0	4893.9	4922.4
127.5°	1021.4	2046.6	4365.1	5062.5	5075.8
130°	1068.0	2093.2	4427.2	5118.9	5223.4
132.5°	1122.3	2132.4	4450.5	5151.2	5308.8
135°	1203.9	2191.2	4310.7	5047.3	5417.5
137.5°	1306.8	2233.3	4176.8	5044.3	5283.6
140°	1368.9	2242.3	4106.8	5155.8	5174.8
142.5°	1438.9	2266.7	4091.3	5143.6	5306.9
145°	1543.7	2303.2	4068.0	4903.2	5339.9
147.5°	1648.6	2326.4	3978.7	4637.9	5019.5
150°	1718.5	2335.5	3893.3	4549.1	4786.5
152.5°	1788.4	2344.7	3784.5	4493.9	4693.3
155°	1873.8	2348.5	3621.4	4364.5	4592.3
157.5°	1963.1	2337.2	3425.3	4128.0	4376.8
160°	2009.7	2323.0	3301.0	3956.5	4174.8
162.5°	2056.3	2316.4	3192.3	3732.1	3988.4
165°	2126.2	2325.6	2922.4	3440.6	3602.0
167.5°	2172.8	2317.1	2669.9	3094.5	3322.4
170°	2203.9	2317.8	2514.6	2829.6	3019.5
172.5°	2227.2	2280.4	2421.4	2587.4	2716.5
175°	2252.5	2280.9	2320.4	2360.3	2407.8
177.5°	2260.2	2275.4	2244.7	2237.3	2252.5
180°	2252.5	2252.5	2252.5	2252.5	2252.5



TEST NUMBER: P1438960
 CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.04	14.71	15.19	15.85	17.44	12.94	13.61	14.09	14.75	16.34
	3H	15.67	16.27	16.83	17.42	19.02	14.46	15.05	15.61	16.20	17.81
	4H	16.29	16.86	17.46	18.01	19.62	15.02	15.59	16.19	16.73	18.35
	6H	16.69	17.21	17.86	18.35	19.98	15.38	15.90	16.56	17.05	18.68
	8H	16.83	17.32	18.00	18.49	20.10	15.52	16.01	16.69	17.17	18.79
	12H	16.90	17.37	18.08	18.52	20.16	15.57	16.04	16.75	17.20	18.84
4H	2H	14.43	15.00	15.60	16.14	17.75	13.55	14.12	14.73	15.27	16.88
	3H	16.28	16.75	17.46	17.92	19.55	15.27	15.74	16.45	16.91	18.54
	4H	17.02	17.45	18.20	18.61	20.26	15.94	16.37	17.12	17.53	19.17
	6H	17.53	17.90	18.71	19.08	20.71	16.40	16.77	17.59	17.95	19.59
	8H	17.73	18.07	18.91	19.25	20.90	16.59	16.93	17.77	18.11	19.76
	12H	17.82	18.14	19.02	19.32	20.98	16.67	16.98	17.86	18.16	19.82
8H	4H	17.16	17.51	18.34	18.68	20.33	16.20	16.54	17.38	17.72	19.37
	6H	17.79	18.08	19.00	19.29	20.94	16.79	17.08	17.99	18.29	19.94
	8H	18.08	18.33	19.29	19.52	21.19	17.06	17.31	18.27	18.51	20.17
	12H	18.25	18.47	19.46	19.66	21.35	17.21	17.42	18.42	18.61	20.31
12H	4H	17.13	17.44	18.33	18.63	20.28	16.19	16.50	17.39	17.69	19.34
	6H	17.82	18.07	19.03	19.26	20.93	16.85	17.10	18.06	18.29	19.96
	8H	18.13	18.35	19.34	19.54	21.24	17.15	17.37	18.36	18.56	20.26