

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438984

Luminaire Tested: CB2-D-030U-030D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438984
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-030U-030D-940-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5059.6 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438984

CATALOG NUMBER: CB2-D-030U-030D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438984

CATALOG NUMBER: CB2-D-030U-030D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																				
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43																				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	41	36																				
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	31																				
4	75	64	56	50	69	59	53	47	51	46	41	43	39	36	35	32	30	26																				
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23																				
6	63	51	43	38	58	48	41	35	41	36	31	35	31	27	29	26	23	20																				
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18																				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16																				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15																				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9456	9456	9456
5°	9376	9391	9456
10°	9322	9301	9293
15°	9175	9115	9040
20°	9030	8830	8707
25°	8788	8540	8300
30°	8545	8168	7859
35°	8265	7787	7416
40°	7968	7429	6995
45°	7669	7056	6584
50°	7400	6691	6185
55°	7069	6312	5808
60°	6690	5952	5431
65°	6287	5551	5055
70°	5844	5103	4573
75°	5316	4616	4142
80°	4754	4042	3751
85°	3657	3327	2738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7669 cd/sqm



TEST NUMBER: P1438984

CATALOG NUMBER: CB2-D-030U-030D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	2.0
10°-20°	284.6	5.6
20°-30°	409.3	8.1
30°-40°	460.0	9.1
40°-50°	444.4	8.8
50°-60°	375.5	7.4
60°-70°	269.7	5.3
70°-80°	147.4	2.9
80°-90°	39.2	0.8
90°-100°	38.3	0.8
100°-110°	157.9	3.1
110°-120°	286.6	5.7
120°-130°	390.0	7.7
130°-140°	450.3	8.9
140°-150°	453.7	9.0
150°-160°	391.6	7.7
160°-170°	265.4	5.2
170°-180°	93.6	1.9
0°-30°	796.0	15.7
0°-40°	1256.0	24.8
0°-60°	2075.8	41.0
0°-90°	2532.1	50.0
90°-120°	482.8	9.5
90°-150°	1776.9	35.1
90°-180°	2527.0	49.9
0°-180°	5059.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1072	1087	1074	1074	1082	102
15°	1018	1027	1011	1001	1003	287
25°	915	915	889	869	864	421
35°	777	768	732	704	698	486
45°	623	610	573	543	535	481
55°	466	448	416	390	382	416
65°	305	294	269	250	245	303
75°	158	148	137	126	123	169
85°	37	34	33	29	27	44
90°	0	0	1	0	1	3
95°	37	33	31	24	24	43
105°	156	154	150	141	140	166
115°	297	296	291	282	281	293
125°	441	446	437	428	428	394
135°	588	595	585	574	578	453
145°	729	737	726	718	723	455
155°	853	861	849	844	850	392
165°	942	952	940	935	943	265
175°	987	998	985	979	981	94
180°	991	991	991	991	991	



TEST NUMBER: P1438984

CATALOG NUMBER: CB2-D-030U-030D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1085.8	1085.8	1085.8	1085.8	1085.8
2.5°	1078.5	1091.5	1081.8	1083.2	1085.2
5°	1072.5	1087.2	1074.2	1074.4	1081.7
7.5°	1064.9	1078.7	1062.4	1059.4	1066.2
10°	1054.2	1068.1	1051.8	1046.0	1050.9
12.5°	1040.3	1053.4	1037.8	1028.7	1033.0
15°	1017.7	1026.6	1011.0	1001.1	1002.7
17.5°	993.1	998.6	976.1	967.7	966.1
20°	974.4	979.3	952.8	941.1	939.5
22.5°	950.5	954.7	926.9	912.5	910.2
25°	914.6	915.4	888.8	868.7	863.8
27.5°	877.0	874.4	844.9	821.1	814.8
30°	849.7	846.5	812.3	787.2	781.5
32.5°	820.4	814.6	780.4	753.3	747.6
35°	777.4	768.4	732.5	704.1	697.6
37.5°	731.5	721.4	686.1	655.2	647.8
40°	700.9	689.5	653.5	622.6	615.3
42.5°	670.3	657.6	620.9	590.0	582.0
45°	622.7	609.7	572.9	542.7	534.6
47.5°	577.5	560.9	525.1	495.2	487.0
50°	546.2	528.4	493.9	464.6	456.5
52.5°	514.3	495.8	462.6	434.6	426.5
55°	465.6	448.5	415.7	389.8	382.5
57.5°	417.4	401.0	371.0	346.2	339.1
60°	384.1	370.3	341.7	318.3	311.8
62.5°	352.2	339.7	312.4	291.0	284.5
65°	305.1	293.8	269.4	250.1	245.3
67.5°	259.4	248.0	228.3	211.1	205.5
70°	229.5	218.1	200.4	184.5	179.6
72.5°	200.9	188.8	174.4	159.9	156.3
75°	158.0	148.2	137.2	126.3	123.1
77.5°	120.1	110.6	102.6	94.9	94.1
80°	94.8	86.7	80.6	75.6	74.8
82.5°	70.8	64.7	60.7	57.0	56.9
85°	36.6	34.1	33.3	29.1	27.4
87.5°	10.6	10.6	9.5	8.0	8.1
90°	0.0	0.0	0.8	0.0	0.8
92.5°	9.3	8.1	7.6	5.0	5.7
95°	37.1	32.6	30.9	24.0	24.0
97.5°	70.0	65.5	63.1	55.9	54.4
100°	93.5	89.0	86.6	78.8	77.3
102.5°	117.7	115.5	111.3	102.9	101.4
105°	156.2	153.9	150.0	141.4	139.9
107.5°	195.7	196.2	190.3	183.3	181.2
110°	224.2	223.4	218.8	211.8	210.3

TEST NUMBER: P1438984

CATALOG NUMBER: CB2-D-030U-030D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	253.2	251.9	247.2	240.2	238.7
115°	296.8	296.1	290.7	282.1	281.4
117.5°	338.3	340.7	334.3	325.3	325.0
120°	368.0	371.0	363.3	355.6	354.0
122.5°	397.0	400.7	393.0	384.0	384.3
125°	441.4	445.9	436.8	427.5	428.3
127.5°	484.2	489.8	481.3	471.9	472.8
130°	513.3	520.1	511.0	501.0	502.5
132.5°	543.0	549.8	540.7	530.0	532.8
135°	588.3	595.1	585.2	574.4	578.2
137.5°	630.9	637.7	626.9	617.9	622.4
140°	659.4	666.2	654.8	646.4	650.9
142.5°	687.2	695.2	683.2	674.2	680.0
145°	729.0	737.3	725.9	717.5	722.8
147.5°	768.5	776.9	765.3	757.2	762.7
150°	793.9	802.2	790.0	783.2	789.3
152.5°	817.4	826.9	814.2	807.4	815.2
155°	852.6	861.0	848.8	843.5	850.3
157.5°	883.3	892.9	880.8	876.3	881.7
160°	903.7	912.7	900.6	896.1	902.1
162.5°	919.1	928.8	917.3	912.2	919.4
165°	942.3	952.1	940.0	934.8	943.1
167.5°	960.6	971.0	958.7	953.3	961.8
170°	971.7	981.5	968.6	962.6	971.7
172.5°	979.1	989.5	976.0	970.0	976.0
175°	987.2	997.7	984.8	978.7	981.0
177.5°	991.0	999.5	989.2	983.8	991.0
180°	991.0	991.0	991.0	991.0	991.0

TEST NUMBER: P1438984
 CATALOG NUMBER: CB2-D-030U-030D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.81	15.66	15.77	16.63	17.91	13.71	14.56	14.67	15.53	16.81
	3H	16.46	17.22	17.43	18.20	19.49	15.24	16.00	16.21	16.98	18.28
	4H	17.08	17.80	18.07	18.79	20.09	15.81	16.53	16.80	17.52	18.82
	6H	17.49	18.15	18.48	19.14	20.46	16.18	16.85	17.18	17.84	19.15
	8H	17.63	18.27	18.63	19.27	20.58	16.32	16.95	17.32	17.96	19.27
	12H	17.71	18.31	18.71	19.31	20.65	16.38	16.99	17.39	17.99	19.32
4H	2H	15.22	15.94	16.21	16.93	18.23	14.34	15.07	15.33	16.05	17.35
	3H	17.09	17.69	18.09	18.70	20.02	16.08	16.68	17.08	17.69	19.01
	4H	17.83	18.38	18.84	19.39	20.73	16.75	17.30	17.76	18.31	19.65
	6H	18.35	18.82	19.37	19.86	21.19	17.23	17.70	18.24	18.73	20.07
	8H	18.56	19.00	19.58	20.02	21.37	17.42	17.86	18.44	18.88	20.23
	12H	18.66	19.06	19.70	20.10	21.46	17.50	17.90	18.54	18.94	20.30
8H	4H	17.99	18.43	19.01	19.45	20.81	17.02	17.47	18.04	18.49	19.84
	6H	18.63	18.99	19.67	20.06	21.41	17.63	17.99	18.67	19.06	20.41
	8H	18.92	19.24	19.97	20.29	21.66	17.90	18.22	18.95	19.28	20.64
	12H	19.09	19.38	20.15	20.42	21.83	18.05	18.33	19.11	19.38	20.79
12H	4H	17.97	18.37	19.01	19.41	20.76	17.03	17.43	18.07	18.47	19.82
	6H	18.66	18.98	19.71	20.03	21.40	17.69	18.01	18.74	19.06	20.43
	8H	18.98	19.26	20.03	20.30	21.71	18.00	18.28	19.05	19.32	20.74