

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438992

Luminaire Tested: CB2-D-030U-055D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438992  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-D-030U-055D-940-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 550 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7364.6 lumens  
Efficiency: N/A  
Efficacy: 134.1 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 54.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438992

CATALOG NUMBER: CB2-D-030U-055D-940-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1438992

CATALOG NUMBER: CB2-D-030U-055D-940-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18064	18064	18064
5°	17911	17939	18064
10°	17810	17767	17753
15°	17528	17413	17270
20°	17252	16869	16633
25°	16789	16315	15858
30°	16324	15605	15013
35°	15789	14876	14167
40°	15222	14192	13362
45°	14652	13479	12578
50°	14138	12783	11814
55°	13505	12058	11093
60°	12781	11370	10374
65°	12012	10604	9656
70°	11163	9747	8736
75°	10155	8819	7911
80°	9082	7728	7167
85°	6984	6345	5236

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14652 cd/sqm



TEST NUMBER: P1438992

CATALOG NUMBER: CB2-D-030U-055D-940-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.1	2.6
10°-20°	543.8	7.4
20°-30°	781.9	10.6
30°-40°	878.8	11.9
40°-50°	848.9	11.5
50°-60°	717.2	9.7
60°-70°	515.2	7.0
70°-80°	281.6	3.8
80°-90°	74.8	1.0
90°-100°	38.3	0.5
100°-110°	157.9	2.1
110°-120°	286.6	3.9
120°-130°	390.0	5.3
130°-140°	450.3	6.1
140°-150°	453.7	6.2
150°-160°	391.6	5.3
160°-170°	265.4	3.6
170°-180°	93.6	1.3
0°-30°	1520.7	20.6
0°-40°	2399.5	32.6
0°-60°	3965.6	53.8
0°-90°	4837.2	65.7
90°-120°	482.8	6.6
90°-150°	1776.9	24.1
90°-180°	2527.0	34.3
0°-180°	7364.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2074	2074	2074	2074	2074	
5°	2049	2077	2052	2052	2066	195
15°	1944	1961	1931	1912	1916	548
25°	1747	1749	1698	1660	1650	804
35°	1485	1468	1399	1345	1333	928
45°	1190	1165	1094	1037	1021	919
55°	890	857	794	745	731	795
65°	583	561	515	478	469	578
75°	302	283	262	241	235	323
85°	70	65	64	56	52	83
90°	0	0	1	0	1	4
95°	37	33	31	24	24	43
105°	156	154	150	141	140	166
115°	297	296	291	282	281	293
125°	441	446	437	428	428	394
135°	588	595	585	574	578	453
145°	729	737	726	718	723	455
155°	853	861	849	844	850	392
165°	942	952	940	935	943	265
175°	987	998	985	979	981	94
180°	991	991	991	991	991	

TEST NUMBER: P1438992

CATALOG NUMBER: CB2-D-030U-055D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2074.3	2074.3	2074.3	2074.3	2074.3
2.5°	2060.4	2085.2	2066.7	2069.4	2073.1
5°	2048.9	2076.9	2052.1	2052.4	2066.4
7.5°	2034.3	2060.7	2029.6	2023.8	2036.9
10°	2014.0	2040.4	2009.2	1998.3	2007.6
12.5°	1987.3	2012.5	1982.5	1965.3	1973.3
15°	1944.1	1961.2	1931.4	1912.4	1915.5
17.5°	1897.1	1907.7	1864.7	1848.7	1845.6
20°	1861.5	1870.8	1820.2	1797.9	1794.8
22.5°	1815.8	1823.8	1770.7	1743.2	1738.9
25°	1747.2	1748.7	1697.9	1659.6	1650.3
27.5°	1675.4	1670.4	1614.1	1568.7	1556.6
30°	1623.3	1617.1	1551.8	1503.9	1493.0
32.5°	1567.4	1556.2	1490.8	1439.1	1428.2
35°	1485.1	1468.0	1399.3	1345.0	1332.6
37.5°	1397.4	1378.1	1310.7	1251.6	1237.6
40°	1339.0	1317.2	1248.4	1189.3	1175.4
42.5°	1280.5	1256.3	1186.2	1127.0	1111.8
45°	1189.7	1164.8	1094.4	1036.8	1021.3
47.5°	1103.2	1071.6	1003.2	946.0	930.4
50°	1043.5	1009.4	943.5	887.5	872.0
52.5°	982.5	947.1	883.7	830.3	814.8
55°	889.5	856.8	794.2	744.6	730.6
57.5°	797.3	766.0	708.7	661.4	647.7
60°	733.8	707.4	652.8	608.0	595.6
62.5°	672.8	648.9	596.9	555.9	543.5
65°	582.9	561.2	514.6	477.9	468.6
67.5°	495.6	473.8	436.2	403.2	392.6
70°	438.4	416.6	382.8	352.4	343.1
72.5°	383.7	360.8	333.2	305.4	298.6
75°	301.8	283.1	262.1	241.3	235.1
77.5°	229.4	211.3	196.0	181.4	179.8
80°	181.1	165.5	154.1	144.5	142.9
82.5°	135.3	123.5	115.9	109.0	108.6
85°	69.9	65.2	63.5	55.5	52.4
87.5°	20.3	20.3	17.9	15.3	15.4
90°	0.0	0.0	0.8	0.0	0.8
92.5°	9.3	8.1	7.6	5.0	5.7
95°	37.1	32.6	30.9	24.0	24.0
97.5°	70.0	65.5	63.1	55.9	54.4
100°	93.5	89.0	86.6	78.8	77.3
102.5°	117.7	115.5	111.3	102.9	101.4
105°	156.2	153.9	150.0	141.4	139.9
107.5°	195.7	196.2	190.3	183.3	181.2
110°	224.2	223.4	218.8	211.8	210.3



TEST NUMBER: P1438992

CATALOG NUMBER: CB2-D-030U-055D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	253.2	251.9	247.2	240.2	238.7
115°	296.8	296.1	290.7	282.1	281.4
117.5°	338.3	340.7	334.3	325.3	325.0
120°	368.0	371.0	363.3	355.6	354.0
122.5°	397.0	400.7	393.0	384.0	384.3
125°	441.4	445.9	436.8	427.5	428.3
127.5°	484.2	489.8	481.3	471.9	472.8
130°	513.3	520.1	511.0	501.0	502.5
132.5°	543.0	549.8	540.7	530.0	532.8
135°	588.3	595.1	585.2	574.4	578.2
137.5°	630.9	637.7	626.9	617.9	622.4
140°	659.4	666.2	654.8	646.4	650.9
142.5°	687.2	695.2	683.2	674.2	680.0
145°	729.0	737.3	725.9	717.5	722.8
147.5°	768.5	776.9	765.3	757.2	762.7
150°	793.9	802.2	790.0	783.2	789.3
152.5°	817.4	826.9	814.2	807.4	815.2
155°	852.6	861.0	848.8	843.5	850.3
157.5°	883.3	892.9	880.8	876.3	881.7
160°	903.7	912.7	900.6	896.1	902.1
162.5°	919.1	928.8	917.3	912.2	919.4
165°	942.3	952.1	940.0	934.8	943.1
167.5°	960.6	971.0	958.7	953.3	961.8
170°	971.7	981.5	968.6	962.6	971.7
172.5°	979.1	989.5	976.0	970.0	976.0
175°	987.2	997.7	984.8	978.7	981.0
177.5°	991.0	999.5	989.2	983.8	991.0
180°	991.0	991.0	991.0	991.0	991.0



TEST NUMBER: P1438992  
 CATALOG NUMBER: CB2-D-030U-055D-940-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.39	19.40	19.21	20.23	21.26	17.30	18.30	18.11	19.13	20.16
	3H	20.05	20.95	20.88	21.80	22.85	18.83	19.74	19.66	20.58	21.64
	4H	20.69	21.54	21.53	22.39	23.46	19.41	20.26	20.26	21.11	22.18
	6H	21.10	21.88	21.95	22.74	23.82	19.79	20.58	20.65	21.44	22.52
	8H	21.25	22.00	22.11	22.87	23.95	19.94	20.68	20.80	21.56	22.64
	12H	21.33	22.04	22.20	22.91	24.02	20.00	20.72	20.87	21.59	22.69
4H	2H	18.82	19.67	19.67	20.52	21.59	17.95	18.80	18.79	19.65	20.72
	3H	20.70	21.41	21.56	22.30	23.38	19.69	20.40	20.55	21.29	22.37
	4H	21.46	22.10	22.33	22.98	24.09	20.37	21.02	21.24	21.90	23.01
	6H	21.98	22.54	22.87	23.45	24.56	20.86	21.42	21.74	22.32	23.43
	8H	22.19	22.71	23.08	23.61	24.74	21.05	21.57	21.94	22.47	23.60
	12H	22.30	22.77	23.21	23.69	24.82	21.15	21.61	22.05	22.53	23.67
8H	4H	21.62	22.14	22.51	23.04	24.17	20.66	21.18	21.55	22.08	23.21
	6H	22.27	22.70	23.19	23.64	24.77	21.27	21.70	22.19	22.64	23.77
	8H	22.56	22.94	23.49	23.88	25.02	21.55	21.93	22.47	22.86	24.00
	12H	22.74	23.08	23.67	24.00	25.20	21.70	22.04	22.63	22.96	24.16
12H	4H	21.61	22.08	22.52	23.00	24.13	20.67	21.14	21.58	22.06	23.19
	6H	22.30	22.68	23.23	23.62	24.76	21.33	21.72	22.26	22.65	23.79
	8H	22.62	22.96	23.55	23.89	25.08	21.65	21.98	22.57	22.91	24.10