

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439095

Luminaire Tested: CB2-D-125U-085D-940-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439095
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-125U-085D-940-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9219.0 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 67.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439095

CATALOG NUMBER: CB2-D-125U-085D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439095

CATALOG NUMBER: CB2-D-125U-085D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																				
1	96	91	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40	34																				
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34	29																				
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	25																				
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25	21																				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22	18																				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16																				
7	57	45	37	32	52	41	35	30	35	29	25	28	24	21	22	19	17	15																				
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	16	13																				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	15	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27573	27573	27573
5°	27340	27381	27574
10°	27185	27120	27099
15°	26754	26579	26361
20°	26333	25749	25389
25°	25625	24903	24205
30°	24917	23818	22917
35°	24099	22706	21624
40°	23235	21664	20395
45°	22363	20573	19198
50°	21580	19510	18033
55°	20613	18405	16932
60°	19507	17355	15836
65°	18336	16184	14738
70°	17039	14875	13332
75°	15498	13459	12073
80°	13862	11796	10943
85°	10652	9692	7994

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22363 cd/sqm



TEST NUMBER: P1439095

CATALOG NUMBER: CB2-D-125U-085D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	1.6
10°-20°	415.0	4.5
20°-30°	596.7	6.5
30°-40°	670.7	7.3
40°-50°	647.9	7.0
50°-60°	547.4	5.9
60°-70°	393.2	4.3
70°-80°	214.9	2.3
80°-90°	57.2	0.6
90°-100°	83.7	0.9
100°-110°	345.3	3.7
110°-120°	626.8	6.8
120°-130°	853.0	9.3
130°-140°	984.7	10.7
140°-150°	992.3	10.8
150°-160°	856.3	9.3
160°-170°	580.4	6.3
170°-180°	204.7	2.2
0°-30°	1160.6	12.6
0°-40°	1831.2	19.9
0°-60°	3026.5	32.8
0°-90°	3691.8	40.0
90°-120°	1055.9	11.5
90°-150°	3885.8	42.1
90°-180°	5527.0	60.0
0°-180°	9219.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1564	1585	1566	1566	1577	148
15°	1484	1497	1474	1460	1462	418
25°	1333	1335	1296	1267	1260	614
35°	1133	1120	1068	1026	1017	708
45°	908	889	835	791	779	701
55°	679	654	606	568	558	607
65°	445	428	393	365	358	441
75°	230	216	200	184	179	246
85°	53	50	48	42	40	63
90°	0	0	2	0	2	5
95°	81	71	68	52	52	94
105°	342	336	328	309	306	362
115°	649	648	636	617	615	641
125°	965	975	955	935	937	862
135°	1286	1301	1280	1256	1264	991
145°	1594	1612	1587	1569	1581	996
155°	1865	1883	1856	1845	1860	857
165°	2061	2082	2056	2044	2062	580
175°	2159	2182	2154	2140	2145	205
180°	2167	2167	2167	2167	2167	

TEST NUMBER: P1439095

CATALOG NUMBER: CB2-D-125U-085D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.1	1583.1	1583.1	1583.1	1583.1
2.5°	1572.5	1591.4	1577.3	1579.3	1582.1
5°	1563.7	1585.1	1566.1	1566.4	1577.1
7.5°	1552.6	1572.7	1548.9	1544.6	1554.5
10°	1537.1	1557.2	1533.4	1525.1	1532.2
12.5°	1516.7	1535.9	1513.1	1499.9	1506.0
15°	1483.7	1496.8	1474.0	1459.5	1461.9
17.5°	1447.8	1455.9	1423.1	1410.9	1408.6
20°	1420.7	1427.8	1389.2	1372.1	1369.8
22.5°	1385.8	1391.9	1351.3	1330.4	1327.1
25°	1333.4	1334.6	1295.8	1266.6	1259.5
27.5°	1278.6	1274.8	1231.8	1197.2	1187.9
30°	1238.9	1234.1	1184.3	1147.8	1139.5
32.5°	1196.2	1187.7	1137.8	1098.3	1090.0
35°	1133.4	1120.4	1067.9	1026.5	1017.0
37.5°	1066.5	1051.8	1000.3	955.2	944.5
40°	1021.9	1005.3	952.8	907.7	897.0
42.5°	977.3	958.8	905.3	860.1	848.5
45°	907.9	889.0	835.2	791.3	779.4
47.5°	842.0	817.8	765.6	722.0	710.1
50°	796.4	770.3	720.0	677.3	665.5
52.5°	749.9	722.8	674.5	633.7	621.9
55°	678.8	653.9	606.1	568.3	557.6
57.5°	608.5	584.6	540.9	504.8	494.3
60°	560.0	539.9	498.2	464.1	454.6
62.5°	513.5	495.2	455.5	424.3	414.8
65°	444.9	428.3	392.7	364.7	357.6
67.5°	378.2	361.6	332.9	307.7	299.7
70°	334.6	318.0	292.1	268.9	261.8
72.5°	292.9	275.3	254.3	233.1	227.9
75°	230.3	216.1	200.0	184.1	179.4
77.5°	175.0	161.3	149.6	138.4	137.2
80°	138.2	126.3	117.6	110.3	109.1
82.5°	103.3	94.3	88.5	83.2	82.9
85°	53.3	49.8	48.5	42.4	40.0
87.5°	15.5	15.5	13.9	11.6	12.0
90°	0.0	0.0	1.7	0.0	1.7
92.5°	20.3	17.6	16.6	10.9	12.5
95°	81.1	71.2	67.6	52.4	52.4
97.5°	153.2	143.2	137.9	122.3	119.0
100°	204.6	194.6	189.3	172.4	169.1
102.5°	257.3	252.7	243.4	225.1	221.8
105°	341.5	336.5	328.0	309.3	306.0
107.5°	428.0	429.0	416.2	400.9	396.3
110°	490.3	488.6	478.4	463.1	459.8



TEST NUMBER: P1439095

CATALOG NUMBER: CB2-D-125U-085D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	550.8	540.6	525.3	522.0
115°	649.2	647.5	635.6	617.0	615.4
117.5°	739.8	745.1	731.0	711.4	710.7
120°	804.7	811.3	794.6	777.6	774.3
122.5°	868.3	876.2	859.5	839.9	840.5
125°	965.3	975.2	955.2	934.9	936.6
127.5°	1059.0	1071.2	1052.5	1031.9	1033.9
130°	1122.5	1137.4	1117.4	1095.5	1098.8
132.5°	1187.4	1202.3	1182.4	1159.2	1165.1
135°	1286.5	1301.4	1279.7	1256.3	1264.5
137.5°	1379.8	1394.7	1371.0	1351.3	1361.2
140°	1442.0	1456.9	1431.9	1413.5	1423.4
142.5°	1502.9	1520.4	1494.1	1474.4	1487.0
145°	1594.2	1612.4	1587.4	1569.1	1580.7
147.5°	1680.7	1698.9	1673.6	1656.0	1667.9
150°	1736.2	1754.4	1727.7	1712.8	1726.0
152.5°	1787.6	1808.4	1780.5	1765.6	1782.8
155°	1864.7	1882.8	1856.2	1844.7	1859.6
157.5°	1931.6	1952.8	1926.2	1916.3	1928.2
160°	1976.2	1996.1	1969.5	1959.6	1972.9
162.5°	2010.0	2031.2	2006.0	1994.9	2010.7
165°	2060.8	2082.3	2055.7	2044.3	2062.5
167.5°	2100.7	2123.5	2096.6	2084.9	2103.4
170°	2125.0	2146.5	2118.2	2105.2	2125.0
172.5°	2141.2	2164.0	2134.5	2121.2	2134.5
175°	2158.8	2182.0	2153.7	2140.3	2145.3
177.5°	2167.3	2185.8	2163.2	2151.4	2167.3
180°	2167.3	2167.3	2167.3	2167.3	2167.3



TEST NUMBER: P1439095
 CATALOG NUMBER: CB2-D-125U-085D-940-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.53	18.30	18.57	19.34	20.75	16.43	17.20	17.47	18.24	19.65
	3H	19.16	19.85	20.21	20.91	22.33	17.95	18.64	19.00	19.69	21.12
	4H	19.79	20.44	20.85	21.50	22.93	18.52	19.17	19.58	20.23	21.66
	6H	20.19	20.79	21.26	21.85	23.29	18.88	19.48	19.95	20.54	21.99
	8H	20.33	20.90	21.41	21.98	23.42	19.02	19.59	20.10	20.67	22.11
	12H	20.40	20.95	21.48	22.02	23.48	19.08	19.62	20.16	20.69	22.16
4H	2H	17.92	18.58	18.99	19.63	21.07	17.05	17.70	18.12	18.76	20.19
	3H	19.79	20.33	20.86	21.41	22.86	18.78	19.32	19.85	20.40	21.85
	4H	20.53	21.03	21.61	22.10	23.57	19.45	19.95	20.53	21.02	22.49
	6H	21.04	21.47	22.13	22.57	24.03	19.92	20.34	21.01	21.44	22.90
	8H	21.24	21.64	22.33	22.73	24.21	20.10	20.50	21.19	21.59	23.07
	12H	21.35	21.71	22.45	22.81	24.29	20.19	20.55	21.30	21.65	23.13
8H	4H	20.68	21.08	21.77	22.17	23.64	19.71	20.11	20.80	21.20	22.68
	6H	21.31	21.64	22.43	22.78	24.25	20.31	20.64	21.43	21.77	23.25
	8H	21.60	21.89	22.72	23.01	24.50	20.59	20.88	21.71	21.99	23.48
	12H	21.77	22.03	22.90	23.14	24.67	20.73	20.99	21.86	22.10	23.63
12H	4H	20.65	21.01	21.76	22.12	23.60	19.71	20.07	20.82	21.18	22.66
	6H	21.34	21.63	22.46	22.75	24.24	20.38	20.66	21.49	21.78	23.27
	8H	21.66	21.91	22.78	23.02	24.55	20.68	20.93	21.80	22.04	23.57