

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438631

Luminaire Tested: CB2-030U-120D-840-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438631  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-030U-120D-840-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6070.8 lumens  
Efficiency: N/A  
Efficacy: 117.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 51.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438631

CATALOG NUMBER: CB2-030U-120D-840-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1438631

CATALOG NUMBER: CB2-030U-120D-840-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78				
1	104	100	96	92	99	96	92	89	87	85	82	80	78	76	73	71	70	66				
2	95	88	81	76	91	84	78	73	77	72	68	70	67	64	64	62	59	56				
3	87	77	70	64	83	74	67	62	68	63	58	63	58	54	57	54	51	48				
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	51	47	44	41				
5	74	62	53	47	70	59	52	46	55	48	43	51	45	41	47	42	39	36				
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34	32				
7	63	50	42	36	60	49	41	36	45	39	34	42	36	32	39	34	31	28				
8	59	46	38	33	56	44	37	32	41	35	30	39	33	29	36	31	27	25				
9	55	42	35	29	52	41	34	29	38	32	27	36	30	26	33	28	25	23				
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	35368	35368	35368
5°	35067	35122	35366
10°	34868	34785	34758
15°	34316	34091	33811
20°	33775	33026	32564
25°	32868	31942	31045
30°	31958	30550	29393
35°	30910	29126	27737
40°	29801	27787	26161
45°	28686	26388	24624
50°	27679	25026	23130
55°	26440	23607	21718
60°	25022	22259	20312
65°	23516	20763	18904
70°	21852	19082	17101
75°	19879	17261	15485
80°	17774	15126	14032
85°	13669	12430	10252

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28686 cd/sqm



TEST NUMBER: P1438631

CATALOG NUMBER: CB2-030U-120D-840-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.0	3.1
10°-20°	532.3	8.8
20°-30°	765.4	12.6
30°-40°	860.2	14.2
40°-50°	831.0	13.7
50°-60°	702.1	11.6
60°-70°	504.3	8.3
70°-80°	275.6	4.5
80°-90°	73.2	1.2
90°-100°	8.2	0.1
100°-110°	52.0	0.9
110°-120°	165.1	2.7
120°-130°	239.6	3.9
130°-140°	257.6	4.2
140°-150°	242.6	4.0
150°-160°	197.6	3.3
160°-170°	128.6	2.1
170°-180°	44.5	0.7
0°-30°	1488.6	24.5
0°-40°	2348.8	38.7
0°-60°	3881.9	63.9
0°-90°	4735.1	78.0
90°-120°	225.2	3.7
90°-150°	965.0	15.9
90°-180°	1336.0	22.0
0°-180°	6070.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2031	2031	2031	2031	2031	
5°	2006	2033	2009	2009	2023	190
15°	1903	1920	1891	1872	1875	536
25°	1710	1712	1662	1625	1615	787
35°	1454	1437	1370	1317	1304	908
45°	1165	1140	1071	1015	1000	900
55°	871	839	777	729	715	778
65°	571	549	504	468	459	566
75°	295	277	256	236	230	316
85°	68	64	62	54	51	81
90°	0	0	0	0	0	3
95°	19	5	6	4	3	24
105°	98	101	10	12	12	103
115°	185	189	190	193	110	181
125°	262	267	267	271	275	234
135°	330	334	333	335	340	254
145°	386	389	386	387	392	241
155°	429	432	427	426	432	198
165°	457	459	454	452	457	129
175°	471	472	466	463	465	45
180°	468	468	468	468	468	

TEST NUMBER: P1438631

CATALOG NUMBER: CB2-030U-120D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2030.6	2030.6	2030.6	2030.6	2030.6
2.5°	2016.9	2041.2	2023.1	2025.7	2029.3
5°	2005.7	2033.1	2008.8	2009.1	2022.8
7.5°	1991.4	2017.2	1986.7	1981.1	1993.9
10°	1971.5	1997.3	1966.8	1956.2	1965.3
12.5°	1945.4	1970.0	1940.7	1923.8	1931.7
15°	1903.1	1919.8	1890.6	1872.1	1875.1
17.5°	1857.1	1867.4	1825.3	1809.7	1806.7
20°	1822.2	1831.4	1781.8	1760.0	1756.9
22.5°	1777.5	1785.4	1733.3	1706.5	1702.2
25°	1710.3	1711.8	1662.1	1624.6	1615.4
27.5°	1640.0	1635.1	1580.0	1535.6	1523.7
30°	1589.0	1582.9	1519.0	1472.2	1461.5
32.5°	1534.3	1523.3	1459.3	1408.7	1398.1
35°	1453.7	1437.0	1369.8	1316.6	1304.5
37.5°	1367.9	1349.1	1283.0	1225.2	1211.5
40°	1310.7	1289.4	1222.1	1164.2	1150.6
42.5°	1253.5	1229.8	1161.1	1103.3	1088.4
45°	1164.6	1140.2	1071.3	1014.9	999.7
47.5°	1080.0	1049.0	982.0	926.0	910.8
50°	1021.5	988.1	923.6	868.8	853.6
52.5°	961.8	927.1	865.1	812.8	797.6
55°	870.7	838.8	777.4	728.9	715.2
57.5°	780.5	749.8	693.8	647.4	634.1
60°	718.3	692.5	639.0	595.2	583.1
62.5°	658.6	635.2	584.3	544.2	532.1
65°	570.6	549.3	503.8	467.8	458.7
67.5°	485.1	463.8	427.0	394.7	384.3
70°	429.1	407.8	374.7	345.0	335.8
72.5°	375.6	353.1	326.2	299.0	292.3
75°	295.4	277.2	256.5	236.2	230.1
77.5°	224.5	206.9	191.9	177.5	176.0
80°	177.2	162.0	150.8	141.5	139.9
82.5°	132.5	120.9	113.5	106.7	106.3
85°	68.4	63.9	62.2	54.3	51.3
87.5°	19.9	19.9	17.4	15.0	15.0
90°	0.0	0.0	0.0	0.3	0.3
92.5°	5.1	2.0	1.4	2.0	2.0
95°	18.6	5.4	5.8	3.7	3.4
97.5°	38.7	8.7	8.3	9.2	9.5
100°	53.9	17.8	9.1	10.5	10.8
102.5°	70.7	66.9	9.4	11.3	11.9
105°	97.5	101.2	10.2	11.9	12.5
107.5°	124.0	127.6	47.3	12.3	12.9
110°	141.6	145.2	149.7	12.5	13.2



TEST NUMBER: P1438631

CATALOG NUMBER: CB2-030U-120D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	158.1	162.5	166.0	27.9	13.8
115°	184.6	188.6	190.4	192.6	110.4
117.5°	208.0	212.9	214.9	218.7	222.4
120°	224.2	228.9	230.3	234.1	238.1
122.5°	240.2	244.3	245.2	249.6	253.3
125°	262.2	266.8	266.9	271.4	275.0
127.5°	284.1	288.1	287.9	291.2	295.3
130°	298.7	301.4	301.5	304.3	308.6
132.5°	310.9	314.6	314.7	317.0	321.3
135°	329.9	333.9	333.3	335.4	339.7
137.5°	347.7	351.6	350.5	352.3	356.7
140°	359.4	362.7	361.1	362.9	367.8
142.5°	370.2	373.5	371.1	372.6	377.9
145°	386.1	389.1	386.5	386.9	391.9
147.5°	400.3	403.2	400.0	400.5	405.1
150°	409.5	412.2	408.1	408.6	413.2
152.5°	417.6	420.0	415.7	415.7	421.1
155°	428.8	431.5	426.8	425.9	431.9
157.5°	439.0	441.4	436.7	436.1	440.7
160°	445.7	447.4	442.7	441.8	446.4
162.5°	450.3	452.3	447.6	446.1	450.8
165°	457.3	458.6	453.9	451.9	456.6
167.5°	463.2	464.7	458.7	457.0	461.9
170°	466.7	467.7	461.7	459.4	464.4
172.5°	468.9	469.6	463.6	461.0	464.4
175°	470.8	471.8	465.7	462.7	465.0
177.5°	471.1	471.7	467.1	464.5	468.4
180°	468.4	468.4	468.4	468.4	468.4

TEST NUMBER: P1438631

CATALOG NUMBER: CB2-030U-120D-840-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.67	22.83	22.34	23.52	24.33	20.57	21.73	21.24	22.42	23.23
	3H	23.33	24.38	24.02	25.08	25.92	22.12	23.16	22.81	23.86	24.70
	4H	23.98	24.96	24.68	25.67	26.53	22.70	23.69	23.41	24.40	25.25
	6H	24.39	25.30	25.12	26.03	26.89	23.09	24.00	23.81	24.72	25.59
	8H	24.55	25.42	25.28	26.16	27.03	23.24	24.11	23.97	24.85	25.72
	12H	24.63	25.46	25.37	26.20	27.09	23.31	24.14	24.05	24.87	25.77
4H	2H	22.11	23.10	22.82	23.81	24.66	21.24	22.22	21.95	22.93	23.79
	3H	24.01	24.83	24.73	25.58	26.45	23.00	23.82	23.72	24.57	25.44
	4H	24.77	25.51	25.51	26.26	27.16	23.68	24.43	24.42	25.18	26.08
	6H	25.30	25.95	26.06	26.72	27.63	24.18	24.82	24.94	25.60	26.51
	8H	25.51	26.12	26.28	26.89	27.81	24.37	24.98	25.14	25.75	26.67
	12H	25.63	26.18	26.42	26.97	27.90	24.48	25.02	25.26	25.81	26.74
8H	4H	24.95	25.55	25.71	26.32	27.24	23.98	24.59	24.74	25.36	26.28
	6H	25.60	26.10	26.39	26.91	27.84	24.60	25.10	25.39	25.91	26.84
	8H	25.89	26.34	26.70	27.15	28.09	24.88	25.32	25.68	26.13	27.07
	12H	26.08	26.47	26.89	27.28	28.27	25.04	25.43	25.85	26.24	27.23
12H	4H	24.94	25.48	25.72	26.28	27.20	24.00	24.54	24.78	25.34	26.26
	6H	25.63	26.08	26.43	26.89	27.83	24.66	25.11	25.47	25.92	26.86
	8H	25.96	26.35	26.77	27.16	28.16	24.98	25.38	25.79	26.18	27.18