

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438856

Luminaire Tested: CB2-B-030U-030D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438856
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-030U-030D-940-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5915.9 lumens
Efficiency: N/A
Efficacy: 161.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438856

CATALOG NUMBER: CB2-B-030U-030D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438856

CATALOG NUMBER: CB2-B-030U-030D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	32	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	26	23
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	19	16	14
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9456	9456	9456
5°	9376	9391	9456
10°	9322	9301	9293
15°	9175	9115	9040
20°	9030	8830	8707
25°	8788	8540	8300
30°	8545	8168	7859
35°	8265	7787	7416
40°	7968	7429	6995
45°	7669	7056	6584
50°	7400	6691	6185
55°	7069	6312	5808
60°	6690	5952	5431
65°	6287	5551	5055
70°	5844	5103	4573
75°	5316	4616	4142
80°	4754	4042	3751
85°	3657	3327	2738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7669 cd/sqm



TEST NUMBER: P1438856

CATALOG NUMBER: CB2-B-030U-030D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	1.7
10°-20°	284.6	4.8
20°-30°	409.3	6.9
30°-40°	460.0	7.8
40°-50°	444.4	7.5
50°-60°	375.5	6.3
60°-70°	269.7	4.6
70°-80°	147.4	2.5
80°-90°	39.1	0.7
90°-100°	38.6	0.7
100°-110°	239.0	4.0
110°-120°	602.6	10.2
120°-130°	724.4	12.2
130°-140°	656.8	11.1
140°-150°	523.7	8.9
150°-160°	357.3	6.0
160°-170°	188.9	3.2
170°-180°	52.6	0.9
0°-30°	796.0	13.5
0°-40°	1256.0	21.2
0°-60°	2075.8	35.1
0°-90°	2532.1	42.8
90°-120°	880.1	14.9
90°-150°	2785.1	47.1
90°-180°	3384.0	57.2
0°-180°	5915.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1072	1087	1074	1074	1082	102
15°	1018	1027	1011	1001	1003	287
25°	915	915	889	869	864	421
35°	777	768	732	704	698	486
45°	623	610	573	543	535	481
55°	466	448	416	390	382	416
65°	305	294	269	250	245	303
75°	158	148	137	126	123	169
85°	37	34	33	29	27	44
90°	0	0	0	0	0	2
95°	20	50	16	11	11	25
105°	98	274	395	99	67	103
115°	169	373	901	839	639	165
125°	220	452	983	1119	1125	197
135°	275	501	986	1154	1239	214
145°	353	527	930	1121	1221	221
155°	428	537	828	998	1050	197
165°	486	532	668	787	824	136
175°	515	522	530	540	550	49
180°	515	515	515	515	515	

TEST NUMBER: P1438856

CATALOG NUMBER: CB2-B-030U-030D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1085.8	1085.8	1085.8	1085.8	1085.8
2.5°	1078.5	1091.5	1081.8	1083.2	1085.2
5°	1072.5	1087.2	1074.2	1074.4	1081.7
7.5°	1064.9	1078.7	1062.4	1059.4	1066.2
10°	1054.2	1068.1	1051.8	1046.0	1050.9
12.5°	1040.3	1053.4	1037.8	1028.7	1033.0
15°	1017.7	1026.6	1011.0	1001.1	1002.7
17.5°	993.1	998.6	976.1	967.7	966.1
20°	974.4	979.3	952.8	941.1	939.5
22.5°	950.5	954.7	926.9	912.5	910.2
25°	914.6	915.4	888.8	868.7	863.8
27.5°	877.0	874.4	844.9	821.1	814.8
30°	849.7	846.5	812.3	787.2	781.5
32.5°	820.4	814.6	780.4	753.3	747.6
35°	777.4	768.4	732.5	704.1	697.6
37.5°	731.5	721.4	686.1	655.2	647.8
40°	700.9	689.5	653.5	622.6	615.3
42.5°	670.3	657.6	620.9	590.0	582.0
45°	622.7	609.7	572.9	542.7	534.6
47.5°	577.5	560.9	525.1	495.2	487.0
50°	546.2	528.4	493.9	464.6	456.5
52.5°	514.3	495.8	462.6	434.6	426.5
55°	465.6	448.5	415.7	389.8	382.5
57.5°	417.4	401.0	371.0	346.2	339.1
60°	384.1	370.3	341.7	318.3	311.8
62.5°	352.2	339.7	312.4	291.0	284.5
65°	305.1	293.8	269.4	250.1	245.3
67.5°	259.4	248.0	228.3	211.1	205.5
70°	229.5	218.1	200.4	184.5	179.6
72.5°	200.9	188.8	174.4	159.9	156.3
75°	158.0	148.2	137.2	126.3	123.1
77.5°	120.1	110.6	102.6	94.9	94.1
80°	94.8	86.7	80.6	75.6	74.8
82.5°	70.8	64.7	60.7	57.0	56.9
85°	36.6	34.1	33.3	29.1	27.4
87.5°	10.6	10.6	9.3	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.3	8.8	3.6	3.6	3.6
95°	20.0	50.4	15.5	11.1	11.1
97.5°	41.7	120.7	83.9	22.6	19.5
100°	57.7	174.9	144.3	33.1	26.6
102.5°	73.7	222.2	227.7	52.6	40.8
105°	97.7	273.5	395.1	99.1	66.6
107.5°	121.2	307.0	605.6	204.6	123.4
110°	135.4	326.4	763.6	319.0	190.9



TEST NUMBER: P1438856

CATALOG NUMBER: CB2-B-030U-030D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	149.6	345.8	850.6	511.3	329.4
115°	168.7	372.7	901.2	839.0	639.3
117.5°	184.7	397.4	944.7	1037.5	978.9
120°	195.3	416.7	967.8	1065.9	1085.5
122.5°	206.0	430.9	980.3	1077.0	1113.9
125°	219.8	452.0	983.4	1118.9	1125.4
127.5°	233.5	467.9	998.0	1157.5	1160.5
130°	244.2	478.6	1012.2	1170.4	1194.2
132.5°	256.6	487.5	1017.5	1177.7	1213.8
135°	275.3	501.0	985.6	1154.0	1238.6
137.5°	298.8	510.6	954.9	1153.3	1208.0
140°	313.0	512.7	939.0	1178.8	1183.1
142.5°	329.0	518.2	935.4	1176.0	1213.3
145°	352.9	526.6	930.1	1121.0	1220.9
147.5°	376.9	531.9	909.7	1060.4	1147.6
150°	392.9	534.0	890.1	1040.1	1094.3
152.5°	408.9	536.1	865.3	1027.5	1073.0
155°	428.4	536.9	828.0	997.9	1050.0
157.5°	448.8	534.4	783.1	943.8	1000.7
160°	459.5	531.1	754.7	904.6	954.5
162.5°	470.1	529.6	729.9	853.3	911.9
165°	486.1	531.7	668.2	786.6	823.5
167.5°	496.8	529.8	610.4	707.5	759.6
170°	503.9	529.9	574.9	646.9	690.3
172.5°	509.2	521.4	553.6	591.6	621.1
175°	515.0	521.5	530.5	539.7	550.5
177.5°	516.8	520.2	513.2	511.5	515.0
180°	515.0	515.0	515.0	515.0	515.0



TEST NUMBER: P1438856
 CATALOG NUMBER: CB2-B-030U-030D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.10	14.89	15.12	15.92	17.29	13.00	13.79	14.02	14.82	16.19
	3H	15.74	16.45	16.77	17.48	18.88	14.52	15.23	15.55	16.27	17.66
	4H	16.37	17.04	17.41	18.07	19.47	15.09	15.76	16.13	16.80	18.20
	6H	16.77	17.38	17.82	18.42	19.84	15.46	16.08	16.51	17.12	18.53
	8H	16.91	17.50	17.97	18.56	19.96	15.60	16.19	16.66	17.25	18.65
	12H	16.98	17.54	18.04	18.59	20.02	15.66	16.22	16.72	17.27	18.70
4H	2H	14.50	15.17	15.55	16.21	17.61	13.63	14.30	14.67	15.34	16.73
	3H	16.36	16.92	17.42	17.99	19.40	15.36	15.91	16.41	16.98	18.39
	4H	17.11	17.62	18.17	18.68	20.11	16.03	16.54	17.09	17.60	19.03
	6H	17.62	18.06	18.69	19.14	20.57	16.50	16.94	17.57	18.02	19.45
	8H	17.83	18.24	18.90	19.31	20.75	16.69	17.10	17.76	18.17	19.61
	12H	17.93	18.30	19.02	19.39	20.84	16.77	17.14	17.86	18.23	19.68
8H	4H	17.26	17.67	18.33	18.74	20.19	16.29	16.71	17.37	17.78	19.22
	6H	17.90	18.24	18.99	19.35	20.79	16.90	17.23	17.99	18.35	19.79
	8H	18.19	18.48	19.29	19.58	21.04	17.17	17.47	18.27	18.56	20.03
	12H	18.36	18.62	19.46	19.71	21.21	17.32	17.58	18.42	18.67	20.17
12H	4H	17.23	17.61	18.32	18.69	20.14	16.29	16.67	17.38	17.75	19.20
	6H	17.93	18.22	19.03	19.32	20.78	16.96	17.26	18.06	18.35	19.81
	8H	18.24	18.50	19.34	19.59	21.09	17.26	17.52	18.37	18.61	20.11