

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438888

Luminaire Tested: CB2-B-055U-030D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438888
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-055U-030D-940-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9064.7 lumens
Efficiency: N/A
Efficacy: 161.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438888

CATALOG NUMBER: CB2-B-055U-030D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438888

CATALOG NUMBER: CB2-B-055U-030D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	76	74	62	60	58	46	45	44	32	31	30	24
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	45	35	29	24	28	24	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9456	9456	9456
5°	9376	9391	9456
10°	9322	9301	9293
15°	9175	9115	9040
20°	9030	8830	8707
25°	8788	8540	8300
30°	8545	8168	7859
35°	8265	7787	7416
40°	7968	7429	6995
45°	7669	7056	6584
50°	7400	6691	6185
55°	7069	6312	5808
60°	6690	5952	5431
65°	6287	5551	5055
70°	5844	5103	4573
75°	5316	4616	4142
80°	4754	4042	3751
85°	3657	3327	2738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7669 cd/sqm



TEST NUMBER: P1438888

CATALOG NUMBER: CB2-B-055U-030D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	1.1
10°-20°	284.6	3.1
20°-30°	409.3	4.5
30°-40°	460.0	5.1
40°-50°	444.4	4.9
50°-60°	375.5	4.1
60°-70°	269.7	3.0
70°-80°	147.4	1.6
80°-90°	39.1	0.4
90°-100°	74.5	0.8
100°-110°	461.3	5.1
110°-120°	1163.3	12.8
120°-130°	1398.5	15.4
130°-140°	1267.9	14.0
140°-150°	1011.1	11.2
150°-160°	689.7	7.6
160°-170°	364.8	4.0
170°-180°	101.5	1.1
0°-30°	796.0	8.8
0°-40°	1256.0	13.9
0°-60°	2075.8	22.9
0°-90°	2532.1	27.9
90°-120°	1699.1	18.7
90°-150°	5376.6	59.3
90°-180°	6533.0	72.1
0°-180°	9064.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1072	1087	1074	1074	1082	102
15°	1018	1027	1011	1001	1003	287
25°	915	915	889	869	864	421
35°	777	768	732	704	698	486
45°	623	610	573	543	535	481
55°	466	448	416	390	382	416
65°	305	294	269	250	245	303
75°	158	148	137	126	123	169
85°	37	34	33	29	27	44
90°	0	0	0	0	0	3
95°	39	97	30	21	21	49
105°	189	528	763	191	129	198
115°	326	720	1740	1620	1234	319
125°	424	873	1898	2160	2173	380
135°	531	967	1903	2228	2391	413
145°	681	1017	1796	2164	2357	426
155°	827	1037	1598	1926	2027	381
165°	938	1026	1290	1519	1590	263
175°	994	1007	1024	1042	1063	94
180°	994	994	994	994	994	

TEST NUMBER: P1438888

CATALOG NUMBER: CB2-B-055U-030D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1085.8	1085.8	1085.8	1085.8	1085.8
2.5°	1078.5	1091.5	1081.8	1083.2	1085.2
5°	1072.5	1087.2	1074.2	1074.4	1081.7
7.5°	1064.9	1078.7	1062.4	1059.4	1066.2
10°	1054.2	1068.1	1051.8	1046.0	1050.9
12.5°	1040.3	1053.4	1037.8	1028.7	1033.0
15°	1017.7	1026.6	1011.0	1001.1	1002.7
17.5°	993.1	998.6	976.1	967.7	966.1
20°	974.4	979.3	952.8	941.1	939.5
22.5°	950.5	954.7	926.9	912.5	910.2
25°	914.6	915.4	888.8	868.7	863.8
27.5°	877.0	874.4	844.9	821.1	814.8
30°	849.7	846.5	812.3	787.2	781.5
32.5°	820.4	814.6	780.4	753.3	747.6
35°	777.4	768.4	732.5	704.1	697.6
37.5°	731.5	721.4	686.1	655.2	647.8
40°	700.9	689.5	653.5	622.6	615.3
42.5°	670.3	657.6	620.9	590.0	582.0
45°	622.7	609.7	572.9	542.7	534.6
47.5°	577.5	560.9	525.1	495.2	487.0
50°	546.2	528.4	493.9	464.6	456.5
52.5°	514.3	495.8	462.6	434.6	426.5
55°	465.6	448.5	415.7	389.8	382.5
57.5°	417.4	401.0	371.0	346.2	339.1
60°	384.1	370.3	341.7	318.3	311.8
62.5°	352.2	339.7	312.4	291.0	284.5
65°	305.1	293.8	269.4	250.1	245.3
67.5°	259.4	248.0	228.3	211.1	205.5
70°	229.5	218.1	200.4	184.5	179.6
72.5°	200.9	188.8	174.4	159.9	156.3
75°	158.0	148.2	137.2	126.3	123.1
77.5°	120.1	110.6	102.6	94.9	94.1
80°	94.8	86.7	80.6	75.6	74.8
82.5°	70.8	64.7	60.7	57.0	56.9
85°	36.6	34.1	33.3	29.1	27.4
87.5°	10.6	10.6	9.3	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.3	17.0	6.9	6.9	6.9
95°	38.6	97.2	30.0	21.4	21.4
97.5°	80.6	233.1	162.0	43.6	37.7
100°	111.4	337.7	278.5	64.0	51.4
102.5°	142.3	428.9	439.7	101.5	78.8
105°	188.6	527.9	762.8	191.4	128.6
107.5°	234.0	592.6	1169.0	395.0	238.3
110°	261.4	630.1	1474.1	615.7	368.5



TEST NUMBER: P1438888

CATALOG NUMBER: CB2-B-055U-030D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.8	667.6	1642.1	987.1	635.9
115°	325.7	719.5	1739.8	1619.7	1234.2
117.5°	356.5	767.2	1823.8	2002.9	1889.8
120°	377.1	804.5	1868.4	2057.8	2095.5
122.5°	397.7	831.8	1892.4	2079.1	2150.4
125°	424.2	872.6	1898.4	2160.1	2172.6
127.5°	450.8	903.3	1926.7	2234.5	2240.4
130°	471.4	923.9	1954.1	2259.4	2305.5
132.5°	495.4	941.2	1964.4	2273.6	2343.2
135°	531.4	967.1	1902.7	2227.8	2391.2
137.5°	576.8	985.8	1843.5	2226.5	2332.1
140°	604.2	989.7	1812.7	2275.7	2284.1
142.5°	635.1	1000.5	1805.8	2270.3	2342.3
145°	681.4	1016.6	1795.5	2164.2	2356.9
147.5°	727.6	1026.8	1756.1	2047.1	2215.5
150°	758.5	1030.9	1718.4	2007.9	2112.7
152.5°	789.4	1034.9	1670.4	1983.5	2071.5
155°	827.1	1036.6	1598.4	1926.4	2026.9
157.5°	866.5	1031.6	1511.9	1822.0	1931.8
160°	887.1	1025.3	1457.0	1746.3	1842.7
162.5°	907.6	1022.4	1409.0	1647.3	1760.4
165°	938.5	1026.5	1289.9	1518.6	1589.8
167.5°	959.1	1022.7	1178.5	1365.9	1466.4
170°	972.8	1023.0	1109.9	1248.9	1332.7
172.5°	983.0	1006.5	1068.8	1142.0	1199.0
175°	994.2	1006.8	1024.2	1041.8	1062.8
177.5°	997.6	1004.3	990.8	987.5	994.2
180°	994.2	994.2	994.2	994.2	994.2



TEST NUMBER: P1438888
 CATALOG NUMBER: CB2-B-055U-030D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.30	12.99	13.43	14.10	15.66	11.20	11.89	12.33	13.00	14.56
	3H	13.93	14.55	15.07	15.67	17.24	12.71	13.33	13.85	14.46	16.03
	4H	14.55	15.13	15.70	16.26	17.84	13.28	13.86	14.42	14.99	16.57
	6H	14.94	15.48	16.10	16.61	18.20	13.64	14.18	14.79	15.31	16.90
	8H	15.09	15.60	16.24	16.74	18.32	13.78	14.29	14.93	15.43	17.01
	12H	15.16	15.64	16.32	16.78	18.38	13.83	14.32	14.99	15.46	17.06
4H	2H	12.69	13.27	13.84	14.40	15.98	11.81	12.40	12.96	13.52	15.10
	3H	14.54	15.03	15.70	16.18	17.77	13.53	14.02	14.69	15.17	16.76
	4H	15.28	15.73	16.44	16.87	18.48	14.20	14.65	15.36	15.79	17.40
	6H	15.79	16.17	16.95	17.34	18.94	14.66	15.05	15.83	16.21	17.81
	8H	15.99	16.35	17.15	17.50	19.12	14.85	15.21	16.01	16.36	17.98
	12H	16.09	16.41	17.27	17.58	19.20	14.93	15.25	16.11	16.42	18.04
8H	4H	15.42	15.78	16.59	16.94	18.55	14.46	14.82	15.62	15.97	17.59
	6H	16.06	16.35	17.24	17.55	19.16	15.05	15.35	16.24	16.55	18.16
	8H	16.35	16.60	17.54	17.78	19.41	15.33	15.58	16.52	16.76	18.39
	12H	16.51	16.74	17.71	17.91	19.58	15.47	15.70	16.66	16.87	18.53
12H	4H	15.39	15.72	16.57	16.88	18.50	14.45	14.78	15.63	15.94	17.56
	6H	16.08	16.34	17.27	17.52	19.15	15.12	15.37	16.31	16.55	18.18
	8H	16.39	16.62	17.59	17.79	19.46	15.41	15.64	16.61	16.81	18.48