

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439385

Luminaire Tested: CB3-B-030U-085D-927-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439385
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-B-030U-085D-927-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
3-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4661.8 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 33.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439385

CATALOG NUMBER: CB3-B-030U-085D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439385

CATALOG NUMBER: CB3-B-030U-085D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	70		
1	102	98	94	91	97	93	90	86	83	81	78	74	72	71	66	65	63	63	63	63	63	63	63	59		
2	94	86	80	75	88	82	76	71	73	69	65	66	62	59	59	56	54	54	54	54	54	54	54	50		
3	86	76	68	62	81	72	65	60	65	60	55	58	54	50	52	49	46	46	46	46	46	46	46	43		
4	78	67	59	53	74	64	57	51	58	52	47	52	47	44	47	43	40	40	40	40	40	40	40	37		
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	35	35	35	35	35	35	32		
6	67	54	46	40	63	52	44	39	47	41	36	43	37	33	38	34	31	31	31	31	31	31	31	28		
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	35	31	28	28	28	28	28	28	28	25		
8	57	45	37	31	54	43	36	31	39	33	29	36	30	27	32	28	25	25	25	25	25	25	25	23		
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	22	22	22	22	22	22	20		
10	50	38	30	26	48	36	29	25	33	27	23	30	25	22	28	24	20	20	20	20	20	20	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15383	15383	15383
5°	15310	15322	15409
10°	15244	15222	15222
15°	15010	15010	14920
20°	14767	14615	14487
25°	14394	14213	13960
30°	14042	13676	13347
35°	13672	13165	12698
40°	13179	12552	12010
45°	12732	12006	11265
50°	12272	11354	10539
55°	11773	10725	9847
60°	11231	10074	9067
65°	10599	9333	8246
70°	9872	8466	7347
75°	8949	7432	6544
80°	7799	6229	5786
85°	6024	5271	5271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12732 cd/sqm



TEST NUMBER: P1439385

CATALOG NUMBER: CB3-B-030U-085D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	2.8
10°-20°	360.4	7.7
20°-30°	523.6	11.2
30°-40°	595.3	12.8
40°-50°	577.9	12.4
50°-60°	487.9	10.5
60°-70°	347.1	7.4
70°-80°	185.5	4.0
80°-90°	49.0	1.1
90°-100°	16.2	0.3
100°-110°	84.7	1.8
110°-120°	213.3	4.6
120°-130°	329.1	7.1
130°-140°	301.3	6.5
140°-150°	222.4	4.8
150°-160°	141.7	3.0
160°-170°	74.6	1.6
170°-180°	23.2	0.5
0°-30°	1012.3	21.7
0°-40°	1607.6	34.5
0°-60°	2673.5	57.3
0°-90°	3255.1	69.8
90°-120°	314.2	6.7
90°-150°	1167.0	25.0
90°-180°	1407.0	30.2
0°-180°	4661.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1348	1365	1349	1347	1357	128
15°	1281	1293	1281	1274	1274	361
25°	1153	1157	1138	1123	1118	531
35°	990	980	953	925	919	617
45°	796	783	750	714	704	614
55°	597	581	544	509	499	534
65°	396	382	349	318	308	392
75°	205	193	170	152	150	218
85°	46	43	41	41	41	55
90°	0	0	0	0	0	2
95°	8	24	10	5	5	11
105°	43	134	97	40	33	46
115°	82	168	402	175	133	80
125°	110	169	527	531	491	98
135°	141	189	427	582	595	109
145°	178	206	356	495	542	111
155°	205	221	306	378	417	95
165°	228	234	246	287	307	64
175°	240	245	238	239	241	23
180°	239	239	239	239	239	

TEST NUMBER: P1439385

CATALOG NUMBER: CB3-B-030U-085D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1359.6	1359.6	1359.6	1359.6	1359.6
2.5°	1352.7	1366.3	1354.2	1355.8	1358.8
5°	1348.0	1365.0	1349.0	1347.3	1356.7
7.5°	1337.6	1353.1	1336.4	1332.6	1341.1
10°	1326.8	1343.8	1324.9	1320.1	1324.9
12.5°	1307.5	1325.2	1310.2	1302.4	1306.3
15°	1281.4	1292.7	1281.4	1273.7	1273.7
17.5°	1249.5	1261.4	1240.1	1234.6	1232.5
20°	1226.4	1236.7	1213.8	1206.0	1203.2
22.5°	1195.5	1205.1	1186.0	1172.8	1169.2
25°	1153.0	1156.8	1138.5	1122.9	1118.2
27.5°	1110.3	1111.2	1086.2	1067.3	1061.0
30°	1074.8	1075.7	1046.8	1026.4	1021.6
32.5°	1039.2	1036.4	1008.9	984.7	981.5
35°	989.8	980.3	953.1	925.0	919.3
37.5°	930.1	924.4	892.3	864.1	855.6
40°	892.3	882.8	849.8	821.6	813.1
42.5°	854.4	843.4	809.6	778.3	769.0
45°	795.7	783.4	750.3	714.3	704.0
47.5°	736.6	723.2	686.8	651.9	640.4
50°	697.2	683.0	645.0	611.0	598.7
52.5°	657.0	642.1	604.1	569.3	559.3
55°	596.8	580.7	543.7	508.7	499.2
57.5°	536.5	520.6	483.8	450.7	439.4
60°	496.3	481.2	445.2	412.1	400.7
62.5°	455.4	441.0	405.8	373.5	362.9
65°	395.9	381.7	348.6	317.5	308.0
67.5°	337.0	324.9	292.2	263.6	256.1
70°	298.4	287.1	255.9	229.7	222.1
72.5°	261.3	249.2	219.6	197.3	192.0
75°	204.7	193.4	170.0	152.5	149.7
77.5°	153.0	143.7	123.4	113.5	112.0
80°	119.7	111.2	95.6	88.8	88.8
82.5°	88.8	81.9	71.7	68.8	68.8
85°	46.4	42.6	40.6	40.6	40.6
87.5°	13.9	13.9	13.1	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	2.5	5.8	1.7	0.9	1.7
95°	8.4	23.9	9.5	5.3	5.3
97.5°	17.5	53.3	24.4	13.0	11.8
100°	24.2	75.7	37.9	18.9	16.9
102.5°	31.8	98.2	57.3	25.6	21.9
105°	43.2	133.8	96.9	39.9	32.7
107.5°	55.8	158.2	159.7	61.5	49.5
110°	64.3	168.3	212.8	80.7	62.2



TEST NUMBER: P1439385

CATALOG NUMBER: CB3-B-030U-085D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	71.9	170.9	283.6	110.0	84.9
115°	82.2	167.7	402.4	175.0	132.7
117.5°	89.8	159.6	492.6	278.4	214.7
120°	94.8	159.7	528.9	356.6	285.5
122.5°	100.7	160.7	539.0	434.3	368.9
125°	109.6	169.3	526.8	531.1	490.9
127.5°	118.4	175.7	493.9	570.9	558.4
130°	124.3	179.9	467.8	584.5	575.2
132.5°	130.2	184.2	449.2	584.8	589.6
135°	141.2	188.6	426.7	581.9	595.2
137.5°	152.3	194.0	405.6	563.4	591.2
140°	159.1	198.2	388.8	543.5	583.7
142.5°	166.7	201.7	372.7	525.0	567.6
145°	178.0	205.9	356.1	495.2	541.5
147.5°	186.9	208.1	337.3	465.1	503.4
150°	192.8	208.2	329.8	438.3	485.7
152.5°	197.9	212.5	320.5	413.8	457.0
155°	205.4	220.9	305.5	378.1	417.2
157.5°	213.0	227.9	287.8	351.4	378.0
160°	218.1	230.4	276.0	338.6	356.1
162.5°	222.3	233.0	263.4	316.7	336.7
165°	227.6	233.7	245.5	287.0	306.6
167.5°	232.4	235.5	246.9	257.8	273.7
170°	234.9	238.0	244.4	255.1	260.2
172.5°	237.5	242.2	241.0	248.3	252.6
175°	240.2	245.4	238.1	239.2	241.3
177.5°	240.8	243.3	241.7	241.7	244.2
180°	239.2	239.2	239.2	239.2	239.2



TEST NUMBER: P1439385
 CATALOG NUMBER: CB3-B-030U-085D-927-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.31	19.36	19.08	20.15	21.11	17.23	18.29	18.00	19.07	20.03
	3H	19.99	20.94	20.77	21.73	22.72	18.66	19.61	19.44	20.40	21.39
	4H	20.63	21.52	21.43	22.33	23.33	19.18	20.08	19.98	20.89	21.88
	6H	21.02	21.85	21.84	22.66	23.68	19.51	20.34	20.32	21.15	22.16
	8H	21.17	21.95	21.99	22.78	23.80	19.64	20.43	20.46	21.26	22.27
	12H	21.24	21.99	22.07	22.82	23.86	19.72	20.47	20.55	21.30	22.34
4H	2H	18.74	19.63	19.54	20.44	21.44	17.88	18.77	18.68	19.58	20.58
	3H	20.65	21.39	21.46	22.23	23.25	19.52	20.26	20.33	21.10	22.12
	4H	21.40	22.08	22.23	22.92	23.96	20.13	20.81	20.96	21.65	22.69
	6H	21.92	22.50	22.76	23.37	24.41	20.55	21.14	21.40	22.00	23.05
	8H	22.11	22.66	22.96	23.52	24.58	20.73	21.28	21.58	22.14	23.20
	12H	22.22	22.71	23.09	23.59	24.66	20.84	21.34	21.71	22.22	23.28
8H	4H	21.55	22.09	22.40	22.95	24.01	20.41	20.96	21.26	21.81	22.88
	6H	22.17	22.63	23.05	23.53	24.59	20.94	21.40	21.82	22.30	23.36
	8H	22.45	22.85	23.34	23.75	24.83	21.20	21.60	22.09	22.50	23.57
	12H	22.62	22.98	23.51	23.87	25.00	21.38	21.74	22.27	22.63	23.76
12H	4H	21.53	22.02	22.40	22.90	23.97	20.42	20.91	21.29	21.79	22.86
	6H	22.19	22.59	23.08	23.49	24.57	21.00	21.40	21.89	22.30	23.38
	8H	22.50	22.85	23.39	23.74	24.87	21.29	21.65	22.18	22.54	23.67