

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439088

Luminaire Tested: CB2-D-125U-055D-940-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439088
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-125U-055D-940-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15891.8 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 132.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439088

CATALOG NUMBER: CB2-D-125U-055D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1439088

CATALOG NUMBER: CB2-D-125U-055D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30					30															
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	32	26					26															
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27	22					22															
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	23	19					19															
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16					16															
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	21	19	18	14					14															
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	12					12															
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11					11															
8	51	39	32	27	46	36	29	25	29	24	21	22	19	17	16	14	12	10					10															
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9					9															
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8					8															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	17911	17939	18064
10°	17810	17767	17753
15°	17528	17413	17270
20°	17252	16869	16633
25°	16789	16315	15858
30°	16324	15605	15013
35°	15789	14876	14167
40°	15222	14192	13362
45°	14652	13479	12578
50°	14138	12783	11814
55°	13505	12058	11093
60°	12781	11370	10374
65°	12012	10604	9656
70°	11163	9747	8736
75°	10155	8819	7911
80°	9082	7728	7167
85°	6984	6345	5236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14652 cd/sqm



TEST NUMBER: P1439088

CATALOG NUMBER: CB2-D-125U-055D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.1	1.2
10°-20°	543.8	3.4
20°-30°	781.9	4.9
30°-40°	878.8	5.5
40°-50°	848.9	5.3
50°-60°	717.2	4.5
60°-70°	515.2	3.2
70°-80°	281.6	1.8
80°-90°	75.0	0.5
90°-100°	167.5	1.1
100°-110°	690.6	4.3
110°-120°	1253.7	7.9
120°-130°	1706.0	10.7
130°-140°	1969.3	12.4
140°-150°	1984.6	12.5
150°-160°	1712.6	10.8
160°-170°	1160.7	7.3
170°-180°	409.4	2.6
0°-30°	1520.7	9.6
0°-40°	2399.5	15.1
0°-60°	3965.6	25.0
0°-90°	4837.4	30.4
90°-120°	2111.7	13.3
90°-150°	7771.6	48.9
90°-180°	11054.0	69.6
0°-180°	15891.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2074	2074	2074	2074	2074	
5°	2049	2077	2052	2052	2066	195
15°	1944	1961	1931	1912	1916	548
25°	1747	1749	1698	1660	1650	804
35°	1485	1468	1399	1345	1333	928
45°	1190	1165	1094	1037	1021	919
55°	890	857	794	745	731	795
65°	583	561	515	478	469	578
75°	302	283	262	241	235	323
85°	70	65	64	56	52	83
90°	0	0	3	0	3	8
95°	162	142	135	105	105	189
105°	683	673	656	619	612	725
115°	1298	1295	1271	1234	1231	1281
125°	1931	1950	1910	1870	1873	1724
135°	2573	2603	2560	2512	2529	1981
145°	3188	3225	3175	3138	3161	1992
155°	3729	3766	3712	3689	3719	1715
165°	4122	4164	4111	4088	4125	1161
175°	4318	4364	4308	4281	4291	410
180°	4334	4334	4334	4334	4334	

TEST NUMBER: P1439088

CATALOG NUMBER: CB2-D-125U-055D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2074.3	2074.3	2074.3	2074.3	2074.3
2.5°	2060.4	2085.2	2066.7	2069.4	2073.1
5°	2048.9	2076.9	2052.1	2052.4	2066.4
7.5°	2034.3	2060.7	2029.6	2023.8	2036.9
10°	2014.0	2040.4	2009.2	1998.3	2007.6
12.5°	1987.3	2012.5	1982.5	1965.3	1973.3
15°	1944.1	1961.2	1931.4	1912.4	1915.5
17.5°	1897.1	1907.7	1864.7	1848.7	1845.6
20°	1861.5	1870.8	1820.2	1797.9	1794.8
22.5°	1815.8	1823.8	1770.7	1743.2	1738.9
25°	1747.2	1748.7	1697.9	1659.6	1650.3
27.5°	1675.4	1670.4	1614.1	1568.7	1556.6
30°	1623.3	1617.1	1551.8	1503.9	1493.0
32.5°	1567.4	1556.2	1490.8	1439.1	1428.2
35°	1485.1	1468.0	1399.3	1345.0	1332.6
37.5°	1397.4	1378.1	1310.7	1251.6	1237.6
40°	1339.0	1317.2	1248.4	1189.3	1175.4
42.5°	1280.5	1256.3	1186.2	1127.0	1111.8
45°	1189.7	1164.8	1094.4	1036.8	1021.3
47.5°	1103.2	1071.6	1003.2	946.0	930.4
50°	1043.5	1009.4	943.5	887.5	872.0
52.5°	982.5	947.1	883.7	830.3	814.8
55°	889.5	856.8	794.2	744.6	730.6
57.5°	797.3	766.0	708.7	661.4	647.7
60°	733.8	707.4	652.8	608.0	595.6
62.5°	672.8	648.9	596.9	555.9	543.5
65°	582.9	561.2	514.6	477.9	468.6
67.5°	495.6	473.8	436.2	403.2	392.6
70°	438.4	416.6	382.8	352.4	343.1
72.5°	383.7	360.8	333.2	305.4	298.6
75°	301.8	283.1	262.1	241.3	235.1
77.5°	229.4	211.3	196.0	181.4	179.8
80°	181.1	165.5	154.1	144.5	142.9
82.5°	135.3	123.5	115.9	109.0	108.6
85°	69.9	65.2	63.5	55.5	52.4
87.5°	20.3	20.3	18.5	15.3	15.9
90°	0.0	0.0	3.4	0.1	3.4
92.5°	40.6	35.3	33.1	21.7	25.0
95°	162.3	142.5	135.2	104.8	104.8
97.5°	306.3	286.5	275.9	244.6	238.0
100°	409.1	389.3	378.7	344.7	338.1
102.5°	514.6	505.3	486.9	450.2	443.6
105°	683.0	673.1	655.9	618.6	612.0
107.5°	856.1	858.1	832.4	801.8	792.5
110°	980.5	977.2	956.8	926.3	919.7



TEST NUMBER: P1439088

CATALOG NUMBER: CB2-D-125U-055D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1107.6	1101.7	1081.3	1050.7	1044.1
115°	1298.3	1295.0	1271.3	1234.0	1230.7
117.5°	1479.6	1490.1	1462.0	1422.7	1421.4
120°	1609.4	1622.6	1589.1	1555.1	1548.5
122.5°	1736.5	1752.4	1718.9	1679.7	1681.1
125°	1930.6	1950.4	1910.3	1869.8	1873.1
127.5°	2117.9	2142.4	2105.1	2063.9	2067.9
130°	2245.0	2274.8	2234.9	2191.1	2197.7
132.5°	2374.9	2404.6	2364.7	2318.3	2330.2
135°	2573.0	2602.7	2559.5	2512.5	2529.0
137.5°	2759.6	2789.4	2742.0	2702.6	2722.4
140°	2884.1	2913.8	2863.8	2827.0	2846.9
142.5°	3005.8	3040.8	2988.2	2948.9	2974.0
145°	3188.4	3224.7	3174.8	3138.2	3161.3
147.5°	3361.5	3397.8	3347.3	3312.0	3335.8
150°	3472.4	3508.7	3455.5	3425.6	3452.1
152.5°	3575.1	3616.8	3560.9	3531.3	3565.7
155°	3729.3	3765.7	3712.4	3689.4	3719.2
157.5°	3863.2	3905.5	3852.4	3832.6	3856.5
160°	3952.5	3992.1	3938.9	3919.3	3945.7
162.5°	4020.1	4062.4	4012.0	3989.7	4021.4
165°	4121.5	4164.5	4111.4	4088.5	4124.9
167.5°	4201.3	4246.9	4193.2	4169.7	4206.7
170°	4250.0	4293.0	4236.5	4210.3	4250.0
172.5°	4282.5	4328.1	4268.9	4242.5	4268.9
175°	4317.6	4363.9	4307.5	4280.7	4290.6
177.5°	4334.5	4371.6	4326.4	4302.8	4334.5
180°	4334.5	4334.5	4334.5	4334.5	4334.5



TEST NUMBER: P1439088
 CATALOG NUMBER: CB2-D-125U-055D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.90	15.60	16.01	16.70	18.23	13.80	14.50	14.91	15.61	17.13
	3H	16.53	17.16	17.65	18.27	19.82	15.31	15.94	16.43	17.06	18.60
	4H	17.15	17.75	18.28	18.86	20.41	15.88	16.48	17.01	17.59	19.14
	6H	17.55	18.10	18.68	19.21	20.77	16.24	16.79	17.38	17.91	19.47
	8H	17.69	18.21	18.83	19.34	20.90	16.38	16.90	17.52	18.03	19.59
	12H	17.76	18.25	18.90	19.38	20.96	16.44	16.93	17.58	18.06	19.63
4H	2H	15.29	15.88	16.42	17.00	18.55	14.41	15.01	15.55	16.12	17.67
	3H	17.14	17.64	18.28	18.78	20.34	16.13	16.63	17.28	17.77	19.33
	4H	17.88	18.34	19.03	19.47	21.05	16.80	17.26	17.95	18.39	19.97
	6H	18.39	18.78	19.54	19.94	21.51	17.27	17.66	18.42	18.81	20.38
	8H	18.59	18.96	19.74	20.10	21.69	17.45	17.82	18.60	18.96	20.55
	12H	18.69	19.02	19.86	20.18	21.77	17.53	17.87	18.70	19.02	20.61
8H	4H	18.03	18.39	19.18	19.53	21.12	17.06	17.43	18.21	18.57	20.16
	6H	18.66	18.96	19.83	20.15	21.73	17.66	17.96	18.83	19.15	20.73
	8H	18.95	19.21	20.13	20.38	21.98	17.93	18.20	19.11	19.36	20.97
	12H	19.12	19.35	20.30	20.51	22.15	18.08	18.31	19.26	19.47	21.11
12H	4H	18.00	18.33	19.16	19.48	21.08	17.06	17.39	18.22	18.54	20.14
	6H	18.69	18.95	19.86	20.12	21.72	17.72	17.98	18.90	19.15	20.75
	8H	19.00	19.23	20.18	20.39	22.03	18.02	18.25	19.20	19.41	21.05