

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439481

Luminaire Tested: CB3-B-125U-085D-927-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439481
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-B-125U-085D-927-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
3-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9407.5 lumens
Efficiency: N/A
Efficacy: 149.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439481

CATALOG NUMBER: CB3-B-125U-085D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439481

CATALOG NUMBER: CB3-B-125U-085D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	35				
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29				
2	86	79	73	68	78	72	67	62	58	54	51	45	42	40	33	31	30	25				
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21				
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18				
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	20	16				
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14				
7	56	44	36	31	51	40	34	29	33	28	24	26	22	20	20	17	15	13				
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11				
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10				
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15383	15383	15383
5°	15310	15322	15409
10°	15244	15222	15222
15°	15010	15010	14920
20°	14767	14615	14487
25°	14394	14213	13960
30°	14042	13676	13347
35°	13672	13165	12698
40°	13179	12552	12010
45°	12732	12006	11265
50°	12272	11354	10539
55°	11773	10725	9847
60°	11231	10074	9067
65°	10599	9333	8246
70°	9872	8466	7347
75°	8949	7432	6544
80°	7799	6229	5786
85°	6024	5271	5271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12732 cd/sqm



TEST NUMBER: P1439481

CATALOG NUMBER: CB3-B-125U-085D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	1.4
10°-20°	360.4	3.8
20°-30°	523.6	5.6
30°-40°	595.3	6.3
40°-50°	577.9	6.1
50°-60°	487.9	5.2
60°-70°	347.1	3.7
70°-80°	185.5	2.0
80°-90°	49.0	0.5
90°-100°	70.7	0.8
100°-110°	370.7	3.9
110°-120°	933.1	9.9
120°-130°	1439.5	15.3
130°-140°	1317.8	14.0
140°-150°	972.6	10.3
150°-160°	620.0	6.6
160°-170°	326.4	3.5
170°-180°	101.6	1.1
0°-30°	1012.3	10.8
0°-40°	1607.6	17.1
0°-60°	2673.5	28.4
0°-90°	3255.1	34.6
90°-120°	1374.5	14.6
90°-150°	5104.4	54.3
90°-180°	6152.0	65.4
0°-180°	9407.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1348	1365	1349	1347	1357	128
15°	1281	1293	1281	1274	1274	361
25°	1153	1157	1138	1123	1118	531
35°	990	980	953	925	919	617
45°	796	783	750	714	704	614
55°	597	581	544	509	499	534
65°	396	382	349	318	308	392
75°	205	193	170	152	150	218
85°	46	43	41	41	41	55
90°	0	0	0	0	0	3
95°	37	104	42	23	23	47
105°	189	585	424	174	143	202
115°	359	733	1760	765	581	350
125°	479	740	2304	2323	2147	429
135°	618	825	1866	2545	2604	477
145°	779	900	1558	2166	2368	484
155°	899	966	1336	1654	1825	414
165°	995	1022	1074	1255	1341	281
175°	1051	1073	1041	1046	1055	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1439481

CATALOG NUMBER: CB3-B-125U-085D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1359.6	1359.6	1359.6	1359.6	1359.6
2.5°	1352.7	1366.3	1354.2	1355.8	1358.8
5°	1348.0	1365.0	1349.0	1347.3	1356.7
7.5°	1337.6	1353.1	1336.4	1332.6	1341.1
10°	1326.8	1343.8	1324.9	1320.1	1324.9
12.5°	1307.5	1325.2	1310.2	1302.4	1306.3
15°	1281.4	1292.7	1281.4	1273.7	1273.7
17.5°	1249.5	1261.4	1240.1	1234.6	1232.5
20°	1226.4	1236.7	1213.8	1206.0	1203.2
22.5°	1195.5	1205.1	1186.0	1172.8	1169.2
25°	1153.0	1156.8	1138.5	1122.9	1118.2
27.5°	1110.3	1111.2	1086.2	1067.3	1061.0
30°	1074.8	1075.7	1046.8	1026.4	1021.6
32.5°	1039.2	1036.4	1008.9	984.7	981.5
35°	989.8	980.3	953.1	925.0	919.3
37.5°	930.1	924.4	892.3	864.1	855.6
40°	892.3	882.8	849.8	821.6	813.1
42.5°	854.4	843.4	809.6	778.3	769.0
45°	795.7	783.4	750.3	714.3	704.0
47.5°	736.6	723.2	686.8	651.9	640.4
50°	697.2	683.0	645.0	611.0	598.7
52.5°	657.0	642.1	604.1	569.3	559.3
55°	596.8	580.7	543.7	508.7	499.2
57.5°	536.5	520.6	483.8	450.7	439.4
60°	496.3	481.2	445.2	412.1	400.7
62.5°	455.4	441.0	405.8	373.5	362.9
65°	395.9	381.7	348.6	317.5	308.0
67.5°	337.0	324.9	292.2	263.6	256.1
70°	298.4	287.1	255.9	229.7	222.1
72.5°	261.3	249.2	219.6	197.3	192.0
75°	204.7	193.4	170.0	152.5	149.7
77.5°	153.0	143.7	123.4	113.5	112.0
80°	119.7	111.2	95.6	88.8	88.8
82.5°	88.8	81.9	71.7	68.8	68.8
85°	46.4	42.6	40.6	40.6	40.6
87.5°	13.9	13.9	13.1	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.1	25.5	7.4	3.8	7.4
95°	36.9	104.4	41.5	23.0	23.0
97.5°	76.5	233.3	106.9	57.0	51.6
100°	106.0	331.3	165.9	82.7	73.7
102.5°	139.2	429.3	250.7	112.1	95.8
105°	188.9	585.4	423.9	174.4	142.8
107.5°	244.2	692.1	698.6	268.8	216.6
110°	281.1	736.1	930.8	353.0	271.9



TEST NUMBER: P1439481

CATALOG NUMBER: CB3-B-125U-085D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	314.3	747.7	1240.5	481.3	371.4
115°	359.4	733.4	1760.2	765.3	580.6
117.5°	392.6	698.1	2154.7	1217.5	939.1
120°	414.7	698.6	2313.2	1559.6	1248.8
122.5°	440.5	702.7	2357.4	1899.4	1613.7
125°	479.2	740.5	2304.0	2323.0	2147.3
127.5°	517.9	768.4	2160.2	2497.2	2442.2
130°	543.7	787.0	2045.9	2556.5	2515.9
132.5°	569.5	805.6	1964.8	2557.9	2578.6
135°	617.5	824.7	1866.2	2544.9	2603.5
137.5°	666.3	848.3	1774.1	2464.3	2586.0
140°	695.8	867.0	1700.3	2377.1	2552.8
142.5°	729.0	882.2	1630.3	2296.2	2482.8
145°	778.7	900.4	1557.5	2165.7	2368.5
147.5°	817.5	910.3	1475.5	2034.1	2201.7
150°	843.3	910.8	1442.3	1917.0	2124.3
152.5°	865.4	929.4	1401.7	1809.7	1998.9
155°	898.6	966.1	1336.3	1653.5	1824.7
157.5°	931.7	996.6	1258.9	1537.1	1653.3
160°	953.8	1007.9	1207.3	1480.9	1557.5
162.5°	972.3	1019.1	1152.0	1385.3	1472.7
165°	995.3	1022.4	1073.7	1255.3	1340.9
167.5°	1016.5	1030.0	1080.1	1127.8	1197.1
170°	1027.6	1041.1	1069.0	1115.6	1138.2
172.5°	1038.6	1059.4	1054.3	1086.1	1105.0
175°	1050.6	1073.1	1041.4	1046.2	1055.2
177.5°	1053.4	1064.2	1057.1	1057.3	1068.1
180°	1046.0	1046.0	1046.0	1046.0	1046.0



TEST NUMBER: P1439481
 CATALOG NUMBER: CB3-B-125U-085D-927-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.02	15.75	16.10	16.83	18.31	13.94	14.67	15.02	15.75	17.23
	3H	16.68	17.33	17.77	18.42	19.91	15.35	16.00	16.44	17.09	18.58
	4H	17.30	17.92	18.40	19.01	20.51	15.86	16.48	16.96	17.57	19.07
	6H	17.68	18.25	18.79	19.34	20.86	16.17	16.74	17.28	17.83	19.34
	8H	17.81	18.36	18.93	19.47	20.97	16.29	16.83	17.40	17.94	19.45
	12H	17.88	18.39	18.99	19.49	21.02	16.36	16.88	17.48	17.98	19.51
4H	2H	15.41	16.03	16.52	17.12	18.62	14.55	15.18	15.66	16.26	17.76
	3H	17.29	17.81	18.40	18.92	20.44	16.16	16.68	17.28	17.80	19.31
	4H	18.03	18.51	19.15	19.62	21.15	16.76	17.24	17.88	18.34	19.88
	6H	18.53	18.94	19.65	20.06	21.59	17.17	17.57	18.29	18.70	20.23
	8H	18.72	19.10	19.84	20.22	21.76	17.34	17.71	18.46	18.84	20.38
	12H	18.81	19.15	19.95	20.29	21.83	17.43	17.78	18.58	18.91	20.46
8H	4H	18.15	18.53	19.28	19.65	21.20	17.01	17.39	18.14	18.52	20.06
	6H	18.77	19.08	19.91	20.24	21.78	17.54	17.85	18.68	19.01	20.55
	8H	19.04	19.32	20.19	20.46	22.02	17.79	18.06	18.94	19.21	20.76
	12H	19.20	19.44	20.36	20.58	22.17	17.96	18.20	19.12	19.34	20.93
12H	4H	18.12	18.46	19.26	19.60	21.14	17.01	17.35	18.15	18.49	20.03
	6H	18.78	19.06	19.93	20.20	21.76	17.59	17.87	18.75	19.01	20.57
	8H	19.08	19.32	20.23	20.46	22.05	17.87	18.11	19.03	19.25	20.84