

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438611

Luminaire Tested: CB2-030U-055D-940-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438611
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-030U-055D-940-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3901.1 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438611

CATALOG NUMBER: CB2-030U-055D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438611

CATALOG NUMBER: CB2-030U-055D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																				
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	58	57	53																				
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	51	48	44																				
3	84	74	67	61	78	70	64	58	62	57	52	54	50	47	47	44	42	38																				
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33																				
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	32	29																				
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	25																				
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	22																				
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20																				
9	53	40	33	28	49	38	31	26	34	28	24	31	26	22	27	23	20	18																				
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18065	18065	18065
5°	17912	17940	18064
10°	17810	17767	17753
15°	17529	17413	17271
20°	17253	16869	16633
25°	16789	16316	15857
30°	16323	15605	15013
35°	15788	14877	14167
40°	15222	14192	13362
45°	14651	13479	12577
50°	14139	12781	11814
55°	13504	12058	11093
60°	12781	11370	10374
65°	12014	10604	9656
70°	11163	9747	8734
75°	10155	8816	7907
80°	9077	7723	7172
85°	6974	6355	5236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14651 cd/sqm



TEST NUMBER: P1438611

CATALOG NUMBER: CB2-030U-055D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	2.5
10°-20°	271.9	7.0
20°-30°	390.9	10.0
30°-40°	439.4	11.3
40°-50°	424.5	10.9
50°-60°	358.6	9.2
60°-70°	257.6	6.6
70°-80°	140.8	3.6
80°-90°	37.4	1.0
90°-100°	9.1	0.2
100°-110°	57.7	1.5
110°-120°	183.2	4.7
120°-130°	265.9	6.8
130°-140°	285.9	7.3
140°-150°	269.2	6.9
150°-160°	219.3	5.6
160°-170°	142.8	3.7
170°-180°	49.3	1.3
0°-30°	760.3	19.5
0°-40°	1199.7	30.8
0°-60°	1982.8	50.8
0°-90°	2418.6	62.0
90°-120°	250.0	6.4
90°-150°	1071.0	27.5
90°-180°	1482.0	38.0
0°-180°	3901.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1037	1037	1037	1037	1037	
5°	1024	1038	1026	1026	1033	97
15°	972	981	966	956	958	274
25°	874	874	849	830	825	402
35°	742	734	700	672	666	464
45°	595	582	547	518	511	460
55°	445	428	397	372	365	398
65°	292	281	257	239	234	289
75°	151	142	131	121	118	161
85°	35	33	32	28	26	42
90°	0	0	0	0	0	2
95°	21	6	6	4	4	26
105°	108	112	11	13	14	114
115°	205	209	211	214	122	201
125°	291	296	296	301	305	260
135°	366	371	370	372	377	282
145°	428	432	429	429	435	268
155°	476	479	474	473	479	219
165°	508	509	504	502	507	143
175°	522	524	517	514	516	50
180°	520	520	520	520	520	



TEST NUMBER: P1438611

CATALOG NUMBER: CB2-030U-055D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1037.2	1037.2	1037.2	1037.2	1037.2
2.5°	1030.2	1042.6	1033.4	1034.7	1036.5
5°	1024.5	1038.4	1026.1	1026.2	1033.2
7.5°	1017.2	1030.4	1014.8	1011.9	1018.4
10°	1007.0	1020.2	1004.6	999.2	1003.8
12.5°	993.7	1006.2	991.3	982.6	986.7
15°	972.1	980.6	965.7	956.2	957.8
17.5°	948.5	953.8	932.3	924.4	922.8
20°	930.8	935.4	910.1	899.0	897.4
22.5°	907.9	911.9	885.3	871.6	869.4
25°	873.6	874.4	849.0	829.8	825.1
27.5°	837.7	835.2	807.0	784.3	778.3
30°	811.6	808.5	775.9	751.9	746.5
32.5°	783.7	778.1	745.4	719.5	714.1
35°	742.5	734.0	699.7	672.5	666.3
37.5°	698.7	689.1	655.3	625.8	618.8
40°	669.5	658.6	624.2	594.7	587.7
42.5°	640.3	628.1	593.1	563.5	555.9
45°	594.8	582.4	547.2	518.4	510.6
47.5°	551.6	535.8	501.6	473.0	465.2
50°	521.8	504.7	471.7	443.8	436.0
52.5°	491.3	473.6	441.9	415.2	407.4
55°	444.7	428.4	397.1	372.3	365.3
57.5°	398.7	383.0	354.4	330.7	323.9
60°	366.9	353.7	326.4	304.0	297.8
62.5°	336.4	324.4	298.4	278.0	271.8
65°	291.5	280.6	257.3	238.9	234.3
67.5°	247.8	236.9	218.1	201.6	196.3
70°	219.2	208.3	191.4	176.2	171.5
72.5°	191.9	180.4	166.6	152.7	149.3
75°	150.9	141.6	131.0	120.6	117.5
77.5°	114.7	105.7	98.0	90.7	89.9
80°	90.5	82.8	77.0	72.3	71.5
82.5°	67.7	61.8	58.0	54.5	54.3
85°	34.9	32.6	31.8	27.8	26.2
87.5°	10.2	10.2	8.9	7.7	7.7
90°	0.0	0.0	0.0	0.4	0.4
92.5°	5.7	2.2	1.5	2.2	2.2
95°	20.7	6.0	6.4	4.1	3.8
97.5°	42.9	9.6	9.2	10.2	10.5
100°	59.8	19.7	10.1	11.7	12.0
102.5°	78.4	74.2	10.5	12.6	13.2
105°	108.3	112.3	11.3	13.2	13.9
107.5°	137.6	141.6	52.5	13.6	14.4
110°	157.1	161.2	166.2	13.9	14.7

TEST NUMBER: P1438611

CATALOG NUMBER: CB2-030U-055D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.5	180.4	184.2	31.0	15.3
115°	204.9	209.3	211.3	213.7	122.5
117.5°	230.8	236.3	238.5	242.7	246.8
120°	248.9	254.0	255.6	259.9	264.3
122.5°	266.6	271.2	272.2	277.0	281.1
125°	291.0	296.1	296.2	301.2	305.2
127.5°	315.3	319.7	319.5	323.2	327.7
130°	331.6	334.5	334.6	337.7	342.5
132.5°	345.1	349.2	349.3	351.8	356.6
135°	366.1	370.6	369.9	372.3	377.0
137.5°	385.9	390.2	389.0	391.0	395.9
140°	398.9	402.5	400.7	402.7	408.2
142.5°	410.9	414.6	411.9	413.6	419.4
145°	428.5	431.9	428.9	429.4	434.9
147.5°	444.3	447.5	444.0	444.5	449.6
150°	454.5	457.4	453.0	453.5	458.6
152.5°	463.5	466.2	461.4	461.3	467.3
155°	475.9	478.9	473.7	472.7	479.3
157.5°	487.2	489.9	484.7	484.0	489.1
160°	494.7	496.5	491.3	490.3	495.5
162.5°	499.8	502.0	496.7	495.1	500.3
165°	507.5	509.0	503.7	501.6	506.7
167.5°	514.1	515.8	509.1	507.2	512.7
170°	518.0	519.1	512.4	509.9	515.4
172.5°	520.4	521.2	514.5	511.6	515.4
175°	522.5	523.6	516.9	513.6	516.1
177.5°	522.9	523.5	518.4	515.5	519.9
180°	519.9	519.9	519.9	519.9	519.9



TEST NUMBER: P1438611

CATALOG NUMBER: CB2-030U-055D-940-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.10	19.06	18.95	19.93	21.02	17.00	17.96	17.85	18.83	19.92
	3H	19.75	20.62	20.61	21.50	22.61	18.53	19.40	19.40	20.28	21.40
	4H	20.38	21.20	21.26	22.09	23.21	19.11	19.93	19.99	20.81	21.94
	6H	20.79	21.55	21.68	22.44	23.58	19.49	20.24	20.38	21.13	22.28
	8H	20.94	21.66	21.84	22.57	23.71	19.63	20.35	20.53	21.26	22.40
	12H	21.02	21.70	21.92	22.61	23.77	19.70	20.38	20.60	21.29	22.45
4H	2H	18.52	19.34	19.40	20.22	21.35	17.65	18.46	18.53	19.35	20.48
	3H	20.40	21.08	21.29	22.00	23.14	19.39	20.07	20.28	20.99	22.13
	4H	21.15	21.77	22.05	22.68	23.85	20.07	20.69	20.97	21.60	22.77
	6H	21.67	22.21	22.59	23.15	24.32	20.55	21.08	21.47	22.02	23.19
	8H	21.88	22.38	22.80	23.31	24.50	20.74	21.24	21.66	22.17	23.36
	12H	21.99	22.44	22.93	23.39	24.58	20.83	21.28	21.78	22.23	23.42
8H	4H	21.31	21.81	22.24	22.75	23.93	20.35	20.85	21.27	21.78	22.96
	6H	21.96	22.37	22.91	23.35	24.53	20.96	21.37	21.91	22.35	23.53
	8H	22.25	22.62	23.21	23.58	24.78	21.23	21.60	22.19	22.56	23.76
	12H	22.43	22.75	23.39	23.71	24.96	21.39	21.71	22.35	22.67	23.92
12H	4H	21.30	21.75	22.24	22.70	23.89	20.36	20.81	21.30	21.76	22.95
	6H	21.99	22.36	22.95	23.32	24.52	21.02	21.39	21.98	22.35	23.55
	8H	22.31	22.63	23.27	23.59	24.84	21.33	21.66	22.29	22.61	23.86