

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438959

Luminaire Tested: CB2-B-125U-055D-940-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438959
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-125U-055D-940-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9818.8 lumens
Efficiency: N/A
Efficacy: 170.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438959

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438959

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25																				
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	28	28	21																				
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18																				
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15																				
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13																				
5	64	53	45	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11																				
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10																				
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12	9																				
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8																				
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7																				
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9	7																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18065	18065	18065
5°	17912	17940	18064
10°	17810	17767	17753
15°	17529	17413	17271
20°	17253	16869	16633
25°	16789	16316	15857
30°	16323	15605	15013
35°	15788	14877	14167
40°	15222	14192	13362
45°	14651	13479	12577
50°	14139	12781	11814
55°	13504	12058	11093
60°	12781	11370	10374
65°	12014	10604	9656
70°	11163	9747	8734
75°	10155	8816	7907
80°	9077	7723	7172
85°	6974	6355	5236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14651 cd/sqm



TEST NUMBER: P1438959

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	1.0
10°-20°	271.9	2.8
20°-30°	390.9	4.0
30°-40°	439.4	4.5
40°-50°	424.5	4.3
50°-60°	358.6	3.7
60°-70°	257.6	2.6
70°-80°	140.8	1.4
80°-90°	37.4	0.4
90°-100°	84.4	0.9
100°-110°	522.6	5.3
110°-120°	1317.9	13.4
120°-130°	1584.2	16.1
130°-140°	1436.3	14.6
140°-150°	1145.4	11.7
150°-160°	781.3	8.0
160°-170°	413.2	4.2
170°-180°	115.0	1.2
0°-30°	760.3	7.7
0°-40°	1199.7	12.2
0°-60°	1982.8	20.2
0°-90°	2418.6	24.6
90°-120°	1924.8	19.6
90°-150°	6090.7	62.0
90°-180°	7400.0	75.4
0°-180°	9818.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1037	1037	1037	1037	1037	
5°	1024	1038	1026	1026	1033	97
15°	972	981	966	956	958	274
25°	874	874	849	830	825	402
35°	742	734	700	672	666	464
45°	595	582	547	518	511	460
55°	445	428	397	372	365	398
65°	292	281	257	239	234	289
75°	151	142	131	121	118	161
85°	35	33	32	28	26	42
90°	0	0	0	0	0	3
95°	44	110	34	24	24	55
105°	214	598	864	217	146	224
115°	369	815	1971	1835	1398	362
125°	481	988	2150	2447	2461	430
135°	602	1096	2155	2524	2709	468
145°	772	1152	2034	2452	2670	483
155°	937	1174	1811	2182	2296	431
165°	1063	1163	1461	1720	1801	298
175°	1126	1140	1160	1180	1204	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P1438959

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1037.2	1037.2	1037.2	1037.2	1037.2
2.5°	1030.2	1042.6	1033.4	1034.7	1036.5
5°	1024.5	1038.4	1026.1	1026.2	1033.2
7.5°	1017.2	1030.4	1014.8	1011.9	1018.4
10°	1007.0	1020.2	1004.6	999.2	1003.8
12.5°	993.7	1006.2	991.3	982.6	986.7
15°	972.1	980.6	965.7	956.2	957.8
17.5°	948.5	953.8	932.3	924.4	922.8
20°	930.8	935.4	910.1	899.0	897.4
22.5°	907.9	911.9	885.3	871.6	869.4
25°	873.6	874.4	849.0	829.8	825.1
27.5°	837.7	835.2	807.0	784.3	778.3
30°	811.6	808.5	775.9	751.9	746.5
32.5°	783.7	778.1	745.4	719.5	714.1
35°	742.5	734.0	699.7	672.5	666.3
37.5°	698.7	689.1	655.3	625.8	618.8
40°	669.5	658.6	624.2	594.7	587.7
42.5°	640.3	628.1	593.1	563.5	555.9
45°	594.8	582.4	547.2	518.4	510.6
47.5°	551.6	535.8	501.6	473.0	465.2
50°	521.8	504.7	471.7	443.8	436.0
52.5°	491.3	473.6	441.9	415.2	407.4
55°	444.7	428.4	397.1	372.3	365.3
57.5°	398.7	383.0	354.4	330.7	323.9
60°	366.9	353.7	326.4	304.0	297.8
62.5°	336.4	324.4	298.4	278.0	271.8
65°	291.5	280.6	257.3	238.9	234.3
67.5°	247.8	236.9	218.1	201.6	196.3
70°	219.2	208.3	191.4	176.2	171.5
72.5°	191.9	180.4	166.6	152.7	149.3
75°	150.9	141.6	131.0	120.6	117.5
77.5°	114.7	105.7	98.0	90.7	89.9
80°	90.5	82.8	77.0	72.3	71.5
82.5°	67.7	61.8	58.0	54.5	54.3
85°	34.9	32.6	31.8	27.8	26.2
87.5°	10.2	10.2	8.9	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.7	19.2	7.8	7.8	7.8
95°	43.7	110.1	34.0	24.3	24.3
97.5°	91.3	264.0	183.5	49.4	42.7
100°	126.2	382.5	315.5	72.5	58.3
102.5°	161.2	485.8	498.1	115.0	89.3
105°	213.6	598.1	864.1	216.8	145.6
107.5°	265.1	671.4	1324.3	447.4	269.9
110°	296.1	713.8	1669.9	697.5	417.5



TEST NUMBER: P1438959

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	327.2	756.3	1860.2	1118.2	720.4
115°	368.9	815.1	1970.9	1834.8	1398.1
117.5°	403.9	869.1	2066.0	2269.0	2140.8
120°	427.2	911.3	2116.5	2331.1	2373.8
122.5°	450.5	942.2	2143.7	2355.3	2436.0
125°	480.6	988.5	2150.5	2447.0	2461.2
127.5°	510.7	1023.3	2182.6	2531.3	2537.9
130°	534.0	1046.6	2213.6	2559.5	2611.7
132.5°	561.2	1066.2	2225.3	2575.6	2654.4
135°	601.9	1095.6	2155.4	2523.7	2708.8
137.5°	653.4	1116.7	2088.4	2522.2	2641.8
140°	684.5	1121.2	2053.4	2577.9	2587.4
142.5°	719.4	1133.3	2045.7	2571.8	2653.4
145°	771.9	1151.6	2034.0	2451.6	2669.9
147.5°	824.3	1163.2	1989.3	2318.9	2509.7
150°	859.2	1167.8	1946.6	2274.6	2393.2
152.5°	894.2	1172.3	1892.3	2247.0	2346.6
155°	936.9	1174.2	1810.7	2182.2	2296.1
157.5°	981.6	1168.6	1712.6	2064.0	2188.4
160°	1004.9	1161.5	1650.5	1978.2	2087.4
162.5°	1028.2	1158.2	1596.1	1866.0	1994.2
165°	1063.1	1162.8	1461.2	1720.3	1801.0
167.5°	1086.4	1158.6	1335.0	1547.3	1661.2
170°	1102.0	1158.9	1257.3	1414.8	1509.7
172.5°	1113.6	1140.2	1210.7	1293.7	1358.3
175°	1126.2	1140.5	1160.2	1180.2	1203.9
177.5°	1130.1	1137.7	1122.3	1118.6	1126.2
180°	1126.2	1126.2	1126.2	1126.2	1126.2

TEST NUMBER: P1438959

CATALOG NUMBER: CB2-B-125U-055D-940-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.04	14.71	15.19	15.85	17.44	12.94	13.61	14.09	14.75	16.34
	3H	15.67	16.27	16.83	17.42	19.02	14.46	15.05	15.61	16.20	17.81
	4H	16.29	16.86	17.46	18.01	19.62	15.02	15.59	16.19	16.73	18.35
	6H	16.69	17.21	17.86	18.35	19.98	15.38	15.90	16.56	17.05	18.68
	8H	16.83	17.32	18.00	18.49	20.10	15.52	16.01	16.69	17.17	18.79
	12H	16.90	17.37	18.08	18.52	20.16	15.57	16.04	16.75	17.20	18.84
4H	2H	14.43	15.00	15.60	16.14	17.75	13.55	14.12	14.73	15.27	16.88
	3H	16.28	16.75	17.46	17.92	19.55	15.27	15.74	16.45	16.91	18.54
	4H	17.02	17.45	18.20	18.61	20.26	15.94	16.37	17.12	17.53	19.17
	6H	17.53	17.90	18.71	19.08	20.71	16.40	16.77	17.59	17.95	19.59
	8H	17.73	18.07	18.91	19.25	20.90	16.59	16.93	17.77	18.11	19.76
	12H	17.82	18.14	19.02	19.32	20.98	16.67	16.98	17.86	18.16	19.82
8H	4H	17.16	17.51	18.34	18.68	20.33	16.19	16.54	17.38	17.71	19.37
	6H	17.79	18.08	19.00	19.29	20.94	16.79	17.08	17.99	18.29	19.94
	8H	18.08	18.33	19.29	19.52	21.19	17.07	17.31	18.27	18.51	20.17
	12H	18.25	18.47	19.46	19.66	21.36	17.21	17.42	18.42	18.61	20.31
12H	4H	17.13	17.44	18.33	18.63	20.28	16.19	16.50	17.39	17.69	19.34
	6H	17.82	18.07	19.03	19.26	20.93	16.85	17.10	18.06	18.29	19.96
	8H	18.13	18.35	19.34	19.54	21.24	17.15	17.37	18.36	18.56	20.26