

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439079

Luminaire Tested: CB2-D-125U-030D-940-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439079
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-125U-030D-940-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6793.4 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439079

CATALOG NUMBER: CB2-D-125U-030D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439079

CATALOG NUMBER: CB2-D-125U-030D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19				
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16				
2	83	76	70	65	73	67	62	58	51	47	45	35	33	32	21	20	20	13				
3	75	67	60	54	66	59	53	49	45	41	38	31	29	27	19	18	17	11				
4	69	59	51	46	60	52	46	41	40	35	32	28	25	23	17	16	14	10				
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9				
6	58	47	39	34	51	41	35	30	32	27	24	22	20	17	14	12	11	8				
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7				
8	49	38	31	26	44	34	27	23	26	21	18	19	16	13	12	10	9	6				
9	46	34	27	23	40	31	25	20	24	19	16	17	14	12	11	9	8	5				
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9456	9456	9456
5°	9377	9391	9455
10°	9322	9301	9294
15°	9175	9115	9039
20°	9030	8830	8708
25°	8788	8540	8300
30°	8546	8169	7860
35°	8265	7786	7416
40°	7967	7428	6994
45°	7670	7055	6584
50°	7400	6690	6183
55°	7069	6313	5806
60°	6692	5953	5431
65°	6289	5551	5053
70°	5841	5103	4573
75°	5316	4616	4139
80°	4754	4042	3751
85°	3657	3317	2738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7670 cd/sqm



TEST NUMBER: P1439079

CATALOG NUMBER: CB2-D-125U-030D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.1	0.8
10°-20°	142.3	2.1
20°-30°	204.6	3.0
30°-40°	230.0	3.4
40°-50°	222.2	3.3
50°-60°	187.7	2.8
60°-70°	134.8	2.0
70°-80°	73.7	1.1
80°-90°	19.7	0.3
90°-100°	83.7	1.2
100°-110°	345.3	5.1
110°-120°	626.8	9.2
120°-130°	853.0	12.6
130°-140°	984.7	14.5
140°-150°	992.3	14.6
150°-160°	856.3	12.6
160°-170°	580.4	8.5
170°-180°	204.7	3.0
0°-30°	398.0	5.9
0°-40°	628.0	9.2
0°-60°	1037.9	15.3
0°-90°	1266.1	18.6
90°-120°	1055.9	15.5
90°-150°	3885.8	57.2
90°-180°	5527.0	81.4
0°-180°	6793.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	543	543	543	543	543	
5°	536	544	537	537	541	51
15°	509	513	506	500	501	143
25°	457	458	444	434	432	211
35°	389	384	366	352	349	243
45°	311	305	286	271	267	241
55°	233	224	208	195	191	208
65°	153	147	135	125	123	151
75°	79	74	69	63	62	84
85°	18	17	17	14	14	22
90°	0	0	2	0	2	4
95°	81	71	68	52	52	94
105°	342	336	328	309	306	362
115°	649	648	636	617	615	641
125°	965	975	955	935	937	862
135°	1286	1301	1280	1256	1264	991
145°	1594	1612	1587	1569	1581	996
155°	1865	1883	1856	1845	1860	857
165°	2061	2082	2056	2044	2062	580
175°	2159	2182	2154	2140	2145	205
180°	2167	2167	2167	2167	2167	

TEST NUMBER: P1439079

CATALOG NUMBER: CB2-D-125U-030D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	542.9	542.9	542.9	542.9	542.9
2.5°	539.3	545.8	540.9	541.6	542.6
5°	536.3	543.6	537.1	537.2	540.8
7.5°	532.4	539.4	531.2	529.7	533.1
10°	527.1	534.0	525.9	523.0	525.5
12.5°	520.1	526.7	518.9	514.4	516.5
15°	508.8	513.3	505.5	500.5	501.3
17.5°	496.5	499.3	488.0	483.9	483.1
20°	487.2	489.7	476.4	470.6	469.8
22.5°	475.2	477.4	463.4	456.3	455.1
25°	457.3	457.7	444.4	434.4	431.9
27.5°	438.5	437.2	422.4	410.6	407.4
30°	424.9	423.2	406.2	393.6	390.8
32.5°	410.2	407.3	390.2	376.7	373.8
35°	388.7	384.2	366.2	352.0	348.8
37.5°	365.7	360.7	343.0	327.6	323.9
40°	350.4	344.8	326.7	311.3	307.6
42.5°	335.1	328.8	310.5	295.0	291.0
45°	311.4	304.9	286.4	271.4	267.3
47.5°	288.8	280.5	262.6	247.6	243.5
50°	273.1	264.2	246.9	232.3	228.2
52.5°	257.2	247.9	231.3	217.3	213.3
55°	232.8	224.3	207.9	194.9	191.2
57.5°	208.7	200.5	185.5	173.1	169.5
60°	192.1	185.1	170.9	159.1	155.9
62.5°	176.1	169.8	156.2	145.5	142.3
65°	152.6	146.9	134.7	125.1	122.6
67.5°	129.7	124.0	114.2	105.5	102.8
70°	114.7	109.0	100.2	92.2	89.8
72.5°	100.4	94.4	87.2	79.9	78.2
75°	79.0	74.1	68.6	63.2	61.5
77.5°	60.0	55.3	51.3	47.5	47.1
80°	47.4	43.3	40.3	37.8	37.4
82.5°	35.4	32.3	30.3	28.5	28.4
85°	18.3	17.1	16.6	14.5	13.7
87.5°	5.3	5.3	5.0	4.0	4.3
90°	0.0	0.0	1.7	0.0	1.7
92.5°	20.3	17.6	16.6	10.9	12.5
95°	81.1	71.2	67.6	52.4	52.4
97.5°	153.2	143.2	137.9	122.3	119.0
100°	204.6	194.6	189.3	172.4	169.1
102.5°	257.3	252.7	243.4	225.1	221.8
105°	341.5	336.5	328.0	309.3	306.0
107.5°	428.0	429.0	416.2	400.9	396.3
110°	490.3	488.6	478.4	463.1	459.8



TEST NUMBER: P1439079

CATALOG NUMBER: CB2-D-125U-030D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	550.8	540.6	525.3	522.0
115°	649.2	647.5	635.6	617.0	615.4
117.5°	739.8	745.1	731.0	711.4	710.7
120°	804.7	811.3	794.6	777.6	774.3
122.5°	868.3	876.2	859.5	839.9	840.5
125°	965.3	975.2	955.2	934.9	936.6
127.5°	1059.0	1071.2	1052.5	1031.9	1033.9
130°	1122.5	1137.4	1117.4	1095.5	1098.8
132.5°	1187.4	1202.3	1182.4	1159.2	1165.1
135°	1286.5	1301.4	1279.7	1256.3	1264.5
137.5°	1379.8	1394.7	1371.0	1351.3	1361.2
140°	1442.0	1456.9	1431.9	1413.5	1423.4
142.5°	1502.9	1520.4	1494.1	1474.4	1487.0
145°	1594.2	1612.4	1587.4	1569.1	1580.7
147.5°	1680.7	1698.9	1673.6	1656.0	1667.9
150°	1736.2	1754.4	1727.7	1712.8	1726.0
152.5°	1787.6	1808.4	1780.5	1765.6	1782.8
155°	1864.7	1882.8	1856.2	1844.7	1859.6
157.5°	1931.6	1952.8	1926.2	1916.3	1928.2
160°	1976.2	1996.1	1969.5	1959.6	1972.9
162.5°	2010.0	2031.2	2006.0	1994.9	2010.7
165°	2060.8	2082.3	2055.7	2044.3	2062.5
167.5°	2100.7	2123.5	2096.6	2084.9	2103.4
170°	2125.0	2146.5	2118.2	2105.2	2125.0
172.5°	2141.2	2164.0	2134.5	2121.2	2134.5
175°	2158.8	2182.0	2153.7	2140.3	2145.3
177.5°	2167.3	2185.8	2163.2	2151.4	2167.3
180°	2167.3	2167.3	2167.3	2167.3	2167.3



TEST NUMBER: P1439079
 CATALOG NUMBER: CB2-D-125U-030D-940-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.71	11.34	11.90	12.51	14.17	9.61	10.24	10.80	11.41	13.07
	3H	12.33	12.90	13.53	14.08	15.75	11.12	11.68	12.31	12.86	14.53
	4H	12.95	13.49	14.15	14.66	16.34	11.68	12.22	12.88	13.39	15.07
	6H	13.34	13.84	14.55	15.01	16.70	12.04	12.53	13.25	13.71	15.40
	8H	13.48	13.95	14.69	15.15	16.82	12.17	12.64	13.38	13.83	15.51
	12H	13.55	14.00	14.76	15.18	16.88	12.23	12.67	13.44	13.86	15.56
4H	2H	11.09	11.63	12.30	12.80	14.48	10.21	10.75	11.42	11.93	13.60
	3H	12.94	13.38	14.15	14.58	16.27	11.93	12.38	13.14	13.58	15.26
	4H	13.67	14.09	14.89	15.27	16.98	12.59	13.01	13.81	14.19	15.90
	6H	14.18	14.53	15.40	15.74	17.44	13.05	13.41	14.27	14.62	16.31
	8H	14.38	14.71	15.59	15.91	17.62	13.24	13.57	14.45	14.77	16.48
	12H	14.47	14.77	15.70	15.98	17.70	13.31	13.61	14.55	14.82	16.54
8H	4H	13.81	14.14	15.03	15.34	17.05	12.85	13.18	14.06	14.38	16.09
	6H	14.44	14.71	15.68	15.96	17.66	13.44	13.71	14.68	14.96	16.66
	8H	14.73	14.97	15.97	16.19	17.91	13.71	13.95	14.95	15.17	16.90
	12H	14.89	15.10	16.14	16.32	18.08	13.85	14.06	15.09	15.28	17.03
12H	4H	13.78	14.08	15.01	15.29	17.00	12.84	13.14	14.07	14.35	16.07
	6H	14.47	14.70	15.71	15.92	17.65	13.50	13.74	14.74	14.96	16.69
	8H	14.77	14.98	16.02	16.20	17.96	13.80	14.00	15.04	15.22	16.98