

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439322

Luminaire Tested: CB3-125U-030D-930-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439322
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-125U-030D-930-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
3-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14442.1 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 109.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439322

CATALOG NUMBER: CB3-125U-030D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1439322

CATALOG NUMBER: CB3-125U-030D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	99	99	99	99	87	87	87	87	65	65	65	44	44	44	25	25	25	16																				
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	22	22	21	14																				
2	82	75	70	65	72	66	62	58	50	46	44	34	32	31	20	19	18	12																				
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	18	16	15	10																				
4	68	58	51	45	60	52	45	41	39	35	31	27	24	22	16	14	13	9																				
5	63	52	44	39	55	46	39	35	34	30	27	24	21	19	14	13	12	8																				
6	58	46	39	33	50	41	35	30	31	26	23	22	19	17	13	11	10	7																				
7	53	42	34	29	47	37	30	26	28	23	20	19	17	15	12	10	9	6																				
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5																				
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5																				
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5607	5607	5607
5°	5580	5584	5616
10°	5556	5548	5548
15°	5471	5471	5438
20°	5382	5327	5280
25°	5247	5180	5088
30°	5118	4984	4865
35°	4983	4798	4628
40°	4803	4574	4377
45°	4640	4376	4105
50°	4473	4138	3841
55°	4290	3909	3589
60°	4094	3672	3305
65°	3863	3401	3005
70°	3598	3085	2678
75°	3261	2708	2385
80°	2844	2271	2111
85°	2194	1921	1921

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4640 cd/sqm



TEST NUMBER: P1439322

CATALOG NUMBER: CB3-125U-030D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	0.6
10°-20°	262.7	1.8
20°-30°	381.7	2.6
30°-40°	434.0	3.0
40°-50°	421.3	2.9
50°-60°	355.7	2.5
60°-70°	253.1	1.8
70°-80°	135.2	0.9
80°-90°	35.9	0.2
90°-100°	94.4	0.7
100°-110°	683.9	4.7
110°-120°	1626.0	11.3
120°-130°	2077.4	14.4
130°-140°	2240.8	15.5
140°-150°	2112.4	14.6
150°-160°	1723.3	11.9
160°-170°	1122.8	7.8
170°-180°	388.1	2.7
0°-30°	737.9	5.1
0°-40°	1171.9	8.1
0°-60°	1948.8	13.5
0°-90°	2373.0	16.4
90°-120°	2404.4	16.6
90°-150°	8835.0	61.2
90°-180°	12069.0	83.6
0°-180°	14442.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	991	991	991	991	991	
5°	983	995	983	982	989	93
15°	934	942	934	928	928	263
25°	840	843	830	819	815	387
35°	722	715	695	674	670	450
45°	580	571	547	521	513	447
55°	435	423	396	371	364	389
65°	289	278	254	231	224	286
75°	149	141	124	111	109	159
85°	34	31	30	30	30	40
90°	0	0	0	3	0	8
95°	173	31	40	43	43	213
105°	866	878	891	65	68	913
115°	1624	1636	1640	1664	1673	1602
125°	2308	2323	2318	2342	2358	2060
135°	2900	2915	2891	2913	2931	2233
145°	3375	3396	3353	3375	3393	2111
155°	3738	3768	3717	3726	3751	1724
165°	3985	4006	3963	3952	3979	1125
175°	4099	4120	4065	4044	4056	390
180°	4090	4090	4090	4090	4090	

TEST NUMBER: P1439322

CATALOG NUMBER: CB3-125U-030D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	991.1	991.1	991.1	991.1	991.1
2.5°	986.0	995.9	987.1	988.3	990.5
5°	982.6	995.0	983.3	982.1	989.0
7.5°	975.0	986.3	974.2	971.4	977.6
10°	967.2	979.5	965.7	962.3	965.7
12.5°	953.1	966.0	955.1	949.3	952.2
15°	934.1	942.3	934.1	928.4	928.4
17.5°	910.8	919.5	903.9	900.0	898.5
20°	894.0	901.5	884.8	879.1	877.1
22.5°	871.4	878.4	864.5	854.9	852.3
25°	840.5	843.2	829.9	818.6	815.1
27.5°	809.3	810.0	791.7	778.0	773.4
30°	783.4	784.1	763.0	748.2	744.7
32.5°	757.5	755.5	735.4	717.8	715.4
35°	721.5	714.6	694.7	674.2	670.1
37.5°	678.0	673.9	650.4	629.8	623.7
40°	650.4	643.5	619.4	598.9	592.7
42.5°	622.8	614.8	590.1	567.3	560.6
45°	580.0	571.1	546.9	520.7	513.1
47.5°	536.9	527.2	500.6	475.2	466.8
50°	508.2	497.9	470.2	445.4	436.4
52.5°	478.9	468.1	440.4	415.0	407.7
55°	435.0	423.3	396.3	370.8	363.9
57.5°	391.1	379.5	352.7	328.5	320.3
60°	361.8	350.8	324.5	300.4	292.1
62.5°	332.0	321.5	295.8	272.2	264.5
65°	288.6	278.3	254.1	231.4	224.5
67.5°	245.7	236.9	213.0	192.2	186.7
70°	217.5	209.2	186.5	167.4	161.9
72.5°	190.5	181.7	160.1	143.8	139.9
75°	149.2	141.0	123.9	111.2	109.1
77.5°	111.5	104.8	90.0	82.8	81.7
80°	87.3	81.1	69.7	64.8	64.8
82.5°	64.8	59.7	52.2	50.1	50.1
85°	33.8	31.0	29.6	29.6	29.6
87.5°	10.1	10.1	9.6	9.6	9.0
90°	0.0	0.0	0.0	3.0	0.0
92.5°	46.8	17.9	14.8	17.9	17.3
95°	172.6	31.0	40.1	43.1	43.1
97.5°	347.6	341.0	46.8	56.1	56.7
100°	480.8	495.8	49.3	58.6	61.6
102.5°	628.7	641.3	91.2	61.1	64.1
105°	866.0	878.0	890.6	64.8	67.8
107.5°	1102.1	1111.1	1119.3	1007.6	377.2
110°	1257.4	1266.4	1269.7	1300.7	1306.7

TEST NUMBER: P1439322

CATALOG NUMBER: CB3-125U-030D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1402.8	1414.3	1420.1	1446.2	1457.1
115°	1624.1	1636.2	1639.5	1664.4	1673.4
117.5°	1834.3	1846.9	1852.8	1872.8	1887.3
120°	1972.4	1987.4	1990.8	2015.8	2027.8
122.5°	2108.0	2125.4	2124.0	2146.6	2163.4
125°	2308.3	2323.3	2317.5	2342.5	2357.6
127.5°	2498.7	2507.8	2495.0	2525.5	2538.2
130°	2619.5	2628.6	2613.4	2641.5	2656.5
132.5°	2730.5	2744.3	2726.8	2752.4	2767.5
135°	2900.0	2915.0	2890.7	2912.7	2930.8
137.5°	3051.0	3069.1	3039.9	3065.5	3081.2
140°	3149.6	3167.7	3131.1	3159.3	3177.3
142.5°	3240.8	3263.7	3219.9	3245.6	3266.1
145°	3374.6	3395.7	3353.0	3375.0	3393.1
147.5°	3501.5	3519.6	3478.7	3494.4	3507.1
150°	3578.0	3596.1	3550.2	3566.0	3581.1
152.5°	3639.6	3664.9	3619.3	3630.3	3652.6
155°	3738.2	3768.4	3716.7	3726.5	3750.6
157.5°	3828.8	3856.0	3804.2	3812.7	3833.8
160°	3883.1	3910.2	3858.4	3862.0	3883.1
162.5°	3925.0	3949.7	3905.3	3899.1	3925.0
165°	3984.8	4005.9	3963.2	3951.5	3978.6
167.5°	4034.7	4058.8	4006.3	3996.6	4027.3
170°	4061.8	4085.9	4031.0	4016.3	4049.5
172.5°	4079.1	4100.8	4048.3	4028.5	4054.4
175°	4098.8	4119.9	4064.9	4043.6	4055.7
177.5°	4104.4	4121.2	4077.2	4058.2	4087.1
180°	4089.6	4089.6	4089.6	4089.6	4089.6



TEST NUMBER: P1439322

CATALOG NUMBER: CB3-125U-030D-930-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.56	9.18	9.76	10.36	12.04	7.48	8.10	8.68	9.28	10.96
	3H	10.21	10.76	11.41	11.95	13.64	8.88	9.43	10.08	10.62	12.31
	4H	10.83	11.35	12.04	12.54	14.24	9.38	9.91	10.60	11.09	12.79
	6H	11.20	11.68	12.42	12.87	14.58	9.69	10.17	10.91	11.36	13.07
	8H	11.33	11.79	12.55	12.99	14.69	9.80	10.26	11.03	11.47	13.17
	12H	11.39	11.83	12.61	13.02	14.74	9.87	10.31	11.10	11.50	13.23
4H	2H	8.94	9.46	10.16	10.65	12.35	8.08	8.61	9.30	9.79	11.49
	3H	10.80	11.24	12.03	12.45	14.17	9.67	10.11	10.90	11.32	13.04
	4H	11.54	11.95	12.77	13.15	14.87	10.27	10.68	11.50	11.87	13.60
	6H	12.03	12.38	13.26	13.60	15.31	10.67	11.02	11.90	12.24	13.95
	8H	12.22	12.54	13.44	13.75	15.48	10.84	11.16	12.06	12.37	14.10
	12H	12.30	12.60	13.55	13.82	15.56	10.93	11.22	12.17	12.44	14.18
8H	4H	11.65	11.98	12.88	13.19	14.92	10.51	10.84	11.74	12.05	13.78
	6H	12.26	12.53	13.51	13.78	15.51	11.03	11.30	12.28	12.55	14.28
	8H	12.54	12.77	13.79	14.00	15.75	11.28	11.51	12.53	12.74	14.49
	12H	12.69	12.89	13.94	14.12	15.90	11.45	11.65	12.70	12.88	14.66
12H	4H	11.61	11.91	12.86	13.13	14.87	10.50	10.80	11.75	12.02	13.76
	6H	12.28	12.51	13.53	13.74	15.49	11.09	11.32	12.34	12.55	14.30
	8H	12.57	12.77	13.82	14.00	15.77	11.36	11.56	12.61	12.79	14.57