

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1057058

Luminaire Tested: CB3-0U-030D-830-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057058
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-0U-030D-830-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
3-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2119.2 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 16.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1057058

CATALOG NUMBER: CB3-OU-030D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1057058

CATALOG NUMBER: CB3-OU-030D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	96	98	95	93		94	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		83	79	76		80
3	91	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	72	64	58	82	71	63	57	69	62	56		66	60	56		64
5	78	65	56	50	75	64	56	50	62	55	49		60	54	49		58
6	72	59	50	44	70	58	50	44	56	49	43		54	48	43		53
7	67	54	45	39	65	53	45	39	51	44	39		50	43	38		48
8	62	49	41	35	61	48	40	35	47	40	35		46	39	34		45
9	58	45	37	32	57	45	37	32	43	36	31		42	36	31		41
10	55	42	34	29	53	41	34	29	40	33	29		39	33	29		38

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5008	5008	5008
5°	4984	4987	5016
10°	4962	4955	4955
15°	4886	4886	4857
20°	4807	4757	4716
25°	4685	4627	4544
30°	4571	4452	4345
35°	4450	4285	4133
40°	4290	4085	3909
45°	4144	3908	3667
50°	3995	3696	3431
55°	3832	3491	3206
60°	3656	3279	2952
65°	3451	3037	2684
70°	3214	2756	2392
75°	2914	2418	2129
80°	2541	2026	1883
85°	1960	1714	1714

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4144 cd/sqm

TEST NUMBER: P1057058

CATALOG NUMBER: CB3-OU-030D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	3.9
10°-20°	234.6	11.1
20°-30°	340.9	16.1
30°-40°	387.6	18.3
40°-50°	376.2	17.8
50°-60°	317.7	15.0
60°-70°	226.0	10.7
70°-80°	120.7	5.7
80°-90°	31.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.0	31.1
0°-40°	1046.6	49.4
0°-60°	1740.5	82.1
0°-90°	2119.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2119.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	885	885	885	885	885	
5°	878	889	878	877	883	83
15°	834	842	834	829	829	235
25°	751	753	741	731	728	346
35°	644	638	620	602	598	402
45°	518	510	488	465	458	400
55°	388	378	354	331	325	347
65°	258	248	227	207	200	255
75°	133	126	111	99	97	142
85°	30	28	26	26	26	37
90°	0	0	0	0	0	

TEST NUMBER: P1057058

CATALOG NUMBER: CB3-OU-030D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	885.2	885.2	885.2	885.2	885.2
2.5°	880.6	889.5	881.6	882.7	884.7
5°	877.6	888.7	878.2	877.1	883.3
7.5°	870.8	880.9	870.1	867.6	873.1
10°	863.8	874.8	862.5	859.5	862.5
12.5°	851.2	862.8	853.0	847.9	850.5
15°	834.2	841.6	834.2	829.2	829.2
17.5°	813.5	821.2	807.3	803.8	802.4
20°	798.4	805.2	790.2	785.2	783.3
22.5°	778.3	784.6	772.1	763.5	761.2
25°	750.6	753.1	741.2	731.1	728.0
27.5°	722.8	723.5	707.1	694.8	690.8
30°	699.7	700.3	681.5	668.2	665.1
32.5°	676.6	674.7	656.8	641.1	639.0
35°	644.4	638.2	620.5	602.2	598.5
37.5°	605.5	601.8	580.9	562.5	557.0
40°	580.9	574.7	553.2	534.9	529.3
42.5°	556.2	549.1	527.1	506.7	500.7
45°	518.0	510.0	488.5	465.1	458.3
47.5°	479.5	470.8	447.1	424.4	416.9
50°	453.9	444.7	419.9	397.8	389.8
52.5°	427.7	418.0	393.3	370.6	364.1
55°	388.5	378.1	353.9	331.2	325.0
57.5°	349.3	339.0	315.0	293.4	286.0
60°	323.1	313.3	289.8	268.3	260.9
62.5°	296.5	287.1	264.2	243.1	236.3
65°	257.8	248.5	226.9	206.7	200.5
67.5°	219.4	211.5	190.2	171.6	166.7
70°	194.3	186.9	166.6	149.5	144.6
72.5°	170.1	162.2	143.0	128.4	125.0
75°	133.3	125.9	110.6	99.3	97.4
77.5°	99.6	93.6	80.3	73.9	72.9
80°	78.0	72.4	62.2	57.8	57.8
82.5°	57.8	53.3	46.6	44.8	44.8
85°	30.2	27.7	26.4	26.4	26.4
87.5°	9.1	9.1	8.5	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)