

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439396

Luminaire Tested: CB3-B-030U-120D-930-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1439396  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-2, G2-2312-242-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB3-B-030U-120D-930-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT  
3-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12839.3 lumens  
Efficiency: N/A  
Efficacy: 135.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 94.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1439396

CATALOG NUMBER: CB3-B-030U-120D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1439396

CATALOG NUMBER: CB3-B-030U-120D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77																												
1	104	100	96	92	99	95	92	88	87	84	81	79	77	75	72	70	69	65																												
2	95	87	81	76	90	84	78	73	76	72	68	70	66	63	64	61	58	55																												
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	57	53	50	47																												
4	80	69	60	54	76	66	58	53	60	54	49	55	50	46	51	47	43	40																												
5	73	61	53	47	70	59	51	45	54	48	43	50	45	40	46	41	38	35																												
6	68	55	47	41	64	53	45	40	49	43	38	45	40	36	42	37	34	31																												
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	34	30	28																												
8	59	46	38	32	56	44	37	32	41	35	30	38	32	28	35	30	27	25																												
9	55	42	34	29	52	41	33	28	38	31	27	35	30	26	33	28	24	22																												
10	51	39	31	26	49	37	30	26	35	29	25	33	27	23	30	26	22	20																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23274	23274	23274
5°	23164	23181	23313
10°	23063	23029	23029
15°	22709	22709	22572
20°	22340	22112	21918
25°	21777	21503	21120
30°	21244	20690	20194
35°	20684	19917	19210
40°	19938	18989	18169
45°	19262	18164	17041
50°	18567	17178	15944
55°	17810	16225	14899
60°	16992	15241	13720
65°	16037	14120	12477
70°	14935	12808	11115
75°	13539	11242	9900
80°	11803	9425	8757
85°	9107	7964	7964

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19262 cd/sqm



TEST NUMBER: P1439396

CATALOG NUMBER: CB3-B-030U-120D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	388.2	3.0
10°-20°	1090.5	8.5
20°-30°	1584.4	12.3
30°-40°	1801.4	14.0
40°-50°	1748.7	13.6
50°-60°	1476.4	11.5
60°-70°	1050.4	8.2
70°-80°	561.2	4.4
80°-90°	148.3	1.2
90°-100°	34.4	0.3
100°-110°	180.1	1.4
110°-120°	453.4	3.5
120°-130°	699.6	5.4
130°-140°	640.4	5.0
140°-150°	472.6	3.7
150°-160°	301.3	2.3
160°-170°	158.6	1.2
170°-180°	49.4	0.4
0°-30°	3063.1	23.9
0°-40°	4864.4	37.9
0°-60°	8089.5	63.0
0°-90°	9849.4	76.7
90°-120°	668.0	5.2
90°-150°	2480.6	19.3
90°-180°	2990.0	23.3
0°-180°	12839.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4114	4114	4114	4114	4114	
5°	4079	4130	4082	4077	4105	387
15°	3877	3912	3877	3854	3854	1092
25°	3489	3500	3445	3398	3384	1607
35°	2995	2966	2884	2799	2782	1866
45°	2408	2370	2270	2162	2130	1857
55°	1806	1757	1645	1539	1511	1614
65°	1198	1155	1055	961	932	1187
75°	619	585	514	462	453	660
85°	140	129	123	123	123	166
90°	0	0	0	0	0	7
95°	18	51	20	11	11	23
105°	92	284	206	85	69	98
115°	175	356	855	372	282	170
125°	233	360	1120	1129	1044	208
135°	300	401	907	1237	1265	232
145°	378	438	757	1052	1151	235
155°	437	470	649	804	887	201
165°	484	497	522	610	652	136
175°	511	522	506	508	513	48
180°	508	508	508	508	508	

TEST NUMBER: P1439396

CATALOG NUMBER: CB3-B-030U-120D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4114.0	4114.0	4114.0	4114.0	4114.0
2.5°	4093.0	4134.1	4097.6	4102.5	4111.7
5°	4078.9	4130.4	4081.9	4076.7	4105.2
7.5°	4047.4	4094.2	4043.9	4032.2	4057.9
10°	4014.7	4066.1	4008.8	3994.5	4008.8
12.5°	3956.2	4009.9	3964.4	3940.7	3952.7
15°	3877.3	3911.6	3877.3	3854.0	3854.0
17.5°	3780.9	3816.9	3752.3	3735.8	3729.5
20°	3710.8	3742.2	3672.8	3649.2	3640.7
22.5°	3617.3	3646.4	3588.6	3548.7	3537.8
25°	3488.7	3500.1	3444.9	3397.8	3383.5
27.5°	3359.6	3362.4	3286.5	3229.4	3210.6
30°	3252.0	3254.9	3167.3	3105.6	3091.3
32.5°	3144.5	3136.0	3052.8	2979.5	2969.8
35°	2994.9	2966.4	2883.9	2798.8	2781.6
37.5°	2814.4	2797.2	2699.8	2614.5	2588.8
40°	2699.8	2671.2	2571.3	2485.9	2460.2
42.5°	2585.3	2552.1	2449.7	2355.0	2327.0
45°	2407.6	2370.5	2270.3	2161.5	2130.0
47.5°	2228.8	2188.2	2078.0	1972.6	1937.8
50°	2109.6	2066.7	1951.8	1848.7	1811.6
52.5°	1988.0	1942.9	1827.9	1722.6	1692.4
55°	1805.7	1757.2	1645.0	1539.2	1510.6
57.5°	1623.4	1575.4	1463.9	1363.7	1329.5
60°	1501.8	1456.1	1347.0	1246.9	1212.6
62.5°	1378.0	1334.5	1227.8	1130.0	1098.0
65°	1198.0	1155.1	1054.8	960.6	932.1
67.5°	1019.7	983.2	884.2	797.7	774.9
70°	902.9	868.6	774.3	694.9	672.0
72.5°	790.7	754.1	664.4	596.9	580.9
75°	619.4	585.2	514.3	461.5	452.9
77.5°	462.8	434.8	373.4	343.5	338.9
80°	362.3	336.6	289.3	268.8	268.8
82.5°	268.8	247.7	216.8	208.0	208.0
85°	140.3	128.8	122.7	122.7	122.7
87.5°	42.1	42.1	39.7	37.4	37.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.4	12.4	3.6	1.8	3.6
95°	17.9	50.8	20.2	11.2	11.2
97.5°	37.2	113.4	52.0	27.7	25.1
100°	51.5	161.0	80.6	40.2	35.8
102.5°	67.6	208.6	121.8	54.5	46.6
105°	91.8	284.5	206.0	84.7	69.4
107.5°	118.7	336.3	339.5	130.6	105.2
110°	136.6	357.7	452.3	171.5	132.1



TEST NUMBER: P1439396

CATALOG NUMBER: CB3-B-030U-120D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	152.7	363.4	602.8	233.9	180.5
115°	174.7	356.4	855.4	371.9	282.2
117.5°	190.8	339.2	1047.1	591.7	456.4
120°	201.5	339.5	1124.2	757.9	606.9
122.5°	214.1	341.5	1145.6	923.0	784.2
125°	232.9	359.9	1119.7	1128.9	1043.5
127.5°	251.7	373.4	1049.8	1213.6	1186.9
130°	264.2	382.5	994.3	1242.4	1222.7
132.5°	276.8	391.5	954.9	1243.1	1253.1
135°	300.1	400.8	906.9	1236.8	1265.2
137.5°	323.8	412.3	862.1	1197.6	1256.7
140°	338.1	421.3	826.3	1155.2	1240.6
142.5°	354.3	428.7	792.3	1115.9	1206.6
145°	378.4	437.6	756.9	1052.5	1151.0
147.5°	397.3	442.4	717.0	988.5	1070.0
150°	409.8	442.6	700.9	931.6	1032.3
152.5°	420.5	451.6	681.2	879.5	971.4
155°	436.7	469.5	649.4	803.6	886.8
157.5°	452.8	484.3	611.8	747.0	803.5
160°	463.5	489.8	586.7	719.7	756.9
162.5°	472.5	495.3	559.8	673.2	715.7
165°	483.7	496.8	521.8	610.0	651.6
167.5°	494.0	500.6	524.9	548.1	581.8
170°	499.4	505.9	519.5	542.2	553.1
172.5°	504.7	514.8	512.4	527.8	537.0
175°	510.6	521.5	506.1	508.4	512.8
177.5°	511.9	517.2	513.7	513.8	519.1
180°	508.3	508.3	508.3	508.3	508.3



TEST NUMBER: P1439396  
 CATALOG NUMBER: CB3-B-030U-120D-930-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.27	21.41	20.96	22.12	22.95	19.19	20.33	19.88	21.04	21.87
	3H	21.95	22.98	22.66	23.70	24.57	20.62	21.65	21.33	22.37	23.23
	4H	22.60	23.57	23.32	24.30	25.17	21.15	22.12	21.88	22.85	23.73
	6H	23.00	23.89	23.73	24.63	25.52	21.48	22.38	22.22	23.12	24.01
	8H	23.14	23.99	23.89	24.75	25.65	21.62	22.47	22.36	23.23	24.12
	12H	23.22	24.03	23.97	24.78	25.70	21.70	22.51	22.45	23.27	24.19
4H	2H	20.71	21.68	21.43	22.41	23.28	19.85	20.82	20.58	21.55	22.42
	3H	22.62	23.43	23.36	24.20	25.09	21.49	22.30	22.23	23.07	23.96
	4H	23.38	24.12	24.14	24.88	25.81	22.11	22.85	22.87	23.61	24.54
	6H	23.90	24.54	24.67	25.33	26.26	22.54	23.18	23.31	23.97	24.90
	8H	24.10	24.69	24.88	25.48	26.42	22.72	23.31	23.49	24.10	25.04
	12H	24.21	24.74	25.01	25.55	26.50	22.83	23.37	23.63	24.18	25.13
8H	4H	23.53	24.13	24.31	24.92	25.86	22.40	22.99	23.17	23.78	24.72
	6H	24.16	24.66	24.97	25.49	26.43	22.94	23.43	23.74	24.26	25.20
	8H	24.44	24.88	25.26	25.71	26.67	23.19	23.63	24.01	24.46	25.42
	12H	24.62	25.01	25.44	25.82	26.84	23.38	23.76	24.20	24.58	25.60
12H	4H	23.52	24.06	24.32	24.86	25.81	22.41	22.94	23.21	23.75	24.70
	6H	24.18	24.62	25.00	25.45	26.41	22.99	23.43	23.81	24.26	25.22
	8H	24.50	24.88	25.32	25.70	26.72	23.29	23.68	24.11	24.49	25.51