

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439314

Luminaire Tested: CB3-125U-030D-830-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439314
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-125U-030D-830-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
3-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12898.4 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 109.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439314

CATALOG NUMBER: CB3-125U-030D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1439314

CATALOG NUMBER: CB3-125U-030D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	99	99	99	99	87	87	87	87	65	65	65	44	44	44	25	25	25	16																				
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	22	22	21	14																				
2	82	75	70	65	72	66	62	58	50	46	44	34	32	31	20	19	18	12																				
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	18	16	15	10																				
4	68	58	51	45	60	52	45	41	39	35	31	27	24	22	16	14	13	9																				
5	63	52	44	39	55	46	39	35	34	30	27	24	21	19	14	13	12	8																				
6	58	46	39	33	50	41	35	30	31	26	23	22	19	17	13	11	10	7																				
7	53	42	34	29	47	37	30	26	28	23	20	19	17	15	12	10	9	6																				
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5																				
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5																				
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5008	5008	5008
5°	4984	4987	5016
10°	4962	4955	4955
15°	4886	4886	4857
20°	4807	4757	4716
25°	4685	4627	4544
30°	4571	4452	4345
35°	4450	4285	4133
40°	4290	4085	3909
45°	4144	3908	3667
50°	3995	3696	3431
55°	3832	3491	3206
60°	3656	3279	2952
65°	3451	3037	2684
70°	3214	2756	2392
75°	2914	2418	2129
80°	2541	2026	1883
85°	1960	1714	1714

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4144 cd/sqm



TEST NUMBER: P1439314

CATALOG NUMBER: CB3-125U-030D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	0.6
10°-20°	234.6	1.8
20°-30°	340.9	2.6
30°-40°	387.6	3.0
40°-50°	376.2	2.9
50°-60°	317.7	2.5
60°-70°	226.0	1.8
70°-80°	120.7	0.9
80°-90°	32.0	0.2
90°-100°	84.3	0.7
100°-110°	610.8	4.7
110°-120°	1452.2	11.3
120°-130°	1855.3	14.4
130°-140°	2001.3	15.5
140°-150°	1886.6	14.6
150°-160°	1539.1	11.9
160°-170°	1002.8	7.8
170°-180°	346.7	2.7
0°-30°	659.0	5.1
0°-40°	1046.6	8.1
0°-60°	1740.5	13.5
0°-90°	2119.3	16.4
90°-120°	2147.4	16.6
90°-150°	7890.7	61.2
90°-180°	10779.0	83.6
0°-180°	12898.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	885	885	885	885	885	
5°	878	889	878	877	883	83
15°	834	842	834	829	829	235
25°	751	753	741	731	728	346
35°	644	638	620	602	598	402
45°	518	510	488	465	458	400
55°	388	378	354	331	325	347
65°	258	248	227	207	200	255
75°	133	126	111	99	97	142
85°	30	28	26	26	26	36
90°	0	0	0	3	0	7
95°	154	28	36	38	38	190
105°	773	784	795	58	61	816
115°	1450	1461	1464	1486	1495	1431
125°	2062	2075	2070	2092	2106	1840
135°	2590	2604	2582	2601	2618	1995
145°	3014	3033	2995	3014	3030	1886
155°	3339	3366	3319	3328	3350	1540
165°	3559	3578	3540	3529	3553	1005
175°	3661	3680	3630	3611	3622	348
180°	3652	3652	3652	3652	3652	

TEST NUMBER: P1439314

CATALOG NUMBER: CB3-125U-030D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	885.2	885.2	885.2	885.2	885.2
2.5°	880.6	889.5	881.6	882.7	884.7
5°	877.6	888.7	878.2	877.1	883.3
7.5°	870.8	880.9	870.1	867.6	873.1
10°	863.8	874.8	862.5	859.5	862.5
12.5°	851.2	862.8	853.0	847.9	850.5
15°	834.2	841.6	834.2	829.2	829.2
17.5°	813.5	821.2	807.3	803.8	802.4
20°	798.4	805.2	790.2	785.2	783.3
22.5°	778.3	784.6	772.1	763.5	761.2
25°	750.6	753.1	741.2	731.1	728.0
27.5°	722.8	723.5	707.1	694.8	690.8
30°	699.7	700.3	681.5	668.2	665.1
32.5°	676.6	674.7	656.8	641.1	639.0
35°	644.4	638.2	620.5	602.2	598.5
37.5°	605.5	601.8	580.9	562.5	557.0
40°	580.9	574.7	553.2	534.9	529.3
42.5°	556.2	549.1	527.1	506.7	500.7
45°	518.0	510.0	488.5	465.1	458.3
47.5°	479.5	470.8	447.1	424.4	416.9
50°	453.9	444.7	419.9	397.8	389.8
52.5°	427.7	418.0	393.3	370.6	364.1
55°	388.5	378.1	353.9	331.2	325.0
57.5°	349.3	339.0	315.0	293.4	286.0
60°	323.1	313.3	289.8	268.3	260.9
62.5°	296.5	287.1	264.2	243.1	236.3
65°	257.8	248.5	226.9	206.7	200.5
67.5°	219.4	211.5	190.2	171.6	166.7
70°	194.3	186.9	166.6	149.5	144.6
72.5°	170.1	162.2	143.0	128.4	125.0
75°	133.3	125.9	110.6	99.3	97.4
77.5°	99.6	93.6	80.3	73.9	72.9
80°	78.0	72.4	62.2	57.8	57.8
82.5°	57.8	53.3	46.6	44.8	44.8
85°	30.2	27.7	26.4	26.4	26.4
87.5°	9.1	9.1	8.5	8.6	8.0
90°	0.0	0.0	0.0	2.7	0.0
92.5°	41.8	16.0	13.2	16.0	15.4
95°	154.1	27.6	35.8	38.5	38.5
97.5°	310.5	304.6	41.8	50.1	50.6
100°	429.4	442.8	44.0	52.4	55.0
102.5°	561.5	572.8	81.5	54.6	57.3
105°	773.4	784.2	795.4	57.9	60.6
107.5°	984.3	992.3	999.7	899.9	336.9
110°	1123.0	1131.1	1134.0	1161.6	1167.0

TEST NUMBER: P1439314

CATALOG NUMBER: CB3-125U-030D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1252.9	1263.1	1268.3	1291.6	1301.3
115°	1450.5	1461.3	1464.3	1486.5	1494.6
117.5°	1638.2	1649.5	1654.7	1672.7	1685.6
120°	1761.5	1775.0	1778.1	1800.3	1811.1
122.5°	1882.6	1898.3	1897.0	1917.1	1932.2
125°	2061.6	2075.0	2069.8	2092.1	2105.6
127.5°	2231.6	2239.7	2228.3	2255.6	2266.9
130°	2339.5	2347.6	2334.0	2359.1	2372.6
132.5°	2438.6	2451.0	2435.3	2458.2	2471.7
135°	2590.0	2603.5	2581.8	2601.4	2617.5
137.5°	2724.9	2741.0	2715.0	2737.9	2751.9
140°	2813.0	2829.1	2796.4	2821.6	2837.7
142.5°	2894.4	2914.9	2875.7	2898.7	2917.0
145°	3013.9	3032.7	2994.6	3014.2	3030.4
147.5°	3127.3	3143.4	3106.9	3120.9	3132.2
150°	3195.5	3211.7	3170.8	3184.8	3198.3
152.5°	3250.6	3273.2	3232.4	3242.2	3262.1
155°	3338.7	3365.6	3319.4	3328.1	3349.7
157.5°	3419.6	3443.8	3397.6	3405.2	3424.0
160°	3468.0	3492.3	3446.0	3449.2	3468.0
162.5°	3505.5	3527.5	3487.8	3482.3	3505.5
165°	3558.9	3577.7	3539.6	3529.1	3553.4
167.5°	3603.4	3625.0	3578.1	3569.4	3596.8
170°	3627.7	3649.2	3600.1	3587.1	3616.7
172.5°	3643.1	3662.5	3615.6	3597.9	3621.1
175°	3660.7	3679.5	3630.4	3611.4	3622.2
177.5°	3665.7	3680.7	3641.4	3624.4	3650.2
180°	3652.4	3652.4	3652.4	3652.4	3652.4



TEST NUMBER: P1439314

CATALOG NUMBER: CB3-125U-030D-830-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.17	8.79	9.37	9.96	11.65	7.09	7.71	8.29	8.89	10.57
	3H	9.81	10.37	11.02	11.56	13.25	8.48	9.04	9.69	10.22	11.92
	4H	10.43	10.96	11.65	12.15	13.85	8.99	9.52	10.20	10.70	12.40
	6H	10.81	11.29	12.03	12.48	14.19	9.29	9.78	10.51	10.97	12.68
	8H	10.94	11.40	12.16	12.60	14.30	9.41	9.87	10.63	11.07	12.77
	12H	11.00	11.43	12.22	12.63	14.35	9.48	9.91	10.70	11.11	12.83
4H	2H	8.54	9.07	9.77	10.26	11.96	7.68	8.21	8.91	9.40	11.10
	3H	10.41	10.85	11.64	12.06	13.77	9.28	9.72	10.51	10.93	12.64
	4H	11.15	11.56	12.38	12.75	14.48	9.88	10.28	11.10	11.48	13.21
	6H	11.64	11.99	12.87	13.21	14.92	10.28	10.62	11.50	11.84	13.56
	8H	11.82	12.15	13.05	13.36	15.09	10.44	10.76	11.67	11.98	13.71
	12H	11.91	12.20	13.15	13.43	15.16	10.53	10.83	11.78	12.05	13.79
8H	4H	11.26	11.58	12.49	12.79	14.53	10.12	10.44	11.35	11.65	13.39
	6H	11.87	12.14	13.11	13.39	15.12	10.64	10.91	11.88	12.16	13.89
	8H	12.14	12.37	13.39	13.60	15.35	10.89	11.12	12.14	12.35	14.10
	12H	12.30	12.50	13.55	13.73	15.50	11.05	11.26	12.31	12.48	14.26
12H	4H	11.22	11.52	12.46	12.74	14.47	10.11	10.41	11.35	11.63	13.36
	6H	11.88	12.12	13.13	13.34	15.09	10.69	10.92	11.94	12.15	13.90
	8H	12.17	12.38	13.42	13.60	15.38	10.96	11.17	12.22	12.39	14.17