

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1057065

Luminaire Tested: CB3-0U-085D-835-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057065
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-0U-085D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
3-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6741.9 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 51.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1057065

CATALOG NUMBER: CB3-OU-085D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1057065

CATALOG NUMBER: CB3-OU-085D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	96	98	95	93	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	72	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15931	15931	15931
5°	15855	15867	15958
10°	15786	15763	15763
15°	15544	15544	15450
20°	15292	15135	15003
25°	14906	14719	14457
30°	14541	14162	13823
35°	14158	13633	13150
40°	13648	12998	12436
45°	13185	12433	11665
50°	12709	11758	10913
55°	12191	11106	10199
60°	11631	10432	9391
65°	10977	9665	8540
70°	10222	8767	7609
75°	9268	7694	6776
80°	8080	6451	5995
85°	6231	5452	5452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13185 cd/sqm

TEST NUMBER: P1057065

CATALOG NUMBER: CB3-OU-085D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.7	3.9
10°-20°	746.4	11.1
20°-30°	1084.5	16.1
30°-40°	1233.0	18.3
40°-50°	1197.0	17.8
50°-60°	1010.6	15.0
60°-70°	719.0	10.7
70°-80°	384.2	5.7
80°-90°	101.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2096.6	31.1
0°-40°	3329.7	49.4
0°-60°	5537.2	82.1
0°-90°	6741.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6741.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2816	2816	2816	2816	2816	
5°	2792	2827	2794	2790	2810	265
15°	2654	2678	2654	2638	2638	748
25°	2388	2396	2358	2326	2316	1100
35°	2050	2030	1974	1916	1904	1277
45°	1648	1623	1554	1480	1458	1271
55°	1236	1203	1126	1054	1034	1105
65°	820	791	722	658	638	812
75°	424	400	352	316	310	452
85°	96	88	84	84	84	118
90°	0	0	0	0	0	

TEST NUMBER: P1057065

CATALOG NUMBER: CB3-OU-085D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2816.0	2816.0	2816.0	2816.0	2816.0
2.5°	2801.6	2829.8	2804.8	2808.1	2814.4
5°	2792.0	2827.2	2794.0	2790.4	2810.0
7.5°	2770.4	2802.5	2768.0	2760.0	2777.6
10°	2748.0	2783.2	2744.0	2734.2	2744.0
12.5°	2708.0	2744.8	2713.6	2697.4	2705.6
15°	2654.0	2677.5	2654.0	2638.0	2638.0
17.5°	2588.0	2612.6	2568.4	2557.1	2552.8
20°	2540.0	2561.5	2514.0	2497.9	2492.0
22.5°	2476.0	2495.9	2456.4	2429.0	2421.6
25°	2388.0	2395.8	2358.0	2325.8	2316.0
27.5°	2299.6	2301.6	2249.6	2210.5	2197.6
30°	2226.0	2228.0	2168.0	2125.8	2116.0
32.5°	2152.4	2146.5	2089.6	2039.4	2032.8
35°	2050.0	2030.4	1974.0	1915.7	1904.0
37.5°	1926.4	1914.7	1848.0	1789.6	1772.0
40°	1848.0	1828.4	1760.0	1701.6	1684.0
42.5°	1769.6	1746.9	1676.8	1612.0	1592.8
45°	1648.0	1622.6	1554.0	1479.5	1458.0
47.5°	1525.6	1497.8	1422.4	1350.3	1326.4
50°	1444.0	1414.7	1336.0	1265.4	1240.0
52.5°	1360.8	1329.9	1251.2	1179.1	1158.4
55°	1236.0	1202.8	1126.0	1053.6	1034.0
57.5°	1111.2	1078.3	1002.0	933.5	910.0
60°	1028.0	996.7	922.0	853.5	830.0
62.5°	943.2	913.5	840.4	773.5	751.6
65°	820.0	790.7	722.0	657.6	638.0
67.5°	698.0	673.0	605.2	546.0	530.4
70°	618.0	594.5	530.0	475.6	460.0
72.5°	541.2	516.2	454.8	408.6	397.6
75°	424.0	400.5	352.0	315.9	310.0
77.5°	316.8	297.6	255.6	235.1	232.0
80°	248.0	230.4	198.0	184.0	184.0
82.5°	184.0	169.5	148.4	142.4	142.4
85°	96.0	88.2	84.0	84.0	84.0
87.5°	28.8	28.8	27.2	25.6	25.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)