

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439149

Luminaire Tested: CB3-030U-120D-835-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1439149  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB3-030U-120D-835-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT  
3-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6143.1 lumens  
Efficiency: N/A  
Efficacy: 132.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 46.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1439149

CATALOG NUMBER: CB3-030U-120D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1439149

CATALOG NUMBER: CB3-030U-120D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	100	96	92	99	96	92	89	87	85	82	80	78	76	73	71	70	66
2	95	88	81	76	91	84	78	73	77	72	69	70	67	64	65	62	59	56
3	87	77	70	64	83	74	67	62	68	63	58	63	58	54	57	54	51	48
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	52	47	44	41
5	74	62	53	47	70	59	52	46	55	48	43	51	45	41	47	42	39	36
6	68	56	47	41	65	53	46	40	50	43	38	46	40	36	42	38	34	32
7	63	50	42	36	60	49	41	36	45	39	34	42	36	32	39	34	30	28
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	36	31	27	25
9	55	42	34	29	52	41	34	29	38	32	27	35	30	26	33	28	25	23
10	51	39	31	26	49	38	31	26	35	29	25	33	28	24	31	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	22679	22679	22679
5°	22571	22587	22717
10°	22473	22439	22439
15°	22128	22128	21995
20°	21768	21546	21357
25°	21219	20954	20580
30°	20700	20161	19677
35°	20154	19407	18719
40°	19429	18503	17703
45°	18769	17699	16606
50°	18092	16738	15536
55°	17355	15811	14519
60°	16558	14852	13369
65°	15627	13758	12157
70°	14553	12478	10831
75°	13194	10951	9648
80°	11500	9181	8536
85°	8867	7763	7763

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18769 cd/sqm



TEST NUMBER: P1439149

CATALOG NUMBER: CB3-030U-120D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.1	3.1
10°-20°	531.3	8.6
20°-30°	771.9	12.6
30°-40°	877.6	14.3
40°-50°	852.0	13.9
50°-60°	719.3	11.7
60°-70°	511.8	8.3
70°-80°	273.4	4.5
80°-90°	72.3	1.2
90°-100°	10.5	0.2
100°-110°	76.2	1.2
110°-120°	181.1	2.9
120°-130°	231.4	3.8
130°-140°	249.6	4.1
140°-150°	235.3	3.8
150°-160°	192.0	3.1
160°-170°	125.1	2.0
170°-180°	43.2	0.7
0°-30°	1492.3	24.3
0°-40°	2370.0	38.6
0°-60°	3941.3	64.2
0°-90°	4798.7	78.1
90°-120°	267.8	4.4
90°-150°	984.1	16.0
90°-180°	1344.0	21.9
0°-180°	6143.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2004	2004	2004	2004	2004	
5°	1987	2012	1989	1986	2000	189
15°	1889	1906	1889	1878	1878	532
25°	1700	1705	1678	1655	1648	783
35°	1459	1445	1405	1364	1355	909
45°	1173	1155	1106	1053	1038	905
55°	880	856	802	750	736	787
65°	584	563	514	468	454	578
75°	302	285	250	225	221	322
85°	68	63	60	60	60	81
90°	0	0	0	0	0	4
95°	19	3	4	5	5	24
105°	96	98	99	7	8	102
115°	181	182	183	185	186	178
125°	257	259	258	261	263	229
135°	323	325	322	324	326	249
145°	376	378	374	376	378	235
155°	416	420	414	415	418	192
165°	444	446	442	440	443	125
175°	457	459	453	450	452	43
180°	456	456	456	456	456	

TEST NUMBER: P1439149

CATALOG NUMBER: CB3-030U-120D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2004.4	2004.4	2004.4	2004.4	2004.4
2.5°	1994.1	2014.2	1996.4	1998.8	2003.2
5°	1987.3	2012.3	1988.7	1986.2	2000.1
7.5°	1971.9	1994.7	1970.2	1964.5	1977.0
10°	1956.0	1981.0	1953.1	1946.2	1953.1
12.5°	1927.5	1953.7	1931.5	1919.9	1925.8
15°	1889.1	1905.8	1889.1	1877.7	1877.7
17.5°	1842.1	1859.6	1828.1	1820.1	1817.0
20°	1807.9	1823.2	1789.4	1777.9	1773.7
22.5°	1762.4	1776.6	1748.4	1728.9	1723.6
25°	1699.7	1705.3	1678.4	1655.4	1648.5
27.5°	1636.8	1638.2	1601.2	1573.4	1564.2
30°	1584.4	1585.8	1543.1	1513.1	1506.1
32.5°	1532.0	1527.9	1487.3	1451.6	1446.9
35°	1459.1	1445.2	1405.0	1363.6	1355.2
37.5°	1371.2	1362.8	1315.4	1273.8	1261.3
40°	1315.4	1301.4	1252.7	1211.2	1198.6
42.5°	1259.6	1243.4	1193.5	1147.4	1133.7
45°	1173.0	1154.9	1106.1	1053.1	1037.8
47.5°	1085.9	1066.1	1012.4	961.1	944.1
50°	1027.8	1006.9	950.9	900.7	882.6
52.5°	968.6	946.6	890.6	839.3	824.5
55°	879.8	856.1	801.5	749.9	736.0
57.5°	790.9	767.5	713.2	664.4	647.7
60°	731.7	709.4	656.3	607.5	590.8
62.5°	671.3	650.2	598.2	550.6	535.0
65°	583.7	562.8	513.9	468.0	454.1
67.5°	496.8	479.0	430.8	388.7	377.5
70°	439.9	423.2	377.2	338.6	327.4
72.5°	385.2	367.4	323.7	290.8	283.0
75°	301.8	285.1	250.5	224.8	220.7
77.5°	225.5	211.8	181.9	167.4	165.1
80°	176.5	164.0	140.9	131.0	131.0
82.5°	131.0	120.7	105.6	101.4	101.4
85°	68.3	62.8	59.8	59.8	59.8
87.5°	20.5	20.5	19.4	18.3	18.2
90°	0.0	0.0	0.0	0.3	0.0
92.5°	5.2	2.0	1.6	2.0	1.9
95°	19.2	3.4	4.5	4.8	4.8
97.5°	38.7	38.0	5.2	6.2	6.3
100°	53.6	55.2	5.5	6.5	6.9
102.5°	70.0	71.4	10.2	6.8	7.1
105°	96.5	97.8	99.2	7.2	7.6
107.5°	122.8	123.8	124.7	112.2	42.0
110°	140.1	141.1	141.4	144.9	145.6



TEST NUMBER: P1439149

CATALOG NUMBER: CB3-030U-120D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	156.3	157.5	158.2	161.1	162.3
115°	180.9	182.3	182.6	185.4	186.4
117.5°	204.3	205.7	206.4	208.6	210.2
120°	219.7	221.4	221.8	224.5	225.9
122.5°	234.8	236.8	236.6	239.1	241.0
125°	257.1	258.8	258.2	260.9	262.6
127.5°	278.3	279.3	277.9	281.3	282.7
130°	291.8	292.8	291.1	294.2	295.9
132.5°	304.2	305.7	303.7	306.6	308.3
135°	323.0	324.7	322.0	324.5	326.5
137.5°	339.9	341.9	338.6	341.5	343.2
140°	350.8	352.9	348.8	351.9	353.9
142.5°	361.0	363.6	358.7	361.5	363.8
145°	375.9	378.2	373.5	375.9	378.0
147.5°	390.0	392.1	387.5	389.3	390.7
150°	398.6	400.6	395.5	397.2	398.9
152.5°	405.4	408.2	403.2	404.4	406.9
155°	416.4	419.8	414.0	415.1	417.8
157.5°	426.5	429.5	423.8	424.7	427.0
160°	432.5	435.6	429.8	430.2	432.5
162.5°	437.2	440.0	435.0	434.3	437.2
165°	443.9	446.2	441.5	440.2	443.2
167.5°	449.4	452.1	446.3	445.2	448.6
170°	452.5	455.1	449.0	447.4	451.1
172.5°	454.4	456.8	450.9	448.7	451.6
175°	456.6	458.9	452.8	450.4	451.8
177.5°	457.2	459.1	454.2	452.0	455.3
180°	455.5	455.5	455.5	455.5	455.5



TEST NUMBER: P1439149  
 CATALOG NUMBER: CB3-030U-120D-835-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.28	21.45	20.95	22.14	22.94	19.20	20.37	19.88	21.06	21.86
	3H	21.97	23.02	22.66	23.72	24.55	20.64	21.69	21.32	22.38	23.22
	4H	22.61	23.60	23.32	24.31	25.16	21.17	22.16	21.88	22.87	23.72
	6H	23.01	23.92	23.73	24.65	25.51	21.50	22.41	22.22	23.13	24.00
	8H	23.16	24.03	23.89	24.77	25.64	21.63	22.50	22.36	23.24	24.11
	12H	23.24	24.06	23.97	24.80	25.69	21.72	22.55	22.46	23.28	24.18
4H	2H	20.72	21.71	21.43	22.42	23.27	19.86	20.85	20.57	21.56	22.41
	3H	22.64	23.46	23.36	24.21	25.08	21.51	22.33	22.23	23.08	23.95
	4H	23.40	24.15	24.14	24.90	25.80	22.13	22.88	22.87	23.63	24.52
	6H	23.92	24.57	24.68	25.34	26.25	22.56	23.21	23.32	23.98	24.89
	8H	24.12	24.72	24.88	25.49	26.41	22.74	23.34	23.50	24.11	25.03
	12H	24.23	24.77	25.01	25.57	26.49	22.86	23.40	23.64	24.19	25.12
8H	4H	23.55	24.16	24.32	24.93	25.85	22.42	23.02	23.18	23.79	24.71
	6H	24.19	24.69	24.98	25.50	26.42	22.96	23.46	23.75	24.27	25.19
	8H	24.46	24.91	25.27	25.72	26.66	23.21	23.66	24.01	24.47	25.41
	12H	24.64	25.03	25.45	25.84	26.83	23.40	23.79	24.21	24.60	25.59
12H	4H	23.54	24.08	24.32	24.88	25.80	22.43	22.97	23.21	23.77	24.69
	6H	24.20	24.65	25.01	25.46	26.40	23.01	23.46	23.82	24.27	25.21
	8H	24.52	24.91	25.32	25.71	26.71	23.31	23.70	24.12	24.51	25.50