

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439363

Luminaire Tested: CB3-125U-120D-930-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1439363  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB3-125U-120D-930-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT  
3-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10959.4 lumens  
Efficiency: N/A  
Efficacy: 145.3 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 75.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1439363

CATALOG NUMBER: CB3-125U-120D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1439363

CATALOG NUMBER: CB3-125U-120D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45				
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32				
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27				
4	74	63	55	50	67	58	51	46	49	44	40	40	37	34	32	30	27	24				
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	26	24	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	30	25	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23274	23274	23274
5°	23164	23180	23313
10°	23062	23029	23029
15°	22709	22709	22572
20°	22340	22112	21918
25°	21778	21503	21121
30°	21244	20691	20194
35°	20684	19916	19210
40°	19938	18988	18169
45°	19262	18163	17041
50°	18567	17178	15944
55°	17811	16225	14899
60°	16992	15241	13720
65°	16037	14120	12476
70°	14933	12806	11115
75°	13539	11239	9897
80°	11807	9422	8757
85°	9100	7971	7971

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19262 cd/sqm



TEST NUMBER: P1439363

CATALOG NUMBER: CB3-125U-120D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	194.1	1.8
10°-20°	545.3	5.0
20°-30°	792.2	7.2
30°-40°	900.7	8.2
40°-50°	874.3	8.0
50°-60°	738.2	6.7
60°-70°	525.2	4.8
70°-80°	280.6	2.6
80°-90°	74.2	0.7
90°-100°	47.2	0.4
100°-110°	342.0	3.1
110°-120°	813.0	7.4
120°-130°	1038.7	9.5
130°-140°	1120.4	10.2
140°-150°	1056.2	9.6
150°-160°	861.6	7.9
160°-170°	561.4	5.1
170°-180°	194.1	1.8
0°-30°	1531.5	14.0
0°-40°	2432.2	22.2
0°-60°	4044.8	36.9
0°-90°	4924.8	44.9
90°-120°	1202.2	11.0
90°-150°	4417.5	40.3
90°-180°	6035.0	55.1
0°-180°	10959.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2057	2057	2057	2057	2057	
5°	2040	2065	2041	2038	2053	194
15°	1939	1956	1939	1927	1927	546
25°	1744	1750	1722	1699	1692	804
35°	1498	1483	1442	1399	1391	933
45°	1204	1185	1135	1081	1065	929
55°	903	879	822	770	755	807
65°	599	578	527	480	466	593
75°	310	293	257	231	226	330
85°	70	64	61	61	61	83
90°	0	0	0	2	0	6
95°	86	16	20	22	22	107
105°	433	439	445	32	34	457
115°	812	818	820	832	837	801
125°	1154	1162	1159	1171	1179	1030
135°	1450	1458	1445	1456	1465	1117
145°	1687	1698	1676	1688	1696	1056
155°	1869	1884	1858	1863	1875	862
165°	1992	2003	1982	1976	1989	563
175°	2049	2060	2032	2022	2028	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P1439363

CATALOG NUMBER: CB3-125U-120D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2057.0	2057.0	2057.0	2057.0	2057.0
2.5°	2046.5	2067.1	2048.8	2051.3	2055.8
5°	2039.5	2065.2	2040.9	2038.3	2052.6
7.5°	2023.7	2047.1	2021.9	2016.1	2029.0
10°	2007.3	2033.0	2004.4	1997.3	2004.4
12.5°	1978.1	2005.0	1982.2	1970.4	1976.4
15°	1938.7	1955.8	1938.7	1927.0	1927.0
17.5°	1890.5	1908.5	1876.1	1867.9	1864.7
20°	1855.4	1871.1	1836.4	1824.6	1820.3
22.5°	1808.6	1823.2	1794.3	1774.3	1768.9
25°	1744.4	1750.1	1722.4	1698.9	1691.8
27.5°	1679.8	1681.2	1643.3	1614.7	1605.3
30°	1626.0	1627.5	1583.7	1552.8	1545.7
32.5°	1572.3	1568.0	1526.4	1489.8	1484.9
35°	1497.5	1483.2	1441.9	1399.4	1390.8
37.5°	1407.2	1398.6	1349.9	1307.2	1294.4
40°	1349.9	1335.6	1285.6	1243.0	1230.1
42.5°	1292.6	1276.1	1224.9	1177.5	1163.5
45°	1203.8	1185.2	1135.1	1080.7	1065.0
47.5°	1114.4	1094.1	1039.0	986.3	968.9
50°	1054.8	1033.4	975.9	924.4	905.8
52.5°	994.0	971.5	914.0	861.3	846.2
55°	902.9	878.6	822.5	769.6	755.3
57.5°	811.7	787.7	731.9	681.9	664.7
60°	750.9	728.1	673.5	623.4	606.3
62.5°	689.0	667.3	613.9	565.0	549.0
65°	599.0	577.6	527.4	480.3	466.0
67.5°	509.9	491.6	442.1	398.9	387.4
70°	451.4	434.3	387.1	347.4	336.0
72.5°	395.3	377.0	332.2	298.4	290.4
75°	309.7	292.6	257.1	230.7	226.4
77.5°	231.4	217.4	186.7	171.8	169.5
80°	181.2	168.3	144.6	134.4	134.4
82.5°	134.4	123.8	108.4	104.0	104.0
85°	70.1	64.4	61.4	61.4	61.4
87.5°	21.0	21.0	19.9	19.0	18.7
90°	0.0	0.0	0.0	1.5	0.0
92.5°	23.4	9.0	7.4	8.9	8.6
95°	86.3	15.5	20.0	21.6	21.6
97.5°	173.8	170.5	23.4	28.1	28.4
100°	240.4	247.9	24.7	29.3	30.8
102.5°	314.3	320.7	45.6	30.5	32.1
105°	433.0	439.0	445.3	32.4	33.9
107.5°	551.0	555.5	559.7	503.8	188.6
110°	628.7	633.2	634.9	650.3	653.3



TEST NUMBER: P1439363

CATALOG NUMBER: CB3-125U-120D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	701.4	707.1	710.0	723.1	728.5
115°	812.1	818.1	819.8	832.2	836.7
117.5°	917.1	923.5	926.4	936.4	943.6
120°	986.2	993.7	995.4	1007.9	1013.9
122.5°	1054.0	1062.7	1062.0	1073.3	1081.7
125°	1154.1	1161.7	1158.8	1171.3	1178.8
127.5°	1249.4	1253.9	1247.5	1262.8	1269.1
130°	1309.8	1314.3	1306.7	1320.7	1328.3
132.5°	1365.2	1372.2	1363.4	1376.2	1383.7
135°	1450.0	1457.5	1445.4	1456.4	1465.4
137.5°	1525.5	1534.5	1519.9	1532.8	1540.6
140°	1574.8	1583.8	1565.6	1579.6	1588.7
142.5°	1620.4	1631.9	1609.9	1622.8	1633.0
145°	1687.3	1697.8	1676.5	1687.5	1696.5
147.5°	1750.8	1759.8	1739.4	1747.2	1753.5
150°	1789.0	1798.0	1775.1	1783.0	1790.5
152.5°	1819.8	1832.5	1809.6	1815.1	1826.3
155°	1869.1	1884.2	1858.3	1863.2	1875.3
157.5°	1914.4	1928.0	1902.1	1906.3	1916.9
160°	1941.5	1955.1	1929.2	1931.0	1941.5
162.5°	1962.5	1974.8	1952.6	1949.5	1962.5
165°	1992.4	2002.9	1981.6	1975.7	1989.3
167.5°	2017.4	2029.4	2003.2	1998.3	2013.7
170°	2030.9	2043.0	2015.5	2008.2	2024.7
172.5°	2039.5	2050.4	2024.1	2014.3	2027.2
175°	2049.4	2059.9	2032.5	2021.8	2027.8
177.5°	2052.2	2060.6	2038.6	2029.1	2043.5
180°	2044.8	2044.8	2044.8	2044.8	2044.8



TEST NUMBER: P1439363

CATALOG NUMBER: CB3-125U-120D-930-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.60	18.40	18.60	19.41	20.76	16.52	17.33	17.52	18.34	19.68
	3H	19.26	19.98	20.27	21.00	22.37	17.93	18.65	18.94	19.67	21.03
	4H	19.89	20.57	20.91	21.59	22.97	18.44	19.13	19.47	20.15	21.52
	6H	20.27	20.90	21.30	21.93	23.31	18.76	19.39	19.79	20.41	21.80
	8H	20.40	21.00	21.44	22.05	23.43	18.88	19.48	19.92	20.52	21.90
	12H	20.47	21.04	21.52	22.08	23.48	18.95	19.52	20.00	20.56	21.96
4H	2H	18.00	18.68	19.03	19.71	21.08	17.14	17.82	18.17	18.85	20.22
	3H	19.88	20.45	20.92	21.50	22.89	18.75	19.32	19.79	20.37	21.76
	4H	20.63	21.15	21.68	22.19	23.60	19.36	19.88	20.40	20.92	22.33
	6H	21.13	21.58	22.18	22.64	24.05	19.77	20.22	20.82	21.28	22.68
	8H	21.32	21.74	22.37	22.80	24.21	19.94	20.35	20.99	21.41	22.83
	12H	21.41	21.79	22.49	22.86	24.29	20.04	20.42	21.11	21.49	22.91
8H	4H	20.75	21.17	21.81	22.23	23.65	19.61	20.03	20.67	21.09	22.51
	6H	21.37	21.72	22.45	22.82	24.23	20.14	20.49	21.22	21.59	23.00
	8H	21.65	21.95	22.73	23.03	24.47	20.39	20.70	21.48	21.78	23.21
	12H	21.81	22.07	22.90	23.15	24.63	20.57	20.83	21.66	21.91	23.39
12H	4H	20.72	21.10	21.80	22.18	23.60	19.61	19.99	20.69	21.07	22.49
	6H	21.39	21.69	22.47	22.78	24.21	20.20	20.50	21.28	21.59	23.02
	8H	21.68	21.95	22.77	23.03	24.51	20.48	20.74	21.57	21.82	23.30