

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439517

Luminaire Tested: CB3-D-030U-085D-935-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1439517  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-3, G2-2312-242-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB3-D-030U-085D-935-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT  
3-INCH APERTURE  
DOWNLIGHT 850 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4682.0 lumens  
Efficiency: N/A  
Efficacy: 138.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 33.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1439517

CATALOG NUMBER: CB3-D-030U-085D-935-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1439517

CATALOG NUMBER: CB3-D-030U-085D-935-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	79	79	79	79	79	79	74														
1	104	99	95	92	98	94	91	88	86	83	80	77	75	74	70	68	67	67	67	67	67	67	67	63														
2	95	87	81	75	90	83	77	73	75	71	67	68	65	62	62	59	57	57	57	57	57	57	57	53														
3	86	77	69	63	82	73	66	61	67	61	57	61	56	53	55	52	49	49	49	49	49	49	49	46														
4	79	68	60	54	75	65	58	52	60	53	49	54	49	45	49	45	42	42	42	42	42	42	42	39														
5	73	61	53	47	69	58	51	45	54	47	42	49	44	40	45	40	37	37	37	37	37	37	37	34														
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	41	36	33	33	33	33	33	33	33	30														
7	63	50	42	36	59	48	40	35	44	38	33	41	35	31	37	33	29	29	29	29	29	29	29	27														
8	58	46	38	32	55	44	36	31	40	34	30	37	32	28	34	30	26	26	26	26	26	26	26	24														
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	24	24	24	24	24	24	22														
10	51	38	31	26	48	37	30	25	34	28	24	32	27	23	29	25	22	22	22	22	22	22	22	20														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16488	16488	16488
5°	16410	16421	16520
10°	16338	16315	16315
15°	16088	16088	15990
20°	15826	15665	15523
25°	15423	15230	14959
30°	15046	14654	14302
35°	14650	14107	13605
40°	14122	13448	12868
45°	13643	12865	12070
50°	13151	12167	11292
55°	12613	11491	10552
60°	12034	10794	9717
65°	11357	10000	8838
70°	10576	9071	7873
75°	9591	7961	7012
80°	8360	6672	6203
85°	6452	5647	5647

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13643 cd/sqm



TEST NUMBER: P1439517

CATALOG NUMBER: CB3-D-030U-085D-935-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.5	2.9
10°-20°	386.3	8.3
20°-30°	561.1	12.0
30°-40°	637.9	13.6
40°-50°	619.3	13.2
50°-60°	522.8	11.2
60°-70°	372.0	7.9
70°-80°	198.7	4.2
80°-90°	52.5	1.1
90°-100°	19.6	0.4
100°-110°	76.6	1.6
110°-120°	136.5	2.9
120°-130°	184.7	3.9
130°-140°	212.4	4.5
140°-150°	213.1	4.6
150°-160°	183.3	3.9
160°-170°	124.1	2.6
170°-180°	43.8	0.9
0°-30°	1084.9	23.2
0°-40°	1722.8	36.8
0°-60°	2864.9	61.2
0°-90°	3488.1	74.5
90°-120°	232.7	5.0
90°-150°	842.9	18.0
90°-180°	1194.0	25.5
0°-180°	4682.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1445	1463	1446	1444	1454	137
15°	1373	1386	1373	1365	1365	387
25°	1235	1240	1220	1203	1198	569
35°	1061	1050	1021	991	985	661
45°	853	839	804	765	754	658
55°	639	622	582	545	535	572
65°	424	409	374	340	330	420
75°	219	207	182	163	160	234
85°	50	46	44	44	44	59
90°	0	0	0	0	0	3
95°	19	17	15	14	15	21
105°	74	74	71	70	70	79
115°	139	140	137	136	136	138
125°	207	210	206	205	205	185
135°	276	279	275	272	275	213
145°	342	345	340	338	341	214
155°	400	403	396	395	399	184
165°	441	445	439	437	441	124
175°	462	466	460	457	459	44
180°	463	463	463	463	463	

TEST NUMBER: P1439517

CATALOG NUMBER: CB3-D-030U-085D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1457.2	1457.2	1457.2	1457.2	1457.2
2.5°	1449.8	1464.3	1451.4	1453.2	1456.4
5°	1444.8	1463.0	1445.8	1444.0	1454.5
7.5°	1433.6	1450.2	1432.4	1428.2	1437.4
10°	1422.0	1440.3	1420.0	1414.9	1420.0
12.5°	1401.3	1420.4	1404.2	1395.9	1400.1
15°	1373.4	1385.5	1373.4	1365.1	1365.1
17.5°	1339.3	1352.0	1329.1	1323.3	1321.0
20°	1314.4	1325.6	1301.0	1292.6	1289.2
22.5°	1281.3	1291.6	1271.2	1256.7	1252.8
25°	1235.4	1239.5	1219.9	1203.2	1198.2
27.5°	1189.7	1190.7	1163.8	1143.6	1136.9
30°	1151.6	1152.6	1121.6	1099.8	1094.7
32.5°	1113.5	1110.5	1081.1	1055.1	1051.7
35°	1060.6	1050.5	1021.3	991.1	985.0
37.5°	996.6	990.6	956.1	925.9	916.7
40°	956.1	946.0	910.5	880.3	871.2
42.5°	915.5	903.8	867.5	834.0	824.0
45°	852.6	839.4	804.0	765.4	754.3
47.5°	789.3	774.9	735.9	698.6	686.2
50°	747.1	731.9	691.2	654.7	641.5
52.5°	704.0	688.0	647.3	610.0	599.3
55°	639.4	622.2	582.5	545.1	534.9
57.5°	574.9	557.9	518.4	482.9	470.8
60°	531.8	515.7	477.0	441.5	429.4
62.5°	488.0	472.6	434.8	400.2	388.8
65°	424.2	409.1	373.5	340.2	330.1
67.5°	361.1	348.2	313.1	282.5	274.4
70°	319.7	307.6	274.2	246.1	238.0
72.5°	280.0	267.0	235.3	211.4	205.7
75°	219.4	207.2	182.1	163.4	160.4
77.5°	163.9	154.0	132.2	121.6	120.0
80°	128.3	119.2	102.4	95.2	95.2
82.5°	95.2	87.7	76.8	73.7	73.7
85°	49.7	45.6	43.5	43.5	43.5
87.5°	14.9	14.9	14.1	13.2	13.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	4.6	2.8	2.3	2.3
95°	18.8	17.1	15.3	14.2	14.6
97.5°	34.7	33.1	30.8	29.8	30.0
100°	45.8	44.4	41.9	40.8	40.8
102.5°	56.6	55.8	53.3	52.2	52.5
105°	74.2	73.9	71.4	70.3	69.6
107.5°	93.7	93.1	90.3	90.2	89.6
110°	106.2	105.9	103.4	103.0	102.7

TEST NUMBER: P1439517

CATALOG NUMBER: CB3-D-030U-085D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	119.0	119.5	116.7	116.4	116.0
115°	139.2	139.9	136.8	136.4	136.0
117.5°	160.0	161.0	157.6	157.2	156.6
120°	173.3	175.4	171.2	170.8	170.5
122.5°	187.0	188.8	184.8	184.2	184.1
125°	207.4	209.9	205.7	205.0	205.3
127.5°	227.9	230.4	226.5	225.1	225.8
130°	241.5	244.3	240.1	238.7	239.8
132.5°	255.5	258.2	254.0	252.7	254.3
135°	276.3	279.1	274.6	272.5	275.3
137.5°	296.7	299.2	294.2	292.8	295.7
140°	310.1	312.5	307.2	305.6	309.0
142.5°	323.2	325.9	320.0	318.3	322.1
145°	342.4	345.2	339.6	337.9	341.0
147.5°	360.9	363.7	358.0	356.1	359.2
150°	372.2	375.4	369.4	367.7	371.2
152.5°	383.3	386.7	380.5	378.5	382.8
155°	399.6	403.1	396.4	394.7	398.9
157.5°	414.2	417.4	411.4	409.7	413.3
160°	423.0	426.5	420.2	418.5	422.7
162.5°	430.7	434.2	428.4	426.2	430.4
165°	441.2	445.0	439.0	436.6	441.2
167.5°	449.9	454.0	447.7	445.5	450.0
170°	455.0	458.8	452.5	449.8	454.3
172.5°	458.4	462.2	455.9	453.2	456.3
175°	462.1	466.3	460.0	457.2	458.9
177.5°	463.7	467.1	462.0	459.6	463.5
180°	463.2	463.2	463.2	463.2	463.2



TEST NUMBER: P1439517

CATALOG NUMBER: CB3-D-030U-085D-935-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.90	20.02	19.62	20.75	21.63	17.82	18.94	18.54	19.68	20.55
	3H	20.59	21.59	21.32	22.33	23.24	19.26	20.26	19.99	21.00	21.91
	4H	21.23	22.17	21.98	22.93	23.85	19.79	20.73	20.53	21.48	22.40
	6H	21.63	22.50	22.39	23.26	24.20	20.12	20.99	20.88	21.75	22.68
	8H	21.77	22.60	22.54	23.39	24.32	20.25	21.08	21.02	21.86	22.79
	12H	21.85	22.64	22.63	23.42	24.38	20.33	21.12	21.11	21.90	22.86
4H	2H	19.34	20.29	20.09	21.04	21.96	18.48	19.43	19.23	20.18	21.10
	3H	21.25	22.04	22.02	22.83	23.77	20.12	20.91	20.89	21.70	22.64
	4H	22.01	22.73	22.79	23.52	24.48	20.74	21.46	21.52	22.25	23.21
	6H	22.53	23.15	23.33	23.96	24.93	21.17	21.79	21.96	22.60	23.57
	8H	22.73	23.30	23.53	24.11	25.10	21.34	21.92	22.14	22.73	23.71
	12H	22.84	23.36	23.66	24.19	25.18	21.46	21.98	22.28	22.81	23.80
8H	4H	22.16	22.74	22.96	23.55	24.53	21.02	21.60	21.82	22.41	23.39
	6H	22.79	23.27	23.62	24.12	25.11	21.56	22.04	22.39	22.89	23.88
	8H	23.07	23.49	23.91	24.34	25.34	21.82	22.24	22.66	23.09	24.09
	12H	23.24	23.62	24.09	24.46	25.52	22.00	22.38	22.85	23.22	24.28
12H	4H	22.15	22.67	22.97	23.50	24.49	21.04	21.56	21.86	22.39	23.38
	6H	22.81	23.23	23.65	24.09	25.09	21.62	22.05	22.46	22.90	23.90
	8H	23.12	23.50	23.96	24.34	25.39	21.91	22.29	22.76	23.13	24.19