

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439346

Luminaire Tested: CB3-125U-085D-840-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439346
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-125U-085D-840-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
3-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18255.7 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 144.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439346

CATALOG NUMBER: CB3-125U-085D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1439346

CATALOG NUMBER: CB3-125U-085D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36					36			
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31					31			
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31	26					26			
3	79	70	63	57	71	63	57	53	52	47	44	41	38	35	30	29	27	22					22			
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19					19			
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17					17			
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15					15			
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13					13			
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12					12			
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13	11					11			
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10					10			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15719	15719	15719
5°	15644	15656	15745
10°	15576	15553	15553
15°	15337	15337	15244
20°	15088	14933	14803
25°	14708	14523	14264
30°	14347	13974	13638
35°	13969	13451	12974
40°	13466	12824	12271
45°	13009	12267	11510
50°	12539	11602	10768
55°	12028	10958	10062
60°	11476	10293	9266
65°	10831	9536	8427
70°	10087	8649	7508
75°	9143	7591	6686
80°	7972	6366	5913
85°	6147	5381	5381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13009 cd/sqm



TEST NUMBER: P1439346

CATALOG NUMBER: CB3-125U-085D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.2	1.4
10°-20°	736.5	4.0
20°-30°	1070.0	5.9
30°-40°	1216.6	6.7
40°-50°	1181.0	6.5
50°-60°	997.1	5.5
60°-70°	709.4	3.9
70°-80°	379.0	2.1
80°-90°	100.3	0.5
90°-100°	90.8	0.5
100°-110°	657.5	3.6
110°-120°	1563.3	8.6
120°-130°	1997.2	10.9
130°-140°	2154.3	11.8
140°-150°	2030.9	11.1
150°-160°	1656.8	9.1
160°-170°	1079.5	5.9
170°-180°	373.2	2.0
0°-30°	2068.7	11.3
0°-40°	3285.3	18.0
0°-60°	5463.4	29.9
0°-90°	6652.1	36.4
90°-120°	2311.6	12.7
90°-150°	8494.1	46.5
90°-180°	11604.0	63.6
0°-180°	18255.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2778	2778	2778	2778	2778	
5°	2755	2790	2757	2753	2772	261
15°	2619	2642	2619	2603	2603	738
25°	2356	2364	2327	2295	2285	1086
35°	2023	2003	1948	1890	1879	1260
45°	1626	1601	1533	1460	1439	1254
55°	1220	1187	1111	1040	1020	1090
65°	809	780	712	649	630	801
75°	418	395	347	312	306	446
85°	95	87	83	83	83	112
90°	0	0	0	3	0	10
95°	166	30	38	42	42	205
105°	833	844	856	62	65	878
115°	1562	1573	1576	1600	1609	1540
125°	2219	2234	2228	2252	2267	1980
135°	2788	2803	2779	2800	2818	2147
145°	3244	3265	3224	3245	3262	2030
155°	3594	3623	3573	3583	3606	1657
165°	3831	3851	3810	3799	3825	1082
175°	3941	3961	3908	3888	3899	375
180°	3932	3932	3932	3932	3932	

TEST NUMBER: P1439346

CATALOG NUMBER: CB3-125U-085D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2778.5	2778.5	2778.5	2778.5	2778.5
2.5°	2764.3	2792.0	2767.4	2770.7	2776.9
5°	2754.8	2789.5	2756.8	2753.2	2772.5
7.5°	2733.5	2765.1	2731.1	2723.2	2740.6
10°	2711.4	2746.1	2707.4	2697.8	2707.4
12.5°	2671.9	2708.2	2677.4	2661.4	2669.5
15°	2618.6	2641.8	2618.6	2602.8	2602.8
17.5°	2553.5	2577.8	2534.2	2523.0	2518.8
20°	2506.1	2527.4	2480.5	2464.6	2458.8
22.5°	2443.0	2462.7	2423.7	2396.6	2389.3
25°	2356.2	2363.9	2326.6	2294.8	2285.1
27.5°	2268.9	2270.9	2219.6	2181.0	2168.3
30°	2196.3	2198.3	2139.1	2097.4	2087.8
32.5°	2123.7	2117.9	2061.7	2012.3	2005.7
35°	2022.7	2003.4	1947.7	1890.2	1878.6
37.5°	1900.7	1889.1	1823.4	1765.7	1748.4
40°	1823.4	1804.1	1736.5	1678.9	1661.6
42.5°	1746.0	1723.6	1654.4	1590.5	1571.6
45°	1626.0	1600.9	1533.3	1459.8	1438.6
47.5°	1505.3	1477.9	1403.4	1332.3	1308.7
50°	1424.7	1395.8	1318.2	1248.6	1223.5
52.5°	1342.7	1312.2	1234.5	1163.4	1143.0
55°	1219.5	1186.7	1111.0	1039.5	1020.2
57.5°	1096.4	1064.0	988.6	921.0	897.9
60°	1014.3	983.4	909.7	842.1	818.9
62.5°	930.6	901.3	829.2	763.2	741.6
65°	809.1	780.1	712.4	648.8	629.5
67.5°	688.7	664.0	597.1	538.8	523.3
70°	609.8	586.6	522.9	469.3	453.9
72.5°	534.0	509.3	448.7	403.1	392.3
75°	418.3	395.2	347.3	311.7	305.9
77.5°	312.6	293.7	252.2	232.0	228.9
80°	244.7	227.3	195.4	181.5	181.5
82.5°	181.5	167.3	146.4	140.5	140.5
85°	94.7	87.0	82.9	82.9	82.9
87.5°	28.4	28.4	26.8	25.8	25.3
90°	0.0	0.0	0.0	2.9	0.0
92.5°	45.0	17.2	14.2	17.2	16.6
95°	165.9	29.8	38.5	41.5	41.5
97.5°	334.2	327.8	45.0	53.9	54.5
100°	462.2	476.7	47.4	56.4	59.3
102.5°	604.4	616.6	87.7	58.7	61.6
105°	832.6	844.2	856.3	62.3	65.2
107.5°	1059.5	1068.2	1076.1	968.7	362.7
110°	1208.9	1217.6	1220.7	1250.5	1256.3



TEST NUMBER: P1439346

CATALOG NUMBER: CB3-125U-085D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1348.7	1359.7	1365.3	1390.4	1400.9
115°	1561.5	1573.0	1576.3	1600.2	1608.9
117.5°	1763.5	1775.7	1781.3	1800.6	1814.5
120°	1896.3	1910.7	1914.0	1938.0	1949.6
122.5°	2026.6	2043.4	2042.0	2063.7	2080.0
125°	2219.2	2233.7	2228.1	2252.1	2266.6
127.5°	2402.3	2411.0	2398.8	2428.1	2440.3
130°	2518.5	2527.2	2512.5	2539.5	2554.0
132.5°	2625.1	2638.5	2621.6	2646.2	2660.7
135°	2788.1	2802.6	2779.2	2800.3	2817.7
137.5°	2933.3	2950.7	2922.6	2947.3	2962.3
140°	3028.1	3045.5	3010.3	3037.4	3054.8
142.5°	3115.8	3137.8	3095.6	3120.4	3140.1
145°	3244.4	3264.7	3223.6	3244.8	3262.2
147.5°	3366.5	3383.8	3344.5	3359.6	3371.8
150°	3439.9	3457.3	3413.3	3428.4	3442.9
152.5°	3499.2	3523.5	3479.6	3490.2	3511.6
155°	3594.0	3623.0	3573.3	3582.7	3605.9
157.5°	3681.1	3707.2	3657.4	3665.6	3685.9
160°	3733.3	3759.3	3709.6	3713.0	3733.3
162.5°	3773.6	3797.3	3754.6	3748.6	3773.6
165°	3831.0	3851.3	3810.3	3799.0	3825.1
167.5°	3879.0	3902.2	3851.8	3842.4	3871.9
170°	3905.1	3928.3	3875.5	3861.4	3893.3
172.5°	3921.7	3942.6	3892.1	3873.1	3898.0
175°	3940.7	3961.0	3908.1	3887.6	3899.2
177.5°	3946.0	3962.2	3919.9	3901.6	3929.4
180°	3931.8	3931.8	3931.8	3931.8	3931.8

TEST NUMBER: P1439346

CATALOG NUMBER: CB3-125U-085D-840-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.31	16.06	16.38	17.13	18.58	14.24	14.98	15.30	16.05	17.50
	3H	16.97	17.64	18.05	18.72	20.19	15.64	16.31	16.72	17.38	18.86
	4H	17.60	18.23	18.69	19.31	20.79	16.15	16.78	17.24	17.86	19.34
	6H	17.98	18.56	19.07	19.64	21.13	16.46	17.05	17.56	18.13	19.62
	8H	18.11	18.66	19.21	19.76	21.24	16.58	17.14	17.69	18.24	19.72
	12H	18.17	18.70	19.28	19.79	21.30	16.66	17.18	17.76	18.27	19.78
4H	2H	15.71	16.34	16.80	17.42	18.90	14.85	15.48	15.94	16.56	18.04
	3H	17.59	18.11	18.69	19.22	20.71	16.46	16.98	17.56	18.09	19.58
	4H	18.33	18.81	19.44	19.91	21.42	17.06	17.54	18.17	18.64	20.15
	6H	18.83	19.24	19.94	20.36	21.86	17.47	17.88	18.58	19.00	20.50
	8H	19.02	19.40	20.13	20.51	22.03	17.63	18.02	18.75	19.13	20.65
	12H	19.11	19.46	20.24	20.58	22.11	17.73	18.08	18.86	19.21	20.73
8H	4H	18.45	18.84	19.56	19.95	21.47	17.31	17.70	18.43	18.81	20.33
	6H	19.07	19.38	20.20	20.54	22.05	17.84	18.16	18.97	19.31	20.82
	8H	19.34	19.62	20.48	20.75	22.29	18.09	18.37	19.23	19.50	21.04
	12H	19.50	19.74	20.64	20.87	22.45	18.26	18.50	19.40	19.63	21.21
12H	4H	18.42	18.77	19.55	19.89	21.42	17.31	17.66	18.44	18.78	20.31
	6H	19.08	19.36	20.22	20.49	22.03	17.89	18.17	19.03	19.30	20.84
	8H	19.38	19.62	20.52	20.75	22.32	18.17	18.41	19.31	19.54	21.12