

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439151

Luminaire Tested: CB3-030U-120D-840-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439151
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-030U-120D-840-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
3-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6061.2 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 46.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439151

CATALOG NUMBER: CB3-030U-120D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439151

CATALOG NUMBER: CB3-030U-120D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	100	96	92	99	96	92	89	87	85	82	80	78	76	73	71	70	66
2	95	88	81	76	91	84	78	73	77	72	69	71	67	64	65	62	59	56
3	87	77	70	64	83	74	67	62	68	63	58	63	58	54	57	54	51	48
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	52	47	44	41
5	74	62	53	47	70	59	52	46	55	48	43	51	45	41	47	42	39	36
6	68	56	47	41	65	53	46	40	50	43	38	46	40	36	42	38	34	32
7	63	50	42	36	60	49	41	36	45	39	34	42	36	32	39	34	30	28
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	36	31	27	25
9	55	42	34	29	52	41	34	29	38	32	27	35	30	26	33	28	25	23
10	51	39	31	26	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22376	22376	22376
5°	22270	22286	22413
10°	22173	22141	22141
15°	21833	21833	21701
20°	21478	21258	21072
25°	20937	20674	20306
30°	20424	19893	19415
35°	19886	19148	18470
40°	19169	18256	17469
45°	18520	17464	16384
50°	17851	16516	15328
55°	17122	15600	14325
60°	16338	14652	13191
65°	15418	13576	11997
70°	14357	12313	10689
75°	13019	10807	9517
80°	11351	9063	8418
85°	8750	7659	7659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18520 cd/sqm



TEST NUMBER: P1439151

CATALOG NUMBER: CB3-030U-120D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	3.1
10°-20°	524.2	8.6
20°-30°	761.6	12.6
30°-40°	865.9	14.3
40°-50°	840.6	13.9
50°-60°	709.7	11.7
60°-70°	505.0	8.3
70°-80°	269.8	4.5
80°-90°	71.3	1.2
90°-100°	10.4	0.2
100°-110°	75.2	1.2
110°-120°	178.7	2.9
120°-130°	228.3	3.8
130°-140°	246.3	4.1
140°-150°	232.2	3.8
150°-160°	189.4	3.1
160°-170°	123.4	2.0
170°-180°	42.7	0.7
0°-30°	1472.5	24.3
0°-40°	2338.4	38.6
0°-60°	3888.7	64.2
0°-90°	4734.7	78.1
90°-120°	264.2	4.4
90°-150°	971.0	16.0
90°-180°	1326.0	21.9
0°-180°	6061.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1978	1978	1978	1978	1978	
5°	1961	1986	1962	1960	1973	186
15°	1864	1880	1864	1853	1853	525
25°	1677	1683	1656	1633	1626	773
35°	1440	1426	1386	1345	1337	897
45°	1157	1140	1091	1039	1024	893
55°	868	845	791	740	726	776
65°	576	555	507	462	448	570
75°	298	281	247	222	218	317
85°	67	62	59	59	59	80
90°	0	0	0	0	0	3
95°	19	3	4	5	5	23
105°	95	96	98	7	8	100
115°	178	180	180	183	184	176
125°	254	255	255	258	259	226
135°	319	320	318	320	322	245
145°	371	373	368	371	373	232
155°	411	414	408	410	412	189
165°	438	440	436	434	437	124
175°	450	453	447	444	446	43
180°	450	450	450	450	450	

TEST NUMBER: P1439151

CATALOG NUMBER: CB3-030U-120D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1977.6	1977.6	1977.6	1977.6	1977.6
2.5°	1967.5	1987.3	1969.8	1972.1	1976.5
5°	1960.8	1985.5	1962.2	1959.7	1973.4
7.5°	1945.6	1968.1	1943.9	1938.3	1950.7
10°	1929.9	1954.6	1927.1	1920.2	1927.1
12.5°	1901.8	1927.6	1905.7	1894.3	1900.1
15°	1863.9	1880.4	1863.9	1852.6	1852.6
17.5°	1817.5	1834.8	1803.8	1795.8	1792.8
20°	1783.8	1798.9	1765.5	1754.2	1750.1
22.5°	1738.9	1752.9	1725.1	1705.9	1700.7
25°	1677.1	1682.6	1656.0	1633.4	1626.5
27.5°	1615.0	1616.4	1579.9	1552.4	1543.3
30°	1563.3	1564.7	1522.6	1492.9	1486.0
32.5°	1511.6	1507.5	1467.5	1432.3	1427.6
35°	1439.7	1426.0	1386.3	1345.4	1337.2
37.5°	1352.9	1344.6	1297.8	1256.8	1244.5
40°	1297.8	1284.1	1236.0	1195.0	1182.7
42.5°	1242.8	1226.8	1177.6	1132.1	1118.6
45°	1157.4	1139.5	1091.4	1039.0	1023.9
47.5°	1071.4	1051.9	998.9	948.3	931.5
50°	1014.1	993.5	938.3	888.7	870.8
52.5°	955.7	934.0	878.7	828.1	813.5
55°	868.0	844.7	790.8	739.9	726.2
57.5°	780.4	757.3	703.7	655.6	639.1
60°	722.0	700.0	647.5	599.4	582.9
62.5°	662.4	641.5	590.2	543.2	527.8
65°	575.9	555.3	507.1	461.8	448.1
67.5°	490.2	472.6	425.0	383.5	372.5
70°	434.0	417.5	372.2	334.0	323.1
72.5°	380.1	362.5	319.4	286.9	279.2
75°	297.8	281.3	247.2	221.8	217.7
77.5°	222.5	209.0	179.5	165.1	162.9
80°	174.2	161.8	139.1	129.2	129.2
82.5°	129.2	119.1	104.2	100.0	100.0
85°	67.4	61.9	59.0	59.0	59.0
87.5°	20.2	20.2	19.1	18.0	18.0
90°	0.0	0.0	0.0	0.3	0.0
92.5°	5.1	2.0	1.6	2.0	1.9
95°	19.0	3.4	4.4	4.7	4.7
97.5°	38.2	37.5	5.1	6.2	6.2
100°	52.8	54.5	5.4	6.4	6.8
102.5°	69.1	70.5	10.0	6.7	7.0
105°	95.2	96.5	97.9	7.1	7.5
107.5°	121.1	122.1	123.0	110.7	41.5
110°	138.2	139.2	139.5	143.0	143.6



TEST NUMBER: P1439151

CATALOG NUMBER: CB3-030U-120D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.2	155.4	156.1	158.9	160.1
115°	178.5	179.8	180.2	182.9	183.9
117.5°	201.6	203.0	203.6	205.8	207.4
120°	216.8	218.4	218.8	221.5	222.9
122.5°	231.7	233.6	233.4	235.9	237.8
125°	253.7	255.3	254.7	257.5	259.1
127.5°	274.6	275.6	274.2	277.6	279.0
130°	287.9	288.9	287.2	290.3	292.0
132.5°	300.1	301.6	299.7	302.5	304.2
135°	318.7	320.4	317.7	320.1	322.1
137.5°	335.3	337.3	334.1	336.9	338.6
140°	346.2	348.1	344.1	347.2	349.2
142.5°	356.2	358.7	353.9	356.7	359.0
145°	370.9	373.2	368.5	370.9	372.9
147.5°	384.8	386.8	382.3	384.1	385.5
150°	393.2	395.2	390.2	391.9	393.6
152.5°	400.0	402.8	397.8	399.0	401.4
155°	410.9	414.2	408.5	409.6	412.2
157.5°	420.8	423.8	418.1	419.0	421.4
160°	426.8	429.8	424.1	424.5	426.8
162.5°	431.4	434.1	429.2	428.5	431.4
165°	438.0	440.3	435.6	434.3	437.3
167.5°	443.4	446.1	440.3	439.2	442.6
170°	446.4	449.1	443.0	441.4	445.1
172.5°	448.3	450.7	444.9	442.8	445.6
175°	450.5	452.8	446.8	444.4	445.7
177.5°	451.1	452.9	448.1	446.0	449.2
180°	449.5	449.5	449.5	449.5	449.5



TEST NUMBER: P1439151

CATALOG NUMBER: CB3-030U-120D-840-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.23	21.40	20.91	22.09	22.89	19.16	20.32	19.83	21.01	21.82
	3H	21.92	22.97	22.61	23.67	24.51	20.59	21.64	21.28	22.34	23.18
	4H	22.57	23.55	23.27	24.26	25.12	21.12	22.11	21.83	22.82	23.67
	6H	22.97	23.88	23.69	24.60	25.46	21.45	22.37	22.17	23.09	23.95
	8H	23.11	23.98	23.84	24.72	25.59	21.59	22.45	22.32	23.20	24.06
	12H	23.19	24.02	23.93	24.75	25.65	21.67	22.50	22.41	23.23	24.13
4H	2H	20.68	21.66	21.39	22.37	23.23	19.82	20.81	20.53	21.52	22.37
	3H	22.59	23.42	23.32	24.16	25.03	21.46	22.29	22.19	23.04	23.90
	4H	23.36	24.10	24.09	24.85	25.75	22.08	22.83	22.82	23.58	24.48
	6H	23.87	24.52	24.63	25.30	26.20	22.51	23.16	23.27	23.93	24.84
	8H	24.07	24.68	24.83	25.45	26.37	22.69	23.29	23.45	24.06	24.98
	12H	24.18	24.73	24.97	25.52	26.45	22.81	23.35	23.59	24.15	25.07
8H	4H	23.51	24.11	24.27	24.88	25.80	22.37	22.97	23.13	23.74	24.66
	6H	24.14	24.64	24.93	25.45	26.37	22.91	23.41	23.70	24.22	25.14
	8H	24.42	24.86	25.22	25.68	26.61	23.16	23.61	23.97	24.42	25.36
	12H	24.60	24.99	25.40	25.79	26.79	23.35	23.75	24.16	24.55	25.54
12H	4H	23.50	24.04	24.28	24.83	25.76	22.39	22.93	23.17	23.72	24.65
	6H	24.16	24.60	24.96	25.42	26.35	22.97	23.41	23.77	24.23	25.16
	8H	24.47	24.86	25.28	25.67	26.66	23.26	23.66	24.07	24.46	25.46