

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439277

Luminaire Tested: CB3-0U-030D-935-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439277
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-0U-030D-935-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE
3-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1196.1 lumens
Efficiency: N/A
Efficacy: 135.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439277

CATALOG NUMBER: CB3-OU-030D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1439277

CATALOG NUMBER: CB3-OU-030D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	109	105	101	97	107	103	99	96	98	95	93	94	92	90	91	89	87	85					85			
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72					72			
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61					61			
4	84	72	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55	53					53			
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48	46					46			
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43	41					41			
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38	36					36			
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34	32					32			
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29					29			
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28	27					27			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5653	5653	5653
5°	5627	5630	5663
10°	5602	5593	5593
15°	5516	5516	5482
20°	5427	5370	5323
25°	5290	5223	5130
30°	5159	5026	4905
35°	5024	4837	4666
40°	4843	4613	4413
45°	4679	4412	4140
50°	4510	4172	3873
55°	4326	3941	3620
60°	4128	3702	3333
65°	3895	3430	3031
70°	3626	3110	2699
75°	3287	2732	2404
80°	2867	2287	2124
85°	2207	1934	1934

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4679 cd/sqm



TEST NUMBER: P1439277

CATALOG NUMBER: CB3-OU-030D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.1	3.9
10°-20°	132.4	11.1
20°-30°	192.4	16.1
30°-40°	218.8	18.3
40°-50°	212.4	17.8
50°-60°	179.3	15.0
60°-70°	127.6	10.7
70°-80°	68.2	5.7
80°-90°	18.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.0	31.1
0°-40°	590.7	49.4
0°-60°	982.4	82.1
0°-90°	1196.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1196.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	500	500	500	500	500	
5°	495	502	496	495	499	47
15°	471	475	471	468	468	133
25°	424	425	418	413	411	195
35°	364	360	350	340	338	227
45°	292	288	276	262	259	226
55°	219	213	200	187	184	196
65°	146	140	128	117	113	144
75°	75	71	62	56	55	80
85°	17	16	15	15	15	21
90°	0	0	0	0	0	



TEST NUMBER: P1439277

CATALOG NUMBER: CB3-OU-030D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	499.6	499.6	499.6	499.6	499.6
2.5°	497.1	502.1	497.6	498.2	499.3
5°	495.4	501.6	495.7	495.1	498.6
7.5°	491.5	497.2	491.1	489.7	492.8
10°	487.6	493.8	486.8	485.1	486.8
12.5°	480.5	487.0	481.5	478.6	480.0
15°	470.9	475.0	470.9	468.0	468.0
17.5°	459.2	463.5	455.7	453.7	452.9
20°	450.7	454.5	446.0	443.2	442.1
22.5°	439.3	442.8	435.8	431.0	429.6
25°	423.7	425.1	418.4	412.6	410.9
27.5°	408.0	408.3	399.1	392.2	389.9
30°	394.9	395.3	384.7	377.2	375.4
32.5°	381.9	380.8	370.7	361.8	360.7
35°	363.7	360.2	350.2	339.9	337.8
37.5°	341.8	339.7	327.9	317.5	314.4
40°	327.9	324.4	312.3	301.9	298.8
42.5°	314.0	309.9	297.5	286.0	282.6
45°	292.4	287.9	275.7	262.5	258.7
47.5°	270.7	265.7	252.4	239.6	235.3
50°	256.2	251.0	237.0	224.5	220.0
52.5°	241.4	236.0	222.0	209.2	205.5
55°	219.3	213.4	199.8	186.9	183.5
57.5°	197.2	191.3	177.8	165.6	161.5
60°	182.4	176.8	163.6	151.4	147.3
62.5°	167.3	162.1	149.1	137.2	133.4
65°	145.5	140.3	128.1	116.7	113.2
67.5°	123.8	119.4	107.4	96.9	94.1
70°	109.6	105.5	94.0	84.4	81.6
72.5°	96.0	91.6	80.7	72.5	70.5
75°	75.2	71.1	62.5	56.0	55.0
77.5°	56.2	52.8	45.3	41.7	41.2
80°	44.0	40.9	35.1	32.6	32.6
82.5°	32.6	30.1	26.3	25.3	25.3
85°	17.0	15.6	14.9	14.9	14.9
87.5°	5.1	5.1	4.8	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1439277

CATALOG NUMBER: CB3-0U-030D-935-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.02	18.60	17.38	18.91	19.22	15.94	17.52	16.30	17.83	18.15
	3H	18.73	20.16	19.11	20.48	20.84	17.40	18.82	17.78	19.15	19.51
	4H	19.39	20.73	19.79	21.08	21.46	17.95	19.29	18.35	19.64	20.01
	6H	19.81	21.05	20.22	21.42	21.81	18.30	19.54	18.71	19.91	20.30
	8H	19.97	21.15	20.39	21.54	21.94	18.44	19.63	18.87	20.01	20.41
	12H	20.06	21.19	20.49	21.57	22.00	18.54	19.67	18.97	20.06	20.48
4H	2H	17.50	18.84	17.90	19.19	19.57	16.65	17.98	17.04	18.33	18.71
	3H	19.45	20.57	19.86	20.97	21.37	18.33	19.44	18.74	19.84	20.24
	4H	20.23	21.24	20.66	21.65	22.09	18.96	19.97	19.39	20.38	20.82
	6H	20.77	21.65	21.23	22.09	22.55	19.41	20.29	19.87	20.73	21.19
	8H	20.98	21.80	21.44	22.24	22.71	19.60	20.42	20.06	20.86	21.33
	12H	21.11	21.85	21.59	22.32	22.79	19.73	20.47	20.22	20.95	21.42
8H	4H	20.41	21.24	20.88	21.68	22.15	19.28	20.10	19.74	20.54	21.01
	6H	21.06	21.74	21.56	22.23	22.71	19.83	20.51	20.33	21.00	21.48
	8H	21.34	21.95	21.85	22.46	22.95	20.09	20.70	20.60	21.21	21.70
	12H	21.54	22.08	22.05	22.57	23.13	20.30	20.84	20.81	21.33	21.89
12H	4H	20.42	21.16	20.90	21.63	22.10	19.31	20.05	19.79	20.52	20.99
	6H	21.08	21.70	21.59	22.20	22.69	19.89	20.51	20.40	21.01	21.50
	8H	21.42	21.96	21.92	22.45	23.01	20.21	20.75	20.72	21.24	21.80