

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1057069

Luminaire Tested: CB3-0U-120D-840-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057069
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-0U-120D-840-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
3-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9469.5 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1057069

CATALOG NUMBER: CB3-0U-120D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1057069

CATALOG NUMBER: CB3-0U-120D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	96	98	95	93	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	72	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22376	22376	22376
5°	22270	22286	22414
10°	22173	22141	22141
15°	21833	21833	21701
20°	21478	21258	21072
25°	20937	20674	20306
30°	20424	19892	19415
35°	19886	19148	18469
40°	19169	18257	17468
45°	18519	17463	16384
50°	17851	16515	15329
55°	17123	15600	14324
60°	16337	14652	13191
65°	15418	13575	11995
70°	14357	12313	10687
75°	13016	10807	9517
80°	11347	9060	8418
85°	8750	7659	7659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 18519 cd/sqm

TEST NUMBER: P1057069

CATALOG NUMBER: CB3-OU-120D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.2	3.9
10°-20°	1048.4	11.1
20°-30°	1523.3	16.1
30°-40°	1731.9	18.3
40°-50°	1681.2	17.8
50°-60°	1419.4	15.0
60°-70°	1009.9	10.7
70°-80°	539.6	5.7
80°-90°	142.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2944.9	31.1
0°-40°	4676.7	49.4
0°-60°	7777.4	82.1
0°-90°	9469.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9469.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3955	3955	3955	3955	3955	
5°	3922	3971	3924	3919	3947	372
15°	3728	3761	3728	3705	3705	1050
25°	3354	3365	3312	3267	3253	1545
35°	2879	2852	2773	2691	2674	1794
45°	2315	2279	2183	2078	2048	1785
55°	1736	1689	1582	1480	1452	1552
65°	1152	1111	1014	924	896	1141
75°	596	563	494	444	435	635
85°	135	124	118	118	118	165
90°	0	0	0	0	0	

TEST NUMBER: P1057069

CATALOG NUMBER: CB3-OU-120D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3955.3	3955.3	3955.3	3955.3	3955.3
2.5°	3935.1	3974.6	3939.6	3944.2	3953.0
5°	3921.6	3971.0	3924.4	3919.4	3946.9
7.5°	3891.2	3936.3	3887.9	3876.6	3901.3
10°	3859.8	3909.2	3854.2	3840.4	3854.2
12.5°	3803.6	3855.2	3811.5	3788.7	3800.2
15°	3727.7	3760.7	3727.7	3705.3	3705.3
17.5°	3635.0	3669.6	3607.5	3591.6	3585.6
20°	3567.6	3597.8	3531.1	3508.4	3500.2
22.5°	3477.7	3505.7	3450.2	3411.8	3401.3
25°	3354.1	3365.1	3312.0	3266.7	3253.0
27.5°	3230.0	3232.7	3159.7	3104.8	3086.7
30°	3126.6	3129.3	3045.1	2985.8	2972.1
32.5°	3023.2	3015.0	2935.0	2864.6	2855.2
35°	2879.4	2851.9	2772.6	2690.8	2674.3
37.5°	2705.8	2689.3	2595.7	2513.6	2488.9
40°	2595.7	2568.2	2472.1	2390.0	2365.3
42.5°	2485.5	2453.7	2355.2	2264.1	2237.2
45°	2314.7	2279.0	2182.7	2078.1	2047.9
47.5°	2142.8	2103.8	1997.9	1896.5	1863.0
50°	2028.2	1987.0	1876.5	1777.4	1741.7
52.5°	1911.3	1867.9	1757.4	1656.2	1627.1
55°	1736.1	1689.4	1581.6	1479.8	1452.3
57.5°	1560.8	1514.6	1407.4	1311.1	1278.2
60°	1443.9	1400.0	1295.0	1198.8	1165.8
62.5°	1324.8	1283.0	1180.4	1086.4	1055.7
65°	1151.8	1110.6	1014.1	923.6	896.1
67.5°	980.4	945.2	850.0	767.0	745.0
70°	868.0	835.1	744.4	668.1	646.1
72.5°	760.2	725.0	638.8	573.8	558.5
75°	595.5	562.6	494.4	443.7	435.4
77.5°	445.0	418.1	359.0	330.3	325.9
80°	348.3	323.6	278.1	258.4	258.4
82.5°	258.4	238.1	208.4	200.0	200.0
85°	134.8	123.9	118.0	118.0	118.0
87.5°	40.5	40.5	38.2	36.0	36.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)