

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1191279

Luminaire Tested: SQ2-FA-075U-050D-L935-UNV-STD-W-4

Issue Date: 9/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1191279
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 9/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-075U-050D-L935-UNV-STD-W-4
Description: CORELITE SQ2 LED LUMINAIRE
FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4923.8 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 41.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	35	33
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12568	12568	12568	12568
5°	12420	13008	12420	10366
10°	12367	13159	12367	9399
15°	12154	13264	12154	10389
20°	11820	13167	11820	10835
25°	11234	13062	11234	10965
30°	10351	12769	10351	11082
35°	9157	12489	9157	10882
40°	7885	12147	7885	11002
45°	7784	11711	7784	11022
50°	7428	11140	7428	11065
55°	7389	10277	7389	10956
60°	6626	9158	6626	10911
65°	5647	8069	5647	10606
70°	4556	6836	4556	9829
75°	3955	5646	3955	9033
80°	3366	4212	3366	7290
85°	2242	2242	2242	4465

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 12125 cd/sqm

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.4
10°-20°	195.7	4.0
20°-30°	297.2	6.0
30°-40°	348.9	7.1
40°-50°	354.1	7.2
50°-60°	310.2	6.3
60°-70°	220.0	4.5
70°-80°	113.3	2.3
80°-90°	24.2	0.5
90°-100°	182.6	3.7
100°-110°	605.5	12.3
110°-120°	600.9	12.2
120°-130°	489.5	9.9
130°-140°	397.8	8.1
140°-150°	308.9	6.3
150°-160°	222.6	4.5
160°-170°	136.3	2.8
170°-180°	46.0	0.9
0°-30°	563.0	11.4
0°-40°	911.9	18.5
0°-60°	1576.1	32.0
0°-90°	1933.7	39.3
90°-120°	1389.0	28.2
90°-150°	2585.2	52.5
90°-180°	2990.0	60.7
0°-180°	4923.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	778	778	778	778	778	
5°	766	803	766	640	766	73
15°	727	794	727	622	727	204
25°	631	733	631	616	631	288
35°	465	634	465	552	465	289
45°	341	513	341	483	341	261
55°	262	365	262	389	262	227
65°	148	211	148	278	148	148
75°	63	90	63	145	63	69
85°	12	12	12	24	12	15
90°	0	4	0	4	0	1
95°	26	79	26	79	26	30
105°	106	1069	106	1069	106	112
115°	189	1188	189	1188	189	187
125°	264	941	264	941	264	235
135°	316	773	316	773	316	245
145°	367	645	367	645	367	230
155°	419	546	419	546	419	193
165°	460	503	460	503	460	130
175°	481	484	481	484	481	46
180°	483	483	483	483	483	

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	773.6	785.4	785.7	785.7	785.7	785.7	785.7	785.4	773.6	773.6	761.5
5°	766.3	787.0	793.5	796.7	802.6	796.7	793.5	787.0	766.3	757.5	709.0
7.5°	759.1	786.8	796.5	802.0	805.0	802.0	796.5	786.8	759.1	719.6	617.9
10°	754.3	786.7	796.5	799.6	802.6	799.6	796.5	786.7	754.3	674.6	591.4
12.5°	747.0	781.9	794.1	797.2	800.1	797.2	794.1	781.9	747.0	634.3	572.0
15°	727.1	774.3	784.5	790.6	793.5	790.6	784.5	774.3	727.1	600.3	558.2
17.5°	702.4	759.6	773.0	778.5	780.8	778.5	773.0	759.6	702.4	569.6	558.8
20°	687.9	749.9	763.3	766.3	766.3	766.3	763.3	749.9	687.9	555.2	573.3
22.5°	668.6	737.6	751.3	751.9	754.3	751.9	751.3	737.6	668.6	538.2	580.5
25°	630.6	710.2	730.1	727.3	733.2	727.3	730.1	710.2	630.6	515.5	579.3
27.5°	584.1	684.4	698.8	701.8	701.8	701.8	698.8	684.4	584.1	493.3	567.2
30°	555.2	667.3	681.9	684.9	684.9	684.9	681.9	667.3	555.2	478.4	555.2
32.5°	518.9	652.3	665.0	665.6	665.6	665.6	665.0	652.3	518.9	463.5	535.8
35°	464.6	626.9	636.6	636.5	633.6	636.5	636.6	626.9	464.6	441.0	512.9
37.5°	410.3	594.4	607.6	603.4	600.4	603.4	607.6	594.4	410.3	418.0	493.6
40°	374.1	574.7	588.3	579.2	576.3	579.2	588.3	574.7	374.1	400.7	476.7
42.5°	354.8	553.1	566.6	555.1	552.1	555.1	566.6	553.1	354.8	383.7	462.2
45°	340.9	517.9	531.0	518.8	512.9	518.8	531.0	517.9	340.9	358.6	437.5
47.5°	319.8	475.6	494.2	476.0	470.1	476.0	494.2	475.6	319.8	332.8	415.2
50°	295.7	449.1	467.7	449.4	443.5	449.4	467.7	449.1	295.7	313.4	398.3
52.5°	278.8	422.7	438.7	418.0	412.1	418.0	438.7	422.7	278.8	289.4	383.8
55°	262.5	383.4	395.2	373.9	365.1	373.9	395.2	383.4	262.5	253.6	356.0
57.5°	224.5	339.5	351.8	327.4	317.4	327.4	351.8	339.5	224.5	216.8	327.1
60°	205.2	308.4	322.8	298.4	283.6	298.4	322.8	308.4	205.2	190.4	307.7
62.5°	183.4	274.9	293.9	269.4	254.6	269.4	293.9	274.9	183.4	173.4	286.0
65°	147.8	227.5	250.4	225.9	211.2	225.9	250.4	227.5	147.8	153.7	250.4
67.5°	115.9	184.3	210.0	183.2	171.4	183.2	210.0	184.3	115.9	135.3	217.8
70°	96.5	155.5	181.0	156.6	144.8	156.6	181.0	155.5	96.5	123.1	196.1
72.5°	84.5	129.3	156.9	130.1	120.7	130.1	156.9	129.3	84.5	111.0	169.6
75°	63.4	89.9	120.7	96.4	90.5	96.4	120.7	89.9	63.4	89.9	132.8
77.5°	45.9	58.3	85.1	64.5	62.2	64.5	85.1	58.3	45.9	67.7	96.5
80°	36.2	39.2	63.4	45.3	45.3	45.3	63.4	39.2	36.2	51.0	72.4
82.5°	24.1	27.1	44.0	30.7	28.4	30.7	44.0	27.1	24.1	36.5	50.7
85°	12.1	12.1	18.1	12.1	12.1	12.1	18.1	12.1	12.1	18.0	24.1
87.5°	2.4	2.6	5.4	3.2	3.2	3.2	5.4	2.6	2.4	5.0	5.4
90°	0.0	1.0	3.0	4.0	4.0	4.0	3.0	1.0	0.0	1.0	3.0
92.5°	8.0	30.9	91.0	29.5	24.8	29.5	91.0	30.9	8.0	30.9	91.0
95°	26.0	76.8	331.0	118.1	79.0	118.1	331.0	76.8	26.0	76.8	331.0
97.5°	47.8	101.0	577.7	336.9	213.0	336.9	577.7	101.0	47.8	101.0	577.7
100°	63.0	113.8	668.9	574.5	381.0	574.5	668.9	113.8	63.0	113.8	668.9
102.5°	79.8	129.1	663.3	878.0	663.3	878.0	663.3	129.1	79.8	129.1	663.3
105°	106.0	151.0	605.9	1143.2	1068.9	1143.2	605.9	151.0	106.0	151.0	605.9
107.5°	132.8	172.9	550.9	1170.1	1226.6	1170.1	550.9	172.9	132.8	172.9	550.9
110°	148.0	188.1	522.9	1143.5	1257.8	1143.5	522.9	188.1	148.0	188.1	522.9

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	164.0	203.3	506.1	1096.2	1241.8	1096.2	506.1	203.3	164.0	203.3	506.1
115°	189.0	226.1	487.9	1015.8	1187.9	1015.8	487.9	226.1	189.0	226.1	487.9
117.5°	213.8	246.8	481.3	939.0	1119.5	939.0	481.3	246.8	213.8	246.8	481.3
120°	229.0	261.2	478.9	890.9	1065.9	890.9	478.9	261.2	229.0	261.2	478.9
122.5°	242.6	274.1	478.9	851.4	1013.1	851.4	478.9	274.1	242.6	274.1	478.9
125°	264.0	293.3	478.9	798.1	940.9	798.1	478.9	293.3	264.0	293.3	478.9
127.5°	281.6	310.3	477.7	757.9	879.9	757.9	477.7	310.3	281.6	310.3	477.7
130°	292.0	322.3	476.9	734.4	843.9	734.4	476.9	322.3	292.0	322.3	476.9
132.5°	301.6	332.7	476.1	715.0	813.5	715.0	476.1	332.7	301.6	332.7	476.1
135°	316.0	348.2	474.9	684.9	772.9	684.9	474.9	348.2	316.0	348.2	474.9
137.5°	331.6	362.6	473.7	655.9	733.5	655.9	473.7	362.6	331.6	362.6	473.7
140°	342.0	372.3	472.9	636.5	707.9	636.5	472.9	372.3	342.0	372.3	472.9
142.5°	351.6	381.1	473.7	617.2	680.7	617.2	473.7	381.1	351.6	381.1	473.7
145°	367.0	394.3	473.9	589.2	644.9	589.2	473.9	394.3	367.0	394.3	473.9
147.5°	383.6	406.4	474.1	565.5	606.9	565.5	474.1	406.4	383.6	406.4	474.1
150°	394.0	414.5	474.9	551.7	586.9	551.7	474.9	414.5	394.0	414.5	474.9
152.5°	403.5	423.3	475.7	540.4	568.5	540.4	475.7	423.3	403.5	423.3	475.7
155°	418.9	433.6	476.9	526.4	545.9	526.4	476.9	433.6	418.9	433.6	476.9
157.5°	433.9	445.3	478.1	516.5	530.3	516.5	478.1	445.3	433.9	445.3	478.1
160°	441.9	451.7	478.9	509.2	519.9	509.2	478.9	451.7	441.9	451.7	478.9
162.5°	449.9	457.4	478.9	504.3	512.7	504.3	478.9	457.4	449.9	457.4	478.9
165°	459.9	464.8	478.9	498.0	502.9	498.0	478.9	464.8	459.9	464.8	478.9
167.5°	469.1	471.7	479.9	492.4	494.9	492.4	479.9	471.7	469.1	471.7	479.9
170°	473.9	474.9	479.9	490.0	490.9	490.0	479.9	474.9	473.9	474.9	479.9
172.5°	477.1	478.1	480.7	487.5	487.7	487.5	480.7	478.1	477.1	478.1	480.7
175°	480.9	480.9	481.9	484.9	483.9	484.9	481.9	480.9	480.9	480.9	481.9
177.5°	482.9	482.9	482.1	483.7	482.1	483.7	482.1	482.9	482.9	482.9	482.1
180°	482.9	482.9	482.9	482.9	482.9	482.9	482.9	482.9	482.9	482.9	482.9

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	754.2	751.9	754.2	761.5	773.6	773.6
5°	654.4	639.6	654.4	709.0	757.5	766.3
7.5°	594.9	590.1	594.9	617.9	719.6	759.1
10°	573.3	573.3	573.3	591.4	674.6	754.3
12.5°	571.1	582.9	571.1	572.0	634.3	747.0
15°	606.8	621.5	606.8	558.2	600.3	727.1
17.5°	618.8	630.6	618.8	558.8	569.6	702.4
20°	618.8	630.6	618.8	573.3	555.2	687.9
22.5°	616.4	628.2	616.4	580.5	538.2	668.6
25°	609.6	615.5	609.6	579.3	515.5	630.6
27.5°	597.5	601.6	597.5	567.2	493.3	584.1
30°	585.5	594.4	585.5	555.2	478.4	555.2
32.5°	573.3	575.1	573.3	535.8	463.5	518.9
35°	555.1	552.1	555.1	512.9	441.0	464.6
37.5°	530.5	534.0	530.5	493.6	418.0	410.3
40°	516.1	522.0	516.1	476.7	400.7	374.1
42.5°	501.6	507.5	501.6	462.2	383.7	354.8
45°	479.8	482.7	479.8	437.5	358.6	340.9
47.5°	454.4	457.4	454.4	415.2	332.8	319.8
50°	437.5	440.5	437.5	398.3	313.4	295.7
52.5°	418.2	421.2	418.2	383.8	289.4	278.8
55°	389.2	389.2	389.2	356.0	253.6	262.5
57.5°	356.1	359.6	356.1	327.1	216.8	224.5
60°	332.0	337.9	332.0	307.7	190.4	205.2
62.5°	310.2	313.8	310.2	286.0	173.4	183.4
65°	274.6	277.6	274.6	250.4	153.7	147.8
67.5°	234.8	237.1	234.8	217.8	135.3	115.9
70°	208.2	208.2	208.2	196.1	123.1	96.5
72.5°	181.7	184.0	181.7	169.6	111.0	84.5
75°	141.9	144.8	141.9	132.8	89.9	63.4
77.5°	102.0	105.0	102.0	96.5	67.7	45.9
80°	75.5	78.4	75.5	72.4	51.0	36.2
82.5°	53.7	54.3	53.7	50.7	36.5	24.1
85°	24.1	24.1	24.1	24.1	18.0	12.1
87.5°	5.6	5.6	5.6	5.4	5.0	2.4
90°	4.0	4.0	4.0	3.0	1.0	0.0
92.5°	29.5	24.8	29.5	91.0	30.9	8.0
95°	118.1	79.0	118.1	331.0	76.8	26.0
97.5°	336.9	213.0	336.9	577.7	101.0	47.8
100°	574.5	381.0	574.5	668.9	113.8	63.0
102.5°	878.0	663.3	878.0	663.3	129.1	79.8
105°	1143.2	1068.9	1143.2	605.9	151.0	106.0
107.5°	1170.1	1226.6	1170.1	550.9	172.9	132.8
110°	1143.5	1257.8	1143.5	522.9	188.1	148.0

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1096.2	1241.8	1096.2	506.1	203.3	164.0
115°	1015.8	1187.9	1015.8	487.9	226.1	189.0
117.5°	939.0	1119.5	939.0	481.3	246.8	213.8
120°	890.9	1065.9	890.9	478.9	261.2	229.0
122.5°	851.4	1013.1	851.4	478.9	274.1	242.6
125°	798.1	940.9	798.1	478.9	293.3	264.0
127.5°	757.9	879.9	757.9	477.7	310.3	281.6
130°	734.4	843.9	734.4	476.9	322.3	292.0
132.5°	715.0	813.5	715.0	476.1	332.7	301.6
135°	684.9	772.9	684.9	474.9	348.2	316.0
137.5°	655.9	733.5	655.9	473.7	362.6	331.6
140°	636.5	707.9	636.5	472.9	372.3	342.0
142.5°	617.2	680.7	617.2	473.7	381.1	351.6
145°	589.2	644.9	589.2	473.9	394.3	367.0
147.5°	565.5	606.9	565.5	474.1	406.4	383.6
150°	551.7	586.9	551.7	474.9	414.5	394.0
152.5°	540.4	568.5	540.4	475.7	423.3	403.5
155°	526.4	545.9	526.4	476.9	433.6	418.9
157.5°	516.5	530.3	516.5	478.1	445.3	433.9
160°	509.2	519.9	509.2	478.9	451.7	441.9
162.5°	504.3	512.7	504.3	478.9	457.4	449.9
165°	498.0	502.9	498.0	478.9	464.8	459.9
167.5°	492.4	494.9	492.4	479.9	471.7	469.1
170°	490.0	490.9	490.0	479.9	474.9	473.9
172.5°	487.5	487.7	487.5	480.7	478.1	477.1
175°	484.9	483.9	484.9	481.9	480.9	480.9
177.5°	483.7	482.1	483.7	482.1	482.9	482.9
180°	482.9	482.9	482.9	482.9	482.9	482.9

TEST NUMBER: P1191279

CATALOG NUMBER: SQ2-FA-075U-050D-L935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.06	14.84	15.11	15.89	17.30	15.29	16.06	16.33	17.11	18.53
	3H	15.15	15.84	16.20	16.90	18.33	16.53	17.22	17.58	18.27	19.71
	4H	15.50	16.15	16.56	17.21	18.65	16.91	17.57	17.98	18.63	20.07
	6H	15.65	16.26	16.73	17.32	18.78	17.07	17.67	18.14	18.73	20.19
	8H	15.69	16.26	16.77	17.34	18.79	17.09	17.66	18.17	18.74	20.19
	12H	15.68	16.22	16.77	17.30	18.77	17.07	17.62	18.16	18.69	20.16
4H	2H	14.98	15.64	16.05	16.70	18.14	15.89	16.55	16.97	17.61	19.05
	3H	16.34	16.89	17.42	17.97	19.43	17.34	17.88	18.42	18.97	20.42
	4H	16.78	17.28	17.87	18.36	19.84	17.80	18.30	18.88	19.38	20.85
	6H	17.01	17.43	18.10	18.54	20.01	18.02	18.44	19.11	19.55	21.02
	8H	17.06	17.46	18.16	18.55	20.04	18.06	18.46	19.16	19.56	21.04
	12H	17.06	17.42	18.17	18.53	20.02	18.05	18.41	19.16	19.51	21.01
8H	4H	17.18	17.58	18.27	18.67	20.16	18.00	18.40	19.10	19.50	20.98
	6H	17.52	17.85	18.63	18.98	20.47	18.31	18.64	19.43	19.77	21.26
	8H	17.63	17.92	18.75	19.04	20.54	18.40	18.69	19.52	19.81	21.31
	12H	17.66	17.92	18.79	19.03	20.57	18.41	18.67	19.54	19.78	21.32
12H	4H	17.17	17.54	18.29	18.64	20.13	17.97	18.33	19.08	19.43	20.93
	6H	17.59	17.88	18.71	19.00	20.50	18.33	18.62	19.45	19.74	21.24
	8H	17.73	17.98	18.85	19.09	20.64	18.44	18.69	19.56	19.80	21.34