

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1191375

Luminaire Tested: SQ2-FA-150U-050D-L935-UNV-STD-W-4

Issue Date: 9/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1191375
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 9/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-150U-050D-L935-UNV-STD-W-4
Description: CORELITE SQ2 LED LUMINAIRE
FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7939.3 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 74.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	25	24	23
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	22	21	20
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	42	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12568	12568	12568	12568
5°	12420	13008	12420	10366
10°	12367	13159	12367	9399
15°	12154	13264	12154	10389
20°	11820	13167	11820	10835
25°	11234	13062	11234	10965
30°	10351	12769	10351	11082
35°	9157	12489	9157	10882
40°	7885	12147	7885	11002
45°	7784	11711	7784	11022
50°	7428	11140	7428	11065
55°	7389	10277	7389	10956
60°	6626	9158	6626	10911
65°	5647	8069	5647	10606
70°	4556	6836	4556	9829
75°	3955	5646	3955	9033
80°	3366	4212	3366	7290
85°	2242	2242	2242	4465

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 12125 cd/sqm

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	0.9
10°-20°	195.7	2.5
20°-30°	297.2	3.7
30°-40°	348.9	4.4
40°-50°	354.1	4.5
50°-60°	310.2	3.9
60°-70°	220.0	2.8
70°-80°	113.3	1.4
80°-90°	24.8	0.3
90°-100°	370.7	4.7
100°-110°	1213.9	15.3
110°-120°	1200.1	15.1
120°-130°	981.0	12.4
130°-140°	800.6	10.1
140°-150°	623.0	7.8
150°-160°	448.6	5.7
160°-170°	274.4	3.5
170°-180°	92.7	1.2
0°-30°	563.0	7.1
0°-40°	911.9	11.5
0°-60°	1576.1	19.9
0°-90°	1934.3	24.4
90°-120°	2784.7	35.1
90°-150°	5189.3	65.4
90°-180°	6005.0	75.6
0°-180°	7939.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	778	778	778	778	778	
5°	766	803	766	640	766	73
15°	727	794	727	622	727	204
25°	631	733	631	616	631	288
35°	465	634	465	552	465	289
45°	341	513	341	483	341	261
55°	262	365	262	389	262	227
65°	148	211	148	278	148	148
75°	63	90	63	145	63	69
85°	12	12	12	24	12	15
90°	1	8	1	8	1	3
95°	52	156	52	156	52	59
105°	211	2175	211	2175	211	222
115°	380	2375	380	2375	380	375
125°	529	1874	529	1874	529	471
135°	637	1551	637	1551	637	493
145°	745	1297	745	1297	745	467
155°	849	1100	849	1100	849	391
165°	927	1013	927	1013	927	261
175°	969	975	969	975	969	92
180°	973	973	973	973	973	

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	773.6	785.4	785.7	785.7	785.7	785.7	785.7	785.4	773.6	773.6	761.5
5°	766.3	787.0	793.5	796.7	802.6	796.7	793.5	787.0	766.3	757.5	709.0
7.5°	759.1	786.8	796.5	802.0	805.0	802.0	796.5	786.8	759.1	719.6	617.9
10°	754.3	786.7	796.5	799.6	802.6	799.6	796.5	786.7	754.3	674.6	591.4
12.5°	747.0	781.9	794.1	797.2	800.1	797.2	794.1	781.9	747.0	634.3	572.0
15°	727.1	774.3	784.5	790.6	793.5	790.6	784.5	774.3	727.1	600.3	558.2
17.5°	702.4	759.6	773.0	778.5	780.8	778.5	773.0	759.6	702.4	569.6	558.8
20°	687.9	749.9	763.3	766.3	766.3	766.3	763.3	749.9	687.9	555.2	573.3
22.5°	668.6	737.6	751.3	751.9	754.3	751.9	751.3	737.6	668.6	538.2	580.5
25°	630.6	710.2	730.1	727.3	733.2	727.3	730.1	710.2	630.6	515.5	579.3
27.5°	584.1	684.4	698.8	701.8	701.8	701.8	698.8	684.4	584.1	493.3	567.2
30°	555.2	667.3	681.9	684.9	684.9	684.9	681.9	667.3	555.2	478.4	555.2
32.5°	518.9	652.3	665.0	665.6	665.6	665.6	665.0	652.3	518.9	463.5	535.8
35°	464.6	626.9	636.6	636.5	633.6	636.5	636.6	626.9	464.6	441.0	512.9
37.5°	410.3	594.4	607.6	603.4	600.4	603.4	607.6	594.4	410.3	418.0	493.6
40°	374.1	574.7	588.3	579.2	576.3	579.2	588.3	574.7	374.1	400.7	476.7
42.5°	354.8	553.1	566.6	555.1	552.1	555.1	566.6	553.1	354.8	383.7	462.2
45°	340.9	517.9	531.0	518.8	512.9	518.8	531.0	517.9	340.9	358.6	437.5
47.5°	319.8	475.6	494.2	476.0	470.1	476.0	494.2	475.6	319.8	332.8	415.2
50°	295.7	449.1	467.7	449.4	443.5	449.4	467.7	449.1	295.7	313.4	398.3
52.5°	278.8	422.7	438.7	418.0	412.1	418.0	438.7	422.7	278.8	289.4	383.8
55°	262.5	383.4	395.2	373.9	365.1	373.9	395.2	383.4	262.5	253.6	356.0
57.5°	224.5	339.5	351.8	327.4	317.4	327.4	351.8	339.5	224.5	216.8	327.1
60°	205.2	308.4	322.8	298.4	283.6	298.4	322.8	308.4	205.2	190.4	307.7
62.5°	183.4	274.9	293.9	269.4	254.6	269.4	293.9	274.9	183.4	173.4	286.0
65°	147.8	227.5	250.4	225.9	211.2	225.9	250.4	227.5	147.8	153.7	250.4
67.5°	115.9	184.3	210.0	183.2	171.4	183.2	210.0	184.3	115.9	135.3	217.8
70°	96.5	155.5	181.0	156.6	144.8	156.6	181.0	155.5	96.5	123.1	196.1
72.5°	84.5	129.3	156.9	130.1	120.7	130.1	156.9	129.3	84.5	111.0	169.6
75°	63.4	89.9	120.7	96.4	90.5	96.4	120.7	89.9	63.4	89.9	132.8
77.5°	45.9	58.3	85.1	64.5	62.2	64.5	85.1	58.3	45.9	67.7	96.5
80°	36.2	39.2	63.4	45.3	45.3	45.3	63.4	39.2	36.2	51.0	72.4
82.5°	24.1	27.1	44.0	30.7	28.4	30.7	44.0	27.1	24.1	36.5	50.7
85°	12.1	12.1	18.1	12.1	12.1	12.1	18.1	12.1	12.1	18.0	24.1
87.5°	2.6	3.0	6.4	3.8	4.0	3.8	6.4	3.0	2.6	5.4	6.4
90°	1.0	3.0	8.0	7.0	8.0	7.0	8.0	3.0	1.0	3.0	8.0
92.5°	17.0	62.0	190.4	61.9	49.6	61.9	190.4	62.0	17.0	62.0	190.4
95°	52.0	150.7	674.0	240.1	156.0	240.1	674.0	150.7	52.0	150.7	674.0
97.5°	94.4	198.8	1156.3	699.5	433.6	699.5	1156.3	198.8	94.4	198.8	1156.3
100°	124.0	223.7	1337.9	1194.8	791.9	1194.8	1337.9	223.7	124.0	223.7	1337.9
102.5°	157.6	255.0	1317.9	1760.5	1364.7	1760.5	1317.9	255.0	157.6	255.0	1317.9
105°	211.0	300.9	1204.9	2289.2	2174.8	2289.2	1204.9	300.9	211.0	300.9	1204.9
107.5°	263.6	346.1	1094.7	2338.7	2464.4	2338.7	1094.7	346.1	263.6	346.1	1094.7
110°	298.0	378.2	1041.9	2281.1	2514.8	2281.1	1041.9	378.2	298.0	378.2	1041.9

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	330.8	408.6	1009.9	2181.0	2480.4	2181.0	1009.9	408.6	330.8	408.6	1009.9
115°	380.0	454.3	978.9	2022.9	2374.8	2022.9	978.9	454.3	380.0	454.3	978.9
117.5°	427.8	497.2	967.1	1867.4	2224.8	1867.4	967.1	497.2	427.8	497.2	967.1
120°	459.0	524.5	963.9	1776.8	2124.8	1776.8	963.9	524.5	459.0	524.5	963.9
122.5°	487.0	550.9	963.9	1698.6	2021.7	1698.6	963.9	550.9	487.0	550.9	963.9
125°	529.0	589.6	964.9	1595.2	1873.9	1595.2	964.9	589.6	529.0	589.6	964.9
127.5°	564.6	626.3	963.7	1519.0	1761.5	1519.0	963.7	626.3	564.6	626.3	963.7
130°	587.0	649.5	962.9	1472.9	1691.9	1472.9	962.9	649.5	587.0	649.5	962.9
132.5°	607.0	671.1	960.5	1433.2	1631.9	1433.2	960.5	671.1	607.0	671.1	960.5
135°	637.0	704.4	956.9	1375.9	1550.9	1375.9	956.9	704.4	637.0	704.4	956.9
137.5°	668.6	735.4	954.7	1316.1	1474.3	1316.1	954.7	735.4	668.6	735.4	954.7
140°	690.9	755.5	953.9	1278.3	1427.9	1278.3	953.9	755.5	690.9	755.5	953.9
142.5°	713.3	774.0	953.9	1238.0	1373.5	1238.0	953.9	774.0	713.3	774.0	953.9
145°	744.9	799.7	954.9	1183.5	1296.9	1183.5	954.9	799.7	744.9	799.7	954.9
147.5°	778.1	823.7	956.3	1136.1	1221.7	1136.1	956.3	823.7	778.1	823.7	956.3
150°	798.9	839.0	957.9	1108.6	1180.9	1108.6	957.9	839.0	798.9	839.0	957.9
152.5°	819.7	855.1	958.7	1085.9	1145.7	1085.9	958.7	855.1	819.7	855.1	958.7
155°	848.9	877.3	960.9	1058.9	1099.9	1058.9	960.9	877.3	848.9	877.3	960.9
157.5°	875.1	895.7	963.1	1037.6	1067.3	1037.6	963.1	895.7	875.1	895.7	963.1
160°	891.9	908.6	963.9	1025.5	1048.9	1025.5	963.9	908.6	891.9	908.6	963.9
162.5°	906.3	919.8	963.9	1015.7	1032.9	1015.7	963.9	919.8	906.3	919.8	963.9
165°	926.9	935.7	964.9	1002.2	1012.9	1002.2	964.9	935.7	926.9	935.7	964.9
167.5°	944.3	948.6	966.1	991.7	997.5	991.7	966.1	948.6	944.3	948.6	966.1
170°	953.9	955.9	966.9	986.0	987.9	986.0	966.9	955.9	953.9	955.9	966.9
172.5°	961.1	962.3	969.3	981.9	982.3	981.9	969.3	962.3	961.1	962.3	969.3
175°	968.9	968.9	969.9	976.9	974.9	976.9	969.9	968.9	968.9	968.9	969.9
177.5°	972.9	972.1	971.3	976.1	972.9	976.1	971.3	972.1	972.9	972.1	971.3
180°	972.9	972.9	972.9	972.9	972.9	972.9	972.9	972.9	972.9	972.9	972.9

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	778.4	778.4	778.4	778.4	778.4	778.4
2.5°	754.2	751.9	754.2	761.5	773.6	773.6
5°	654.4	639.6	654.4	709.0	757.5	766.3
7.5°	594.9	590.1	594.9	617.9	719.6	759.1
10°	573.3	573.3	573.3	591.4	674.6	754.3
12.5°	571.1	582.9	571.1	572.0	634.3	747.0
15°	606.8	621.5	606.8	558.2	600.3	727.1
17.5°	618.8	630.6	618.8	558.8	569.6	702.4
20°	618.8	630.6	618.8	573.3	555.2	687.9
22.5°	616.4	628.2	616.4	580.5	538.2	668.6
25°	609.6	615.5	609.6	579.3	515.5	630.6
27.5°	597.5	601.6	597.5	567.2	493.3	584.1
30°	585.5	594.4	585.5	555.2	478.4	555.2
32.5°	573.3	575.1	573.3	535.8	463.5	518.9
35°	555.1	552.1	555.1	512.9	441.0	464.6
37.5°	530.5	534.0	530.5	493.6	418.0	410.3
40°	516.1	522.0	516.1	476.7	400.7	374.1
42.5°	501.6	507.5	501.6	462.2	383.7	354.8
45°	479.8	482.7	479.8	437.5	358.6	340.9
47.5°	454.4	457.4	454.4	415.2	332.8	319.8
50°	437.5	440.5	437.5	398.3	313.4	295.7
52.5°	418.2	421.2	418.2	383.8	289.4	278.8
55°	389.2	389.2	389.2	356.0	253.6	262.5
57.5°	356.1	359.6	356.1	327.1	216.8	224.5
60°	332.0	337.9	332.0	307.7	190.4	205.2
62.5°	310.2	313.8	310.2	286.0	173.4	183.4
65°	274.6	277.6	274.6	250.4	153.7	147.8
67.5°	234.8	237.1	234.8	217.8	135.3	115.9
70°	208.2	208.2	208.2	196.1	123.1	96.5
72.5°	181.7	184.0	181.7	169.6	111.0	84.5
75°	141.9	144.8	141.9	132.8	89.9	63.4
77.5°	102.0	105.0	102.0	96.5	67.7	45.9
80°	75.5	78.4	75.5	72.4	51.0	36.2
82.5°	53.7	54.3	53.7	50.7	36.5	24.1
85°	24.1	24.1	24.1	24.1	18.0	12.1
87.5°	6.2	6.4	6.2	6.4	5.4	2.6
90°	7.0	8.0	7.0	8.0	3.0	1.0
92.5°	61.9	49.6	61.9	190.4	62.0	17.0
95°	240.1	156.0	240.1	674.0	150.7	52.0
97.5°	699.5	433.6	699.5	1156.3	198.8	94.4
100°	1194.8	791.9	1194.8	1337.9	223.7	124.0
102.5°	1760.5	1364.7	1760.5	1317.9	255.0	157.6
105°	2289.2	2174.8	2289.2	1204.9	300.9	211.0
107.5°	2338.7	2464.4	2338.7	1094.7	346.1	263.6
110°	2281.1	2514.8	2281.1	1041.9	378.2	298.0

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	2181.0	2480.4	2181.0	1009.9	408.6	330.8
115°	2022.9	2374.8	2022.9	978.9	454.3	380.0
117.5°	1867.4	2224.8	1867.4	967.1	497.2	427.8
120°	1776.8	2124.8	1776.8	963.9	524.5	459.0
122.5°	1698.6	2021.7	1698.6	963.9	550.9	487.0
125°	1595.2	1873.9	1595.2	964.9	589.6	529.0
127.5°	1519.0	1761.5	1519.0	963.7	626.3	564.6
130°	1472.9	1691.9	1472.9	962.9	649.5	587.0
132.5°	1433.2	1631.9	1433.2	960.5	671.1	607.0
135°	1375.9	1550.9	1375.9	956.9	704.4	637.0
137.5°	1316.1	1474.3	1316.1	954.7	735.4	668.6
140°	1278.3	1427.9	1278.3	953.9	755.5	690.9
142.5°	1238.0	1373.5	1238.0	953.9	774.0	713.3
145°	1183.5	1296.9	1183.5	954.9	799.7	744.9
147.5°	1136.1	1221.7	1136.1	956.3	823.7	778.1
150°	1108.6	1180.9	1108.6	957.9	839.0	798.9
152.5°	1085.9	1145.7	1085.9	958.7	855.1	819.7
155°	1058.9	1099.9	1058.9	960.9	877.3	848.9
157.5°	1037.6	1067.3	1037.6	963.1	895.7	875.1
160°	1025.5	1048.9	1025.5	963.9	908.6	891.9
162.5°	1015.7	1032.9	1015.7	963.9	919.8	906.3
165°	1002.2	1012.9	1002.2	964.9	935.7	926.9
167.5°	991.7	997.5	991.7	966.1	948.6	944.3
170°	986.0	987.9	986.0	966.9	955.9	953.9
172.5°	981.9	982.3	981.9	969.3	962.3	961.1
175°	976.9	974.9	976.9	969.9	968.9	968.9
177.5°	976.1	972.9	976.1	971.3	972.1	972.9
180°	972.9	972.9	972.9	972.9	972.9	972.9

TEST NUMBER: P1191375

CATALOG NUMBER: SQ2-FA-150U-050D-L935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.10	12.76	13.25	13.90	15.50	13.32	13.99	14.47	15.13	16.72
	3H	13.17	13.77	14.33	14.91	16.53	14.55	15.15	15.71	16.29	17.90
	4H	13.51	14.08	14.68	15.23	16.84	14.93	15.50	16.10	16.64	18.26
	6H	13.67	14.19	14.84	15.34	16.97	15.08	15.60	16.25	16.75	18.38
	8H	13.70	14.19	14.87	15.36	16.98	15.10	15.60	16.28	16.76	18.38
	12H	13.69	14.16	14.87	15.31	16.96	15.08	15.55	16.26	16.71	18.35
4H	2H	13.00	13.57	14.17	14.71	16.33	13.91	14.48	15.08	15.63	17.24
	3H	14.35	14.82	15.53	15.99	17.62	15.34	15.82	16.52	16.99	18.62
	4H	14.79	15.22	15.97	16.38	18.03	15.80	16.24	16.98	17.40	19.04
	6H	15.00	15.38	16.19	16.56	18.19	16.01	16.39	17.20	17.57	19.20
	8H	15.06	15.40	16.24	16.58	18.23	16.06	16.40	17.24	17.58	19.23
	12H	15.05	15.36	16.25	16.55	18.21	16.04	16.35	17.24	17.54	19.19
8H	4H	15.17	15.52	16.35	16.69	18.34	16.00	16.34	17.18	17.52	19.17
	6H	15.51	15.79	16.71	17.01	18.66	16.30	16.59	17.50	17.80	19.45
	8H	15.62	15.87	16.83	17.06	18.73	16.39	16.64	17.60	17.83	19.50
	12H	15.65	15.87	16.86	17.06	18.76	16.40	16.61	17.61	17.81	19.51
12H	4H	15.16	15.48	16.36	16.66	18.32	15.96	16.27	17.16	17.46	19.11
	6H	15.58	15.83	16.79	17.02	18.69	16.32	16.57	17.53	17.76	19.43
	8H	15.71	15.93	16.92	17.12	18.82	16.42	16.64	17.63	17.83	19.53