

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1191286

Luminaire Tested: SQ2-FA-075U-075D-L940-UNV-STD-W-4

Issue Date: 9/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1191286
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 9/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-075U-075D-L940-UNV-STD-W-4
Description: CORELITE SQ2 LED LUMINAIRE
FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6113.3 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	81	75	70	82	75	70	66	63	60	56	53	50	47	43	41	39
3	81	72	64	59	74	66	60	55	56	51	47	47	43	40	38	35	33
4	74	63	56	50	68	59	52	46	50	44	40	41	38	34	34	31	29
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	51	43	37	57	47	40	35	40	34	30	34	29	26	28	24	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19178	19178	19178	19178
5°	18953	19848	18953	15819
10°	18871	20077	18871	14341
15°	18546	20239	18546	15853
20°	18036	20093	18036	16533
25°	17142	19930	17142	16732
30°	15793	19484	15793	16910
35°	13975	19056	13975	16606
40°	12033	18533	12033	16788
45°	11878	17872	11878	16819
50°	11333	17000	11333	16885
55°	11274	15682	11274	16718
60°	10111	13976	10111	16650
65°	8619	12313	8619	16183
70°	6954	10433	6954	14998
75°	6032	8615	6032	13787
80°	5133	6425	5133	11130
85°	3409	3409	3409	6817

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 18502 cd/sqm

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.9	1.7
10°-20°	298.6	4.9
20°-30°	453.5	7.4
30°-40°	532.4	8.7
40°-50°	540.3	8.8
50°-60°	473.3	7.7
60°-70°	335.8	5.5
70°-80°	172.9	2.8
80°-90°	36.8	0.6
90°-100°	193.2	3.2
100°-110°	640.4	10.5
110°-120°	635.6	10.4
120°-130°	517.7	8.5
130°-140°	420.8	6.9
140°-150°	326.8	5.3
150°-160°	235.4	3.9
160°-170°	144.2	2.4
170°-180°	48.7	0.8
0°-30°	859.0	14.1
0°-40°	1391.4	22.8
0°-60°	2405.0	39.3
0°-90°	2950.4	48.3
90°-120°	1469.2	24.0
90°-150°	2734.5	44.7
90°-180°	3163.0	51.7
0°-180°	6113.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1188	1188	1188	1188	1188	
5°	1169	1225	1169	976	1169	111
15°	1110	1211	1110	948	1110	312
25°	962	1119	962	939	962	439
35°	709	967	709	842	709	442
45°	520	783	520	737	520	398
55°	400	557	400	594	400	346
65°	226	322	226	424	226	225
75°	97	138	97	221	97	105
85°	18	18	18	37	18	23
90°	0	4	0	4	0	2
95°	28	84	28	84	28	31
105°	112	1131	112	1131	112	118
115°	200	1256	200	1256	200	198
125°	279	995	279	995	279	248
135°	334	818	334	818	334	259
145°	388	682	388	682	388	243
155°	443	578	443	578	443	204
165°	486	532	486	532	486	137
175°	509	512	509	512	509	48
180°	511	511	511	511	511	

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8
2.5°	1180.4	1198.4	1198.8	1198.8	1198.8	1198.8	1198.8	1198.4	1180.4	1180.4	1162.0
5°	1169.4	1200.9	1210.8	1215.6	1224.6	1215.6	1210.8	1200.9	1169.4	1155.9	1081.9
7.5°	1158.3	1200.6	1215.4	1223.8	1228.3	1223.8	1215.4	1200.6	1158.3	1098.0	942.9
10°	1151.0	1200.5	1215.4	1220.1	1224.6	1220.1	1215.4	1200.5	1151.0	1029.4	902.4
12.5°	1139.9	1193.0	1211.7	1216.4	1220.9	1216.4	1211.7	1193.0	1139.9	967.9	872.9
15°	1109.5	1181.5	1197.0	1206.3	1210.8	1206.3	1197.0	1181.5	1109.5	916.0	851.7
17.5°	1071.8	1159.1	1179.5	1187.9	1191.5	1187.9	1179.5	1159.1	1071.8	869.2	852.6
20°	1049.7	1144.2	1164.8	1169.4	1169.4	1169.4	1164.8	1144.2	1049.7	847.1	874.7
22.5°	1020.2	1125.5	1146.4	1147.4	1151.0	1147.4	1146.4	1125.5	1020.2	821.2	885.8
25°	962.2	1083.7	1114.1	1109.7	1118.7	1109.7	1114.1	1083.7	962.2	786.6	883.9
27.5°	891.3	1044.4	1066.2	1070.9	1070.9	1070.9	1066.2	1044.4	891.3	752.7	865.5
30°	847.1	1018.2	1040.5	1045.1	1045.1	1045.1	1040.5	1018.2	847.1	730.1	847.1
32.5°	791.9	995.3	1014.7	1015.6	1015.6	1015.6	1014.7	995.3	791.9	707.2	817.6
35°	709.0	956.6	971.4	971.3	966.8	971.3	971.4	956.6	709.0	673.0	782.7
37.5°	626.1	907.0	927.2	920.7	916.2	920.7	927.2	907.0	626.1	637.8	753.2
40°	570.9	877.0	897.7	883.8	879.3	883.8	897.7	877.0	570.9	611.4	727.4
42.5°	541.4	843.9	864.6	847.0	842.5	847.0	864.6	843.9	541.4	585.5	705.3
45°	520.2	790.3	810.3	791.7	782.7	791.7	810.3	790.3	520.2	547.2	667.6
47.5°	488.0	725.7	754.1	726.3	717.3	726.3	754.1	725.7	488.0	507.8	633.5
50°	451.2	685.3	713.6	685.8	676.8	685.8	713.6	685.3	451.2	478.2	607.7
52.5°	425.4	645.1	669.4	637.9	628.9	637.9	669.4	645.1	425.4	441.6	585.6
55°	400.5	585.1	603.1	570.6	557.1	570.6	603.1	585.1	400.5	387.0	543.3
57.5°	342.5	518.1	536.8	499.6	484.3	499.6	536.8	518.1	342.5	330.8	499.1
60°	313.1	470.6	492.6	455.3	432.8	455.3	492.6	470.6	313.1	290.6	469.6
62.5°	279.9	419.5	448.4	411.1	388.6	411.1	448.4	419.5	279.9	264.6	436.4
65°	225.6	347.1	382.1	344.8	322.3	344.8	382.1	347.1	225.6	234.6	382.1
67.5°	176.8	281.2	320.4	279.5	261.5	279.5	320.4	281.2	176.8	206.5	332.4
70°	147.3	237.4	276.2	239.0	221.0	239.0	276.2	237.4	147.3	187.8	299.2
72.5°	128.9	197.3	239.4	198.6	184.2	198.6	239.4	197.3	128.9	169.4	258.7
75°	96.7	137.2	184.2	147.1	138.1	147.1	184.2	137.2	96.7	137.2	202.6
77.5°	70.0	88.9	129.8	98.4	94.8	98.4	129.8	88.9	70.0	103.3	147.3
80°	55.2	59.7	96.7	69.1	69.1	69.1	96.7	59.7	55.2	77.8	110.5
82.5°	36.8	41.3	67.2	46.9	43.3	46.9	67.2	41.3	36.8	55.7	77.3
85°	18.4	18.4	27.6	18.4	18.4	18.4	27.6	18.4	18.4	27.4	36.8
87.5°	3.7	3.9	8.0	4.5	4.5	4.5	8.0	3.9	3.7	7.5	8.0
90°	0.0	1.0	3.2	4.2	4.2	4.2	3.2	1.0	0.0	1.0	3.2
92.5°	8.5	32.7	96.2	31.2	26.2	31.2	96.2	32.7	8.5	32.7	96.2
95°	27.5	81.3	350.1	124.9	83.6	124.9	350.1	81.3	27.5	81.3	350.1
97.5°	50.6	106.8	611.1	356.4	225.3	356.4	611.1	106.8	50.6	106.8	611.1
100°	66.6	120.4	707.6	607.7	403.0	607.7	707.6	120.4	66.6	120.4	707.6
102.5°	84.4	136.5	701.6	928.7	701.6	928.7	701.6	136.5	84.4	136.5	701.6
105°	112.1	159.7	640.9	1209.2	1130.6	1209.2	640.9	159.7	112.1	159.7	640.9
107.5°	140.5	182.9	582.8	1237.7	1297.5	1237.7	582.8	182.9	140.5	182.9	582.8
110°	156.5	198.9	553.1	1209.5	1330.5	1209.5	553.1	198.9	156.5	198.9	553.1

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	173.5	215.0	535.4	1159.5	1313.6	1159.5	535.4	215.0	173.5	215.0	535.4
115°	199.9	239.2	516.1	1074.5	1256.5	1074.5	516.1	239.2	199.9	239.2	516.1
117.5°	226.1	261.1	509.1	993.2	1184.1	993.2	509.1	261.1	226.1	261.1	509.1
120°	242.2	276.3	506.6	942.3	1127.4	942.3	506.6	276.3	242.2	276.3	506.6
122.5°	256.6	289.9	506.6	900.6	1071.6	900.6	506.6	289.9	256.6	289.9	506.6
125°	279.2	310.2	506.6	844.3	995.2	844.3	506.6	310.2	279.2	310.2	506.6
127.5°	297.8	328.2	505.3	801.7	930.7	801.7	505.3	328.2	297.8	328.2	505.3
130°	308.8	340.9	504.5	776.8	892.6	776.8	504.5	340.9	308.8	340.9	504.5
132.5°	319.0	351.9	503.6	756.3	860.5	756.3	503.6	351.9	319.0	351.9	503.6
135°	334.2	368.3	502.4	724.5	817.6	724.5	502.4	368.3	334.2	368.3	502.4
137.5°	350.7	383.6	501.1	693.8	775.9	693.8	501.1	383.6	350.7	383.6	501.1
140°	361.7	393.8	500.3	673.3	748.8	673.3	500.3	393.8	361.7	393.8	500.3
142.5°	371.9	403.1	501.1	652.8	720.0	652.8	501.1	403.1	371.9	403.1	501.1
145°	388.2	417.1	501.3	623.2	682.2	623.2	501.3	417.1	388.2	417.1	501.3
147.5°	405.7	429.9	501.5	598.1	642.0	598.1	501.5	429.9	405.7	429.9	501.5
150°	416.7	438.4	502.4	583.6	620.8	583.6	502.4	438.4	416.7	438.4	502.4
152.5°	426.9	447.8	503.2	571.6	601.4	571.6	503.2	447.8	426.9	447.8	503.2
155°	443.1	458.7	504.5	556.8	577.5	556.8	504.5	458.7	443.1	458.7	504.5
157.5°	459.0	471.0	505.8	546.3	561.0	546.3	505.8	471.0	459.0	471.0	505.8
160°	467.5	477.8	506.6	538.6	550.0	538.6	506.6	477.8	467.5	477.8	506.6
162.5°	475.9	483.8	506.6	533.5	542.4	533.5	506.6	483.8	475.9	483.8	506.6
165°	486.5	491.7	506.6	526.8	532.0	526.8	506.6	491.7	486.5	491.7	506.6
167.5°	496.2	498.9	507.7	520.8	523.5	520.8	507.7	498.9	496.2	498.9	507.7
170°	501.3	502.4	507.7	518.3	519.3	518.3	507.7	502.4	501.3	502.4	507.7
172.5°	504.7	505.7	508.5	515.7	515.9	515.7	508.5	505.7	504.7	505.7	508.5
175°	508.7	508.7	509.8	512.9	511.9	512.9	509.8	508.7	508.7	508.7	509.8
177.5°	510.8	510.8	510.0	511.6	510.0	511.6	510.0	510.8	510.8	510.8	510.0
180°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8
2.5°	1150.9	1147.3	1150.9	1162.0	1180.4	1180.4
5°	998.5	976.0	998.5	1081.9	1155.9	1169.4
7.5°	907.7	900.5	907.7	942.9	1098.0	1158.3
10°	874.7	874.7	874.7	902.4	1029.4	1151.0
12.5°	871.5	889.5	871.5	872.9	967.9	1139.9
15°	925.9	948.4	925.9	851.7	916.0	1109.5
17.5°	944.2	962.2	944.2	852.6	869.2	1071.8
20°	944.2	962.2	944.2	874.7	847.1	1049.7
22.5°	940.5	958.5	940.5	885.8	821.2	1020.2
25°	930.2	939.2	930.2	883.9	786.6	962.2
27.5°	911.7	918.0	911.7	865.5	752.7	891.3
30°	893.4	907.0	893.4	847.1	730.1	847.1
32.5°	874.8	877.5	874.8	817.6	707.2	791.9
35°	847.0	842.5	847.0	782.7	673.0	709.0
37.5°	809.5	814.9	809.5	753.2	637.8	626.1
40°	787.5	796.5	787.5	727.4	611.4	570.9
42.5°	765.4	774.4	765.4	705.3	585.5	541.4
45°	732.1	736.6	732.1	667.6	547.2	520.2
47.5°	693.4	697.9	693.4	633.5	507.8	488.0
50°	667.7	672.2	667.7	607.7	478.2	451.2
52.5°	638.2	642.7	638.2	585.6	441.6	425.4
55°	593.9	593.9	593.9	543.3	387.0	400.5
57.5°	543.4	548.8	543.4	499.1	330.8	342.5
60°	506.6	515.6	506.6	469.6	290.6	313.1
62.5°	473.4	478.8	473.4	436.4	264.6	279.9
65°	419.1	423.6	419.1	382.1	234.6	225.6
67.5°	358.3	361.9	358.3	332.4	206.5	176.8
70°	317.7	317.7	317.7	299.2	187.8	147.3
72.5°	277.2	280.8	277.2	258.7	169.4	128.9
75°	216.5	221.0	216.5	202.6	137.2	96.7
77.5°	155.7	160.2	155.7	147.3	103.3	70.0
80°	115.2	119.7	115.2	110.5	77.8	55.2
82.5°	82.0	82.9	82.0	77.3	55.7	36.8
85°	36.8	36.8	36.8	36.8	27.4	18.4
87.5°	8.2	8.2	8.2	8.0	7.5	3.7
90°	4.2	4.2	4.2	3.2	1.0	0.0
92.5°	31.2	26.2	31.2	96.2	32.7	8.5
95°	124.9	83.6	124.9	350.1	81.3	27.5
97.5°	356.4	225.3	356.4	611.1	106.8	50.6
100°	607.7	403.0	607.7	707.6	120.4	66.6
102.5°	928.7	701.6	928.7	701.6	136.5	84.4
105°	1209.2	1130.6	1209.2	640.9	159.7	112.1
107.5°	1237.7	1297.5	1237.7	582.8	182.9	140.5
110°	1209.5	1330.5	1209.5	553.1	198.9	156.5

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1159.5	1313.6	1159.5	535.4	215.0	173.5
115°	1074.5	1256.5	1074.5	516.1	239.2	199.9
117.5°	993.2	1184.1	993.2	509.1	261.1	226.1
120°	942.3	1127.4	942.3	506.6	276.3	242.2
122.5°	900.6	1071.6	900.6	506.6	289.9	256.6
125°	844.3	995.2	844.3	506.6	310.2	279.2
127.5°	801.7	930.7	801.7	505.3	328.2	297.8
130°	776.8	892.6	776.8	504.5	340.9	308.8
132.5°	756.3	860.5	756.3	503.6	351.9	319.0
135°	724.5	817.6	724.5	502.4	368.3	334.2
137.5°	693.8	775.9	693.8	501.1	383.6	350.7
140°	673.3	748.8	673.3	500.3	393.8	361.7
142.5°	652.8	720.0	652.8	501.1	403.1	371.9
145°	623.2	682.2	623.2	501.3	417.1	388.2
147.5°	598.1	642.0	598.1	501.5	429.9	405.7
150°	583.6	620.8	583.6	502.4	438.4	416.7
152.5°	571.6	601.4	571.6	503.2	447.8	426.9
155°	556.8	577.5	556.8	504.5	458.7	443.1
157.5°	546.3	561.0	546.3	505.8	471.0	459.0
160°	538.6	550.0	538.6	506.6	477.8	467.5
162.5°	533.5	542.4	533.5	506.6	483.8	475.9
165°	526.8	532.0	526.8	506.6	491.7	486.5
167.5°	520.8	523.5	520.8	507.7	498.9	496.2
170°	518.3	519.3	518.3	507.7	502.4	501.3
172.5°	515.7	515.9	515.7	508.5	505.7	504.7
175°	512.9	511.9	512.9	509.8	508.7	508.7
177.5°	511.6	510.0	511.6	510.0	510.8	510.8
180°	510.8	510.8	510.8	510.8	510.8	510.8

TEST NUMBER: P1191286

CATALOG NUMBER: SQ2-FA-075U-075D-L940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.45	17.29	17.42	18.28	19.58	17.68	18.52	18.65	19.51	20.80
	3H	17.54	18.30	18.52	19.29	20.61	18.92	19.67	19.90	20.67	21.99
	4H	17.89	18.61	18.89	19.61	20.93	19.31	20.02	20.30	21.02	22.35
	6H	18.05	18.71	19.06	19.72	21.05	19.47	20.13	20.47	21.13	22.47
	8H	18.09	18.71	19.10	19.73	21.07	19.49	20.12	20.50	21.14	22.47
	12H	18.08	18.68	19.10	19.69	21.05	19.47	20.07	20.49	21.08	22.44
4H	2H	17.38	18.09	18.38	19.09	20.42	18.29	19.00	19.29	20.00	21.33
	3H	18.74	19.34	19.76	20.37	21.71	19.74	20.33	20.75	21.36	22.70
	4H	19.19	19.73	20.21	20.75	22.12	20.20	20.75	21.22	21.77	23.13
	6H	19.41	19.88	20.45	20.93	22.29	20.43	20.89	21.46	21.94	23.30
	8H	19.47	19.91	20.50	20.94	22.32	20.47	20.91	21.50	21.95	23.32
	12H	19.47	19.87	20.52	20.92	22.30	20.46	20.86	21.51	21.91	23.29
8H	4H	19.59	20.02	20.62	21.06	22.43	20.41	20.85	21.44	21.89	23.26
	6H	19.93	20.29	20.99	21.37	22.74	20.72	21.08	21.78	22.16	23.53
	8H	20.05	20.36	21.11	21.43	22.82	20.82	21.13	21.88	22.20	23.59
	12H	20.08	20.36	21.15	21.42	22.85	20.83	21.11	21.90	22.17	23.60
12H	4H	19.59	19.98	20.64	21.03	22.41	20.38	20.78	21.43	21.83	23.21
	6H	20.00	20.32	21.07	21.38	22.77	20.74	21.06	21.81	22.12	23.51
	8H	20.15	20.42	21.21	21.48	22.92	20.85	21.13	21.92	22.19	23.62