

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439359

Luminaire Tested: CB3-125U-120D-840-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1439359
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-2, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-125U-120D-840-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
3-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10536.6 lumens
Efficiency: N/A
Efficacy: 139.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1439359

CATALOG NUMBER: CB3-125U-120D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1439359

CATALOG NUMBER: CB3-125U-120D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45				
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32				
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27				
4	74	63	55	50	67	58	51	46	49	44	40	40	37	34	32	30	27	24				
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	26	24	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	30	25	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22376	22376	22376
5°	22270	22286	22413
10°	22173	22141	22141
15°	21833	21833	21701
20°	21478	21258	21072
25°	20937	20674	20306
30°	20424	19893	19415
35°	19886	19148	18470
40°	19169	18256	17469
45°	18520	17464	16384
50°	17851	16516	15328
55°	17122	15600	14325
60°	16338	14652	13191
65°	15418	13576	11997
70°	14357	12313	10689
75°	13019	10807	9517
80°	11351	9063	8418
85°	8750	7659	7659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18520 cd/sqm



TEST NUMBER: P1439359

CATALOG NUMBER: CB3-125U-120D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	1.8
10°-20°	524.2	5.0
20°-30°	761.6	7.2
30°-40°	865.9	8.2
40°-50°	840.6	8.0
50°-60°	709.7	6.7
60°-70°	505.0	4.8
70°-80°	269.8	2.6
80°-90°	71.3	0.7
90°-100°	45.4	0.4
100°-110°	328.8	3.1
110°-120°	781.7	7.4
120°-130°	998.6	9.5
130°-140°	1077.2	10.2
140°-150°	1015.5	9.6
150°-160°	828.4	7.9
160°-170°	539.7	5.1
170°-180°	186.6	1.8
0°-30°	1472.5	14.0
0°-40°	2338.4	22.2
0°-60°	3888.7	36.9
0°-90°	4734.8	44.9
90°-120°	1155.8	11.0
90°-150°	4247.1	40.3
90°-180°	5802.0	55.1
0°-180°	10536.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1978	1978	1978	1978	1978	
5°	1961	1986	1962	1960	1973	186
15°	1864	1880	1864	1853	1853	525
25°	1677	1683	1656	1633	1626	773
35°	1440	1426	1386	1345	1337	897
45°	1157	1140	1091	1039	1024	893
55°	868	845	791	740	726	776
65°	576	555	507	462	448	570
75°	298	281	247	222	218	317
85°	67	62	59	59	59	80
90°	0	0	0	1	0	6
95°	83	15	19	21	21	102
105°	416	422	428	31	33	439
115°	781	786	788	800	804	770
125°	1110	1117	1114	1126	1133	990
135°	1394	1401	1390	1400	1409	1074
145°	1622	1632	1612	1622	1631	1015
155°	1797	1812	1787	1791	1803	829
165°	1916	1926	1905	1900	1913	541
175°	1970	1980	1954	1944	1950	187
180°	1966	1966	1966	1966	1966	

TEST NUMBER: P1439359

CATALOG NUMBER: CB3-125U-120D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1977.6	1977.6	1977.6	1977.6	1977.6
2.5°	1967.5	1987.3	1969.8	1972.1	1976.5
5°	1960.8	1985.5	1962.2	1959.7	1973.4
7.5°	1945.6	1968.1	1943.9	1938.3	1950.7
10°	1929.9	1954.6	1927.1	1920.2	1927.1
12.5°	1901.8	1927.6	1905.7	1894.3	1900.1
15°	1863.9	1880.4	1863.9	1852.6	1852.6
17.5°	1817.5	1834.8	1803.8	1795.8	1792.8
20°	1783.8	1798.9	1765.5	1754.2	1750.1
22.5°	1738.9	1752.9	1725.1	1705.9	1700.7
25°	1677.1	1682.6	1656.0	1633.4	1626.5
27.5°	1615.0	1616.4	1579.9	1552.4	1543.3
30°	1563.3	1564.7	1522.6	1492.9	1486.0
32.5°	1511.6	1507.5	1467.5	1432.3	1427.6
35°	1439.7	1426.0	1386.3	1345.4	1337.2
37.5°	1352.9	1344.6	1297.8	1256.8	1244.5
40°	1297.8	1284.1	1236.0	1195.0	1182.7
42.5°	1242.8	1226.8	1177.6	1132.1	1118.6
45°	1157.4	1139.5	1091.4	1039.0	1023.9
47.5°	1071.4	1051.9	998.9	948.3	931.5
50°	1014.1	993.5	938.3	888.7	870.8
52.5°	955.7	934.0	878.7	828.1	813.5
55°	868.0	844.7	790.8	739.9	726.2
57.5°	780.4	757.3	703.7	655.6	639.1
60°	722.0	700.0	647.5	599.4	582.9
62.5°	662.4	641.5	590.2	543.2	527.8
65°	575.9	555.3	507.1	461.8	448.1
67.5°	490.2	472.6	425.0	383.5	372.5
70°	434.0	417.5	372.2	334.0	323.1
72.5°	380.1	362.5	319.4	286.9	279.2
75°	297.8	281.3	247.2	221.8	217.7
77.5°	222.5	209.0	179.5	165.1	162.9
80°	174.2	161.8	139.1	129.2	129.2
82.5°	129.2	119.1	104.2	100.0	100.0
85°	67.4	61.9	59.0	59.0	59.0
87.5°	20.2	20.2	19.1	18.3	18.0
90°	0.0	0.0	0.0	1.4	0.0
92.5°	22.5	8.6	7.1	8.6	8.3
95°	83.0	14.9	19.3	20.7	20.7
97.5°	167.1	163.9	22.5	27.0	27.3
100°	231.1	238.3	23.7	28.2	29.6
102.5°	302.2	308.3	43.9	29.4	30.8
105°	416.3	422.1	428.1	31.1	32.6
107.5°	529.8	534.1	538.1	484.4	181.3
110°	604.4	608.8	610.4	625.2	628.1



TEST NUMBER: P1439359

CATALOG NUMBER: CB3-125U-120D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	674.4	679.9	682.7	695.2	700.4
115°	780.7	786.5	788.1	800.1	804.4
117.5°	881.8	887.8	890.7	900.3	907.2
120°	948.1	955.4	957.0	969.0	974.8
122.5°	1013.3	1021.7	1021.0	1031.9	1040.0
125°	1109.6	1116.9	1114.1	1126.1	1133.3
127.5°	1201.2	1205.5	1199.4	1214.0	1220.1
130°	1259.2	1263.6	1256.3	1269.8	1277.0
132.5°	1312.6	1319.2	1310.8	1323.1	1330.3
135°	1394.0	1401.3	1389.6	1400.2	1408.9
137.5°	1466.6	1475.3	1461.3	1473.6	1481.2
140°	1514.0	1522.7	1505.2	1518.7	1527.4
142.5°	1557.9	1568.9	1547.8	1560.2	1570.0
145°	1622.2	1632.3	1611.8	1622.4	1631.1
147.5°	1683.2	1691.9	1672.3	1679.8	1685.9
150°	1720.0	1728.7	1706.6	1714.2	1721.5
152.5°	1749.6	1761.8	1739.8	1745.1	1755.8
155°	1797.0	1811.5	1786.6	1791.3	1802.9
157.5°	1840.6	1853.6	1828.7	1832.8	1842.9
160°	1866.6	1879.7	1854.8	1856.5	1866.6
162.5°	1886.8	1898.7	1877.3	1874.3	1886.8
165°	1915.5	1925.7	1905.2	1899.5	1912.6
167.5°	1939.5	1951.1	1925.9	1921.2	1936.0
170°	1952.6	1964.1	1937.7	1930.7	1946.6
172.5°	1960.9	1971.3	1946.0	1936.5	1949.0
175°	1970.3	1980.5	1954.0	1943.8	1949.6
177.5°	1973.0	1981.1	1960.0	1950.8	1964.7
180°	1965.9	1965.9	1965.9	1965.9	1965.9



TEST NUMBER: P1439359
 CATALOG NUMBER: CB3-125U-120D-840-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.46	18.27	18.46	19.28	20.62	16.38	17.19	17.38	18.20	19.54
	3H	19.12	19.85	20.13	20.86	22.23	17.79	18.51	18.80	19.53	20.90
	4H	19.75	20.43	20.77	21.46	22.83	18.31	18.99	19.33	20.01	21.38
	6H	20.13	20.76	21.17	21.79	23.17	18.62	19.25	19.66	20.28	21.66
	8H	20.27	20.87	21.31	21.91	23.29	18.74	19.34	19.78	20.39	21.76
	12H	20.33	20.90	21.38	21.94	23.34	18.82	19.39	19.86	20.42	21.83
4H	2H	17.86	18.55	18.89	19.57	20.94	17.00	17.69	18.03	18.71	20.08
	3H	19.75	20.32	20.78	21.37	22.75	18.62	19.19	19.66	20.24	21.62
	4H	20.49	21.01	21.54	22.06	23.46	19.22	19.74	20.27	20.79	22.19
	6H	20.99	21.44	22.05	22.51	23.91	19.63	20.08	20.69	21.14	22.55
	8H	21.18	21.60	22.24	22.66	24.08	19.80	20.22	20.86	21.28	22.69
	12H	21.28	21.66	22.35	22.73	24.15	19.90	20.28	20.98	21.35	22.78
8H	4H	20.62	21.04	21.67	22.09	23.51	19.48	19.90	20.53	20.96	22.37
	6H	21.23	21.58	22.31	22.68	24.10	20.00	20.35	21.08	21.45	22.87
	8H	21.51	21.81	22.60	22.90	24.33	20.26	20.56	21.34	21.64	23.08
	12H	21.67	21.94	22.76	23.02	24.49	20.43	20.70	21.52	21.78	23.25
12H	4H	20.59	20.97	21.66	22.04	23.46	19.48	19.86	20.55	20.93	22.35
	6H	21.25	21.55	22.34	22.64	24.07	20.06	20.37	21.15	21.45	22.88
	8H	21.55	21.81	22.64	22.89	24.37	20.34	20.61	21.43	21.69	23.16